

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204263

Luminaire Tested: **LE_6B15D010 EC6B10209727 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209727 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1370.5 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204263

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204263

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	96	90	85	100	94	89	84	91	86	83		87	84	81		85
3	95	86	79	73	93	84	78	73	82	76	72		79	74	70		76
4	88	77	70	64	86	76	69	63	74	68	63		72	66	62		69
5	81	70	62	56	79	69	62	56	67	60	55		65	59	55		63
6	76	64	56	50	74	63	55	50	61	54	49		60	54	49		58
7	71	58	51	45	69	58	50	45	56	49	45		55	49	44		54
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50
9	62	50	42	37	61	49	42	37	48	41	37		47	41	37		46
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204263

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.4	5.5
10°-20°	195.1	14.2
20°-30°	255.2	18.6
30°-40°	270.2	19.7
40°-50°	252.0	18.4
50°-60°	190.9	13.9
60°-70°	103.4	7.5
70°-80°	27.7	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	525.7	38.4
0°-40°	796.0	58.1
0°-60°	1238.9	90.4
0°-90°	1370.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1370.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	817	
5°	805	75
15°	697	195
25°	555	255
35°	432	270
45°	328	252
55°	214	191
65°	104	103
75°	24	28
85°	0	0
90°	0	



TEST NUMBER: P204263

CATALOG NUMBER: LE_6B15D010 EC6B10209727 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	817.2
2.5°	814.2
5°	805.2
7.5°	785.8
10°	760.4
12.5°	730.4
15°	697.4
17.5°	659.9
20°	626.9
22.5°	589.4
25°	554.9
27.5°	520.4
30°	487.4
32.5°	458.9
35°	431.9
37.5°	404.9
40°	379.4
42.5°	353.9
45°	328.4
47.5°	299.9
50°	271.4
52.5°	243.0
55°	214.5
57.5°	184.5
60°	156.0
62.5°	129.0
65°	103.5
67.5°	79.5
70°	58.5
72.5°	40.5
75°	24.0
77.5°	10.5
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)