

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192556

Luminaire Tested: **LDA6A60935D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192556
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60935D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5599.7 lumens
Efficiency: N/A
Efficacy: 78.0 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192556

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192556

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	102		103	100	98		99	97	95		95	94	93
2	105	99	94	90	103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	79	96	88	83	78		86	81	77		83	79	76		81	77	74
4	91	82	75	70	89	80	74	69		78	73	68		76	71	67		74	70	67
5	85	74	67	62	83	73	67	61		71	65	61		70	64	60		68	63	60
6	79	68	60	55	77	67	60	55		65	59	54		64	58	54		62	57	54
7	74	62	55	49	72	61	54	49		60	54	49		59	53	49		57	52	48
8	69	57	50	44	67	56	49	44		55	49	44		54	48	44		53	48	44
9	64	52	45	40	63	52	45	40		51	44	40		50	44	40		49	44	40
10	60	48	41	37	59	48	41	36		47	41	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	59803	59803	59803
5°	158700	55442	21208
10°	346414	44833	6324
15°	522897	32758	5499
20°	608242	22484	8628
25°	670787	24268	57475
30°	742152	18269	17870
35°	753172	9342	6692
40°	770501	3800	3206
45°	776964	2341	1938
50°	654512	1603	1245
55°	216183	1099	698
60°	42497	1031	450
65°	4994	1349	532
70°	1330	1507	657
75°	233	1991	1101
80°	0	3283	1642
85°	0	6542	2579



TEST NUMBER: P1192556

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.2	2.6
10°-20°	733.0	13.1
20°-30°	1446.9	25.8
30°-40°	1632.1	29.1
40°-50°	1295.6	23.1
50°-60°	316.8	5.7
60°-70°	16.9	0.3
70°-80°	7.2	0.1
80°-90°	6.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2325.1	41.5
0°-40°	3957.2	70.7
0°-60°	5569.6	99.5
0°-90°	5599.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5599.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1091	1091	1091	1091	1091	
5°	2884	2161	1008	506	385	381
15°	9213	4897	577	114	97	2584
25°	11090	5936	401	726	950	5136
35°	11254	3778	140	110	100	7078
45°	10022	1177	30	31	25	7511
55°	2262	51	12	12	7	2654
65°	38	9	10	8	4	94
75°	1	5	9	8	5	3
85°	0	5	10	7	4	0
90°	0	0	0	0	0	

TEST NUMBER: P1192556

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1893.0	1856.6	1873.3	1847.2	1773.3	1750.4	1769.1	1741.0	1656.5	1624.2	1591.0
5°	2883.9	2851.6	2862.1	2802.6	2664.0	2616.1	2613.0	2527.6	2356.7	2260.8	2160.9
7.5°	4372.7	4328.0	4315.4	4172.8	3906.0	3806.0	3757.0	3546.5	3224.6	2996.5	2772.5
10°	6223.1	6266.9	6222.1	5990.7	5571.9	5384.4	5265.7	4867.7	4287.3	3852.9	3434.1
12.5°	8078.8	8105.8	8021.4	7733.9	7201.4	6976.4	6801.3	6291.8	5527.2	4789.5	4164.3
15°	9213.4	9341.4	9262.2	9061.2	8648.6	8375.6	8218.3	7589.0	6626.3	5815.7	4896.8
17.5°	10021.8	10140.6	10074.9	9910.3	9444.7	9224.8	9122.7	8604.8	7556.7	6526.3	5444.8
20°	10426.1	10570.9	10511.5	10324.9	9983.3	9799.9	9675.9	9170.6	8225.6	7054.5	5810.5
22.5°	10700.0	10860.5	10795.9	10626.1	10278.2	10064.5	10006.2	9528.0	8575.7	7371.3	5965.8
25°	11089.7	11224.1	11041.8	10832.4	10488.6	10263.5	10228.1	9739.4	8743.4	7491.0	5935.5
27.5°	11368.9	11528.4	11218.9	11006.4	10613.6	10377.1	10331.3	9871.8	8759.1	7396.2	5690.7
30°	11724.2	11621.1	11349.2	11040.7	10621.9	10369.8	10311.4	9794.6	8602.7	7047.2	5211.5
32.5°	11583.6	11558.6	11286.6	10924.1	10533.3	10279.1	10201.0	9557.1	8173.6	6445.0	4533.2
35°	11254.3	11333.6	11106.4	10881.3	10395.9	10131.2	10022.9	9207.0	7526.5	5669.9	3777.8
37.5°	11061.6	11111.7	10967.9	10692.7	10211.4	9863.5	9658.1	8618.3	6679.5	4692.6	3049.6
40°	10766.8	10893.9	10755.2	10439.6	9884.3	9407.1	9049.7	7554.6	5563.6	3699.7	2384.9
42.5°	10443.8	10557.3	10425.0	10046.7	9262.2	8622.6	8028.7	6304.4	4356.0	2826.6	1788.9
45°	10021.8	10123.9	9886.4	9297.7	8187.1	7304.6	6711.8	4951.1	3285.0	2076.4	1177.3
47.5°	9261.3	9234.2	8897.6	7982.9	6614.9	5824.0	5134.3	3546.5	2183.8	1176.3	585.5
50°	7674.4	7421.3	6926.4	5864.7	4439.4	3585.0	3114.2	1830.5	990.8	569.9	367.8
52.5°	4970.8	4688.4	4235.3	3254.8	2131.6	1710.8	1372.1	827.3	516.8	321.9	144.8
55°	2261.9	2061.8	1772.3	1314.8	914.8	760.5	643.9	418.8	277.1	119.8	51.1
57.5°	861.7	795.0	706.4	563.7	423.0	365.7	303.2	201.1	86.5	44.8	30.2
60°	387.6	359.5	330.2	258.3	181.3	130.3	98.9	54.2	36.4	26.1	19.7
62.5°	132.3	110.4	91.6	65.7	49.0	42.8	37.5	30.2	21.9	17.7	13.5
65°	38.5	37.5	35.5	31.2	25.0	22.9	21.9	17.7	13.5	11.5	9.4
67.5°	18.8	17.7	16.7	15.6	12.6	11.5	11.5	10.4	8.3	7.3	6.2
70°	8.3	8.3	7.3	7.3	6.2	6.2	6.2	5.2	5.2	5.2	5.2
72.5°	4.1	4.1	4.1	3.2	3.2	3.2	3.2	4.1	4.1	5.2	5.2
75°	1.1	2.1	2.1	2.1	2.1	3.2	3.2	4.1	4.1	5.2	5.2
77.5°	1.1	1.1	1.1	2.1	2.1	2.1	3.2	4.1	4.1	5.2	5.2
80°	0.0	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.1	5.2	5.2
82.5°	0.0	1.1	1.1	2.1	2.1	2.1	3.2	3.2	4.1	5.2	5.2
85°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.1	5.2	5.2
87.5°	0.0	0.0	1.1	1.1	2.1	2.1	3.2	3.2	4.1	5.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192556

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	1509.7	1487.8	1401.4	1334.7	1303.4	1301.3	1231.5	1188.8	1113.8	1055.4	1000.2
5°	1984.8	1887.9	1712.8	1574.3	1507.6	1473.3	1335.7	1236.7	1107.6	1007.5	908.6
7.5°	2468.2	2283.8	2037.9	1774.4	1665.9	1599.3	1386.7	1228.3	1056.5	916.9	793.9
10°	2963.1	2638.1	2271.3	1923.3	1767.0	1654.5	1381.5	1166.9	968.9	805.4	670.9
12.5°	3478.8	2966.2	2455.7	2020.1	1814.0	1665.9	1334.7	1077.3	861.7	687.6	559.4
15°	3913.3	3220.4	2572.4	2043.2	1799.3	1620.1	1234.7	963.8	747.0	577.2	460.5
17.5°	4248.8	3363.1	2594.2	1986.9	1718.1	1518.0	1105.5	838.7	626.2	476.1	360.5
20°	4417.6	3385.1	2525.5	1853.4	1571.1	1364.8	958.5	711.6	525.1	385.4	286.5
22.5°	4430.1	3283.0	2375.5	1681.6	1409.6	1200.3	837.6	613.7	460.5	346.0	272.0
25°	4267.6	3086.0	2174.4	1505.5	1244.0	1055.4	751.2	588.7	463.7	401.2	368.9
27.5°	3959.1	2813.1	1953.5	1329.5	1101.2	955.4	715.8	588.7	502.2	453.2	464.6
30°	3531.9	2465.0	1646.2	1089.8	896.0	768.9	562.6	440.8	346.0	288.6	278.2
32.5°	2977.7	2017.1	1276.3	805.4	653.3	554.3	380.3	276.1	223.0	217.8	211.5
35°	2450.5	1593.0	968.9	594.9	481.3	391.8	242.7	162.6	147.9	139.6	133.3
37.5°	1935.8	1191.9	695.9	432.3	330.2	249.0	125.0	105.3	91.6	83.4	76.0
40°	1455.5	856.4	490.7	261.5	172.9	107.4	75.1	64.6	57.3	53.1	51.1
42.5°	1029.3	569.9	304.3	110.4	82.3	67.8	52.0	45.8	41.7	39.6	37.5
45°	598.1	354.2	123.0	64.6	52.0	46.9	38.5	34.4	32.3	30.2	29.1
47.5°	374.0	142.7	63.6	41.7	36.4	33.4	28.1	27.1	25.0	24.0	24.0
50°	151.1	63.6	39.6	29.1	26.1	25.0	21.9	20.8	18.8	18.8	18.8
52.5°	57.3	37.5	27.1	20.8	18.8	17.7	15.6	15.6	14.6	14.6	14.6
55°	33.4	25.0	18.8	14.6	13.5	13.5	12.6	12.6	11.5	11.5	11.5
57.5°	21.9	16.7	13.5	10.4	10.4	10.4	9.4	9.4	9.4	9.4	9.4
60°	14.6	11.5	9.4	8.3	8.3	8.3	8.3	9.4	9.4	9.4	9.4
62.5°	10.4	9.4	8.3	8.3	8.3	8.3	8.3	9.4	9.4	9.4	10.4
65°	8.3	7.3	7.3	7.3	7.3	8.3	8.3	9.4	9.4	10.4	10.4
67.5°	6.2	6.2	6.2	6.2	7.3	7.3	8.3	9.4	9.4	9.4	10.4
70°	5.2	6.2	6.2	7.3	7.3	7.3	8.3	8.3	9.4	9.4	10.4
72.5°	5.2	6.2	6.2	7.3	7.3	7.3	8.3	9.4	9.4	9.4	10.4
75°	5.2	6.2	6.2	7.3	7.3	7.3	8.3	9.4	9.4	9.4	10.4
77.5°	6.2	6.2	7.3	7.3	7.3	8.3	8.3	9.4	9.4	10.4	10.4
80°	6.2	6.2	7.3	7.3	7.3	8.3	8.3	9.4	9.4	10.4	10.4
82.5°	6.2	6.2	7.3	7.3	7.3	8.3	8.3	9.4	9.4	10.4	10.4
85°	6.2	6.2	7.3	7.3	7.3	8.3	8.3	9.4	9.4	10.4	10.4
87.5°	6.2	6.2	7.3	7.3	7.3	8.3	8.3	9.4	9.4	9.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192556

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	973.2	925.1	873.1	856.4	839.7	807.4	787.7	752.2	726.1	700.2	679.4
5°	842.9	766.8	703.2	676.2	650.1	605.4	574.1	536.5	506.3	480.4	456.4
7.5°	707.4	619.9	556.4	529.2	503.3	454.3	414.7	367.8	332.3	303.2	279.2
10°	582.4	499.0	430.3	398.0	367.8	316.7	279.2	241.8	211.5	186.4	164.6
12.5°	474.0	384.5	314.6	290.6	261.5	219.8	184.4	143.8	126.1	118.8	113.6
15°	367.8	287.6	229.2	207.3	181.3	141.7	126.1	118.8	113.6	110.4	106.3
17.5°	280.3	213.6	156.2	141.7	133.3	125.0	120.9	115.6	112.5	111.5	108.3
20°	219.8	161.5	147.0	142.7	142.7	140.6	137.6	137.6	136.5	139.6	139.6
22.5°	226.0	226.0	238.6	237.5	254.2	270.9	283.4	324.0	346.9	395.9	429.3
25°	394.8	432.3	476.1	489.6	522.0	569.9	619.9	682.4	726.1	773.1	791.8
27.5°	492.8	499.0	492.8	508.4	487.5	475.1	479.3	486.6	486.6	489.6	502.2
30°	291.7	306.3	319.9	330.2	325.1	319.9	317.8	302.1	302.1	295.9	290.6
32.5°	197.9	195.8	193.8	197.9	193.8	193.8	190.7	191.7	185.5	181.3	179.3
35°	135.4	129.2	121.9	123.0	118.8	117.7	114.5	114.5	110.4	108.3	107.4
37.5°	75.1	75.1	71.9	72.9	71.9	71.9	71.9	72.9	71.9	71.9	72.9
40°	51.1	51.1	50.0	51.1	50.0	51.1	52.0	52.0	52.0	52.0	51.1
42.5°	38.5	38.5	37.5	38.5	37.5	38.5	39.6	39.6	39.6	39.6	39.6
45°	30.2	30.2	30.2	30.2	30.2	30.2	30.2	31.2	31.2	30.2	30.2
47.5°	24.0	25.0	24.0	24.0	24.0	24.0	25.0	25.0	24.0	24.0	24.0
50°	19.7	19.7	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.8	18.8
52.5°	15.6	14.6	14.6	13.5	13.5	13.5	13.5	13.5	13.5	13.5	12.6
55°	11.5	11.5	10.4	10.4	10.4	11.5	11.5	11.5	11.5	10.4	10.4
57.5°	10.4	10.4	10.4	9.4	9.4	10.4	10.4	9.4	9.4	9.4	8.3
60°	9.4	10.4	9.4	9.4	9.4	9.4	9.4	8.3	8.3	8.3	7.3
62.5°	10.4	10.4	9.4	9.4	9.4	9.4	8.3	8.3	8.3	7.3	7.3
65°	10.4	10.4	10.4	9.4	9.4	9.4	9.4	8.3	8.3	7.3	7.3
67.5°	10.4	10.4	10.4	10.4	9.4	9.4	9.4	8.3	8.3	8.3	7.3
70°	10.4	10.4	10.4	10.4	10.4	9.4	9.4	9.4	8.3	8.3	7.3
72.5°	10.4	10.4	10.4	9.4	9.4	9.4	9.4	9.4	8.3	8.3	7.3
75°	10.4	10.4	10.4	9.4	9.4	9.4	9.4	8.3	8.3	8.3	7.3
77.5°	10.4	10.4	10.4	9.4	9.4	9.4	9.4	8.3	8.3	8.3	7.3
80°	10.4	10.4	10.4	9.4	9.4	9.4	9.4	8.3	8.3	8.3	7.3
82.5°	10.4	10.4	10.4	9.4	9.4	9.4	9.4	8.3	8.3	7.3	7.3
85°	10.4	10.4	9.4	9.4	9.4	9.4	8.3	8.3	7.3	7.3	6.2
87.5°	9.4	9.4	9.4	9.4	8.3	8.3	8.3	7.3	6.2	6.2	5.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192556

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9	1090.9
2.5°	654.3	650.1	647.1	653.3	651.2	625.1	628.3	627.2
5°	429.3	419.9	412.6	415.7	407.4	395.9	387.6	385.4
7.5°	255.3	244.8	238.6	232.4	230.3	215.7	209.5	213.6
10°	140.6	126.1	125.0	121.9	117.7	114.5	112.5	113.6
12.5°	108.3	107.4	105.3	104.2	102.1	101.0	100.0	98.9
15°	103.1	102.1	101.0	100.0	98.9	98.0	96.9	96.9
17.5°	106.3	106.3	105.3	104.2	104.2	105.3	104.2	103.1
20°	138.6	138.6	140.6	143.8	143.8	147.0	151.1	147.9
22.5°	450.1	473.0	501.2	509.5	558.5	598.1	670.9	638.7
25°	823.0	875.2	887.7	905.4	932.4	946.0	932.4	950.2
27.5°	500.1	517.8	519.8	520.9	527.2	526.2	512.7	520.9
30°	290.6	297.0	294.9	293.8	291.7	280.3	278.2	282.3
32.5°	182.3	180.2	179.3	178.2	178.2	171.9	175.0	172.9
35°	104.2	107.4	106.3	105.3	102.1	101.0	101.0	100.0
37.5°	69.8	70.8	69.8	68.7	66.7	65.7	64.6	63.6
40°	50.0	51.1	50.0	49.0	47.9	46.9	45.8	44.8
42.5°	37.5	38.5	37.5	37.5	35.5	34.4	33.4	32.3
45°	29.1	28.1	28.1	28.1	27.1	26.1	25.0	25.0
47.5°	24.0	24.0	24.0	22.9	21.9	21.9	21.9	20.8
50°	17.7	18.8	17.7	17.7	16.7	15.6	15.6	14.6
52.5°	12.6	12.6	11.5	11.5	10.4	9.4	9.4	9.4
55°	9.4	9.4	9.4	8.3	8.3	7.3	7.3	7.3
57.5°	8.3	7.3	7.3	7.3	6.2	6.2	5.2	5.2
60°	7.3	6.2	6.2	5.2	5.2	4.1	4.1	4.1
62.5°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
65°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
67.5°	6.2	6.2	5.2	5.2	5.2	4.1	4.1	4.1
70°	6.2	6.2	6.2	5.2	5.2	5.2	4.1	4.1
72.5°	7.3	6.2	6.2	6.2	5.2	5.2	5.2	5.2
75°	7.3	6.2	6.2	6.2	5.2	5.2	5.2	5.2
77.5°	7.3	6.2	6.2	6.2	5.2	5.2	5.2	5.2
80°	6.2	6.2	6.2	5.2	5.2	5.2	5.2	5.2
82.5°	6.2	6.2	6.2	6.2	5.2	5.2	5.2	5.2
85°	6.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1
87.5°	5.2	4.1	4.1	3.2	3.2	3.2	2.1	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)