

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192559

Luminaire Tested: **LDA6A60935D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192559
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26685)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60935D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4544.3 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 2.12 / 1.05 / 1.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192559

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192559

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	76	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55		
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44		
8	67	55	47	42	65	54	47	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	43	38	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	80421	80421	80421
5°	129231	78841	50286
10°	191106	75511	33756
15°	260416	71436	25068
20°	322092	67404	23767
25°	373153	66361	39014
30°	407132	63573	39044
35°	418436	54951	30544
40°	407478	43245	23787
45°	369472	31988	18746
50°	291103	23632	12707
55°	173566	16831	7264
60°	88765	11194	2741
65°	42443	5941	1219
70°	20035	2677	1170
75°	8155	1758	1313
80°	3978	1957	1294
85°	2013	3271	2013

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192559

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.6	3.3
10°-20°	532.0	11.7
20°-30°	1001.5	22.0
30°-40°	1219.5	26.8
40°-50°	1015.1	22.3
50°-60°	486.2	10.7
60°-70°	116.8	2.6
70°-80°	18.4	0.4
80°-90°	4.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1684.1	37.1
0°-40°	2903.6	63.9
0°-60°	4404.9	96.9
0°-90°	4544.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4544.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1467	1467	1467	1467	1467	
5°	2348	1992	1433	1042	914	257
15°	4588	3117	1259	571	442	1315
25°	6169	3644	1097	622	645	2834
35°	6252	3200	821	478	456	3874
45°	4766	2139	413	254	242	3609
55°	1816	882	176	99	76	1711
65°	327	191	46	15	9	374
75°	38	20	8	7	6	52
85°	3	3	5	4	3	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192559

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0
2.5°	1897.3	1830.7	1851.5	1847.4	1843.1	1821.3	1805.7	1792.0	1757.7	1757.7	1713.9
5°	2348.4	2270.3	2290.1	2275.6	2256.8	2223.4	2193.2	2158.8	2095.3	2068.2	1992.1
7.5°	2864.2	2775.7	2793.3	2764.2	2724.6	2679.8	2630.8	2566.2	2465.2	2403.6	2285.9
10°	3433.1	3307.0	3317.4	3273.7	3208.0	3147.6	3100.8	2977.8	2834.0	2731.9	2567.3
12.5°	3971.8	3861.3	3864.5	3802.9	3708.1	3634.1	3563.3	3400.8	3209.1	3063.2	2846.5
15°	4588.5	4453.1	4420.9	4337.5	4213.5	4122.8	4025.9	3820.7	3580.0	3387.3	3117.3
17.5°	5085.6	4945.9	4925.1	4847.0	4669.8	4560.4	4438.5	4207.2	3902.0	3662.3	3331.0
20°	5521.1	5382.5	5347.1	5245.9	5042.8	4917.8	4770.9	4497.9	4164.5	3869.7	3495.6
22.5°	5877.4	5725.3	5675.2	5550.2	5324.2	5183.4	5004.3	4706.2	4334.3	4005.1	3593.6
25°	6169.1	5996.2	5932.6	5790.9	5536.7	5381.4	5184.5	4851.1	4445.8	4082.2	3643.5
27.5°	6355.6	6182.7	6112.8	5950.3	5664.9	5498.2	5283.5	4923.0	4485.4	4092.6	3633.2
30°	6431.7	6252.5	6173.3	5988.9	5681.5	5505.4	5281.4	4891.7	4434.4	4017.6	3545.6
32.5°	6384.8	6208.7	6120.1	5920.1	5600.3	5410.6	5186.6	4770.9	4300.0	3868.6	3393.5
35°	6252.5	6078.5	5986.8	5773.2	5439.8	5241.8	5018.8	4588.5	4112.4	3671.7	3199.7
37.5°	6024.2	5859.7	5754.5	5542.9	5207.4	5005.3	4784.5	4349.9	3863.4	3448.7	2975.6
40°	5694.0	5537.8	5433.5	5207.4	4890.7	4686.5	4478.1	4037.4	3578.9	3174.7	2718.4
42.5°	5273.1	5129.3	5029.3	4809.5	4507.2	4306.2	4115.5	3692.5	3255.9	2871.4	2440.2
45°	4765.7	4640.7	4542.7	4360.4	4062.3	3871.8	3699.8	3316.3	2892.3	2539.1	2139.1
47.5°	4168.6	4065.5	3970.7	3805.0	3536.3	3355.9	3214.2	2863.2	2503.7	2171.4	1830.7
50°	3413.3	3339.4	3265.3	3093.5	2903.9	2746.4	2643.3	2330.8	2040.0	1779.6	1497.3
52.5°	2573.5	2528.7	2476.6	2353.7	2226.6	2134.8	2043.2	1805.7	1587.9	1394.0	1174.2
55°	1816.0	1793.1	1752.4	1702.5	1605.6	1543.1	1463.9	1343.0	1174.2	1043.9	882.5
57.5°	1227.3	1221.1	1193.0	1162.8	1109.6	1088.8	1022.1	944.0	849.1	752.2	637.7
60°	809.6	796.0	789.8	773.1	732.5	715.8	691.8	641.8	583.5	515.7	444.9
62.5°	520.9	513.6	508.5	501.2	476.1	476.1	452.2	429.3	385.6	343.9	297.9
65°	327.2	320.8	319.9	314.6	305.3	301.1	283.4	266.7	245.9	223.0	190.7
67.5°	210.4	201.1	195.8	192.8	186.4	179.3	172.9	165.6	149.0	135.5	114.7
70°	125.0	116.7	115.6	116.7	109.4	108.3	102.1	96.9	85.4	77.1	64.6
72.5°	70.8	66.7	65.7	65.7	61.4	60.4	56.3	53.1	46.9	40.6	35.5
75°	38.5	35.5	35.5	35.5	33.4	32.3	30.2	29.1	25.0	22.9	19.7
77.5°	21.9	20.8	20.8	19.7	18.8	17.7	16.7	16.7	14.6	13.5	12.6
80°	12.6	12.6	12.6	12.6	11.5	11.5	10.5	10.5	9.4	9.4	8.3
82.5°	7.3	7.3	7.3	7.3	7.3	7.3	6.2	6.2	6.2	6.2	5.2
85°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
87.5°	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.1	2.1	2.1	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192559

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0
2.5°	1694.2	1662.9	1660.8	1615.0	1585.7	1561.8	1544.1	1522.2	1473.3	1446.2	1426.3
5°	1939.0	1874.4	1841.0	1757.7	1711.8	1671.3	1621.2	1569.2	1488.8	1432.7	1386.7
7.5°	2193.2	2085.9	2015.0	1891.1	1828.6	1765.0	1680.7	1596.2	1486.8	1402.5	1332.6
10°	2429.7	2277.6	2165.0	1998.3	1917.1	1833.7	1715.0	1601.4	1465.0	1356.5	1264.9
12.5°	2662.1	2462.0	2306.8	2095.3	1996.3	1893.2	1741.0	1598.3	1437.8	1307.6	1200.3
15°	2884.0	2632.8	2434.9	2179.7	2064.0	1940.1	1757.7	1588.9	1406.6	1258.7	1136.7
17.5°	3061.2	2763.1	2525.6	2231.8	2101.5	1960.9	1751.5	1561.8	1363.8	1206.5	1073.2
20°	3183.0	2846.5	2575.6	2252.6	2109.8	1958.7	1727.4	1524.3	1319.1	1155.4	1020.1
22.5°	3248.7	2884.0	2589.1	2246.3	2097.4	1939.0	1698.3	1489.9	1283.6	1120.1	990.8
25°	3272.6	2887.2	2574.6	2219.3	2069.3	1907.7	1664.0	1457.7	1255.5	1097.1	976.3
27.5°	3244.4	2843.4	2521.5	2163.0	2010.9	1851.5	1608.8	1411.8	1213.8	1063.8	950.2
30°	3148.7	2741.3	2417.3	2062.9	1914.0	1760.8	1521.1	1327.4	1146.1	1004.3	896.0
32.5°	2996.5	2591.2	2270.3	1925.5	1781.7	1634.7	1405.5	1221.1	1052.4	918.9	822.0
35°	2808.0	2412.0	2099.5	1765.0	1629.6	1490.9	1273.2	1099.3	940.9	821.1	726.3
37.5°	2594.3	2213.0	1910.8	1603.5	1465.9	1335.7	1124.3	975.2	823.1	713.7	627.2
40°	2354.8	1984.8	1709.8	1410.7	1289.9	1171.0	975.2	839.7	701.2	604.3	529.3
42.5°	2098.4	1753.5	1499.3	1230.5	1109.6	1001.3	825.2	703.2	580.3	500.1	440.8
45°	1826.5	1522.2	1278.4	1037.7	928.3	834.6	674.1	563.7	474.0	412.6	367.8
47.5°	1542.0	1273.2	1056.5	847.0	750.2	668.9	539.7	455.3	384.5	339.6	305.3
50°	1255.5	1015.8	844.0	665.8	582.5	517.8	422.0	363.6	311.6	277.1	251.1
52.5°	981.4	785.6	646.0	502.2	438.7	393.8	329.3	288.6	249.1	223.0	203.1
55°	725.2	591.9	472.0	364.7	327.2	299.0	253.2	224.0	195.8	176.1	161.5
57.5°	524.1	424.1	336.6	267.7	242.7	224.0	190.7	170.8	151.1	136.5	125.0
60°	367.8	292.8	237.5	195.8	178.2	165.6	141.7	129.2	114.7	102.1	90.7
62.5°	241.8	196.9	165.6	138.6	128.2	118.8	102.1	92.7	80.2	71.9	61.4
65°	157.3	129.2	110.4	92.7	84.4	80.2	68.7	61.4	53.1	45.8	39.6
67.5°	95.9	80.2	69.8	58.4	54.2	50.0	42.8	37.5	32.3	27.1	24.0
70°	53.1	46.9	40.6	34.4	31.3	29.1	25.0	22.9	18.8	16.7	13.5
72.5°	31.3	27.1	24.0	19.7	18.8	17.7	14.6	13.5	11.5	10.5	9.4
75°	18.8	15.6	14.6	12.6	11.5	11.5	10.5	9.4	8.3	8.3	7.3
77.5°	11.5	10.5	9.4	8.3	8.3	8.3	7.3	7.3	7.3	6.2	6.2
80°	7.3	7.3	7.3	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
82.5°	5.2	5.2	5.2	4.1	5.2	4.1	5.2	5.2	5.2	5.2	5.2
85°	3.2	3.2	4.1	4.1	4.1	4.1	4.1	5.2	5.2	5.2	5.2
87.5°	3.2	3.2	4.1	4.1	4.1	4.1	4.1	5.2	5.2	5.2	4.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192559

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0
2.5°	1403.4	1364.9	1336.8	1315.9	1323.2	1286.8	1275.2	1235.8	1221.1	1221.1	1200.3
5°	1339.9	1278.4	1230.5	1200.3	1198.2	1146.1	1119.0	1069.1	1041.9	1022.1	1002.3
7.5°	1263.8	1184.7	1121.1	1084.6	1074.2	1012.8	976.3	926.2	885.7	859.6	835.6
10°	1182.6	1087.7	1015.8	974.1	958.5	891.9	844.0	798.0	754.3	727.2	702.3
12.5°	1104.4	1001.3	922.1	879.3	859.6	790.9	741.9	693.9	652.2	624.2	599.0
15°	1032.5	923.2	839.7	797.1	775.1	707.5	658.5	611.6	571.0	544.9	522.0
17.5°	964.9	853.4	770.0	728.3	704.3	641.8	594.9	549.1	512.7	488.6	467.8
20°	913.8	803.3	726.3	689.7	665.8	607.5	566.8	527.2	496.9	479.3	459.5
22.5°	891.9	789.8	724.1	690.8	674.1	627.2	599.0	571.0	551.2	548.0	535.6
25°	888.7	799.1	744.9	716.9	706.4	670.9	654.4	636.6	622.0	626.2	628.3
27.5°	875.2	791.8	747.1	723.1	714.7	685.6	673.0	656.4	646.0	651.2	653.3
30°	828.3	751.2	709.6	689.7	681.4	652.2	641.8	623.1	614.8	615.7	614.8
32.5°	755.4	682.4	643.9	626.2	616.8	590.8	579.3	562.6	550.2	549.1	547.0
35°	666.8	601.1	565.8	550.2	540.8	518.9	508.5	492.8	478.3	477.2	475.1
37.5°	576.1	517.8	487.7	474.0	465.7	448.1	435.5	425.0	415.8	411.5	410.5
40°	488.6	436.6	414.7	404.2	398.0	379.2	373.0	362.5	355.3	351.1	350.1
42.5°	406.4	369.8	352.2	342.8	337.5	324.0	316.7	308.4	301.1	297.0	295.9
45°	344.9	314.6	297.9	290.8	286.5	274.1	268.8	260.5	254.2	251.1	250.1
47.5°	287.6	263.6	252.1	243.8	242.7	232.4	225.1	218.9	212.5	209.5	208.4
50°	235.4	215.7	206.3	201.1	200.1	189.6	184.4	179.3	174.0	170.8	168.8
52.5°	193.8	175.0	168.8	161.5	160.5	151.1	147.0	141.7	136.5	132.3	129.2
55°	153.2	138.6	132.3	126.1	125.0	114.7	110.4	104.2	98.9	94.8	90.7
57.5°	116.7	105.3	98.9	92.7	91.6	84.4	77.1	71.9	66.7	61.4	58.4
60°	85.4	74.0	66.7	63.6	60.4	53.1	47.9	43.7	39.6	36.4	33.4
62.5°	56.3	47.9	42.8	38.5	36.4	31.3	28.1	25.0	22.9	21.9	20.8
65°	34.4	29.1	25.0	22.9	22.9	19.7	17.7	15.6	14.6	14.6	13.5
67.5°	20.8	17.7	15.6	14.6	13.5	12.6	11.5	11.5	10.5	10.5	9.4
70°	12.6	11.5	10.5	9.4	9.4	9.4	9.4	9.4	8.3	8.3	8.3
72.5°	9.4	8.3	8.3	8.3	8.3	8.3	8.3	8.3	7.3	7.3	7.3
75°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	6.2
77.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
80°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	5.2	5.2	5.2
82.5°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
85°	5.2	5.2	5.2	5.2	5.2	5.2	4.1	4.1	4.1	4.1	4.1
87.5°	5.2	4.1	4.1	4.1	4.1	4.1	3.2	3.2	3.2	3.2	2.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192559

CATALOG NUMBER: LDA6A60935D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0	1467.0
2.5°	1189.8	1198.2	1185.7	1177.4	1169.0	1175.3	1146.1	1133.6
5°	983.5	974.1	967.9	960.6	948.2	950.2	925.3	913.8
7.5°	813.8	807.4	791.8	783.5	771.0	771.0	748.1	738.7
10°	679.4	670.0	655.3	648.0	636.6	627.2	615.7	606.4
12.5°	577.2	566.8	554.3	548.0	536.5	529.3	517.8	520.0
15°	501.2	490.7	479.3	473.0	463.7	456.4	447.0	441.7
17.5°	448.1	438.7	429.3	423.0	415.8	409.4	401.2	400.1
20°	443.8	436.6	431.4	427.2	420.9	416.8	412.6	407.4
22.5°	531.4	532.4	533.5	533.5	534.5	534.5	535.6	525.1
25°	627.2	638.7	638.7	641.8	651.2	651.2	649.1	645.0
27.5°	652.2	663.8	660.6	662.7	672.0	674.1	666.8	667.9
30°	610.5	621.0	614.8	615.7	622.0	622.0	612.7	616.8
32.5°	540.8	547.0	538.6	538.6	543.8	542.9	536.5	536.5
35°	466.8	469.9	462.6	465.7	465.7	462.6	456.4	456.4
37.5°	403.2	404.2	397.0	398.0	398.0	394.9	388.6	388.6
40°	342.8	346.0	339.6	341.7	339.6	336.6	333.4	332.4
42.5°	289.7	291.7	286.5	289.7	288.6	288.6	287.6	288.6
45°	243.8	245.9	241.8	243.8	244.8	243.8	240.7	241.8
47.5°	202.2	204.2	204.2	202.2	201.1	195.8	192.8	192.8
50°	163.5	162.6	161.5	158.4	155.2	152.1	149.0	149.0
52.5°	123.0	120.9	119.8	116.7	115.6	112.5	112.5	109.4
55°	84.4	83.4	83.4	80.2	80.2	77.1	76.0	76.0
57.5°	53.1	51.1	52.2	50.0	49.0	45.8	45.8	44.8
60°	30.2	29.1	29.1	28.1	27.1	25.0	25.0	25.0
62.5°	19.7	18.8	18.8	17.7	17.7	16.7	16.7	15.6
65°	12.6	11.5	11.5	10.5	10.5	9.4	9.4	9.4
67.5°	9.4	8.3	8.3	8.3	8.3	8.3	7.3	7.3
70°	8.3	8.3	7.3	7.3	7.3	7.3	7.3	7.3
72.5°	7.3	7.3	7.3	7.3	6.2	6.2	6.2	6.2
75°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
77.5°	6.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
80°	5.2	5.2	5.2	5.2	5.2	5.2	4.1	4.1
82.5°	5.2	4.1	4.1	4.1	4.1	4.1	4.1	4.1
85°	4.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2
87.5°	2.1	2.1	2.1	2.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)