

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192577

Luminaire Tested: **LDA6A60950D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192577
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A60950D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5577.9 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 71.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192577

CATALOG NUMBER: LDA6A60950D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192577

CATALOG NUMBER: LDA6A60950D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	86331	86331	86331
5°	167268	82264	27751
10°	284196	71993	12458
15°	437925	57418	19807
20°	633952	37366	34460
25°	930108	36057	44307
30°	1081470	34163	33948
35°	1094634	18096	17942
40°	906284	6820	7543
45°	684474	2326	2752
50°	468300	853	853
55°	65135	736	105
60°	1699	724	0
65°	428	999	0
70°	176	1234	0
75°	0	1631	0
80°	0	2778	347
85°	0	5535	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192577

CATALOG NUMBER: LDA6A60950D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.2	3.0
10°-20°	698.3	12.5
20°-30°	1593.0	28.6
30°-40°	1843.5	33.1
40°-50°	1111.8	19.9
50°-60°	151.0	2.7
60°-70°	4.9	0.1
70°-80°	5.3	0.1
80°-90°	4.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2456.6	44.0
0°-40°	4300.1	77.1
0°-60°	5562.9	99.7
0°-90°	5577.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5577.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1575	1575	1575	1575	1575	
5°	3040	2489	1495	818	504	354
15°	7716	4337	1012	311	349	2284
25°	15377	5140	596	717	732	6959
35°	16357	3918	270	276	268	9857
45°	8829	1067	30	37	36	6904
55°	682	8	8	6	1	1336
65°	3	4	8	4	0	5
75°	0	6	8	6	0	0
85°	0	6	9	6	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1192577

CATALOG NUMBER: LDA6A60950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8
2.5°	2277.2	2256.2	2265.1	2241.9	2183.1	2170.9	2169.8	2154.3	2104.3	2065.5	2019.1
5°	3039.6	3038.7	3044.1	2994.3	2891.2	2859.1	2843.6	2805.8	2685.1	2592.0	2489.0
7.5°	3991.6	3985.0	3978.3	3887.5	3725.7	3663.5	3623.8	3487.4	3321.2	3156.1	2972.1
10°	5105.4	5102.0	5076.4	4916.9	4657.6	4543.4	4465.9	4249.9	3982.8	3747.8	3435.3
12.5°	6398.5	6368.6	6323.3	6089.4	5733.7	5609.6	5438.9	5096.5	4686.4	4326.4	3889.6
15°	7716.2	7672.9	7592.1	7291.8	6850.7	6639.0	6427.4	5976.4	5420.1	4897.0	4337.4
17.5°	9005.0	8957.4	8767.8	8258.0	7827.0	7568.8	7333.8	6714.3	6060.5	5388.0	4678.6
20°	10866.8	10693.8	10363.6	9560.2	8759.0	8293.6	8018.7	7363.8	6554.8	5771.4	4921.4
22.5°	13353.4	12970.0	12266.3	10960.9	9816.2	9144.7	8694.6	7823.6	6910.5	6021.8	5071.0
25°	15376.9	15202.9	14402.9	12545.6	10759.2	9967.9	9341.9	8189.4	7169.9	6189.1	5139.7
27.5°	16681.3	16638.0	15723.8	13857.7	11529.3	10491.1	9791.8	8431.0	7295.1	6224.5	5106.4
30°	17084.6	17152.2	16274.5	14303.1	11752.2	10596.2	9831.6	8434.2	7198.7	6063.9	4893.7
32.5°	17054.8	17058.1	15982.1	13918.6	11389.8	10290.5	9499.3	8153.9	6843.0	5661.6	4489.2
35°	16356.6	16184.9	14968.1	12737.3	10546.4	9576.8	8841.0	7610.8	6256.7	5056.6	3918.5
37.5°	14824.1	14599.1	13180.5	11224.6	9547.9	8651.4	8057.4	6898.3	5558.6	4410.5	3328.9
40°	12664.2	12345.0	11174.8	9818.4	8455.4	7781.6	7282.9	6101.6	4811.8	3776.6	2776.0
42.5°	10502.1	10345.8	9572.4	8469.7	7536.7	6902.8	6382.0	5267.1	4093.5	3151.7	2076.8
45°	8828.8	8694.6	8174.9	7448.0	6532.7	5954.2	5452.2	4397.2	3180.4	2114.4	1067.2
47.5°	7609.8	7501.2	7003.7	6240.1	5236.2	4603.4	4085.8	2883.5	1801.9	913.1	267.1
50°	5491.0	5380.1	4892.6	4008.3	3101.8	2572.0	2199.7	1287.7	510.8	185.0	27.8
52.5°	2691.7	2600.9	2269.5	1698.8	1140.4	820.0	599.6	241.6	58.7	19.9	13.3
55°	681.5	626.1	522.0	328.0	160.7	96.4	62.1	22.2	14.5	11.0	7.7
57.5°	38.8	37.6	34.3	25.5	18.9	16.6	14.5	11.0	7.7	6.6	5.6
60°	15.5	14.5	13.3	11.0	8.8	7.7	7.7	5.6	4.5	4.5	4.5
62.5°	6.6	6.6	6.6	5.6	4.5	4.5	4.5	3.3	4.5	4.5	4.5
65°	3.3	3.3	3.3	2.2	2.2	2.2	3.3	3.3	3.3	4.5	4.5
67.5°	2.2	1.1	1.1	1.1	2.2	2.2	2.2	3.3	3.3	4.5	4.5
70°	1.1	1.1	1.1	1.1	2.2	2.2	2.2	3.3	3.3	4.5	5.6
72.5°	0.0	1.1	1.1	1.1	2.2	2.2	2.2	3.3	3.3	4.5	5.6
75°	0.0	1.1	1.1	1.1	2.2	2.2	2.2	3.3	4.5	4.5	5.6
77.5°	0.0	1.1	1.1	1.1	2.2	2.2	2.2	3.3	4.5	4.5	5.6
80°	0.0	1.1	1.1	1.1	2.2	2.2	2.2	3.3	4.5	4.5	5.6
82.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.3	4.5	4.5	5.6
85°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.3	4.5	4.5	5.6
87.5°	0.0	0.0	1.1	1.1	2.2	2.2	2.2	3.3	3.3	4.5	5.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192577

CATALOG NUMBER: LDA6A60950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8
2.5°	1959.3	1919.3	1860.7	1821.9	1784.1	1748.7	1690.0	1656.7	1596.8	1541.4	1493.8
5°	2364.9	2265.1	2144.3	2041.3	1974.8	1909.3	1790.9	1703.3	1593.5	1494.9	1404.1
7.5°	2774.9	2598.6	2400.3	2230.7	2127.7	2026.9	1849.5	1707.7	1552.6	1411.8	1277.7
10°	3147.2	2882.4	2601.9	2359.3	2219.7	2088.9	1855.0	1666.6	1467.1	1293.3	1124.8
12.5°	3492.9	3130.5	2764.9	2448.0	2275.1	2117.6	1831.8	1601.3	1364.2	1158.0	961.9
15°	3801.1	3335.6	2883.5	2498.9	2296.1	2110.0	1777.6	1509.4	1242.2	1011.7	763.6
17.5°	4034.9	3463.1	2935.6	2491.1	2258.5	2051.3	1684.4	1394.0	1112.6	833.4	553.0
20°	4176.6	3517.3	2924.5	2431.3	2177.4	1958.1	1573.6	1268.8	956.3	640.5	487.6
22.5°	4236.5	3512.9	2872.4	2341.7	2077.7	1856.2	1467.1	1146.9	792.4	579.6	508.7
25°	4246.5	3467.5	2799.3	2242.9	1979.1	1758.6	1359.7	1008.4	688.2	596.1	569.6
27.5°	4170.1	3361.1	2661.9	2101.1	1840.7	1612.4	1199.0	801.2	646.0	593.9	611.7
30°	3944.0	3118.3	2419.1	1851.8	1600.2	1371.9	856.5	628.4	536.3	539.7	544.0
32.5°	3546.2	2714.9	2029.1	1487.2	1212.3	904.2	533.0	420.0	407.8	407.8	405.5
35°	3015.3	2221.9	1592.3	940.9	602.9	434.4	275.9	277.1	271.4	270.4	269.3
37.5°	2466.8	1753.0	1008.4	389.0	261.6	181.7	162.9	165.2	162.9	166.3	164.0
40°	1944.8	1082.6	368.0	124.1	92.0	88.7	90.9	93.2	93.2	95.3	95.3
42.5°	1130.3	359.0	96.4	49.8	49.8	47.6	48.8	51.0	52.1	53.2	52.1
45°	335.8	74.3	31.1	27.8	27.8	26.6	26.6	27.8	28.8	30.0	30.0
47.5°	53.2	21.0	17.8	15.5	15.5	15.5	15.5	15.5	16.6	16.6	17.8
50°	16.6	13.3	11.0	10.0	10.0	8.8	8.8	10.0	10.0	10.0	11.0
52.5°	10.0	7.7	7.7	6.6	7.7	7.7	6.6	7.7	7.7	7.7	8.8
55°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	7.7	7.7	7.7
57.5°	5.6	5.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6
60°	5.6	5.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	7.7
62.5°	5.6	5.6	6.6	6.6	6.6	6.6	6.6	6.6	7.7	7.7	7.7
65°	5.6	5.6	6.6	6.6	6.6	6.6	6.6	7.7	7.7	7.7	7.7
67.5°	5.6	6.6	6.6	6.6	6.6	7.7	7.7	7.7	7.7	7.7	7.7
70°	5.6	6.6	6.6	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
72.5°	5.6	6.6	6.6	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7
75°	6.6	6.6	6.6	7.7	7.7	7.7	7.7	7.7	7.7	7.7	8.8
77.5°	6.6	6.6	7.7	7.7	7.7	7.7	7.7	7.7	8.8	8.8	8.8
80°	6.6	6.6	7.7	7.7	7.7	7.7	7.7	8.8	8.8	8.8	8.8
82.5°	6.6	6.6	7.7	7.7	7.7	7.7	7.7	8.8	8.8	8.8	8.8
85°	6.6	6.6	7.7	7.7	7.7	7.7	7.7	8.8	8.8	8.8	8.8
87.5°	6.6	6.6	7.7	7.7	7.7	7.7	7.7	8.8	8.8	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192577

CATALOG NUMBER: LDA6A60950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8
2.5°	1452.9	1401.8	1377.5	1343.1	1318.7	1264.4	1242.2	1204.6	1173.5	1122.6	1125.9
5°	1326.5	1230.0	1164.7	1113.7	1078.3	991.8	934.1	873.2	817.8	749.1	723.6
7.5°	1151.4	1032.8	933.1	872.1	826.7	711.5	584.0	484.2	408.9	354.6	333.5
10°	976.4	822.2	663.8	569.6	504.3	393.3	336.9	310.2	285.9	256.0	236.1
12.5°	772.4	553.0	408.9	371.2	344.6	308.0	271.4	242.7	248.2	249.3	257.1
15°	527.5	397.8	352.5	327.0	298.1	277.1	289.2	296.9	311.4	312.5	322.5
17.5°	428.9	373.5	336.9	335.8	338.0	350.2	369.0	379.1	397.8	402.3	416.7
20°	428.9	396.7	427.8	427.8	433.3	449.9	474.3	488.7	509.7	517.6	535.2
22.5°	488.7	510.8	549.6	554.1	556.4	574.1	605.0	619.4	643.8	648.2	667.2
25°	596.1	616.2	651.7	655.0	656.1	669.3	692.5	700.3	717.1	708.1	719.2
27.5°	630.4	639.4	661.5	663.8	658.2	663.8	672.7	672.7	678.2	660.5	663.8
30°	554.1	556.4	567.4	568.6	556.4	558.5	559.6	558.5	557.3	538.6	538.6
32.5°	411.1	411.1	425.6	422.2	408.9	412.3	412.3	412.3	411.1	395.6	393.3
35°	272.6	273.7	285.9	283.7	273.7	275.9	275.9	279.3	275.9	267.1	264.9
37.5°	166.3	167.3	172.8	174.0	170.7	171.7	172.8	171.7	174.0	169.5	167.3
40°	96.4	98.6	103.1	104.2	103.1	103.1	104.2	105.4	109.7	104.2	101.9
42.5°	56.5	57.6	59.8	59.8	59.8	59.8	60.9	62.1	63.1	62.1	60.9
45°	32.2	33.2	34.3	34.3	35.5	34.3	35.5	35.5	36.6	35.5	35.5
47.5°	18.9	18.9	19.9	19.9	21.0	19.9	21.0	21.0	21.0	19.9	19.9
50°	11.0	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2	11.0	11.0
52.5°	8.8	8.8	8.8	8.8	8.8	7.7	7.7	7.7	7.7	6.6	6.6
55°	7.7	7.7	7.7	7.7	7.7	7.7	6.6	5.6	5.6	4.5	4.5
57.5°	6.6	7.7	7.7	7.7	7.7	6.6	6.6	5.6	4.5	3.3	3.3
60°	7.7	7.7	7.7	7.7	6.6	6.6	6.6	5.6	4.5	3.3	3.3
62.5°	7.7	7.7	7.7	7.7	7.7	6.6	6.6	5.6	4.5	3.3	3.3
65°	7.7	7.7	7.7	7.7	7.7	6.6	6.6	5.6	4.5	3.3	3.3
67.5°	7.7	7.7	7.7	7.7	7.7	6.6	6.6	5.6	4.5	4.5	3.3
70°	7.7	8.8	8.8	7.7	7.7	7.7	6.6	5.6	5.6	4.5	3.3
72.5°	7.7	8.8	8.8	7.7	7.7	7.7	6.6	5.6	5.6	4.5	3.3
75°	8.8	8.8	8.8	8.8	7.7	7.7	6.6	6.6	5.6	4.5	3.3
77.5°	8.8	8.8	8.8	8.8	7.7	7.7	6.6	6.6	5.6	4.5	3.3
80°	8.8	8.8	8.8	8.8	8.8	7.7	7.7	6.6	5.6	4.5	4.5
82.5°	8.8	8.8	8.8	8.8	8.8	7.7	7.7	6.6	5.6	4.5	4.5
85°	8.8	8.8	8.8	8.8	8.8	7.7	7.7	6.6	5.6	4.5	3.3
87.5°	8.8	8.8	8.8	8.8	7.7	7.7	6.6	6.6	5.6	4.5	3.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192577

CATALOG NUMBER: LDA6A60950D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8	1574.8
2.5°	1084.9	1059.3	1048.3	1066.1	1057.2	1030.5	1036.2	1019.5
5°	647.2	608.4	584.0	595.1	559.6	527.5	527.5	504.3
7.5°	312.5	300.4	293.6	295.9	288.2	278.2	272.6	272.6
10°	219.3	215.0	216.1	216.1	222.8	221.6	225.0	223.8
12.5°	260.4	262.6	263.7	268.1	273.7	273.7	277.1	274.9
15°	333.5	331.4	338.0	339.1	348.0	349.0	353.5	349.0
17.5°	424.4	428.9	435.4	434.4	452.2	453.2	453.2	452.2
20°	546.3	549.6	556.4	558.5	579.6	581.8	589.6	590.7
22.5°	679.3	679.3	682.6	687.0	707.0	708.1	711.5	711.5
25°	724.8	718.0	719.2	724.8	735.8	731.3	734.7	732.5
27.5°	666.0	656.1	653.8	661.5	669.3	657.1	661.5	661.5
30°	540.8	531.9	529.8	537.5	543.1	529.8	534.1	536.3
32.5°	395.6	390.1	389.0	394.5	398.9	387.8	392.2	395.6
35°	267.1	264.9	262.6	263.7	270.4	261.6	266.0	268.1
37.5°	169.5	165.2	166.3	168.4	172.8	167.3	171.7	171.7
40°	104.2	101.9	101.9	104.2	106.3	101.9	104.2	105.4
42.5°	60.9	60.9	60.9	62.1	63.1	60.9	60.9	62.1
45°	35.5	34.3	34.3	35.5	36.6	34.3	35.5	35.5
47.5°	19.9	18.9	18.9	19.9	19.9	18.9	19.9	19.9
50°	11.0	10.0	10.0	11.0	11.0	10.0	10.0	10.0
52.5°	5.6	5.6	5.6	5.6	5.6	5.6	4.5	4.5
55°	3.3	3.3	2.2	2.2	2.2	2.2	2.2	1.1
57.5°	2.2	2.2	1.1	1.1	1.1	1.1	0.0	0.0
60°	2.2	2.2	1.1	1.1	1.1	0.0	0.0	0.0
62.5°	2.2	2.2	1.1	1.1	1.1	0.0	0.0	0.0
65°	2.2	2.2	1.1	1.1	1.1	0.0	0.0	0.0
67.5°	2.2	2.2	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.3	2.2	2.2	1.1	1.1	1.1	0.0	0.0
72.5°	3.3	2.2	2.2	2.2	1.1	1.1	0.0	0.0
75°	3.3	2.2	2.2	2.2	1.1	1.1	0.0	0.0
77.5°	3.3	2.2	2.2	2.2	1.1	1.1	1.1	0.0
80°	3.3	2.2	2.2	2.2	1.1	1.1	1.1	1.1
82.5°	3.3	2.2	2.2	2.2	1.1	1.1	1.1	1.1
85°	3.3	2.2	2.2	2.2	1.1	1.1	1.1	0.0
87.5°	3.3	2.2	2.2	2.2	1.1	1.1	1.1	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)