

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192678

Luminaire Tested: **LDA6A65950D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192678
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26685)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A65950D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5045.3 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 2.12 / 1.05 / 1.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 66.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192678

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192678

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		86
3	96	88	81	76	94	86	80	76	84	78	74		81	77	73		79
4	89	79	72	67	87	78	71	66	76	70	65		74	69	64		72
5	83	72	64	59	81	71	64	58	69	63	58		67	61	57		65
6	77	65	58	52	75	64	57	52	63	56	51		61	55	51		60
7	72	60	52	46	70	59	51	46	57	51	46		56	50	46		55
8	67	55	47	42	65	54	47	41	53	46	41		51	45	41		50
9	62	50	43	38	61	50	42	37	48	42	37		47	41	37		46
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	89280	89280	89280
5°	143484	87525	55828
10°	212170	83838	37474
15°	289122	79302	27838
20°	357597	74837	26386
25°	414284	73674	43309
30°	452006	70587	43342
35°	464560	61007	33910
40°	452398	48011	26407
45°	410198	35508	20801
50°	323196	26234	14115
55°	192700	18685	8067
60°	98545	12433	3048
65°	47126	6603	1349
70°	22247	2965	1298
75°	9065	1949	1483
80°	4357	2210	1484
85°	2139	3585	2139

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192678

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.2	3.3
10°-20°	590.7	11.7
20°-30°	1111.8	22.0
30°-40°	1353.9	26.8
40°-50°	1127.0	22.3
50°-60°	539.8	10.7
60°-70°	129.6	2.6
70°-80°	20.4	0.4
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1869.7	37.1
0°-40°	3223.6	63.9
0°-60°	4890.4	96.9
0°-90°	5045.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5045.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1629	1629	1629	1629	1629	
5°	2607	2212	1590	1157	1014	286
15°	5094	3461	1397	634	490	1460
25°	6849	4045	1218	691	716	3146
35°	6942	3552	912	531	507	4301
45°	5291	2375	458	282	268	4006
55°	2016	980	196	110	84	1899
65°	363	212	51	16	10	416
75°	43	22	9	8	7	58
85°	3	3	6	5	3	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192678

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6
2.5°	2106.4	2032.5	2055.6	2050.9	2046.3	2022.1	2004.6	1989.6	1951.5	1951.5	1902.9
5°	2607.4	2520.5	2542.5	2526.3	2505.6	2468.5	2435.0	2396.8	2326.3	2296.1	2211.8
7.5°	3179.9	3081.6	3101.3	3068.8	3024.9	2975.1	2920.8	2849.1	2736.9	2668.6	2537.9
10°	3811.5	3671.5	3683.1	3634.5	3561.7	3494.6	3442.5	3306.0	3146.3	3033.1	2850.3
12.5°	4409.5	4286.9	4290.4	4222.2	4116.9	4034.8	3956.1	3775.6	3562.7	3400.9	3160.2
15°	5094.3	4944.0	4908.2	4815.6	4677.9	4577.2	4469.7	4241.7	3974.6	3760.5	3461.0
17.5°	5646.2	5491.1	5468.0	5381.3	5184.6	5063.1	4927.7	4671.0	4332.0	4066.1	3698.1
20°	6129.7	5975.7	5936.5	5824.3	5598.7	5459.9	5296.7	4993.8	4623.5	4296.2	3880.9
22.5°	6525.3	6356.4	6300.8	6162.0	5911.0	5754.9	5555.9	5225.1	4812.1	4446.6	3989.6
25°	6849.1	6657.1	6586.6	6429.3	6146.9	5974.7	5756.0	5385.8	4935.8	4532.2	4045.2
27.5°	7056.3	6864.2	6786.7	6606.2	6289.3	6104.2	5865.9	5465.6	4979.9	4543.7	4033.5
30°	7140.6	6941.7	6853.8	6649.0	6307.7	6112.3	5863.5	5430.9	4923.2	4460.5	3936.4
32.5°	7088.6	6893.1	6794.8	6572.7	6217.6	6007.0	5758.4	5296.7	4773.9	4295.0	3767.6
35°	6941.7	6748.5	6646.6	6409.6	6039.4	5819.6	5572.1	5094.3	4565.8	4076.4	3552.3
37.5°	6688.3	6505.5	6388.8	6154.0	5781.6	5557.1	5311.8	4829.4	4289.3	3828.9	3303.7
40°	6321.7	6148.2	6032.4	5781.6	5429.8	5203.1	4971.8	4482.4	3973.4	3524.7	3018.0
42.5°	5854.4	5694.7	5583.7	5339.6	5004.2	4780.9	4569.2	4099.6	3614.9	3188.0	2709.1
45°	5291.0	5152.2	5043.4	4841.1	4510.2	4298.5	4107.6	3682.0	3211.2	2819.0	2374.8
47.5°	4628.2	4513.7	4408.5	4224.5	3926.0	3725.9	3568.6	3178.9	2779.7	2410.6	2032.5
50°	3789.6	3707.4	3625.3	3434.4	3223.8	3049.2	2934.7	2587.6	2265.0	1975.7	1662.2
52.5°	2857.2	2807.5	2749.7	2613.1	2472.0	2370.2	2268.4	2004.6	1762.9	1547.7	1303.6
55°	2016.2	1990.8	1945.6	1890.1	1782.6	1713.2	1625.2	1491.0	1303.6	1159.1	979.8
57.5°	1362.7	1355.6	1324.5	1291.0	1232.0	1208.8	1134.8	1048.0	942.8	835.2	707.9
60°	898.8	883.8	876.8	858.3	813.2	794.7	768.0	712.6	647.7	572.5	494.0
62.5°	578.3	570.2	564.5	556.4	528.6	528.6	502.0	476.5	428.0	381.8	330.8
65°	363.3	356.2	355.2	349.3	338.9	334.3	314.7	296.2	273.0	247.6	211.6
67.5°	233.6	223.3	217.5	214.0	207.0	199.0	192.1	184.0	165.5	150.4	127.3
70°	138.8	129.5	128.4	129.5	121.4	120.3	113.4	107.5	94.8	85.6	71.8
72.5°	78.6	74.0	72.8	72.8	68.3	67.1	62.4	59.0	52.0	45.1	39.3
75°	42.8	39.3	39.3	39.3	37.0	35.8	33.6	32.3	27.8	25.5	21.9
77.5°	24.2	23.2	23.2	21.9	20.8	19.7	18.5	18.5	16.2	15.1	13.8
80°	13.8	13.8	13.8	13.8	12.8	12.8	11.5	11.5	10.4	10.4	9.2
82.5°	8.1	8.1	8.1	8.1	8.1	8.1	7.0	7.0	7.0	7.0	5.7
85°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
87.5°	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.3	2.3	2.3	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192678

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6
2.5°	1880.9	1846.2	1843.9	1793.0	1760.6	1734.0	1714.3	1690.0	1635.6	1605.6	1583.6
5°	2152.8	2081.0	2044.0	1951.5	1900.5	1855.4	1799.9	1742.1	1653.1	1590.5	1539.6
7.5°	2435.0	2315.9	2237.1	2099.6	2030.2	1959.5	1865.9	1772.2	1650.7	1557.0	1479.5
10°	2697.6	2528.7	2403.8	2218.6	2128.4	2035.9	1904.0	1777.9	1626.5	1506.1	1404.3
12.5°	2955.5	2733.4	2561.0	2326.3	2216.3	2101.8	1932.9	1774.4	1596.3	1451.7	1332.7
15°	3201.8	2923.1	2703.4	2420.0	2291.5	2153.8	1951.5	1764.0	1561.6	1397.3	1262.0
17.5°	3398.6	3067.7	2803.9	2477.7	2333.1	2177.0	1944.6	1734.0	1514.2	1339.5	1191.4
20°	3533.8	3160.2	2859.5	2500.9	2342.5	2174.7	1918.0	1692.3	1464.4	1282.8	1132.5
22.5°	3606.8	3201.8	2874.6	2493.9	2328.5	2152.8	1885.5	1654.1	1425.1	1243.4	1100.1
25°	3633.4	3205.3	2858.3	2463.9	2297.4	2118.1	1847.4	1618.3	1393.9	1218.0	1083.9
27.5°	3602.1	3156.7	2799.4	2401.5	2232.5	2055.6	1786.0	1567.5	1347.6	1181.0	1055.0
30°	3495.6	3043.5	2683.6	2290.4	2124.9	1955.0	1688.9	1473.7	1272.4	1115.1	994.8
32.5°	3326.9	2877.0	2520.5	2137.7	1978.1	1814.9	1560.5	1355.6	1168.3	1020.2	912.7
35°	3117.5	2677.9	2330.8	1959.5	1809.2	1655.3	1413.6	1220.4	1044.6	911.6	806.3
37.5°	2880.4	2456.9	2121.5	1780.3	1627.6	1482.9	1248.1	1082.7	913.8	792.5	696.4
40°	2614.2	2203.7	1898.2	1566.2	1432.1	1300.2	1082.7	932.4	778.4	670.9	587.6
42.5°	2329.7	1946.9	1664.6	1366.1	1232.0	1111.7	916.1	780.8	644.3	555.3	489.3
45°	2027.8	1690.0	1419.3	1152.1	1030.7	926.6	748.4	625.8	526.3	458.0	408.4
47.5°	1712.0	1413.6	1172.9	940.5	832.9	742.7	599.1	505.4	426.9	377.1	338.9
50°	1393.9	1127.9	937.0	739.2	646.7	574.9	468.4	403.7	345.8	307.6	278.7
52.5°	1089.7	872.1	717.2	557.5	486.9	437.3	365.6	320.4	276.4	247.6	225.5
55°	805.1	657.1	524.0	404.9	363.3	332.0	281.1	248.7	217.5	195.5	179.3
57.5°	581.9	470.8	373.7	297.2	269.6	248.7	211.6	189.7	167.8	151.5	138.8
60°	408.4	325.1	263.7	217.5	197.8	184.0	157.4	143.5	127.3	113.4	100.7
62.5°	268.3	218.6	184.0	153.9	142.3	131.9	113.4	103.0	89.0	79.9	68.3
65°	174.6	143.5	122.6	103.0	93.7	89.0	76.4	68.3	59.0	50.9	43.9
67.5°	106.4	89.0	77.5	64.8	60.2	55.5	47.4	41.7	35.8	30.1	26.6
70°	59.0	52.0	45.1	38.2	34.7	32.3	27.8	25.5	20.8	18.5	15.1
72.5°	34.7	30.1	26.6	21.9	20.8	19.7	16.2	15.1	12.8	11.5	10.4
75°	20.8	17.3	16.2	13.8	12.8	12.8	11.5	10.4	9.2	9.2	8.1
77.5°	12.8	11.5	10.4	9.2	9.2	9.2	8.1	8.1	8.1	7.0	7.0
80°	8.1	8.1	8.1	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
82.5°	5.7	5.7	5.7	4.7	5.7	4.7	5.7	5.7	5.7	5.7	5.7
85°	3.4	3.4	4.7	4.7	4.7	4.7	4.7	5.7	5.7	5.7	5.7
87.5°	3.4	3.4	4.7	4.7	4.7	4.7	4.7	5.7	5.7	5.7	4.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192678

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6
2.5°	1558.1	1515.4	1484.1	1461.0	1469.1	1428.6	1415.9	1371.9	1355.6	1355.6	1332.7
5°	1487.6	1419.3	1366.1	1332.7	1330.3	1272.4	1242.4	1186.8	1156.8	1134.8	1112.8
7.5°	1403.2	1315.2	1244.7	1204.2	1192.6	1124.3	1083.9	1028.4	983.2	954.3	927.7
10°	1312.9	1207.6	1127.9	1081.6	1064.2	990.2	937.0	886.1	837.4	807.4	779.7
12.5°	1226.2	1111.7	1023.7	976.2	954.3	878.1	823.6	770.3	724.2	692.8	665.2
15°	1146.4	1024.9	932.4	884.9	860.6	785.4	731.1	679.0	633.9	605.0	579.6
17.5°	1071.2	947.4	854.9	808.6	782.0	712.6	660.5	609.6	569.1	542.6	519.4
20°	1014.5	891.9	806.3	765.9	739.2	674.3	629.2	585.3	551.7	532.1	510.1
22.5°	990.2	876.8	803.9	766.9	748.4	696.4	665.2	633.9	611.9	608.5	594.6
25°	986.6	887.2	827.1	795.9	784.3	745.0	726.4	706.7	690.6	695.2	697.5
27.5°	971.7	879.1	829.4	802.8	793.5	761.2	747.3	728.8	717.2	723.0	725.2
30°	919.6	834.0	787.8	765.9	756.5	724.2	712.6	691.7	682.4	683.7	682.4
32.5°	838.7	757.7	714.9	695.2	684.7	655.8	643.2	624.6	610.8	609.6	607.3
35°	740.3	667.5	628.2	610.8	600.4	576.2	564.5	547.1	531.0	529.8	527.5
37.5°	639.6	574.9	541.4	526.3	517.0	497.4	483.5	472.0	461.6	456.9	455.8
40°	542.6	484.6	460.4	448.9	441.8	421.1	414.1	402.6	394.5	389.8	388.6
42.5°	451.2	410.7	390.9	380.5	374.7	359.8	351.7	342.4	334.3	329.7	328.5
45°	382.8	349.3	330.8	322.7	318.1	304.2	298.5	289.1	282.3	278.7	277.7
47.5°	319.2	292.8	280.0	270.6	269.6	258.0	249.9	242.9	236.0	232.5	231.4
50°	261.5	239.5	229.1	223.3	222.0	210.6	204.8	199.0	193.1	189.7	187.4
52.5°	215.2	194.4	187.4	179.3	178.2	167.8	163.1	157.4	151.5	147.0	143.5
55°	170.0	153.9	147.0	139.9	138.8	127.3	122.6	115.6	109.9	105.2	100.7
57.5°	129.5	116.9	109.9	103.0	101.8	93.7	85.6	79.9	74.0	68.3	64.8
60°	94.8	82.2	74.0	70.5	67.1	59.0	53.2	48.6	43.9	40.5	37.0
62.5°	62.4	53.2	47.4	42.8	40.5	34.7	31.3	27.8	25.5	24.2	23.2
65°	38.2	32.3	27.8	25.5	25.5	21.9	19.7	17.3	16.2	16.2	15.1
67.5°	23.2	19.7	17.3	16.2	15.1	13.8	12.8	12.8	11.5	11.5	10.4
70°	13.8	12.8	11.5	10.4	10.4	10.4	10.4	10.4	9.2	9.2	9.2
72.5°	10.4	9.2	9.2	9.2	9.2	9.2	9.2	9.2	8.1	8.1	8.1
75°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	7.0
77.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
80°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	5.7	5.7	5.7
82.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
85°	5.7	5.7	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7	4.7
87.5°	5.7	4.7	4.7	4.7	4.7	4.7	3.4	3.4	3.4	3.4	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192678

CATALOG NUMBER: LDA6A65950D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6	1628.6
2.5°	1321.0	1330.3	1316.4	1307.1	1297.9	1304.8	1272.4	1258.5
5°	1092.0	1081.6	1074.6	1066.5	1052.7	1055.0	1027.1	1014.5
7.5°	903.4	896.5	879.1	870.0	855.9	855.9	830.5	820.1
10°	754.2	743.8	727.6	719.5	706.7	696.4	683.7	673.2
12.5°	640.8	629.2	615.4	608.5	595.7	587.6	574.9	577.2
15°	556.4	544.9	532.1	525.2	514.8	506.7	496.3	490.5
17.5°	497.4	486.9	476.5	469.7	461.6	454.6	445.4	444.2
20°	492.8	484.6	478.9	474.2	467.4	462.7	458.0	452.3
22.5°	590.0	591.0	592.3	592.3	593.4	593.4	594.6	583.0
25°	696.4	709.1	709.1	712.6	723.0	723.0	720.7	716.0
27.5°	724.2	736.8	733.3	735.7	746.1	748.4	740.3	741.4
30°	677.9	689.4	682.4	683.7	690.6	690.6	680.3	684.7
32.5°	600.4	607.3	598.1	598.1	603.8	602.7	595.7	595.7
35°	518.2	521.7	513.6	517.0	517.0	513.6	506.7	506.7
37.5°	447.7	448.9	440.8	441.8	441.8	438.4	431.4	431.4
40°	380.5	384.1	377.1	379.4	377.1	373.7	370.2	369.0
42.5°	321.6	323.9	318.1	321.6	320.4	320.4	319.2	320.4
45°	270.6	273.0	268.3	270.6	271.9	270.6	267.2	268.3
47.5°	224.4	226.7	226.7	224.4	223.3	217.5	214.0	214.0
50°	181.6	180.5	179.3	175.9	172.3	168.9	165.5	165.5
52.5°	136.4	134.2	133.0	129.5	128.4	125.0	125.0	121.4
55°	93.7	92.6	92.6	89.0	89.0	85.6	84.4	84.4
57.5°	59.0	56.7	57.9	55.5	54.3	50.9	50.9	49.8
60°	33.6	32.3	32.3	31.3	30.1	27.8	27.8	27.8
62.5°	21.9	20.8	20.8	19.7	19.7	18.5	18.5	17.3
65°	13.8	12.8	12.8	11.5	11.5	10.4	10.4	10.4
67.5°	10.4	9.2	9.2	9.2	9.2	9.2	8.1	8.1
70°	9.2	9.2	8.1	8.1	8.1	8.1	8.1	8.1
72.5°	8.1	8.1	8.1	8.1	7.0	7.0	7.0	7.0
75°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
77.5°	7.0	5.7	5.7	5.7	5.7	5.7	5.7	5.7
80°	5.7	5.7	5.7	5.7	5.7	5.7	4.7	4.7
82.5°	5.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
85°	4.7	3.4	3.4	3.4	3.4	3.4	3.4	3.4
87.5°	2.3	2.3	2.3	2.3	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)