

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192684

Luminaire Tested: **LDA6A70927D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70927D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5918.2 lumens
Efficiency: N/A
Efficacy: 75.8 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192684

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



TEST NUMBER: P1192684

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	58521	58521	58521
5°	150126	53241	16580
10°	292630	40909	7966
15°	525309	27787	10692
20°	779926	21095	17642
25°	886503	17378	27667
30°	960977	19003	26023
35°	1012225	12321	16128
40°	1034116	5467	7850
45°	934004	2085	2923
50°	614828	819	819
55°	168367	717	0
60°	33627	822	0
65°	2374	1116	0
70°	353	1378	0
75°	0	2033	0
80°	0	3031	316
85°	0	6038	629

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P1192684

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.8	2.2
10°-20°	694.7	11.7
20°-30°	1574.6	26.6
30°-40°	1890.1	31.9
40°-50°	1332.1	22.5
50°-60°	274.8	4.6
60°-70°	9.7	0.2
70°-80°	5.8	0.1
80°-90°	5.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2400.1	40.6
0°-40°	4290.2	72.5
0°-60°	5897.1	99.6
0°-90°	5918.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5918.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1068	1068	1068	1068	1068	
5°	2728	1988	968	402	301	336
15°	9256	4072	490	174	188	2747
25°	14656	4926	287	402	457	6764
35°	15125	3449	184	241	241	9403
45°	12047	1183	27	36	38	8861
55°	1762	24	8	5	0	2321
65°	18	5	9	5	0	54
75°	0	5	10	6	0	0
85°	0	6	10	6	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192684

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5
2.5°	1819.7	1764.8	1786.4	1723.0	1708.9	1697.1	1708.9	1640.0	1601.3	1551.8	1512.0
5°	2728.1	2662.4	2677.5	2566.6	2516.0	2481.6	2475.2	2333.1	2226.5	2109.2	1987.7
7.5°	3797.7	3735.3	3726.6	3554.5	3450.1	3391.0	3366.1	3162.8	2978.7	2769.9	2541.9
10°	5256.9	5115.0	5070.8	4821.2	4622.0	4496.1	4341.2	4016.2	3693.3	3378.1	3087.4
12.5°	6955.1	6877.6	6767.9	6327.8	5979.0	5800.5	5569.1	5061.1	4572.6	4051.7	3565.3
15°	9255.9	8980.5	8793.1	8157.1	7595.5	7319.9	6982.0	6205.1	5466.8	4807.1	4072.2
17.5°	11504.0	11359.8	11067.1	10241.7	9376.5	8941.7	8438.1	7382.4	6339.5	5401.1	4503.7
20°	13369.0	13233.4	12899.8	12121.7	11161.8	10520.4	9886.6	8438.1	7075.6	5874.7	4792.0
22.5°	14262.1	14176.0	13903.8	13237.7	12419.8	11809.7	11128.4	9336.7	7620.2	6184.7	4923.4
25°	14656.0	14616.2	14440.7	13915.6	13145.1	12627.5	11984.0	9972.7	7959.1	6328.8	4925.5
27.5°	15055.3	15062.8	14675.4	14260.0	13529.4	13032.1	12412.2	10254.5	8020.5	6248.1	4764.1
30°	15181.1	15101.6	14930.5	14334.3	13640.2	13111.8	12446.7	10124.4	7768.7	5916.6	4442.3
32.5°	15129.5	15098.3	14909.9	14279.4	13451.8	12869.6	12114.1	9607.9	7271.5	5443.1	3986.0
35°	15125.2	15067.1	14635.6	14094.3	13075.2	12356.3	11360.9	8772.7	6567.7	4819.0	3449.1
37.5°	14851.8	14707.6	14383.8	13654.2	12311.1	11399.6	10283.6	7752.5	5706.8	4118.5	2916.3
40°	14450.5	14256.8	13830.6	12726.5	10987.5	9937.2	8848.1	6593.5	4795.3	3427.5	2350.3
42.5°	13612.2	13319.4	12716.8	11198.4	9223.7	8276.6	7370.6	5419.5	3910.7	2792.7	1794.0
45°	12047.4	11647.1	10832.5	9165.6	7451.2	6678.6	5950.0	4360.5	3130.4	2071.5	1182.7
47.5°	9683.1	9312.0	8570.4	7296.2	5843.4	5190.3	4609.1	3243.5	2122.1	1199.8	565.0
50°	7209.1	6890.6	6311.6	5070.8	3922.6	3409.3	2912.0	1842.3	994.4	570.3	234.5
52.5°	4301.4	4143.2	3629.8	2811.9	1937.1	1669.0	1339.7	780.2	501.4	206.6	63.6
55°	1761.6	1626.0	1433.4	1150.4	842.6	714.5	611.3	385.2	156.0	43.0	23.7
57.5°	796.3	766.1	679.0	533.8	387.4	325.0	219.6	73.2	34.4	21.6	13.9
60°	306.7	276.5	236.7	128.1	54.9	46.3	37.7	24.7	17.3	11.8	8.6
62.5°	44.1	42.0	37.7	30.2	23.7	21.6	18.3	12.9	9.6	7.5	6.5
65°	18.3	18.3	16.1	12.9	10.8	9.6	8.6	6.5	5.3	5.3	5.3
67.5°	7.5	7.5	6.5	5.3	4.3	4.3	4.3	3.2	4.3	4.3	5.3
70°	2.2	2.2	2.2	2.2	2.2	2.2	3.2	3.2	4.3	4.3	5.3
72.5°	0.0	0.0	1.0	1.0	2.2	2.2	2.2	3.2	4.3	5.3	5.3
75°	0.0	0.0	1.0	1.0	2.2	2.2	2.2	3.2	4.3	5.3	5.3
77.5°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.3	5.3	5.3
80°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.3	5.3	6.5
82.5°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.3	5.3	6.5
85°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.3	5.3	6.5
87.5°	0.0	0.0	1.0	1.0	2.2	2.2	3.2	3.2	4.3	5.3	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192684

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5
2.5°	1477.5	1408.6	1389.4	1329.1	1278.5	1253.8	1222.6	1152.5	1099.8	1029.9	987.9
5°	1902.6	1772.4	1669.0	1543.2	1460.4	1406.5	1322.6	1194.5	1091.3	967.5	879.2
7.5°	2362.1	2124.3	1938.1	1730.4	1610.9	1517.3	1374.3	1190.2	1038.5	873.8	737.1
10°	2805.5	2450.4	2157.7	1859.6	1702.4	1572.3	1375.3	1143.9	942.7	734.9	590.9
12.5°	3196.2	2737.7	2325.6	1942.4	1747.7	1585.2	1338.7	1061.1	817.9	604.8	477.8
15°	3522.3	2960.5	2444.0	1973.6	1750.9	1557.2	1262.4	942.7	679.0	489.6	400.3
17.5°	3769.8	3077.8	2480.5	1935.9	1688.5	1477.5	1145.0	793.2	551.0	415.4	336.8
20°	3897.7	3100.4	2427.9	1833.7	1573.3	1357.0	991.2	643.5	467.1	361.6	282.0
22.5°	3914.0	3036.8	2301.9	1687.4	1428.0	1210.6	821.1	536.9	416.4	319.7	248.6
25°	3818.2	2899.1	2122.1	1521.7	1268.7	1042.8	668.2	481.0	378.8	287.3	286.3
27.5°	3613.7	2662.4	1906.9	1329.1	1076.2	848.0	567.1	434.7	337.9	304.6	324.0
30°	3325.3	2359.0	1642.2	1085.8	840.5	652.1	477.8	358.3	297.1	300.2	316.4
32.5°	2934.6	1982.2	1331.1	795.3	601.5	490.8	358.3	244.3	246.5	247.5	261.6
35°	2444.0	1589.5	994.4	534.8	422.9	345.4	202.3	179.7	182.9	184.1	193.7
37.5°	1958.6	1221.4	660.7	356.2	265.9	181.9	126.0	120.5	122.7	121.7	132.4
40°	1500.1	851.3	396.0	176.4	102.2	85.0	77.5	74.2	75.3	76.4	82.8
42.5°	1062.2	461.7	195.9	66.7	53.8	49.5	46.3	44.1	45.2	45.2	49.5
45°	539.1	218.4	66.7	36.5	33.4	30.2	28.0	26.9	26.9	26.9	29.0
47.5°	233.5	72.0	31.2	22.6	20.4	19.4	17.3	16.1	16.1	16.1	17.3
50°	73.2	29.0	19.4	15.1	12.9	11.8	10.8	10.8	10.8	9.6	10.8
52.5°	26.9	18.3	12.9	9.6	8.6	8.6	8.6	7.5	8.6	7.5	8.6
55°	16.1	11.8	8.6	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
57.5°	10.8	8.6	7.5	7.5	6.5	6.5	7.5	7.5	7.5	7.5	7.5
60°	7.5	7.5	6.5	6.5	6.5	6.5	7.5	7.5	7.5	7.5	7.5
62.5°	6.5	6.5	6.5	6.5	6.5	6.5	7.5	7.5	7.5	7.5	8.6
65°	5.3	6.5	6.5	6.5	6.5	6.5	7.5	7.5	8.6	8.6	8.6
67.5°	5.3	6.5	6.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	8.6
70°	6.5	6.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	8.6	9.6
72.5°	6.5	6.5	7.5	7.5	7.5	7.5	8.6	8.6	9.6	9.6	9.6
75°	6.5	7.5	7.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6	9.6
77.5°	6.5	7.5	7.5	8.6	8.6	8.6	8.6	9.6	9.6	9.6	9.6
80°	6.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6	9.6	9.6	10.8
82.5°	6.5	7.5	7.5	8.6	8.6	8.6	9.6	9.6	9.6	9.6	10.8
85°	7.5	7.5	8.6	8.6	8.6	8.6	9.6	9.6	9.6	9.6	10.8
87.5°	7.5	7.5	8.6	8.6	8.6	8.6	9.6	9.6	10.8	9.6	10.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192684

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5
2.5°	931.9	869.5	826.5	810.3	779.1	729.6	700.6	673.7	623.1	612.3	584.4
5°	778.1	678.0	607.0	580.1	544.6	502.6	461.7	434.7	402.5	389.5	370.1
7.5°	613.4	513.4	452.0	430.5	405.6	371.3	334.6	307.7	274.4	257.3	241.0
10°	482.1	407.8	356.2	334.6	308.9	272.2	234.5	199.2	170.0	151.7	148.5
12.5°	391.7	330.4	275.5	252.9	222.7	186.2	159.3	158.2	156.0	155.0	157.2
15°	320.7	261.6	203.3	178.6	170.0	169.0	172.1	175.4	174.3	177.6	179.7
17.5°	263.7	200.2	187.2	188.4	189.4	192.7	198.0	206.6	207.6	213.1	217.4
20°	215.3	212.0	217.4	221.7	224.9	231.4	243.2	253.9	257.3	264.7	273.4
22.5°	244.3	253.9	265.9	271.2	275.5	287.3	300.2	317.5	324.0	333.6	345.4
25°	294.9	311.0	329.3	335.8	342.2	361.6	376.6	397.2	402.5	414.3	426.2
27.5°	336.8	354.0	373.4	382.1	387.4	406.8	419.7	432.5	432.5	439.0	447.6
30°	330.4	344.4	360.5	367.0	369.1	383.1	396.0	400.3	398.2	401.3	407.8
32.5°	274.4	285.1	298.1	303.4	305.6	315.3	326.1	326.1	325.0	325.0	329.3
35°	203.3	210.9	217.4	222.7	226.0	232.5	242.2	241.0	241.0	238.8	242.2
37.5°	136.6	140.9	148.5	150.7	151.7	156.0	163.6	163.6	161.5	162.5	164.6
40°	82.8	88.3	92.6	93.6	95.8	99.1	104.4	104.4	104.4	104.4	105.4
42.5°	49.5	52.8	55.9	55.9	57.1	61.4	63.6	63.6	63.6	63.6	64.6
45°	29.0	30.2	32.4	33.4	33.4	35.5	36.5	36.5	36.5	36.5	37.7
47.5°	17.3	18.3	18.3	19.4	19.4	20.4	21.6	21.6	20.4	20.4	20.4
50°	10.8	10.8	10.8	10.8	11.8	11.8	11.8	11.8	11.8	11.8	10.8
52.5°	8.6	8.6	8.6	8.6	7.5	7.5	7.5	7.5	6.5	6.5	5.3
55°	7.5	7.5	7.5	7.5	7.5	6.5	6.5	6.5	5.3	4.3	3.2
57.5°	7.5	7.5	7.5	7.5	7.5	6.5	6.5	5.3	4.3	4.3	3.2
60°	7.5	7.5	7.5	7.5	7.5	6.5	6.5	5.3	4.3	4.3	3.2
62.5°	8.6	8.6	7.5	7.5	7.5	6.5	6.5	5.3	5.3	4.3	3.2
65°	8.6	8.6	7.5	7.5	7.5	7.5	6.5	6.5	5.3	4.3	3.2
67.5°	8.6	8.6	8.6	8.6	7.5	7.5	7.5	6.5	5.3	4.3	3.2
70°	9.6	9.6	8.6	8.6	8.6	7.5	7.5	6.5	5.3	5.3	4.3
72.5°	9.6	9.6	8.6	8.6	8.6	8.6	7.5	6.5	6.5	5.3	4.3
75°	9.6	9.6	9.6	9.6	8.6	8.6	7.5	7.5	6.5	5.3	4.3
77.5°	9.6	9.6	9.6	9.6	8.6	8.6	8.6	7.5	6.5	5.3	4.3
80°	9.6	9.6	9.6	9.6	9.6	8.6	8.6	7.5	6.5	5.3	4.3
82.5°	10.8	10.8	9.6	9.6	9.6	8.6	8.6	7.5	6.5	5.3	5.3
85°	10.8	10.8	9.6	9.6	9.6	8.6	8.6	7.5	6.5	6.5	5.3
87.5°	10.8	10.8	9.6	9.6	9.6	8.6	8.6	7.5	6.5	6.5	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192684

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5	1067.5
2.5°	567.1	534.8	524.1	531.6	523.0	516.5	507.9	503.6
5°	355.2	331.5	324.0	326.1	318.5	312.0	303.4	301.3
7.5°	218.4	195.9	187.2	187.2	178.6	171.1	165.8	162.5
10°	146.4	142.1	143.1	144.2	143.1	144.2	140.9	143.1
12.5°	157.2	155.0	157.2	158.2	158.2	160.3	156.0	159.3
15°	182.9	180.8	184.1	186.2	186.2	189.4	185.1	188.4
17.5°	223.9	222.7	228.2	230.4	231.4	236.7	231.4	235.7
20°	283.0	282.0	289.5	292.8	291.6	302.4	294.9	302.4
22.5°	359.5	357.3	368.0	371.3	372.3	386.4	379.9	385.2
25°	435.8	438.0	443.3	448.8	449.8	461.7	452.0	457.4
27.5°	452.0	448.8	452.0	458.4	459.6	464.9	456.3	460.6
30°	409.0	403.5	404.6	412.1	414.3	416.4	409.0	411.1
32.5°	332.6	324.0	324.0	331.5	333.6	336.8	324.0	329.3
35°	245.3	237.8	237.8	243.2	244.3	246.5	236.7	241.0
37.5°	167.8	161.5	163.6	165.8	166.8	169.0	167.8	166.8
40°	107.6	103.2	106.6	106.6	107.6	108.7	108.7	109.7
42.5°	65.7	62.4	64.6	64.6	65.7	65.7	65.7	66.7
45°	37.7	36.5	36.5	37.7	37.7	37.7	36.5	37.7
47.5°	20.4	19.4	20.4	20.4	20.4	20.4	20.4	20.4
50°	10.8	9.6	9.6	9.6	9.6	9.6	9.6	9.6
52.5°	5.3	4.3	4.3	4.3	3.2	4.3	3.2	3.2
55°	3.2	2.2	2.2	2.2	1.0	1.0	0.0	0.0
57.5°	2.2	1.0	1.0	1.0	0.0	0.0	0.0	0.0
60°	2.2	1.0	1.0	1.0	0.0	0.0	0.0	0.0
62.5°	2.2	1.0	1.0	1.0	0.0	0.0	0.0	0.0
65°	2.2	1.0	1.0	1.0	0.0	0.0	0.0	0.0
67.5°	3.2	2.2	1.0	1.0	1.0	0.0	0.0	0.0
70°	3.2	2.2	2.2	1.0	1.0	0.0	0.0	0.0
72.5°	3.2	2.2	2.2	2.2	1.0	1.0	0.0	0.0
75°	3.2	2.2	2.2	2.2	1.0	1.0	0.0	0.0
77.5°	3.2	3.2	2.2	2.2	1.0	1.0	1.0	0.0
80°	4.3	3.2	2.2	2.2	2.2	1.0	1.0	1.0
82.5°	4.3	3.2	2.2	2.2	2.2	1.0	1.0	1.0
85°	4.3	3.2	3.2	2.2	2.2	1.0	1.0	1.0
87.5°	4.3	3.2	3.2	2.2	2.2	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)