

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192689

Luminaire Tested: **LDA6A70927D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192689
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26684)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70927D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4435.5 lumens
Efficiency: N/A
Efficacy: 56.8 lumens/watt
Spacing Criteria (0/90/45): 2.21 / 1.07 / 1.54
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192689

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192689

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	61		
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54		
6	77	65	57	51	75	64	57	51	62	56	51	61	55	50	59	54	50	48		
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35		
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	69967	69967	69967
5°	111160	69112	44893
10°	166780	66320	30137
15°	238997	62849	22299
20°	315488	58764	18581
25°	378663	57282	27147
30°	423116	57427	41006
35°	435013	51424	35001
40°	419193	40891	26034
45°	369449	30367	20025
50°	288110	22490	13859
55°	166627	16449	8946
60°	77888	11446	4002
65°	36424	6291	1673
70°	16894	2773	1202
75°	7074	1822	1377
80°	3031	2052	1673
85°	629	3334	2705

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192689

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.0	3.0
10°-20°	484.5	10.9
20°-30°	959.2	21.6
30°-40°	1240.1	28.0
40°-50°	1019.1	23.0
50°-60°	471.1	10.6
60°-70°	107.6	2.4
70°-80°	17.6	0.4
80°-90°	4.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1575.6	35.5
0°-40°	2815.8	63.5
0°-60°	4305.9	97.1
0°-90°	4435.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4435.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1276	1276	1276	1276	1276	
5°	2020	1737	1256	908	816	223
15°	4211	2816	1107	496	393	1230
25°	6260	3504	947	465	449	2883
35°	6500	3207	768	510	523	4025
45°	4765	2165	392	260	258	3627
55°	1743	843	172	111	94	1639
65°	281	172	48	18	13	322
75°	33	19	9	8	6	44
85°	1	3	5	5	4	3
90°	0	0	0	0	0	

TEST NUMBER: P1192689

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3
2.5°	1620.7	1596.0	1611.1	1618.6	1579.9	1588.5	1592.8	1562.6	1554.0	1537.9	1490.6
5°	2020.0	1991.0	2002.8	2002.8	1945.7	1949.0	1946.9	1889.8	1858.6	1817.7	1736.9
7.5°	2490.3	2461.2	2463.4	2452.6	2371.9	2366.6	2332.1	2262.2	2200.8	2125.5	2005.0
10°	2996.1	2978.9	2968.1	2941.2	2834.7	2816.4	2765.8	2654.9	2553.8	2438.6	2268.7
12.5°	3590.2	3555.8	3524.6	3481.5	3342.7	3308.2	3237.1	3076.8	2928.3	2766.9	2542.0
15°	4211.1	4184.2	4133.7	4065.8	3888.2	3833.5	3740.9	3525.6	3340.5	3104.8	2816.4
17.5°	4853.6	4804.1	4729.9	4634.1	4419.9	4342.5	4227.3	3951.8	3706.3	3412.6	3063.9
20°	5407.9	5369.1	5266.8	5143.2	4897.7	4794.5	4658.9	4320.9	4020.7	3672.0	3261.9
22.5°	5888.9	5837.3	5711.3	5561.8	5287.4	5159.3	5006.4	4628.7	4262.8	3858.2	3407.3
25°	6260.2	6221.5	6071.9	5897.5	5596.3	5447.7	5278.8	4850.4	4444.7	4000.3	3504.0
27.5°	6562.6	6497.0	6330.2	6133.2	5808.2	5634.9	5456.3	4987.1	4548.0	4072.3	3540.7
30°	6684.2	6616.4	6439.9	6221.5	5877.1	5686.6	5502.5	5002.1	4540.5	4047.6	3496.5
32.5°	6661.6	6585.1	6396.9	6165.6	5813.5	5610.2	5424.0	4904.2	4432.8	3935.7	3377.1
35°	6500.2	6436.8	6241.9	5999.8	5648.9	5434.8	5239.9	4725.6	4253.1	3762.4	3207.1
37.5°	6257.0	6166.6	5984.7	5741.5	5370.2	5171.1	4978.5	4470.5	4008.8	3522.4	2995.0
40°	5857.7	5749.0	5567.1	5355.1	5002.1	4804.1	4628.7	4154.1	3699.9	3245.8	2742.2
42.5°	5355.1	5270.1	5101.2	4882.7	4558.8	4369.4	4212.2	3756.0	3353.5	2932.6	2463.4
45°	4765.4	4683.6	4539.4	4342.5	4049.7	3885.1	3740.9	3335.1	2972.4	2588.2	2165.3
47.5°	4127.2	4046.4	3920.6	3747.3	3485.8	3343.7	3217.9	2885.3	2543.0	2207.3	1836.0
50°	3378.2	3267.3	3198.5	3053.2	2834.7	2714.2	2617.2	2319.1	2066.4	1796.2	1487.3
52.5°	2521.5	2485.9	2387.0	2284.8	2130.9	2041.5	1978.1	1786.5	1576.6	1380.7	1145.0
55°	1743.4	1711.2	1650.9	1588.5	1485.1	1440.0	1392.5	1276.3	1136.4	1003.0	842.6
57.5°	1102.1	1125.6	1087.0	1051.4	989.0	972.9	936.3	868.5	782.4	698.4	598.3
60°	710.4	723.2	698.4	678.0	643.6	630.7	613.4	572.6	520.8	472.5	404.6
62.5°	449.8	456.3	442.3	430.5	411.1	405.8	393.9	370.3	339.1	309.9	266.9
65°	280.8	286.3	276.5	269.0	257.3	258.3	247.5	233.5	215.3	197.0	172.1
67.5°	173.3	176.4	170.0	165.8	158.2	158.2	151.7	143.1	131.3	120.5	104.4
70°	105.4	106.6	102.2	100.1	94.8	93.6	90.4	84.0	76.4	68.9	59.2
72.5°	61.4	62.4	59.2	57.1	53.8	53.8	51.6	48.5	45.2	38.7	33.4
75°	33.4	34.4	32.4	31.2	29.0	30.2	28.0	26.9	23.7	21.6	19.4
77.5°	17.3	18.3	17.3	16.1	16.1	16.1	15.1	13.9	13.9	11.8	11.8
80°	9.6	9.6	9.6	9.6	9.6	8.6	8.6	8.6	8.6	8.6	7.5
82.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	4.3
85°	1.0	1.0	2.2	2.2	2.2	2.2	2.2	2.2	2.2	3.2	3.2
87.5°	0.0	0.0	1.0	1.0	1.0	1.0	1.0	2.2	2.2	2.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192689

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3
2.5°	1476.5	1475.5	1425.9	1404.5	1387.2	1360.3	1340.9	1320.5	1302.2	1268.9	1240.8
5°	1696.1	1665.9	1584.2	1532.4	1500.2	1457.2	1409.8	1362.5	1316.2	1255.9	1206.5
7.5°	1926.4	1861.9	1739.1	1653.1	1603.5	1543.2	1463.6	1389.4	1314.0	1231.2	1160.1
10°	2145.9	2040.5	1884.4	1753.2	1685.3	1607.8	1498.1	1394.7	1295.7	1191.4	1103.1
12.5°	2369.8	2219.1	2015.7	1845.6	1759.6	1663.7	1522.8	1394.7	1272.0	1151.5	1047.1
15°	2591.5	2392.3	2139.4	1928.6	1824.2	1710.0	1540.1	1387.2	1243.0	1107.4	991.2
17.5°	2780.9	2534.4	2229.8	1985.5	1862.9	1733.8	1538.9	1364.6	1204.3	1057.9	934.1
20°	2928.3	2636.6	2293.4	2014.6	1876.8	1735.9	1521.8	1331.3	1160.1	1007.3	880.3
22.5°	3028.3	2703.4	2325.6	2020.0	1872.5	1724.1	1494.8	1297.9	1120.3	967.5	840.5
25°	3090.8	2736.7	2335.4	2012.4	1857.6	1703.6	1470.0	1268.9	1094.4	947.0	828.7
27.5°	3102.7	2727.1	2316.0	1981.2	1822.0	1667.0	1434.5	1240.8	1071.9	935.3	828.7
30°	3044.6	2664.7	2250.3	1911.3	1755.3	1603.5	1375.4	1190.2	1032.0	907.2	810.4
32.5°	2933.7	2549.5	2141.6	1807.9	1656.2	1514.2	1294.6	1118.2	965.3	850.1	763.0
35°	2773.4	2395.6	2000.6	1677.8	1530.3	1398.0	1181.7	1020.2	875.0	768.4	687.6
37.5°	2578.6	2210.4	1836.0	1529.3	1389.4	1265.6	1058.9	907.2	772.8	672.7	600.5
40°	2341.7	2010.3	1650.9	1365.6	1232.2	1120.3	929.8	783.4	656.4	571.4	505.9
42.5°	2094.2	1786.5	1453.9	1182.7	1064.4	957.8	788.9	657.6	544.6	474.7	422.9
45°	1839.2	1537.9	1247.3	1006.3	916.8	797.5	641.5	534.9	443.3	391.7	350.9
47.5°	1551.8	1296.8	1028.9	816.8	723.2	642.5	512.2	426.2	367.0	321.8	290.6
50°	1243.0	1039.6	814.6	633.9	556.3	495.1	399.3	340.1	294.9	263.7	240.0
52.5°	955.7	795.3	613.4	464.9	416.4	370.3	311.0	270.2	237.8	214.1	197.0
55°	710.4	580.1	441.2	344.4	309.9	279.8	244.3	212.0	188.4	172.1	158.2
57.5°	500.4	404.6	309.9	249.6	231.4	212.0	185.1	163.6	147.4	134.6	123.8
60°	334.8	275.5	218.4	182.9	170.0	157.2	139.9	124.8	113.0	104.4	93.6
62.5°	224.9	185.1	152.9	131.3	122.7	114.0	102.2	91.5	82.8	74.2	65.7
65°	144.2	122.7	103.2	89.3	82.8	78.5	69.9	62.4	55.9	48.5	42.0
67.5°	88.3	76.4	64.6	55.9	52.8	49.5	44.1	38.7	34.4	29.0	24.7
70°	51.6	45.2	38.7	33.4	32.4	30.2	25.9	22.6	20.4	17.3	15.1
72.5°	30.2	26.9	22.6	20.4	19.4	17.3	16.1	13.9	11.8	10.8	9.6
75°	17.3	15.1	12.9	11.8	11.8	10.8	9.6	9.6	8.6	8.6	7.5
77.5°	10.8	9.6	8.6	8.6	8.6	7.5	7.5	7.5	7.5	6.5	6.5
80°	7.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
82.5°	4.3	4.3	4.3	4.3	4.3	5.3	5.3	5.3	5.3	5.3	6.5
85°	3.2	4.3	4.3	4.3	4.3	4.3	5.3	5.3	5.3	5.3	5.3
87.5°	3.2	4.3	4.3	4.3	4.3	4.3	5.3	5.3	5.3	5.3	5.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192689

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3
2.5°	1224.7	1207.5	1154.7	1173.1	1139.7	1112.8	1110.7	1094.4	1066.5	1051.4	1044.0
5°	1168.8	1130.0	1065.4	1069.7	1031.0	989.0	966.5	944.9	908.4	885.6	870.7
7.5°	1099.9	1047.1	970.8	965.3	924.5	873.8	841.6	811.4	771.6	742.6	724.3
10°	1027.7	963.1	873.8	867.4	824.4	769.5	732.9	698.4	657.6	628.5	609.1
12.5°	961.0	886.8	797.5	781.2	739.4	683.3	643.6	607.0	567.1	542.4	519.8
15°	897.6	816.8	722.1	707.0	666.2	610.3	566.1	533.8	496.1	472.5	452.0
17.5°	834.0	751.2	657.6	640.3	601.6	547.7	509.0	474.7	440.2	417.6	399.3
20°	779.2	696.3	604.8	587.6	552.0	500.4	464.9	432.7	401.5	379.9	364.8
22.5°	743.7	662.9	580.1	565.0	531.6	485.3	452.0	424.1	397.2	376.6	364.8
25°	741.6	671.5	597.3	588.7	560.7	522.0	498.3	481.0	464.9	448.8	444.5
27.5°	754.4	697.4	635.0	632.8	610.3	584.4	573.6	568.3	559.7	554.2	561.8
30°	746.9	698.4	645.6	645.6	628.5	610.3	604.8	602.6	597.3	598.3	607.0
32.5°	707.0	662.9	612.3	613.4	602.6	582.2	578.9	577.9	571.4	570.4	576.8
35°	635.0	594.0	552.0	553.2	544.6	525.1	520.8	518.7	510.0	505.9	510.0
37.5°	552.0	518.7	478.8	478.8	470.4	455.3	450.9	446.6	441.2	437.0	437.0
40°	467.1	440.2	407.8	406.8	400.3	385.2	380.9	377.8	372.4	364.8	367.0
42.5°	395.0	370.3	344.4	342.2	337.9	325.0	320.7	316.4	311.0	304.6	304.6
45°	328.3	312.0	289.5	288.5	284.1	273.4	270.2	264.7	260.4	253.9	253.9
47.5°	273.4	260.4	242.2	241.0	237.8	228.2	224.9	220.6	216.3	212.0	212.0
50°	229.2	216.3	201.3	200.2	198.0	190.5	186.2	182.9	179.7	176.4	174.3
52.5°	188.4	177.6	165.8	164.6	162.5	155.0	151.7	149.5	146.4	140.9	140.9
55°	151.7	143.1	132.4	131.3	129.1	122.7	119.5	115.2	110.9	105.4	104.4
57.5°	118.3	110.9	102.2	101.2	97.9	92.6	87.1	82.8	78.5	74.2	72.0
60°	89.3	80.7	73.2	71.0	68.9	61.4	57.1	52.8	48.5	45.2	43.0
62.5°	60.3	54.9	46.3	45.2	43.0	38.7	33.4	31.2	29.0	26.9	25.9
65°	37.7	33.4	29.0	28.0	25.9	22.6	20.4	19.4	18.3	17.3	16.1
67.5°	22.6	20.4	17.3	17.3	16.1	15.1	12.9	12.9	11.8	11.8	10.8
70°	13.9	12.9	11.8	10.8	10.8	10.8	9.6	9.6	9.6	9.6	9.6
72.5°	9.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
75°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
77.5°	7.5	7.5	6.5	7.5	7.5	7.5	7.5	6.5	7.5	6.5	6.5
80°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
82.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	5.3	5.3	5.3	5.3
85°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	4.3
87.5°	5.3	5.3	5.3	5.3	5.3	4.3	4.3	4.3	4.3	3.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192689

CATALOG NUMBER: LDA6A70927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3	1276.3
2.5°	1046.1	1015.9	1027.7	1010.6	1005.1	1000.8	994.4	1014.9
5°	864.2	831.9	839.5	822.2	814.6	807.1	799.7	815.8
7.5°	713.5	682.3	685.5	670.5	662.9	654.3	646.8	659.7
10°	596.2	567.1	568.3	554.2	546.7	538.1	531.6	541.4
12.5°	506.9	480.0	480.0	469.2	462.7	453.1	447.6	455.3
15°	439.2	415.4	415.4	404.6	399.3	390.7	385.2	392.9
17.5°	387.4	366.0	366.0	358.3	353.0	345.4	341.1	347.6
20°	353.0	334.8	335.8	328.3	324.0	315.3	313.2	318.5
22.5°	356.2	339.1	341.1	335.8	331.5	325.0	322.8	330.4
25°	445.5	432.7	440.2	440.2	442.3	432.7	437.0	448.8
27.5°	572.6	566.1	577.9	573.6	582.2	582.2	586.5	601.6
30°	618.8	613.4	626.4	625.2	633.9	631.7	633.9	647.8
32.5°	585.4	580.1	590.9	589.7	596.2	590.9	591.9	603.8
35°	514.4	509.0	516.5	515.5	519.8	513.4	516.5	523.0
37.5°	439.2	433.7	438.0	437.0	438.0	430.5	434.8	438.0
40°	369.1	362.7	369.1	364.8	366.0	358.3	359.5	363.8
42.5°	308.9	301.4	306.7	306.7	306.7	301.4	302.4	306.7
45°	257.3	251.8	255.1	253.9	255.1	250.8	253.9	258.3
47.5°	213.1	208.8	210.9	209.8	209.8	205.5	206.6	206.6
50°	175.4	171.1	172.1	171.1	168.0	162.5	161.5	162.5
52.5°	138.8	133.4	133.4	131.3	129.1	124.8	124.8	126.0
55°	102.2	97.9	97.9	96.9	94.8	91.5	91.5	93.6
57.5°	68.9	65.7	66.7	65.7	65.7	61.4	63.6	63.6
60°	42.0	39.8	39.8	38.7	36.5	35.5	34.4	36.5
62.5°	24.7	23.7	23.7	22.6	22.6	21.6	21.6	21.6
65°	16.1	15.1	15.1	13.9	13.9	12.9	11.8	12.9
67.5°	10.8	9.6	9.6	9.6	9.6	8.6	8.6	8.6
70°	9.6	8.6	8.6	8.6	8.6	7.5	7.5	7.5
72.5°	8.6	7.5	8.6	7.5	7.5	7.5	7.5	7.5
75°	7.5	7.5	7.5	6.5	6.5	6.5	6.5	6.5
77.5°	6.5	6.5	6.5	6.5	6.5	5.3	5.3	5.3
80°	6.5	5.3	5.3	5.3	5.3	5.3	5.3	5.3
82.5°	5.3	5.3	5.3	5.3	5.3	4.3	4.3	4.3
85°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
87.5°	3.2	3.2	3.2	3.2	3.2	2.2	2.2	2.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)