

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203224

Luminaire Tested: **LE_6B15D010 EC6B10208035 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203224
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208035 6LBMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1373.1 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203224

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBMH1

Luminous Intensity Polar Plot






TEST NUMBER: P203224

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	105	103	104	102	100		100	99	97		97
2	107	102	97	93	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	60	55	75	65	59	55	64	59	55		63	58	55		62
9	72	62	56	51	71	61	55	51	60	55	51		60	55	51		59
10	69	58	52	48	68	58	52	48	57	52	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203224

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.2	9.0
10°-20°	321.4	23.4
20°-30°	416.5	30.3
30°-40°	309.2	22.5
40°-50°	130.5	9.5
50°-60°	46.3	3.4
60°-70°	17.9	1.3
70°-80°	6.2	0.5
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	862.1	62.8
0°-40°	1171.4	85.3
0°-60°	1348.2	98.2
0°-90°	1373.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1373.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1359	
5°	1330	124
15°	1147	321
25°	924	416
35°	490	309
45°	161	130
55°	49	46
65°	18	18
75°	6	6
85°	0	1
90°	0	



TEST NUMBER: P203224

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1358.9
2.5°	1355.0
5°	1329.5
7.5°	1292.2
10°	1247.1
12.5°	1198.1
15°	1147.1
17.5°	1090.2
20°	1039.2
22.5°	986.2
25°	923.6
27.5°	837.2
30°	735.4
32.5°	615.8
35°	490.2
37.5°	384.4
40°	292.1
42.5°	217.6
45°	160.8
47.5°	117.6
50°	86.2
52.5°	64.8
55°	49.0
57.5°	37.2
60°	29.4
62.5°	21.6
65°	17.6
67.5°	13.8
70°	9.8
72.5°	7.9
75°	5.9
77.5°	3.9
80°	2.0
82.5°	2.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)