

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203327

Luminaire Tested: **LE_6B15D010 EC6B10208035 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203327
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208035 6LBMWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1482.7 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203327

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203327

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		93
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	85	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	87	78	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203327

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.1	11.4
10°-20°	415.2	28.0
20°-30°	480.4	32.4
30°-40°	307.1	20.7
40°-50°	87.1	5.9
50°-60°	15.5	1.0
60°-70°	6.3	0.4
70°-80°	2.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1064.7	71.8
0°-40°	1371.7	92.5
0°-60°	1474.3	99.4
0°-90°	1482.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1482.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1850	
5°	1817	169
15°	1489	415
25°	1060	480
35°	485	307
45°	101	87
55°	14	16
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P203327

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1849.9
2.5°	1847.9
5°	1817.0
7.5°	1761.2
10°	1682.9
12.5°	1592.1
15°	1489.0
17.5°	1381.8
20°	1276.6
22.5°	1173.5
25°	1060.0
27.5°	936.2
30°	798.1
32.5°	643.5
35°	484.6
37.5°	350.6
40°	243.4
42.5°	160.9
45°	101.0
47.5°	59.8
50°	35.0
52.5°	20.6
55°	14.4
57.5°	12.4
60°	10.2
62.5°	8.2
65°	6.1
67.5°	4.1
70°	4.1
72.5°	2.0
75°	2.0
77.5°	2.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)