

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192695

Luminaire Tested: **LDA6A70927D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192695
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26685)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70927D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4693.7 lumens
Efficiency: N/A
Efficacy: 60.1 lumens/watt
Spacing Criteria (0/90/45): 2.12 / 1.05 / 1.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192695

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192695

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	76	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55		
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44		
8	67	55	47	42	65	54	47	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	43	38	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	83064	83064	83064
5°	133485	81427	51931
10°	197391	77999	34869
15°	268980	73786	25897
20°	332675	69627	24543
25°	385419	68550	40297
30°	420514	65675	40323
35°	432189	56751	31548
40°	420881	44669	24560
45°	381621	33042	19351
50°	300672	24417	13125
55°	179282	17385	7503
60°	91681	11556	2840
65°	43831	6136	1245
70°	20693	2773	1202
75°	8430	1822	1377
80°	4072	2052	1357
85°	2013	3334	2013



TEST NUMBER: P1192695

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	3.3
10°-20°	549.5	11.7
20°-30°	1034.4	22.0
30°-40°	1259.6	26.8
40°-50°	1048.5	22.3
50°-60°	502.2	10.7
60°-70°	120.6	2.6
70°-80°	19.0	0.4
80°-90°	4.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1739.5	37.1
0°-40°	2999.1	63.9
0°-60°	4549.7	96.9
0°-90°	4693.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4693.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1515	1515	1515	1515	1515	
5°	2426	2058	1480	1076	944	266
15°	4739	3220	1300	590	456	1358
25°	6372	3763	1133	642	666	2927
35°	6458	3305	848	494	471	4001
45°	4922	2209	426	263	250	3727
55°	1876	912	182	102	78	1767
65°	338	197	47	15	10	387
75°	40	20	9	8	6	54
85°	3	3	5	4	3	5
90°	0	0	0	0	0	

TEST NUMBER: P1192695

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2
2.5°	1959.7	1890.8	1912.3	1908.0	1903.7	1881.1	1865.0	1850.9	1815.4	1815.4	1770.3
5°	2425.7	2345.0	2365.4	2350.3	2330.9	2296.6	2265.4	2229.8	2164.1	2136.2	2057.6
7.5°	2958.3	2866.9	2885.1	2855.1	2814.2	2767.9	2717.3	2650.6	2546.2	2482.6	2361.1
10°	3546.0	3415.7	3426.5	3381.4	3313.5	3251.1	3202.6	3075.7	2927.1	2821.7	2651.6
12.5°	4102.4	3988.3	3991.5	3927.9	3830.0	3753.7	3680.5	3512.7	3314.6	3163.9	2940.1
15°	4739.4	4599.5	4566.1	4480.1	4352.0	4258.4	4158.3	3946.3	3697.7	3498.6	3219.9
17.5°	5252.7	5108.5	5087.1	5006.3	4823.4	4710.3	4584.5	4345.5	4030.2	3782.7	3440.5
20°	5702.5	5559.4	5522.9	5418.5	5208.6	5079.5	4927.8	4645.8	4301.4	3996.8	3610.6
22.5°	6070.6	5913.5	5861.9	5732.7	5499.2	5354.0	5168.8	4861.0	4476.8	4136.7	3711.7
25°	6371.9	6193.3	6127.7	5981.3	5718.8	5558.4	5355.0	5010.6	4592.0	4216.4	3763.3
27.5°	6564.6	6386.0	6313.8	6146.0	5851.1	5678.9	5457.2	5084.9	4632.8	4227.2	3752.6
30°	6643.1	6458.0	6376.2	6185.8	5868.3	5686.4	5455.1	5052.6	4580.2	4149.7	3662.2
32.5°	6594.8	6412.9	6321.4	6114.8	5784.3	5588.5	5357.1	4927.8	4441.3	3995.8	3505.0
35°	6458.0	6278.3	6183.7	5963.1	5618.7	5414.2	5183.9	4739.4	4247.6	3792.3	3304.9
37.5°	6222.4	6052.4	5943.7	5725.2	5378.7	5169.9	4941.7	4492.9	3990.3	3562.1	3073.5
40°	5881.3	5719.8	5612.2	5378.7	5051.6	4840.6	4625.3	4170.1	3696.6	3279.1	2807.8
42.5°	5446.4	5297.9	5194.6	4967.6	4655.5	4447.8	4250.9	3813.9	3363.0	2965.9	2520.3
45°	4922.4	4793.3	4692.1	4503.7	4196.0	3999.0	3821.5	3425.4	2987.4	2622.6	2209.4
47.5°	4305.7	4199.1	4101.2	3930.1	3652.6	3466.4	3320.0	2957.3	2586.0	2242.8	1890.8
50°	3525.5	3449.1	3372.7	3195.2	2999.3	2836.8	2730.3	2407.4	2107.2	1838.1	1546.4
52.5°	2658.1	2611.9	2558.0	2431.0	2299.7	2205.1	2110.4	1865.0	1640.1	1440.0	1212.8
55°	1875.8	1852.1	1810.1	1758.5	1658.4	1593.8	1512.0	1387.2	1212.8	1078.3	911.5
57.5°	1267.7	1261.2	1232.2	1201.0	1146.1	1124.6	1055.8	974.9	877.0	776.9	658.6
60°	836.2	822.2	815.8	798.5	756.5	739.3	714.5	662.9	602.6	532.8	459.6
62.5°	538.1	530.6	525.1	517.7	491.8	491.8	467.1	443.3	398.2	355.2	307.7
65°	337.9	331.5	330.4	325.0	315.3	311.0	292.8	275.5	253.9	230.4	197.0
67.5°	217.4	207.6	202.3	199.2	192.7	185.1	178.6	171.1	153.9	139.9	118.3
70°	129.1	120.5	119.5	120.5	113.0	111.9	105.4	100.1	88.3	79.7	66.7
72.5°	73.2	68.9	67.7	67.7	63.6	62.4	58.1	54.9	48.5	42.0	36.5
75°	39.8	36.5	36.5	36.5	34.4	33.4	31.2	30.2	25.9	23.7	20.4
77.5°	22.6	21.6	21.6	20.4	19.4	18.3	17.3	17.3	15.1	13.9	12.9
80°	12.9	12.9	12.9	12.9	11.8	11.8	10.8	10.8	9.6	9.6	8.6
82.5°	7.5	7.5	7.5	7.5	7.5	7.5	6.5	6.5	6.5	6.5	5.3
85°	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
87.5°	0.0	0.0	1.0	1.0	1.0	1.0	1.0	2.2	2.2	2.2	3.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192695

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2
2.5°	1749.9	1717.5	1715.3	1668.0	1638.0	1613.1	1594.8	1572.3	1521.7	1493.8	1473.3
5°	2002.8	1936.1	1901.6	1815.4	1768.1	1726.1	1674.5	1620.7	1537.9	1479.7	1432.4
7.5°	2265.4	2154.5	2081.3	1953.2	1888.6	1823.0	1735.9	1648.6	1535.7	1448.5	1376.4
10°	2509.7	2352.5	2236.3	2064.1	1980.1	1894.1	1771.4	1654.1	1513.0	1401.2	1306.5
12.5°	2749.5	2543.0	2382.6	2164.1	2061.9	1955.3	1798.3	1650.8	1485.1	1350.5	1239.8
15°	2978.9	2719.5	2515.0	2251.3	2131.9	2003.8	1815.4	1641.1	1452.8	1300.1	1174.1
17.5°	3161.8	2853.9	2608.6	2305.2	2170.6	2025.4	1809.1	1613.1	1408.6	1246.1	1108.4
20°	3287.6	2940.1	2660.2	2326.6	2179.2	2023.2	1784.2	1574.4	1362.5	1193.5	1053.6
22.5°	3355.5	2978.9	2674.3	2320.2	2166.3	2002.8	1754.2	1538.9	1325.8	1156.8	1023.4
25°	3380.2	2982.0	2659.2	2292.3	2137.2	1970.4	1718.7	1505.5	1296.8	1133.3	1008.3
27.5°	3351.2	2936.9	2604.3	2234.2	2077.0	1912.3	1661.6	1458.2	1253.8	1098.7	981.4
30°	3252.1	2831.3	2496.7	2130.8	1976.9	1818.7	1571.3	1371.1	1183.7	1037.5	925.5
32.5°	3095.1	2676.5	2345.0	1988.7	1840.3	1688.5	1451.8	1261.2	1087.0	949.2	849.1
35°	2900.2	2491.3	2168.4	1823.0	1683.1	1540.1	1315.0	1135.4	971.8	848.0	750.0
37.5°	2679.6	2285.8	1973.7	1656.2	1514.2	1379.6	1161.2	1007.3	850.1	737.2	647.8
40°	2432.2	2050.1	1766.0	1457.1	1332.3	1209.6	1007.3	867.4	724.3	624.2	546.7
42.5°	2167.4	1811.1	1548.5	1271.0	1146.1	1034.2	852.3	726.5	599.5	516.5	455.3
45°	1886.5	1572.3	1320.5	1071.9	958.8	862.1	696.3	582.2	489.6	426.2	379.9
47.5°	1592.7	1315.0	1091.3	874.9	774.8	690.9	557.5	470.2	397.2	350.9	315.3
50°	1296.8	1049.3	871.7	687.6	601.6	534.9	435.8	375.6	321.8	286.3	259.4
52.5°	1013.8	811.4	667.2	518.7	453.1	406.8	340.1	298.1	257.3	230.4	209.8
55°	749.0	611.3	487.5	376.6	337.9	308.9	261.6	231.4	202.3	181.9	166.8
57.5°	541.2	438.0	347.6	276.5	250.8	231.4	197.0	176.4	156.0	140.9	129.1
60°	379.9	302.4	245.3	202.3	184.1	171.1	146.4	133.4	118.3	105.4	93.6
62.5°	249.6	203.3	171.1	143.1	132.4	122.7	105.4	95.8	82.8	74.2	63.6
65°	162.5	133.4	114.0	95.8	87.1	82.8	71.0	63.6	54.9	47.3	40.8
67.5°	99.1	82.8	72.0	60.3	55.9	51.6	44.1	38.7	33.4	28.0	24.7
70°	54.9	48.5	42.0	35.5	32.4	30.2	25.9	23.7	19.4	17.3	13.9
72.5°	32.4	28.0	24.7	20.4	19.4	18.3	15.1	13.9	11.8	10.8	9.6
75°	19.4	16.1	15.1	12.9	11.8	11.8	10.8	9.6	8.6	8.6	7.5
77.5°	11.8	10.8	9.6	8.6	8.6	8.6	7.5	7.5	7.5	6.5	6.5
80°	7.5	7.5	7.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
82.5°	5.3	5.3	5.3	4.3	5.3	4.3	5.3	5.3	5.3	5.3	5.3
85°	3.2	3.2	4.3	4.3	4.3	4.3	4.3	5.3	5.3	5.3	5.3
87.5°	3.2	3.2	4.3	4.3	4.3	4.3	4.3	5.3	5.3	5.3	4.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192695

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2
2.5°	1449.6	1409.8	1380.7	1359.2	1366.8	1329.1	1317.2	1276.3	1261.2	1261.2	1239.8
5°	1383.9	1320.5	1271.0	1239.8	1237.7	1183.7	1155.8	1104.2	1076.2	1055.8	1035.3
7.5°	1305.4	1223.6	1158.0	1120.3	1109.5	1046.0	1008.3	956.7	914.7	887.8	863.1
10°	1221.4	1123.5	1049.3	1006.1	990.0	921.2	871.7	824.4	779.1	751.2	725.3
12.5°	1140.7	1034.2	952.4	908.2	887.8	816.8	766.3	716.7	673.7	644.6	618.8
15°	1066.5	953.5	867.4	823.2	800.7	730.8	680.2	631.7	589.7	562.8	539.1
17.5°	996.5	881.3	795.3	752.2	727.5	662.9	614.4	567.1	529.5	504.7	483.2
20°	943.7	829.7	750.0	712.4	687.6	627.4	585.4	544.6	513.4	495.1	474.5
22.5°	921.2	815.8	747.9	713.5	696.3	647.8	618.8	589.7	569.3	566.1	553.2
25°	918.0	825.4	769.5	740.4	729.6	693.1	675.8	657.6	642.5	646.8	649.0
27.5°	904.0	817.9	771.6	746.9	738.2	708.1	695.3	678.0	667.2	672.5	674.7
30°	855.6	775.9	732.9	712.4	703.9	673.7	662.9	643.5	635.0	636.0	635.0
32.5°	780.2	704.9	665.1	646.8	637.0	610.1	598.3	581.1	568.3	567.1	565.0
35°	688.8	620.9	584.4	568.3	558.5	535.9	525.1	509.0	493.9	492.9	490.8
37.5°	595.2	534.9	503.6	489.6	481.0	462.7	449.8	439.0	429.4	425.1	424.1
40°	504.7	450.9	428.4	417.6	411.1	391.7	385.2	374.4	367.0	362.7	361.6
42.5°	419.7	382.1	363.8	354.0	348.7	334.8	327.1	318.5	311.0	306.7	305.6
45°	356.2	325.0	307.7	300.2	295.9	283.0	277.7	269.0	262.6	259.4	258.3
47.5°	297.1	272.2	260.4	251.8	250.8	240.0	232.5	226.0	219.6	216.3	215.3
50°	243.2	222.7	213.1	207.6	206.6	195.9	190.5	185.1	179.7	176.4	174.3
52.5°	200.2	180.8	174.3	166.8	165.8	156.0	151.7	146.4	140.9	136.6	133.4
55°	158.2	143.1	136.6	130.3	129.1	118.3	114.0	107.6	102.2	97.9	93.6
57.5°	120.5	108.7	102.2	95.8	94.8	87.1	79.7	74.2	68.9	63.6	60.3
60°	88.3	76.4	68.9	65.7	62.4	54.9	49.5	45.2	40.8	37.7	34.4
62.5°	58.1	49.5	44.1	39.8	37.7	32.4	29.0	25.9	23.7	22.6	21.6
65°	35.5	30.2	25.9	23.7	23.7	20.4	18.3	16.1	15.1	15.1	13.9
67.5°	21.6	18.3	16.1	15.1	13.9	12.9	11.8	11.8	10.8	10.8	9.6
70°	12.9	11.8	10.8	9.6	9.6	9.6	9.6	9.6	8.6	8.6	8.6
72.5°	9.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	7.5	7.5	7.5
75°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.5
77.5°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
80°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	5.3	5.3	5.3
82.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
85°	5.3	5.3	5.3	5.3	5.3	5.3	4.3	4.3	4.3	4.3	4.3
87.5°	5.3	4.3	4.3	4.3	4.3	4.3	3.2	3.2	3.2	3.2	2.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192695

CATALOG NUMBER: LDA6A70927D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2	1515.2
2.5°	1229.0	1237.7	1224.7	1216.1	1207.5	1213.9	1183.7	1170.9
5°	1015.9	1006.1	999.8	992.2	979.3	981.4	955.7	943.7
7.5°	840.5	834.0	817.9	809.3	796.3	796.3	772.6	763.0
10°	701.7	691.9	676.8	669.4	657.6	647.8	636.0	626.4
12.5°	596.2	585.4	572.5	566.1	554.2	546.7	534.9	536.9
15°	517.7	506.9	495.1	488.6	478.8	471.4	461.7	456.3
17.5°	462.7	453.1	443.3	436.9	429.4	422.9	414.3	413.3
20°	458.4	450.9	445.5	441.2	434.8	430.5	426.2	420.7
22.5°	548.9	549.9	551.0	551.0	552.0	552.0	553.2	542.4
25°	647.8	659.7	659.7	662.9	672.5	672.5	670.5	666.2
27.5°	673.7	685.5	682.3	684.5	694.1	696.3	688.8	689.8
30°	630.7	641.3	635.0	636.0	642.5	642.5	632.8	637.0
32.5°	558.5	565.0	556.3	556.3	561.8	560.7	554.2	554.2
35°	482.1	485.3	477.8	481.0	481.0	477.8	471.4	471.4
37.5°	416.4	417.6	410.0	411.1	411.1	407.8	401.5	401.5
40°	354.0	357.3	350.9	353.0	350.9	347.6	344.4	343.2
42.5°	299.2	301.4	295.9	299.2	298.1	298.1	297.1	298.1
45°	251.8	253.9	249.6	251.8	252.9	251.8	248.6	249.6
47.5°	208.8	210.9	210.9	208.8	207.6	202.3	199.2	199.2
50°	169.0	167.8	166.8	163.6	160.3	157.2	153.9	153.9
52.5°	127.0	124.8	123.8	120.5	119.5	116.2	116.2	113.0
55°	87.1	86.1	86.1	82.8	82.8	79.7	78.5	78.5
57.5°	54.9	52.8	53.8	51.6	50.6	47.3	47.3	46.3
60°	31.2	30.2	30.2	29.0	28.0	25.9	25.9	25.9
62.5°	20.4	19.4	19.4	18.3	18.3	17.3	17.3	16.1
65°	12.9	11.8	11.8	10.8	10.8	9.6	9.6	9.6
67.5°	9.6	8.6	8.6	8.6	8.6	8.6	7.5	7.5
70°	8.6	8.6	7.5	7.5	7.5	7.5	7.5	7.5
72.5°	7.5	7.5	7.5	7.5	6.5	6.5	6.5	6.5
75°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
77.5°	6.5	5.3	5.3	5.3	5.3	5.3	5.3	5.3
80°	5.3	5.3	5.3	5.3	5.3	5.3	4.3	4.3
82.5°	5.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
85°	4.3	3.2	3.2	3.2	3.2	3.2	3.2	3.2
87.5°	2.2	2.2	2.2	2.2	1.0	1.0	1.0	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)