

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P201217

Luminaire Tested: **LE\_6B15D010 EC6B10208035 6LBN1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P201217  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35135)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LE\_6B15D010 EC6B10208035 6LBN1LI  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1493.6 lumens  
Efficiency: N/A  
Efficacy: 104.5 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P201217

CATALOG NUMBER: LE\_6B15D010 EC6B10208035 6LBN1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P201217

CATALOG NUMBER: LE\_6B15D010 EC6B10208035 6LBN1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|--|-----|-----|-----|--|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |  | 20  |     |     |  |  | 20  |     |     |  |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |  | 50  |     |     |  |  | 30  |     |     |  |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  |  | 50  | 30  | 10  |  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |  |     |     |     |  |  |     |     |     |  |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  |  | 106 | 106 | 106 |  |  | 102 |
| 1   | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 |  | 105 | 104 | 102 |  |  | 102 | 100 | 99  |  |  | 98  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  |  | 100 | 97  | 95  |  |  | 97  | 95  | 93  |  |  | 94  |
| 3   | 105 | 99  | 94  | 91  | 103 | 97  | 93  | 90  |  | 95  | 91  | 89  |  |  | 92  | 90  | 87  |  |  | 90  |
| 4   | 100 | 93  | 88  | 85  | 98  | 92  | 88  | 84  |  | 90  | 86  | 83  |  |  | 88  | 85  | 82  |  |  | 86  |
| 5   | 96  | 88  | 83  | 79  | 94  | 87  | 83  | 79  |  | 86  | 82  | 78  |  |  | 84  | 80  | 78  |  |  | 83  |
| 6   | 92  | 84  | 79  | 75  | 90  | 83  | 78  | 75  |  | 82  | 77  | 74  |  |  | 80  | 76  | 74  |  |  | 79  |
| 7   | 88  | 80  | 74  | 71  | 87  | 79  | 74  | 70  |  | 78  | 73  | 70  |  |  | 77  | 73  | 70  |  |  | 76  |
| 8   | 84  | 76  | 71  | 67  | 83  | 75  | 70  | 67  |  | 74  | 70  | 67  |  |  | 73  | 69  | 66  |  |  | 73  |
| 9   | 81  | 73  | 67  | 64  | 80  | 72  | 67  | 64  |  | 71  | 67  | 63  |  |  | 70  | 66  | 63  |  |  | 70  |
| 10  | 78  | 69  | 64  | 61  | 77  | 69  | 64  | 61  |  | 68  | 64  | 61  |  |  | 67  | 63  | 60  |  |  | 67  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 36666 |
| 5°  | 34322 |
| 10° | 28011 |
| 15° | 20577 |
| 20° | 14308 |
| 25° | 10575 |
| 30° | 7927  |
| 35° | 4945  |
| 40° | 2414  |
| 45° | 845   |
| 50° | 126   |
| 55° | 94    |
| 60° | 54    |
| 65° | 31    |
| 70° | 38    |
| 75° | 0     |
| 80° | 0     |
| 85° | 0     |



TEST NUMBER: P201217

CATALOG NUMBER: LE\_6B15D010 EC6B10208035 6LBN1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 281.4  | 18.8      |
| 10°-20°   | 507.7  | 34.0      |
| 20°-30°   | 411.2  | 27.5      |
| 30°-40°   | 236.2  | 15.8      |
| 40°-50°   | 50.5   | 3.4       |
| 50°-60°   | 4.4    | 0.3       |
| 60°-70°   | 1.7    | 0.1       |
| 70°-80°   | 0.5    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1200.3 | 80.4      |
| 0°-40°    | 1436.5 | 96.2      |
| 0°-60°    | 1491.5 | 99.9      |
| 0°-90°    | 1493.6 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1493.6 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3386 |      |
| 5°  | 3158 | 281  |
| 15° | 1836 | 508  |
| 25° | 885  | 411  |
| 35° | 374  | 236  |
| 45° | 55   | 51   |
| 55° | 5    | 4    |
| 65° | 1    | 2    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P201217

CATALOG NUMBER: LE\_6B15D010 EC6B10208035 6LBN1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3386.0 |
| 2.5°  | 3332.0 |
| 5°    | 3157.5 |
| 7.5°  | 2877.5 |
| 10°   | 2547.4 |
| 12.5° | 2203.4 |
| 15°   | 1835.5 |
| 17.5° | 1504.1 |
| 20°   | 1241.6 |
| 22.5° | 1043.2 |
| 25°   | 885.1  |
| 27.5° | 757.0  |
| 30°   | 634.0  |
| 32.5° | 506.0  |
| 35°   | 374.1  |
| 37.5° | 258.6  |
| 40°   | 170.8  |
| 42.5° | 103.0  |
| 45°   | 55.2   |
| 47.5° | 22.6   |
| 50°   | 7.5    |
| 52.5° | 6.2    |
| 55°   | 5.0    |
| 57.5° | 3.8    |
| 60°   | 2.5    |
| 62.5° | 2.5    |
| 65°   | 1.2    |
| 67.5° | 1.2    |
| 70°   | 1.2    |
| 72.5° | 1.2    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)