

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192703

Luminaire Tested: **LDA6A70930D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192703
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26690)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70930D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5883.9 lumens
Efficiency: N/A
Efficacy: 75.3 lumens/watt
Spacing Criteria (0/90/45): 2.55 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192703

CATALOG NUMBER: LDA6A70930D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192703

CATALOG NUMBER: LDA6A70930D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	75	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65		
5	85	74	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	59288	59288	59288
5°	153054	54947	17180
10°	290359	41928	5773
15°	519186	27259	5755
20°	773608	18546	10478
25°	882710	23130	65834
30°	954609	19313	19687
35°	1002755	9403	6170
40°	1018623	3378	3127
45°	907536	2233	1876
50°	582855	1569	1279
55°	153447	1099	659
60°	34230	1140	504
65°	3282	1349	597
70°	1106	1667	737
75°	254	2203	1228
80°	0	3631	1831
85°	0	6542	2893



TEST NUMBER: P1192703

CATALOG NUMBER: LDA6A70930D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	131.3	2.2
10°-20°	685.4	11.6
20°-30°	1608.2	27.3
30°-40°	1849.8	31.4
40°-50°	1314.0	22.3
50°-60°	267.2	4.5
60°-70°	13.4	0.2
70°-80°	8.0	0.1
80°-90°	6.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2425.0	41.2
0°-40°	4274.8	72.7
0°-60°	5856.0	99.5
0°-90°	5883.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5883.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1082	1082	1082	1082	1082	
5°	2781	2012	998	400	312	339
15°	9148	4113	480	108	101	2744
25°	14593	4954	382	835	1088	6726
35°	14984	3478	140	104	92	9308
45°	11706	1237	29	31	24	8627
55°	1606	32	12	12	7	2165
65°	25	9	10	9	5	61
75°	1	6	10	9	6	3
85°	0	6	10	8	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192703

CATALOG NUMBER: LDA6A70930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5
2.5°	1863.5	1807.1	1779.3	1778.2	1697.7	1724.1	1697.7	1677.0	1602.0	1571.0	1519.1
5°	2781.3	2712.3	2656.9	2632.8	2494.6	2464.7	2450.9	2380.5	2224.0	2132.9	2012.0
7.5°	3863.9	3791.5	3700.5	3627.8	3427.5	3371.0	3334.2	3213.3	2981.8	2798.7	2572.9
10°	5216.1	5173.5	5026.1	4892.5	4588.4	4470.9	4360.3	4078.2	3775.4	3408.0	3116.5
12.5°	7037.0	6936.7	6674.2	6407.0	5930.2	5755.2	5572.0	5120.4	4657.6	4081.7	3600.2
15°	9148.0	9062.8	8658.5	8223.3	7544.8	7257.0	6970.1	6259.6	5547.8	4806.1	4112.7
17.5°	11578.2	11416.8	11014.9	10279.0	9329.9	8877.4	8342.9	7437.7	6410.4	5402.7	4541.2
20°	13260.7	13165.1	12825.5	12119.4	11039.1	10441.3	9778.0	8535.3	7130.3	5880.7	4822.2
22.5°	14181.0	14085.4	13830.9	13207.8	12322.2	11722.1	10951.7	9423.3	7673.8	6201.9	4954.6
25°	14593.3	14531.2	14391.7	13883.8	13063.9	12523.6	11794.6	10037.1	8013.6	6348.2	4953.5
27.5°	14974.5	14990.6	14646.2	14228.2	13472.7	12930.3	12239.2	10313.5	8080.3	6274.5	4794.6
30°	15080.5	15040.2	14889.2	14300.8	13597.1	13006.2	12265.7	10167.3	7820.1	5948.6	4479.0
32.5°	15014.8	15015.9	14874.3	14248.9	13422.1	12760.9	11928.2	9643.3	7313.3	5437.2	3988.3
35°	14983.7	14973.4	14606.0	14056.7	13006.2	12228.9	11179.6	8802.5	6610.7	4784.2	3478.1
37.5°	14675.1	14612.9	14348.0	13602.8	12228.9	11234.9	10105.1	7774.1	5745.8	4104.7	2955.3
40°	14234.0	14155.6	13724.9	12656.1	10899.8	9790.7	8667.7	6609.6	4840.6	3428.7	2372.5
42.5°	13329.9	13200.9	12547.8	11130.1	9188.3	8156.4	7225.8	5444.1	3957.3	2783.8	1822.0
45°	11706.0	11495.2	10591.2	9110.1	7417.0	6607.3	5820.7	4363.8	3168.4	2073.1	1236.9
47.5°	9399.1	9168.7	8348.8	7159.0	5806.9	5150.5	4482.4	3213.3	2143.3	1208.2	620.8
50°	6834.2	6675.3	5950.9	4947.7	3839.8	3289.3	2776.7	1792.0	1028.4	584.0	254.5
52.5°	3937.7	3823.7	3319.2	2604.0	1888.8	1581.3	1271.4	782.0	524.0	231.5	81.8
55°	1605.5	1539.8	1318.8	1117.2	838.5	724.4	604.7	390.4	176.2	55.2	32.2
57.5°	785.4	777.4	648.4	519.4	382.4	308.6	232.7	78.4	42.6	27.6	20.7
60°	312.2	300.5	206.2	119.8	66.9	54.1	46.0	32.2	24.2	18.4	15.0
62.5°	54.1	52.9	44.9	38.0	31.1	27.6	25.3	19.6	16.1	12.7	11.5
65°	25.3	25.3	23.0	20.7	17.3	16.1	15.0	12.7	10.4	9.2	9.2
67.5°	12.7	12.7	11.5	10.4	9.2	9.2	8.1	8.1	6.9	6.9	6.9
70°	6.9	6.9	6.9	5.8	5.8	5.8	5.8	5.8	4.6	5.8	5.8
72.5°	4.6	4.6	4.6	3.5	2.3	3.5	3.5	3.5	4.6	5.8	5.8
75°	1.2	1.2	1.2	2.3	2.3	2.3	3.5	3.5	4.6	5.8	5.8
77.5°	1.2	1.2	1.2	1.2	2.3	2.3	2.3	3.5	4.6	5.8	5.8
80°	0.0	1.2	1.2	1.2	2.3	2.3	2.3	3.5	4.6	5.8	5.8
82.5°	0.0	0.0	1.2	1.2	2.3	2.3	2.3	3.5	4.6	5.8	5.8
85°	0.0	0.0	1.2	1.2	2.3	2.3	2.3	3.5	4.6	5.8	5.8
87.5°	0.0	0.0	1.2	1.2	2.3	2.3	2.3	3.5	4.6	5.8	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192703

CATALOG NUMBER: LDA6A70930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5
2.5°	1496.1	1436.2	1397.0	1328.0	1299.2	1286.4	1223.1	1162.0	1103.3	1060.8	995.1
5°	1920.0	1824.3	1678.1	1540.9	1481.1	1443.1	1318.8	1203.6	1094.1	998.5	884.5
7.5°	2375.9	2179.1	1949.9	1729.9	1626.2	1557.2	1364.8	1196.7	1039.9	894.8	739.4
10°	2813.7	2503.8	2169.9	1855.4	1714.9	1611.2	1360.2	1144.8	941.0	753.2	586.3
12.5°	3186.8	2786.1	2342.6	1934.9	1751.7	1619.3	1317.6	1055.0	807.4	605.8	460.7
15°	3501.2	3002.5	2456.6	1961.4	1741.4	1584.8	1234.6	931.8	661.0	480.3	372.0
17.5°	3722.3	3107.3	2483.1	1916.4	1668.8	1488.0	1109.1	773.9	519.4	388.1	293.6
20°	3851.3	3121.1	2418.7	1807.1	1542.1	1351.0	951.4	608.1	421.5	317.9	228.1
22.5°	3870.9	3053.2	2292.0	1659.6	1395.8	1211.6	792.3	509.0	383.5	297.1	223.5
25°	3776.5	2918.5	2127.2	1515.6	1263.4	1074.6	685.3	514.8	430.7	382.4	397.3
27.5°	3593.3	2696.2	1938.4	1368.2	1125.2	934.1	647.2	538.9	469.9	478.0	505.6
30°	3312.3	2382.8	1666.5	1118.3	861.5	711.8	514.8	388.1	322.5	305.1	306.3
32.5°	2898.8	1990.1	1308.4	776.2	579.4	480.3	326.0	216.6	217.7	201.6	200.5
35°	2426.7	1602.0	979.0	520.5	400.8	334.0	192.4	152.0	146.2	140.5	132.4
37.5°	1959.1	1238.1	651.8	355.9	255.7	185.4	96.8	79.5	73.8	69.2	69.2
40°	1491.5	866.1	403.1	186.6	103.7	76.1	57.5	48.3	47.2	47.2	46.0
42.5°	1082.6	511.3	218.9	73.8	57.5	50.6	40.3	35.7	35.7	35.7	35.7
45°	575.9	260.3	84.1	46.0	38.0	35.7	29.9	27.6	27.6	28.8	28.8
47.5°	266.0	97.9	42.6	31.1	26.5	26.5	23.0	21.9	21.9	23.0	23.0
50°	95.6	40.3	27.6	21.9	19.6	20.7	18.4	17.3	18.4	18.4	18.4
52.5°	36.8	25.3	19.6	17.3	15.0	16.1	13.8	13.8	15.0	15.0	15.0
55°	23.0	18.4	15.0	12.7	11.5	12.7	11.5	11.5	11.5	11.5	11.5
57.5°	16.1	13.8	11.5	10.4	9.2	10.4	10.4	10.4	10.4	10.4	10.4
60°	12.7	10.4	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.4	10.4
62.5°	10.4	9.2	9.2	9.2	9.2	9.2	9.2	9.2	10.4	10.4	10.4
65°	9.2	8.1	9.2	9.2	8.1	9.2	9.2	9.2	10.4	10.4	11.5
67.5°	6.9	6.9	6.9	8.1	8.1	8.1	9.2	9.2	10.4	10.4	10.4
70°	6.9	6.9	8.1	8.1	8.1	8.1	9.2	9.2	10.4	10.4	10.4
72.5°	6.9	6.9	8.1	8.1	8.1	9.2	9.2	9.2	10.4	10.4	10.4
75°	6.9	6.9	8.1	8.1	8.1	9.2	9.2	9.2	10.4	10.4	10.4
77.5°	6.9	6.9	8.1	8.1	8.1	9.2	9.2	10.4	10.4	10.4	10.4
80°	6.9	8.1	8.1	9.2	9.2	9.2	9.2	10.4	10.4	11.5	11.5
82.5°	6.9	8.1	8.1	9.2	9.2	9.2	9.2	10.4	10.4	11.5	11.5
85°	6.9	8.1	8.1	9.2	9.2	9.2	9.2	10.4	10.4	10.4	10.4
87.5°	6.9	8.1	8.1	9.2	9.2	9.2	9.2	9.2	10.4	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192703

CATALOG NUMBER: LDA6A70930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5
2.5°	951.4	894.8	838.5	810.9	786.6	752.1	708.3	672.5	634.6	615.0	570.2
5°	794.6	698.0	616.2	577.1	547.0	505.6	460.7	428.4	399.6	383.5	354.7
7.5°	615.0	522.8	451.5	421.5	399.6	358.2	324.8	291.3	261.4	239.6	210.8
10°	475.7	404.2	345.5	316.8	292.5	248.8	208.5	177.3	145.1	123.2	114.0
12.5°	377.8	311.0	251.1	222.3	197.0	152.0	122.1	116.3	110.6	108.3	104.8
15°	290.2	229.2	165.8	137.0	126.7	120.9	114.0	112.9	108.3	108.3	104.8
17.5°	217.7	149.7	126.7	124.4	123.2	120.9	117.5	116.3	115.2	115.2	114.0
20°	156.6	145.1	141.6	143.9	145.1	147.4	146.2	146.2	150.8	161.2	158.9
22.5°	220.0	238.4	258.0	264.9	290.2	315.6	338.6	367.4	435.4	513.6	532.0
25°	435.4	490.6	541.2	569.0	610.4	666.8	721.0	787.7	835.0	874.1	919.0
27.5°	541.2	562.1	553.9	557.5	552.8	544.7	547.0	560.9	553.9	533.2	541.2
30°	320.2	336.3	327.1	331.7	319.1	319.1	315.6	322.5	317.9	309.9	307.4
32.5°	208.5	217.7	216.6	216.6	212.0	209.7	201.6	199.3	191.2	176.2	172.7
35°	125.5	119.8	114.0	110.6	108.3	108.3	107.1	107.1	103.7	100.2	99.1
37.5°	68.0	69.2	69.2	69.2	69.2	71.5	70.3	70.3	70.3	68.0	68.0
40°	47.2	49.5	49.5	49.5	50.6	50.6	50.6	51.8	50.6	50.6	50.6
42.5°	36.8	38.0	36.8	36.8	38.0	38.0	38.0	39.1	39.1	39.1	38.0
45°	29.9	29.9	28.8	29.9	29.9	31.1	31.1	31.1	31.1	29.9	29.9
47.5°	24.2	24.2	24.2	24.2	25.3	25.3	25.3	25.3	25.3	25.3	25.3
50°	19.6	19.6	19.6	20.7	20.7	20.7	19.6	20.7	20.7	20.7	19.6
52.5°	15.0	15.0	15.0	15.0	15.0	13.8	13.8	13.8	13.8	13.8	12.7
55°	11.5	11.5	11.5	11.5	11.5	12.7	11.5	12.7	11.5	11.5	10.4
57.5°	10.4	10.4	10.4	10.4	11.5	11.5	10.4	10.4	10.4	9.2	9.2
60°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	9.2	8.1	8.1
62.5°	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1	8.1
65°	11.5	11.5	10.4	11.5	11.5	10.4	10.4	9.2	9.2	8.1	8.1
67.5°	11.5	11.5	11.5	11.5	11.5	11.5	10.4	10.4	9.2	9.2	8.1
70°	11.5	11.5	11.5	11.5	11.5	11.5	10.4	10.4	9.2	9.2	8.1
72.5°	11.5	11.5	11.5	11.5	11.5	11.5	10.4	10.4	10.4	9.2	8.1
75°	11.5	11.5	11.5	11.5	11.5	10.4	10.4	10.4	9.2	9.2	8.1
77.5°	11.5	11.5	11.5	11.5	11.5	10.4	10.4	10.4	9.2	9.2	8.1
80°	11.5	11.5	11.5	11.5	11.5	11.5	10.4	10.4	9.2	9.2	8.1
82.5°	11.5	11.5	11.5	11.5	11.5	10.4	10.4	10.4	9.2	9.2	8.1
85°	11.5	10.4	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1	6.9
87.5°	10.4	10.4	10.4	10.4	10.4	9.2	9.2	8.1	6.9	5.8	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192703

CATALOG NUMBER: LDA6A70930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5	1081.5
2.5°	570.2	559.8	555.1	547.0	540.1	536.6	524.0	538.9
5°	349.0	336.3	332.9	326.0	317.9	313.3	304.0	312.2
7.5°	199.3	184.2	177.3	171.5	163.5	156.6	148.5	153.1
10°	111.7	107.1	108.3	104.8	103.7	102.5	101.4	103.7
12.5°	103.7	100.2	101.4	99.1	97.9	97.9	96.8	97.9
15°	104.8	101.4	103.7	101.4	100.2	100.2	99.1	101.4
17.5°	114.0	111.7	114.0	111.7	112.9	111.7	112.9	114.0
20°	160.0	163.5	170.4	165.8	169.2	173.8	179.6	179.6
22.5°	563.2	636.9	646.1	683.0	777.4	773.9	837.3	839.6
25°	983.6	988.2	1029.6	1015.8	1016.9	1065.4	1060.8	1088.4
27.5°	565.6	564.4	572.5	557.5	562.1	565.6	552.8	567.9
30°	315.6	309.9	313.3	305.1	305.1	307.4	304.0	311.0
32.5°	175.0	170.4	170.4	164.6	163.5	162.3	158.9	162.3
35°	100.2	96.8	97.9	95.6	93.3	92.2	91.0	92.2
37.5°	69.2	66.9	68.0	65.7	63.4	62.3	61.0	62.3
40°	50.6	49.5	49.5	47.2	46.0	44.9	43.7	43.7
42.5°	38.0	36.8	36.8	34.5	33.4	32.2	31.1	32.2
45°	28.8	27.6	27.6	26.5	25.3	24.2	24.2	24.2
47.5°	25.3	24.2	25.3	24.2	23.0	23.0	23.0	23.0
50°	19.6	19.6	19.6	18.4	17.3	17.3	16.1	15.0
52.5°	12.7	11.5	11.5	10.4	10.4	9.2	9.2	9.2
55°	10.4	9.2	9.2	8.1	8.1	6.9	6.9	6.9
57.5°	8.1	8.1	6.9	6.9	5.8	5.8	5.8	5.8
60°	6.9	6.9	6.9	5.8	5.8	4.6	4.6	4.6
62.5°	6.9	5.8	5.8	5.8	4.6	4.6	4.6	4.6
65°	6.9	5.8	5.8	5.8	4.6	4.6	4.6	4.6
67.5°	6.9	5.8	5.8	5.8	4.6	4.6	4.6	4.6
70°	8.1	6.9	6.9	5.8	5.8	5.8	4.6	4.6
72.5°	8.1	6.9	6.9	6.9	5.8	5.8	5.8	5.8
75°	8.1	6.9	6.9	6.9	5.8	5.8	5.8	5.8
77.5°	8.1	6.9	6.9	6.9	5.8	5.8	5.8	5.8
80°	8.1	6.9	6.9	6.9	5.8	5.8	5.8	5.8
82.5°	6.9	6.9	6.9	5.8	5.8	5.8	5.8	5.8
85°	6.9	5.8	5.8	5.8	4.6	4.6	4.6	4.6
87.5°	4.6	4.6	3.5	3.5	3.5	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)