

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204048

Luminaire Tested: **LE_6B15D010 EC6B10208035 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204048
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208035 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1355.9 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204048

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204048

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	103		109	106	103	101		102	100	98		98	97	95		95	93	92
2	105	99	94	90		102	97	92	89		94	90	87		91	87	85		88	85	83
3	98	90	84	79		96	89	83	79		86	81	77		84	80	76		81	78	75
4	92	83	76	71		90	82	76	71		80	74	70		77	73	69		75	71	68
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	59		80	70	63	59		68	63	58		67	62	58		66	61	57
7	77	66	59	54		75	65	59	54		64	58	54		63	57	53		61	57	53
8	72	61	55	50		71	61	54	50		60	54	49		59	53	49		58	53	49
9	69	58	51	46		67	57	51	46		56	50	46		55	50	46		54	49	46
10	65	54	47	43		64	54	47	43		53	47	43		52	46	43		51	46	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204048

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.3	7.6
10°-20°	273.7	20.2
20°-30°	365.4	27.0
30°-40°	294.8	21.7
40°-50°	141.3	10.4
50°-60°	83.7	6.2
60°-70°	55.7	4.1
70°-80°	29.8	2.2
80°-90°	8.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	742.4	54.8
0°-40°	1037.2	76.5
0°-60°	1262.2	93.1
0°-90°	1355.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1355.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1112	
5°	1099	103
15°	974	274
25°	800	365
35°	472	295
45°	174	141
55°	93	84
65°	56	56
75°	28	30
85°	6	8
90°	0	



TEST NUMBER: P204048

CATALOG NUMBER: LE_6B15D010 EC6B10208035 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1112.0
2.5°	1112.0
5°	1099.1
7.5°	1077.5
10°	1047.4
12.5°	1015.0
15°	974.1
17.5°	935.2
20°	892.1
22.5°	846.9
25°	799.5
27.5°	750.0
30°	678.9
32.5°	579.8
35°	472.0
37.5°	372.9
40°	288.8
42.5°	224.1
45°	174.5
47.5°	137.9
50°	116.4
52.5°	103.5
55°	92.6
57.5°	84.0
60°	73.2
62.5°	64.6
65°	56.0
67.5°	47.4
70°	41.0
72.5°	34.5
75°	28.0
77.5°	21.5
80°	17.2
82.5°	12.9
85°	6.5
87.5°	2.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)