

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192709

Luminaire Tested: **LDA6A70930D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192709
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70930D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6190.3 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192709

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192709

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	102		103	100	98		99	97	95		95	94	93
2	105	99	94	90	103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	79	96	88	83	78		86	81	77		83	79	76		81	77	74
4	91	82	75	70	89	80	74	69		78	73	68		76	71	67		74	70	67
5	85	74	67	62	83	73	67	61		71	65	61		70	64	60		68	63	60
6	79	68	60	55	77	67	60	55		65	59	54		64	58	54		62	57	54
7	74	62	55	49	72	61	54	49		60	54	49		59	53	49		57	52	48
8	69	57	50	44	67	56	49	44		55	49	44		54	48	44		53	48	44
9	64	52	45	40	63	52	45	40		51	44	40		50	44	40		49	44	40
10	60	48	41	37	59	48	41	36		47	41	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	66108	66108	66108
5°	175440	61286	23454
10°	382948	49554	6986
15°	578034	36209	6078
20°	672385	24864	9538
25°	741527	26826	63536
30°	820417	20199	19763
35°	832603	10326	7402
40°	851753	4201	3542
45°	858895	2589	2140
50°	723541	1765	1373
55°	238988	1214	774
60°	46981	1140	504
65°	5526	1492	597
70°	1475	1667	737
75°	254	2203	1228
80°	0	3631	1831
85°	0	7233	2893



TEST NUMBER: P1192709

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.5	2.6
10°-20°	810.4	13.1
20°-30°	1599.5	25.8
30°-40°	1804.2	29.1
40°-50°	1432.3	23.1
50°-60°	350.2	5.7
60°-70°	18.7	0.3
70°-80°	8.0	0.1
80°-90°	6.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2570.3	41.5
0°-40°	4374.5	70.7
0°-60°	6157.0	99.5
0°-90°	6190.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6190.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1206	1206	1206	1206	1206	
5°	3188	2389	1114	560	426	421
15°	10185	5413	638	126	107	2857
25°	12259	6562	444	803	1050	5678
35°	12441	4176	154	122	111	7824
45°	11079	1302	33	34	28	8303
55°	2500	56	13	13	8	2933
65°	43	10	12	9	5	104
75°	1	6	10	9	6	3
85°	0	6	12	8	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192709

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9
2.5°	2092.7	2052.4	2070.8	2042.1	1960.2	1934.9	1955.6	1924.6	1831.2	1795.6	1758.8
5°	3188.1	3152.3	3163.8	3098.2	2945.1	2892.0	2888.6	2794.1	2605.3	2499.3	2388.7
7.5°	4833.9	4784.4	4770.6	4612.7	4317.9	4207.3	4153.3	3920.6	3564.7	3312.5	3064.9
10°	6879.4	6927.8	6878.2	6622.5	6159.5	5952.3	5821.0	5381.0	4739.5	4259.2	3796.2
12.5°	8930.6	8960.7	8867.3	8549.4	7960.8	7712.1	7518.7	6955.4	6110.0	5294.6	4603.5
15°	10184.9	10326.6	10239.0	10016.8	9560.7	9258.9	9085.0	8389.4	7325.1	6429.1	5413.2
17.5°	11078.6	11209.9	11137.4	10955.4	10440.6	10197.6	10084.7	9512.3	8353.7	7214.5	6019.0
20°	11525.6	11685.6	11620.0	11413.8	11036.1	10833.3	10696.3	10137.8	9093.1	7798.5	6423.4
22.5°	11828.5	12005.8	11934.5	11746.7	11362.1	11125.9	11061.4	10532.8	9480.1	8148.6	6594.9
25°	12259.2	12407.7	12206.3	11974.8	11594.7	11346.0	11306.7	10766.6	9665.6	8281.1	6561.6
27.5°	12567.9	12744.1	12402.0	12167.0	11732.9	11471.5	11420.7	10912.8	9682.8	8176.3	6290.8
30°	12960.6	12846.6	12546.1	12205.1	11742.1	11463.4	11398.9	10827.6	9510.0	7790.4	5761.1
32.5°	12805.2	12777.6	12476.9	12076.2	11644.2	11363.2	11276.8	10565.0	9035.4	7124.7	5011.3
35°	12441.2	12528.7	12277.6	12028.8	11492.2	11199.6	11079.8	10178.0	8320.2	6267.8	4176.3
37.5°	12228.1	12283.4	12124.5	11820.5	11288.3	10903.6	10676.7	9527.2	7383.9	5187.4	3371.2
40°	11902.2	12042.6	11889.5	11540.5	10926.6	10399.2	10004.0	8351.4	6150.3	4089.9	2636.4
42.5°	11545.1	11670.6	11524.4	11106.4	10239.0	9531.8	8875.4	6969.2	4815.4	3124.7	1977.5
45°	11078.6	11191.5	10928.9	10278.3	9050.4	8074.9	7419.6	5473.2	3631.4	2295.4	1301.5
47.5°	10237.9	10207.9	9835.9	8824.8	7312.5	6438.3	5675.8	3920.6	2414.1	1300.3	647.2
50°	8483.8	8203.9	7656.9	6483.2	4907.6	3963.2	3442.6	2023.6	1095.3	630.0	406.5
52.5°	5495.0	5182.8	4681.9	3598.1	2356.5	1891.2	1516.9	914.5	571.3	355.9	160.0
55°	2500.5	2279.3	1959.1	1453.5	1011.2	840.8	711.8	463.0	306.4	132.4	56.4
57.5°	952.5	878.7	781.0	623.1	467.6	404.2	335.2	222.3	95.6	49.5	33.4
60°	428.5	397.3	365.1	285.6	200.5	143.9	109.4	59.8	40.3	28.8	21.9
62.5°	146.2	122.1	101.4	72.6	54.1	47.2	41.4	33.4	24.2	19.6	15.0
65°	42.6	41.4	39.1	34.5	27.6	25.3	24.2	19.6	15.0	12.7	10.4
67.5°	20.7	19.6	18.4	17.3	13.8	12.7	12.7	11.5	9.2	8.1	6.9
70°	9.2	9.2	8.1	8.1	6.9	6.9	6.9	5.8	5.8	5.8	5.8
72.5°	4.6	4.6	4.6	3.5	3.5	3.5	3.5	4.6	4.6	5.8	5.8
75°	1.2	2.3	2.3	2.3	2.3	3.5	3.5	4.6	4.6	5.8	5.8
77.5°	1.2	1.2	1.2	2.3	2.3	2.3	3.5	4.6	4.6	5.8	5.8
80°	0.0	1.2	1.2	2.3	2.3	2.3	3.5	3.5	4.6	5.8	5.8
82.5°	0.0	1.2	1.2	2.3	2.3	2.3	3.5	3.5	4.6	5.8	5.8
85°	0.0	0.0	1.2	1.2	2.3	2.3	3.5	3.5	4.6	5.8	5.8
87.5°	0.0	0.0	1.2	1.2	2.3	2.3	3.5	3.5	4.6	5.8	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192709

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9
2.5°	1668.9	1644.7	1549.1	1475.3	1440.8	1438.5	1361.3	1314.2	1231.2	1166.8	1105.6
5°	2194.0	2086.9	1893.5	1740.4	1666.6	1628.6	1476.5	1367.1	1224.3	1113.7	1004.3
7.5°	2728.5	2524.6	2252.9	1961.4	1841.6	1768.0	1533.0	1357.9	1167.9	1013.5	877.6
10°	3275.5	2916.2	2510.8	2126.2	1953.3	1828.9	1527.3	1290.0	1071.1	890.2	741.7
12.5°	3845.7	3279.0	2714.7	2233.3	2005.2	1841.6	1475.3	1190.9	952.5	760.1	618.5
15°	4326.0	3560.1	2843.7	2258.6	1989.1	1791.0	1364.8	1065.4	825.8	638.0	509.0
17.5°	4696.8	3717.9	2867.9	2196.3	1899.3	1678.1	1222.0	927.2	692.2	526.3	398.5
20°	4883.5	3742.0	2791.8	2049.0	1736.8	1508.9	1059.6	786.7	580.5	426.2	316.8
22.5°	4897.3	3629.1	2626.0	1858.9	1558.3	1326.8	926.0	678.4	509.0	382.4	300.7
25°	4717.5	3411.4	2403.7	1664.3	1375.1	1166.8	830.4	650.7	512.5	443.5	407.7
27.5°	4376.6	3109.7	2159.5	1469.6	1217.4	1056.2	791.3	650.7	555.2	501.0	513.6
30°	3904.5	2725.1	1819.7	1204.7	990.5	850.0	621.9	487.2	382.4	319.1	307.6
32.5°	3291.6	2229.8	1410.9	890.2	722.1	612.7	420.5	305.3	246.5	240.7	233.8
35°	2709.0	1761.1	1071.1	657.6	532.0	433.1	268.3	179.6	163.5	154.3	147.4
37.5°	2140.0	1317.6	769.3	478.0	365.1	275.2	138.2	116.3	101.4	92.2	84.1
40°	1608.9	946.8	542.5	289.0	191.2	118.6	83.0	71.5	63.4	58.7	56.4
42.5°	1137.9	630.0	336.3	122.1	91.0	74.9	57.5	50.6	46.0	43.7	41.4
45°	661.2	391.6	135.9	71.5	57.5	51.8	42.6	38.0	35.7	33.4	32.2
47.5°	413.4	157.7	70.3	46.0	40.3	36.8	31.1	29.9	27.6	26.5	26.5
50°	166.9	70.3	43.7	32.2	28.8	27.6	24.2	23.0	20.7	20.7	20.7
52.5°	63.4	41.4	29.9	23.0	20.7	19.6	17.3	17.3	16.1	16.1	16.1
55°	36.8	27.6	20.7	16.1	15.0	15.0	13.8	13.8	12.7	12.7	12.7
57.5°	24.2	18.4	15.0	11.5	11.5	11.5	10.4	10.4	10.4	10.4	10.4
60°	16.1	12.7	10.4	9.2	9.2	9.2	9.2	10.4	10.4	10.4	10.4
62.5°	11.5	10.4	9.2	9.2	9.2	9.2	9.2	10.4	10.4	10.4	11.5
65°	9.2	8.1	8.1	8.1	8.1	9.2	9.2	10.4	10.4	11.5	11.5
67.5°	6.9	6.9	6.9	6.9	8.1	8.1	9.2	10.4	10.4	10.4	11.5
70°	5.8	6.9	6.9	8.1	8.1	8.1	9.2	9.2	10.4	10.4	11.5
72.5°	5.8	6.9	6.9	8.1	8.1	8.1	9.2	10.4	10.4	10.4	11.5
75°	5.8	6.9	6.9	8.1	8.1	8.1	9.2	10.4	10.4	10.4	11.5
77.5°	6.9	6.9	8.1	8.1	8.1	9.2	9.2	10.4	10.4	11.5	11.5
80°	6.9	6.9	8.1	8.1	8.1	9.2	9.2	10.4	10.4	11.5	11.5
82.5°	6.9	6.9	8.1	8.1	8.1	9.2	9.2	10.4	10.4	11.5	11.5
85°	6.9	6.9	8.1	8.1	8.1	9.2	9.2	10.4	10.4	11.5	11.5
87.5°	6.9	6.9	8.1	8.1	8.1	9.2	9.2	10.4	10.4	10.4	11.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192709

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9
2.5°	1075.7	1022.8	965.2	946.8	928.3	892.5	870.7	831.6	802.8	773.9	750.9
5°	931.8	847.7	777.4	747.5	718.7	669.2	634.6	593.2	559.8	530.9	504.4
7.5°	782.1	685.3	615.0	585.1	556.3	502.1	458.4	406.5	367.4	335.2	308.7
10°	643.8	551.7	475.7	440.0	406.5	350.1	308.7	267.2	233.8	206.2	182.0
12.5°	524.0	425.1	347.8	321.4	289.0	243.0	203.9	158.9	139.3	131.3	125.5
15°	406.5	317.9	253.4	229.2	200.5	156.6	139.3	131.3	125.5	122.1	117.5
17.5°	309.9	236.1	172.7	156.6	147.4	138.2	133.6	127.8	124.4	123.2	119.8
20°	243.0	178.5	162.3	157.7	157.7	155.4	152.0	152.0	150.8	154.3	154.3
22.5°	249.9	249.9	263.7	262.6	281.0	299.4	313.3	358.2	383.5	437.7	474.5
25°	436.6	478.0	526.3	541.4	577.1	630.0	685.3	754.4	802.8	854.6	875.3
27.5°	544.8	551.7	544.8	562.1	538.9	525.1	529.7	537.8	537.8	541.4	555.2
30°	322.5	338.6	353.6	365.1	359.3	353.6	351.3	334.0	334.0	327.1	321.4
32.5°	218.9	216.6	214.3	218.9	214.3	214.3	210.8	212.0	205.1	200.5	198.2
35°	149.7	142.8	134.7	135.9	131.3	130.1	126.7	126.7	122.1	119.8	118.6
37.5°	83.0	83.0	79.5	80.7	79.5	79.5	79.5	80.7	79.5	79.5	80.7
40°	56.4	56.4	55.2	56.4	55.2	56.4	57.5	57.5	57.5	57.5	56.4
42.5°	42.6	42.6	41.4	42.6	41.4	42.6	43.7	43.7	43.7	43.7	43.7
45°	33.4	33.4	33.4	33.4	33.4	33.4	33.4	34.5	34.5	33.4	33.4
47.5°	26.5	27.6	26.5	26.5	26.5	26.5	27.6	27.6	26.5	26.5	26.5
50°	21.9	21.9	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7	20.7
52.5°	17.3	16.1	16.1	15.0	15.0	15.0	15.0	15.0	15.0	15.0	13.8
55°	12.7	12.7	11.5	11.5	11.5	12.7	12.7	12.7	12.7	11.5	11.5
57.5°	11.5	11.5	11.5	10.4	10.4	11.5	11.5	10.4	10.4	10.4	9.2
60°	10.4	11.5	10.4	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1
62.5°	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1	8.1
65°	11.5	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1
67.5°	11.5	11.5	11.5	11.5	10.4	10.4	10.4	9.2	9.2	9.2	8.1
70°	11.5	11.5	11.5	11.5	11.5	10.4	10.4	10.4	9.2	9.2	8.1
72.5°	11.5	11.5	11.5	10.4	10.4	10.4	10.4	10.4	9.2	9.2	8.1
75°	11.5	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1
77.5°	11.5	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1
80°	11.5	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1
82.5°	11.5	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1
85°	11.5	11.5	10.4	10.4	10.4	10.4	9.2	9.2	8.1	8.1	6.9
87.5°	10.4	10.4	10.4	10.4	9.2	9.2	9.2	8.1	6.9	6.9	5.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192709

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9	1205.9
2.5°	723.3	718.7	715.2	722.1	719.8	691.1	694.5	693.4
5°	474.5	464.2	456.1	459.6	450.4	437.7	428.5	426.2
7.5°	282.1	270.6	263.7	256.8	254.5	238.4	231.5	236.1
10°	155.4	139.3	138.2	134.7	130.1	126.7	124.4	125.5
12.5°	119.8	118.6	116.3	115.2	112.9	111.7	110.6	109.4
15°	114.0	112.9	111.7	110.6	109.4	108.3	107.1	107.1
17.5°	117.5	117.5	116.3	115.2	115.2	116.3	115.2	114.0
20°	153.1	153.1	155.4	158.9	158.9	162.3	166.9	163.5
22.5°	497.5	522.8	554.0	563.2	617.3	661.2	741.7	706.0
25°	909.9	967.5	981.3	1000.8	1030.9	1045.8	1030.9	1050.4
27.5°	552.9	572.5	574.8	575.9	582.8	581.7	566.7	575.9
30°	321.4	328.3	326.0	324.8	322.5	309.9	307.6	312.2
32.5°	201.6	199.3	198.2	197.0	197.0	190.1	193.5	191.2
35°	115.2	118.6	117.5	116.3	112.9	111.7	111.7	110.6
37.5°	77.2	78.4	77.2	76.1	73.8	72.6	71.5	70.3
40°	55.2	56.4	55.2	54.1	52.9	51.8	50.6	49.5
42.5°	41.4	42.6	41.4	41.4	39.1	38.0	36.8	35.7
45°	32.2	31.1	31.1	31.1	29.9	28.8	27.6	27.6
47.5°	26.5	26.5	26.5	25.3	24.2	24.2	24.2	23.0
50°	19.6	20.7	19.6	19.6	18.4	17.3	17.3	16.1
52.5°	13.8	13.8	12.7	12.7	11.5	10.4	10.4	10.4
55°	10.4	10.4	10.4	9.2	9.2	8.1	8.1	8.1
57.5°	9.2	8.1	8.1	8.1	6.9	6.9	5.8	5.8
60°	8.1	6.9	6.9	5.8	5.8	4.6	4.6	4.6
62.5°	6.9	5.8	5.8	5.8	4.6	4.6	4.6	4.6
65°	6.9	5.8	5.8	5.8	4.6	4.6	4.6	4.6
67.5°	6.9	6.9	5.8	5.8	5.8	4.6	4.6	4.6
70°	6.9	6.9	6.9	5.8	5.8	5.8	4.6	4.6
72.5°	8.1	6.9	6.9	6.9	5.8	5.8	5.8	5.8
75°	8.1	6.9	6.9	6.9	5.8	5.8	5.8	5.8
77.5°	8.1	6.9	6.9	6.9	5.8	5.8	5.8	5.8
80°	6.9	6.9	6.9	5.8	5.8	5.8	5.8	5.8
82.5°	6.9	6.9	6.9	6.9	5.8	5.8	5.8	5.8
85°	6.9	5.8	5.8	5.8	4.6	4.6	4.6	4.6
87.5°	5.8	4.6	4.6	3.5	3.5	3.5	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)