

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192712

Luminaire Tested: **LDA6A70930D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26685)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70930D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5023.6 lumens
Efficiency: N/A
Efficacy: 64.3 lumens/watt
Spacing Criteria (0/90/45): 2.12 / 1.05 / 1.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192712

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192712

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	76	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55		
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44		
8	67	55	47	42	65	54	47	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	43	38	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	88902	88902	88902
5°	142862	87156	55591
10°	211258	83482	37318
15°	287879	78968	27713
20°	356057	74516	26276
25°	412506	73359	43121
30°	450069	70283	43165
35°	462566	60739	33756
40°	450451	47811	26292
45°	408438	35360	20715
50°	321798	26131	14038
55°	191869	18609	8038
60°	98128	12378	3026
65°	46905	6564	1349
70°	22151	2949	1298
75°	9023	1949	1461
80°	4357	2178	1452
85°	2201	3648	2201

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192712

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.5	3.3
10°-20°	588.1	11.7
20°-30°	1107.1	22.0
30°-40°	1348.1	26.8
40°-50°	1122.2	22.3
50°-60°	537.5	10.7
60°-70°	129.1	2.6
70°-80°	20.3	0.4
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1861.7	37.1
0°-40°	3209.8	63.9
0°-60°	4869.4	96.9
0°-90°	5023.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5023.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1622	1622	1622	1622	1622	
5°	2596	2202	1584	1152	1010	284
15°	5072	3446	1391	631	488	1454
25°	6820	4028	1213	688	713	3132
35°	6912	3537	908	529	504	4283
45°	5268	2365	456	281	267	3989
55°	2008	976	195	109	84	1891
65°	362	211	51	16	10	414
75°	43	22	9	8	7	58
85°	4	4	6	5	4	5
90°	0	0	0	0	0	

TEST NUMBER: P1192712

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7
2.5°	2097.4	2023.6	2046.7	2042.1	2037.4	2013.3	1996.0	1981.1	1943.1	1943.1	1894.7
5°	2596.1	2509.7	2531.7	2515.4	2494.7	2457.9	2424.5	2386.4	2316.3	2286.4	2202.2
7.5°	3166.2	3068.3	3087.9	3055.7	3012.0	2962.3	2908.3	2836.8	2725.1	2657.2	2527.1
10°	3795.1	3655.7	3667.2	3618.9	3546.3	3479.6	3427.7	3291.8	3132.9	3020.0	2838.0
12.5°	4390.7	4268.4	4271.9	4204.0	4099.2	4017.4	3939.2	3759.4	3547.5	3386.3	3146.7
15°	5072.4	4922.7	4887.1	4794.9	4657.8	4557.6	4450.5	4223.6	3957.6	3744.5	3446.1
17.5°	5621.9	5467.6	5444.6	5358.1	5162.3	5041.4	4906.6	4650.9	4313.5	4048.6	3682.2
20°	6103.3	5950.1	5911.0	5799.3	5574.7	5436.4	5274.0	4972.2	4603.6	4277.8	3864.2
22.5°	6497.3	6329.0	6273.8	6135.5	5885.6	5730.1	5532.0	5202.5	4791.4	4427.5	3972.5
25°	6819.7	6628.6	6558.3	6401.7	6120.5	5949.0	5731.3	5362.7	4914.7	4512.8	4027.7
27.5°	7025.9	6834.6	6757.6	6577.8	6262.3	6078.0	5840.7	5442.1	4958.4	4524.3	4016.2
30°	7110.0	6911.9	6824.3	6620.5	6280.7	6086.0	5838.4	5407.6	4902.0	4441.3	3919.5
32.5°	7058.1	6863.5	6765.6	6544.5	6190.9	5981.2	5733.6	5274.0	4753.5	4276.6	3751.4
35°	6911.9	6719.5	6618.2	6382.1	6013.4	5794.7	5548.1	5072.4	4546.1	4058.9	3537.1
37.5°	6659.6	6477.6	6361.3	6127.4	5756.6	5533.1	5289.0	4808.7	4270.7	3812.5	3289.5
40°	6294.5	6121.7	6006.5	5756.6	5406.5	5180.7	4950.3	4463.1	3956.4	3509.5	3005.1
42.5°	5829.2	5670.2	5559.6	5316.6	4982.7	4760.4	4549.6	4081.9	3599.4	3174.3	2697.5
45°	5268.3	5130.1	5021.8	4820.2	4490.8	4280.1	4090.0	3666.1	3197.3	2806.9	2364.6
47.5°	4608.2	4494.2	4389.5	4206.3	3909.1	3709.9	3553.2	3165.1	2767.8	2400.4	2023.6
50°	3773.2	3691.5	3609.7	3419.6	3210.0	3036.1	2922.1	2576.5	2255.2	1967.3	1655.1
52.5°	2844.9	2795.4	2737.7	2601.8	2461.4	2360.0	2258.6	1996.0	1755.3	1541.1	1298.0
55°	2007.5	1982.2	1937.4	1882.0	1774.9	1705.9	1618.3	1484.7	1298.0	1154.1	975.5
57.5°	1356.9	1350.0	1318.8	1285.4	1226.6	1203.6	1130.0	1043.5	938.7	831.6	704.9
60°	895.0	880.0	873.0	854.6	809.7	791.3	764.9	709.5	645.1	570.2	491.8
62.5°	575.9	567.9	562.1	554.0	526.3	526.3	499.8	474.5	426.2	380.1	329.4
65°	361.6	354.7	353.6	347.8	337.5	332.9	313.3	294.9	271.8	246.5	210.8
67.5°	232.7	222.3	216.6	213.1	206.2	198.2	191.2	183.2	164.6	149.7	126.7
70°	138.2	129.0	127.8	129.0	120.9	119.8	112.9	107.1	94.5	85.3	71.5
72.5°	78.4	73.8	72.6	72.6	68.0	66.9	62.3	58.8	51.8	44.9	39.1
75°	42.6	39.1	39.1	39.1	36.8	35.7	33.4	32.2	27.6	25.3	21.9
77.5°	24.2	23.0	23.0	21.9	20.7	19.6	18.4	18.4	16.1	15.0	13.8
80°	13.8	13.8	13.8	13.8	12.7	12.7	11.5	11.5	10.4	10.4	9.2
82.5°	8.1	8.1	8.1	8.1	8.1	8.1	6.9	6.9	6.9	6.9	5.8
85°	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
87.5°	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.3	2.3	2.3	3.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192712

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7
2.5°	1872.8	1838.3	1836.0	1785.2	1753.0	1726.6	1707.0	1682.7	1628.6	1598.7	1576.7
5°	2143.4	2072.1	2035.1	1943.1	1892.4	1847.5	1792.1	1734.6	1645.9	1583.8	1533.0
7.5°	2424.5	2305.9	2227.5	2090.5	2021.3	1951.2	1857.8	1764.5	1643.6	1550.3	1473.2
10°	2686.0	2517.9	2393.3	2209.1	2119.3	2027.1	1895.8	1770.3	1619.4	1499.7	1398.3
12.5°	2942.8	2721.6	2550.1	2316.3	2206.8	2092.8	1924.6	1766.8	1589.5	1445.4	1326.8
15°	3188.1	2910.6	2691.7	2409.6	2281.6	2144.6	1943.1	1756.5	1554.9	1391.4	1256.6
17.5°	3384.0	3054.5	2791.9	2467.1	2323.2	2167.7	1936.2	1726.6	1507.7	1333.7	1186.3
20°	3518.7	3146.7	2847.2	2490.1	2332.4	2165.3	1909.6	1685.0	1458.1	1277.3	1127.6
22.5°	3591.3	3188.1	2862.1	2483.2	2318.6	2143.4	1877.4	1647.0	1419.0	1238.2	1095.3
25°	3617.8	3191.6	2846.0	2453.3	2287.5	2108.9	1839.4	1611.4	1387.9	1212.8	1079.2
27.5°	3586.7	3143.2	2787.3	2391.0	2222.9	2046.7	1778.3	1560.6	1341.8	1176.0	1050.4
30°	3480.7	3030.4	2672.2	2280.5	2115.8	1946.6	1681.6	1467.4	1267.0	1110.3	990.5
32.5°	3312.5	2864.4	2509.7	2128.5	1969.6	1807.1	1553.7	1350.0	1163.3	1015.9	908.8
35°	3104.1	2666.4	2320.9	1951.2	1801.3	1648.2	1407.5	1215.1	1040.1	907.6	802.8
37.5°	2868.0	2446.4	2112.4	1772.6	1620.6	1476.6	1242.8	1078.0	909.9	789.0	693.4
40°	2603.0	2194.2	1890.1	1559.5	1425.9	1294.6	1078.0	928.3	775.2	668.1	585.1
42.5°	2319.7	1938.5	1657.4	1360.3	1226.6	1106.8	912.2	777.5	641.5	552.9	487.2
45°	2019.0	1682.7	1413.2	1147.2	1026.3	922.6	745.2	623.1	524.0	456.1	406.5
47.5°	1704.7	1407.5	1167.9	936.4	829.3	739.4	596.6	503.3	425.1	375.5	337.5
50°	1387.9	1123.0	932.9	735.9	643.9	572.5	466.5	401.9	344.4	306.4	277.5
52.5°	1084.9	868.4	714.1	555.2	484.9	435.4	363.9	319.1	275.2	246.5	224.6
55°	801.7	654.3	521.7	403.1	361.6	330.6	279.8	247.6	216.6	194.7	178.6
57.5°	579.4	468.8	372.0	296.1	268.3	247.6	210.8	188.9	166.9	150.8	138.2
60°	406.5	323.7	262.6	216.6	197.0	183.2	156.6	142.8	126.7	112.9	100.2
62.5°	267.2	217.7	183.2	153.1	141.6	131.3	112.9	102.5	88.7	79.5	68.0
65°	173.8	142.8	122.1	102.5	93.3	88.7	76.1	68.0	58.8	50.6	43.7
67.5°	106.0	88.7	77.2	64.6	60.0	55.2	47.2	41.4	35.7	29.9	26.5
70°	58.8	51.8	44.9	38.0	34.5	32.2	27.6	25.3	20.7	18.4	15.0
72.5°	34.5	29.9	26.5	21.9	20.7	19.6	16.1	15.0	12.7	11.5	10.4
75°	20.7	17.3	16.1	13.8	12.7	12.7	11.5	10.4	9.2	9.2	8.1
77.5°	12.7	11.5	10.4	9.2	9.2	9.2	8.1	8.1	8.1	6.9	6.9
80°	8.1	8.1	8.1	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
82.5°	5.8	5.8	5.8	4.6	5.8	4.6	5.8	5.8	5.8	5.8	5.8
85°	3.5	3.5	4.6	4.6	4.6	4.6	4.6	5.8	5.8	5.8	5.8
87.5°	3.5	3.5	4.6	4.6	4.6	4.6	4.6	5.8	5.8	5.8	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192712

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7
2.5°	1551.4	1508.9	1477.8	1454.6	1462.7	1422.4	1409.8	1366.1	1350.0	1350.0	1326.8
5°	1481.2	1413.2	1360.3	1326.8	1324.5	1267.0	1237.1	1181.7	1151.8	1130.0	1107.9
7.5°	1397.1	1309.6	1239.4	1199.0	1187.5	1119.6	1079.2	1024.0	979.0	950.2	923.7
10°	1307.3	1202.4	1123.0	1076.9	1059.6	985.9	932.9	882.3	833.9	804.0	776.4
12.5°	1220.8	1106.8	1019.4	972.1	950.2	874.1	820.1	767.2	721.0	689.9	662.3
15°	1141.5	1020.5	928.3	881.2	856.9	782.1	727.9	676.1	631.1	602.4	577.1
17.5°	1066.5	943.3	851.1	805.1	778.7	709.5	657.7	607.0	566.7	540.2	517.1
20°	1010.2	888.1	802.8	762.6	735.9	671.5	626.5	582.8	549.4	529.9	507.9
22.5°	985.9	873.0	800.5	763.7	745.2	693.4	662.3	631.1	609.3	605.8	592.0
25°	982.4	883.5	823.5	792.5	781.0	741.7	723.3	703.7	687.6	692.2	694.5
27.5°	967.5	875.3	825.8	799.4	790.2	757.8	744.0	725.6	714.1	719.8	722.1
30°	915.7	830.4	784.4	762.6	753.2	721.0	709.5	688.8	679.6	680.7	679.6
32.5°	835.0	754.4	711.8	692.2	681.9	653.1	640.3	621.9	608.1	607.0	604.7
35°	737.1	664.6	625.4	608.1	597.8	573.6	562.1	544.8	528.7	527.6	525.1
37.5°	636.9	572.5	539.1	524.0	514.8	495.2	481.4	469.9	459.6	455.0	453.8
40°	540.2	482.6	458.4	446.9	440.0	419.3	412.4	400.8	392.7	388.1	387.0
42.5°	449.2	408.8	389.3	378.9	373.2	358.2	350.1	340.9	332.9	328.3	327.1
45°	381.2	347.8	329.4	321.4	316.8	303.0	297.2	287.9	281.0	277.5	276.4
47.5°	317.9	291.3	278.7	269.5	268.3	256.8	248.8	241.9	235.0	231.5	230.4
50°	260.3	238.4	228.1	222.3	221.2	209.7	203.9	198.2	192.4	188.9	186.6
52.5°	214.3	193.5	186.6	178.6	177.4	166.9	162.3	156.6	150.8	146.2	142.8
55°	169.2	153.1	146.2	139.3	138.2	126.7	122.1	115.2	109.4	104.8	100.2
57.5°	129.0	116.3	109.4	102.5	101.4	93.3	85.3	79.5	73.8	68.0	64.6
60°	94.5	81.8	73.8	70.3	66.9	58.8	52.9	48.3	43.7	40.3	36.8
62.5°	62.3	52.9	47.2	42.6	40.3	34.5	31.1	27.6	25.3	24.2	23.0
65°	38.0	32.2	27.6	25.3	25.3	21.9	19.6	17.3	16.1	16.1	15.0
67.5°	23.0	19.6	17.3	16.1	15.0	13.8	12.7	12.7	11.5	11.5	10.4
70°	13.8	12.7	11.5	10.4	10.4	10.4	10.4	10.4	9.2	9.2	9.2
72.5°	10.4	9.2	9.2	9.2	9.2	9.2	9.2	9.2	8.1	8.1	8.1
75°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	6.9
77.5°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
80°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	5.8	5.8	5.8
82.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
85°	5.8	5.8	5.8	5.8	5.8	5.8	4.6	4.6	4.6	4.6	4.6
87.5°	5.8	4.6	4.6	4.6	4.6	4.6	3.5	3.5	3.5	3.5	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192712

CATALOG NUMBER: LDA6A70930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7	1621.7
2.5°	1315.3	1324.5	1310.7	1301.5	1292.3	1299.2	1267.0	1253.2
5°	1087.2	1076.9	1070.0	1061.9	1048.1	1050.4	1022.8	1010.2
7.5°	899.6	892.7	875.3	866.1	852.3	852.3	827.0	816.6
10°	750.9	740.6	724.4	716.4	703.7	693.4	680.7	670.4
12.5°	638.0	626.5	612.7	605.8	593.2	585.1	572.5	574.8
15°	554.0	542.5	529.9	522.8	512.5	504.4	494.1	488.3
17.5°	495.2	484.9	474.5	467.6	459.6	452.7	443.5	442.3
20°	490.6	482.6	476.8	472.2	465.3	460.7	456.1	450.4
22.5°	587.4	588.6	589.7	589.7	590.9	590.9	592.0	580.5
25°	693.4	706.0	706.0	709.5	719.8	719.8	717.5	712.9
27.5°	721.0	733.6	730.2	732.5	742.9	745.2	737.1	738.2
30°	675.0	686.5	679.6	680.7	687.6	687.6	677.3	681.9
32.5°	597.8	604.7	595.5	595.5	601.2	600.1	593.2	593.2
35°	515.9	519.4	511.3	514.8	514.8	511.3	504.4	504.4
37.5°	445.8	446.9	438.9	440.0	440.0	436.6	429.7	429.7
40°	378.9	382.4	375.5	377.8	375.5	372.0	368.5	367.4
42.5°	320.2	322.5	316.8	320.2	319.1	319.1	317.9	319.1
45°	269.5	271.8	267.2	269.5	270.6	269.5	266.0	267.2
47.5°	223.5	225.8	225.8	223.5	222.3	216.6	213.1	213.1
50°	180.9	179.7	178.6	175.0	171.5	168.1	164.6	164.6
52.5°	135.9	133.6	132.4	129.0	127.8	124.4	124.4	120.9
55°	93.3	92.2	92.2	88.7	88.7	85.3	84.1	84.1
57.5°	58.8	56.4	57.5	55.2	54.1	50.6	50.6	49.5
60°	33.4	32.2	32.2	31.1	29.9	27.6	27.6	27.6
62.5°	21.9	20.7	20.7	19.6	19.6	18.4	18.4	17.3
65°	13.8	12.7	12.7	11.5	11.5	10.4	10.4	10.4
67.5°	10.4	9.2	9.2	9.2	9.2	9.2	8.1	8.1
70°	9.2	9.2	8.1	8.1	8.1	8.1	8.1	8.1
72.5°	8.1	8.1	8.1	8.1	6.9	6.9	6.9	6.9
75°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
77.5°	6.9	5.8	5.8	5.8	5.8	5.8	5.8	5.8
80°	5.8	5.8	5.8	5.8	5.8	5.8	4.6	4.6
82.5°	5.8	4.6	4.6	4.6	4.6	4.6	4.6	4.6
85°	4.6	3.5	3.5	3.5	3.5	3.5	3.5	3.5
87.5°	2.3	2.3	2.3	2.3	1.2	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)