

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192713

Luminaire Tested: **LDA6A70935D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192713
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70935D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6188.6 lumens
Efficiency: N/A
Efficacy: 79.2 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192713

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192713

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	95776	95776	95776
5°	185587	91267	30784
10°	315308	79869	13822
15°	485865	63706	21975
20°	703345	41455	38229
25°	1031939	40012	49158
30°	1199874	37905	37664
35°	1214466	20077	19910
40°	1005498	7564	8359
45°	759412	2574	3055
50°	519565	947	947
55°	72265	822	124
60°	1897	800	0
65°	480	1116	0
70°	208	1378	0
75°	0	1822	0
80°	0	3094	410
85°	0	6164	0

TEST NUMBER: P1192713

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.3	3.0
10°-20°	774.8	12.5
20°-30°	1767.4	28.6
30°-40°	2045.3	33.0
40°-50°	1233.5	19.9
50°-60°	167.6	2.7
60°-70°	5.4	0.1
70°-80°	5.9	0.1
80°-90°	5.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2725.5	44.0
0°-40°	4770.8	77.1
0°-60°	6171.9	99.7
0°-90°	6188.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6188.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1747	1747	1747	1747	1747	
5°	3372	2762	1658	907	559	393
15°	8561	4812	1122	346	387	2534
25°	17060	5702	662	796	813	7721
35°	18147	4348	300	306	298	10936
45°	9795	1184	33	41	39	7659
55°	756	9	9	6	1	1482
65°	4	5	9	5	0	6
75°	0	6	9	6	0	0
85°	0	6	10	6	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P1192713

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	2526.6	2503.2	2513.1	2487.2	2422.1	2408.6	2407.3	2390.2	2334.8	2291.8	2240.1
5°	3372.5	3371.3	3377.3	3322.1	3207.8	3172.1	3154.9	3113.0	2979.0	2875.8	2761.5
7.5°	4428.6	4421.3	4413.8	4313.0	4133.6	4064.7	4020.4	3869.3	3684.8	3501.6	3297.5
10°	5664.3	5660.5	5632.4	5455.2	5167.6	5040.9	4954.8	4715.1	4418.7	4158.2	3811.5
12.5°	7099.1	7065.9	7015.5	6756.0	6361.4	6223.6	6034.3	5654.4	5199.5	4799.9	4315.5
15°	8560.9	8513.0	8423.3	8090.0	7600.6	7365.8	7131.0	6630.6	6013.4	5433.1	4812.3
17.5°	9990.8	9937.9	9727.7	9162.1	8683.9	8397.4	8136.7	7449.5	6724.1	5977.8	5190.9
20°	12056.3	11864.6	11498.2	10606.8	9717.9	9201.5	8896.5	8169.9	7272.5	6403.2	5460.1
22.5°	14815.3	14390.0	13609.2	12160.8	10890.8	10145.7	9646.6	8680.1	7667.1	6681.1	5626.2
25°	17060.4	16867.3	15979.6	13919.0	11937.1	11059.2	10364.5	9085.9	7954.8	6866.7	5702.4
27.5°	18507.4	18459.6	17445.2	15374.7	12791.5	11639.6	10863.8	9353.9	8093.7	6906.1	5665.4
30°	18955.1	19030.0	18056.2	15869.1	13038.7	11756.3	10907.9	9357.7	7986.7	6727.8	5429.5
32.5°	18921.9	18925.5	17731.7	15442.4	12636.7	11417.0	10539.1	9046.5	7592.2	6281.5	4980.7
35°	18147.2	17956.7	16606.7	14131.7	11701.0	10625.2	9808.9	8444.1	6941.6	5610.2	4347.5
37.5°	16446.8	16197.2	14623.5	12453.5	10593.3	9598.7	8939.7	7653.6	6167.1	4893.4	3693.4
40°	14050.6	13696.4	12398.1	10893.3	9381.0	8633.5	8080.2	6769.5	5338.4	4190.1	3079.8
42.5°	11651.8	11478.5	10620.4	9396.9	8361.8	7658.4	7080.7	5843.7	4541.7	3496.7	2304.0
45°	9795.4	9646.6	9069.9	8263.4	7247.9	6606.0	6049.1	4878.6	3528.6	2345.9	1184.0
47.5°	8442.9	8322.4	7770.3	6923.2	5809.4	5107.4	4533.2	3199.2	1999.2	1013.0	296.4
50°	6092.1	5969.1	5428.2	4447.0	3441.3	2853.6	2440.5	1428.6	566.8	205.3	30.8
52.5°	2986.4	2885.6	2518.0	1884.7	1265.1	909.8	665.2	268.0	65.1	22.1	14.8
55°	756.1	694.7	579.1	363.9	178.3	107.0	68.9	24.6	16.0	12.4	8.6
57.5°	43.0	41.8	38.1	28.3	20.9	18.4	16.0	12.4	8.6	7.3	6.2
60°	17.3	16.0	14.8	12.4	9.8	8.6	8.6	6.2	4.9	4.9	4.9
62.5°	7.3	7.3	7.3	6.2	4.9	4.9	4.9	3.7	4.9	4.9	4.9
65°	3.7	3.7	3.7	2.4	2.4	2.4	3.7	3.7	3.7	4.9	4.9
67.5°	2.4	1.3	1.3	1.3	2.4	2.4	2.4	3.7	3.7	4.9	4.9
70°	1.3	1.3	1.3	1.3	2.4	2.4	2.4	3.7	3.7	4.9	6.2
72.5°	0.0	1.3	1.3	1.3	2.4	2.4	2.4	3.7	3.7	4.9	6.2
75°	0.0	1.3	1.3	1.3	2.4	2.4	2.4	3.7	4.9	4.9	6.2
77.5°	0.0	1.3	1.3	1.3	2.4	2.4	2.4	3.7	4.9	4.9	6.2
80°	0.0	1.3	1.3	1.3	2.4	2.4	2.4	3.7	4.9	4.9	6.2
82.5°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	4.9	4.9	6.2
85°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	4.9	4.9	6.2
87.5°	0.0	0.0	1.3	1.3	2.4	2.4	2.4	3.7	3.7	4.9	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192713

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	2173.8	2129.5	2064.3	2021.3	1979.5	1940.1	1875.0	1838.1	1771.7	1710.2	1657.4
5°	2623.7	2513.1	2379.1	2264.6	2190.9	2118.4	1986.8	1889.8	1768.0	1658.5	1557.7
7.5°	3078.7	2883.1	2663.1	2475.0	2360.6	2248.7	2052.0	1894.7	1722.5	1566.4	1417.5
10°	3491.8	3197.9	2886.9	2617.5	2462.7	2317.6	2058.2	1849.2	1627.8	1434.8	1247.9
12.5°	3875.3	3473.3	3067.6	2715.9	2524.2	2349.5	2032.4	1776.6	1513.5	1284.8	1067.3
15°	4217.1	3700.7	3199.2	2772.5	2547.5	2341.0	1972.2	1674.5	1378.3	1122.5	847.1
17.5°	4476.5	3842.1	3257.0	2763.9	2505.6	2275.7	1868.8	1546.7	1234.3	924.6	613.6
20°	4634.0	3902.3	3244.6	2697.5	2415.9	2172.5	1745.8	1407.8	1061.1	710.6	541.0
22.5°	4700.3	3897.5	3186.8	2598.0	2305.3	2059.4	1627.8	1272.5	879.0	643.1	564.4
25°	4711.3	3847.1	3105.7	2488.5	2195.9	1951.2	1508.6	1118.9	763.6	661.5	632.0
27.5°	4626.5	3729.1	2953.3	2331.1	2042.2	1789.0	1330.3	888.9	716.8	659.0	678.7
30°	4375.7	3459.7	2684.0	2054.4	1775.5	1522.1	950.3	697.1	595.0	598.8	603.7
32.5°	3934.4	3012.2	2251.1	1649.9	1345.1	1003.3	591.4	466.0	452.4	452.4	449.9
35°	3345.4	2465.1	1766.8	1043.8	668.8	482.0	306.1	307.4	301.3	300.0	298.8
37.5°	2736.9	1945.0	1118.9	431.5	290.2	201.6	180.8	183.2	180.8	184.5	181.9
40°	2157.8	1201.3	408.2	137.8	102.1	98.4	100.8	103.2	103.2	105.7	105.7
42.5°	1254.0	398.3	107.0	55.4	55.4	52.9	54.1	56.5	57.8	59.0	57.8
45°	372.6	82.4	34.4	30.8	30.8	29.5	29.5	30.8	31.9	33.2	33.2
47.5°	59.0	23.3	19.7	17.3	17.3	17.3	17.3	17.3	18.4	18.4	19.7
50°	18.4	14.8	12.4	11.1	11.1	9.8	9.8	11.1	11.1	11.1	12.4
52.5°	11.1	8.6	8.6	7.3	8.6	8.6	7.3	8.6	8.6	8.6	9.8
55°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	8.6	8.6	8.6
57.5°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
60°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	8.6
62.5°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	7.3	8.6	8.6	8.6
65°	6.2	6.2	7.3	7.3	7.3	7.3	7.3	8.6	8.6	8.6	8.6
67.5°	6.2	7.3	7.3	7.3	7.3	8.6	8.6	8.6	8.6	8.6	8.6
70°	6.2	7.3	7.3	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
72.5°	6.2	7.3	7.3	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
75°	7.3	7.3	7.3	8.6	8.6	8.6	8.6	8.6	8.6	8.6	9.8
77.5°	7.3	7.3	8.6	8.6	8.6	8.6	8.6	8.6	9.8	9.8	9.8
80°	7.3	7.3	8.6	8.6	8.6	8.6	8.6	9.8	9.8	9.8	9.8
82.5°	7.3	7.3	8.6	8.6	8.6	8.6	8.6	9.8	9.8	9.8	9.8
85°	7.3	7.3	8.6	8.6	8.6	8.6	8.6	9.8	9.8	9.8	9.8
87.5°	7.3	7.3	8.6	8.6	8.6	8.6	8.6	9.8	9.8	9.8	9.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192713

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1611.8	1555.3	1528.3	1490.2	1463.1	1402.9	1378.3	1336.4	1302.1	1245.4	1249.2
5°	1471.8	1364.8	1292.2	1235.6	1196.2	1100.3	1036.5	968.9	907.4	831.1	802.8
7.5°	1277.5	1145.9	1035.2	967.6	917.1	789.3	647.9	537.2	453.7	393.4	370.1
10°	1083.2	912.2	736.5	632.0	559.4	436.4	373.7	344.2	317.2	284.0	261.9
12.5°	856.9	613.6	453.7	411.8	382.4	341.8	301.3	269.2	275.4	276.7	285.3
15°	585.3	441.5	391.0	362.7	330.7	307.4	321.0	329.4	345.5	346.7	357.8
17.5°	475.8	414.3	373.7	372.6	375.0	388.5	409.4	420.5	441.5	446.3	462.3
20°	475.8	440.2	474.5	474.5	480.7	499.1	526.2	542.3	565.6	574.2	593.9
22.5°	542.3	566.8	609.8	614.7	617.2	636.9	671.2	687.3	714.4	719.3	740.1
25°	661.5	683.6	723.0	726.6	727.9	742.6	768.4	777.1	795.5	785.7	797.9
27.5°	699.6	709.3	733.9	736.5	730.3	736.5	746.3	746.3	752.5	732.8	736.5
30°	614.7	617.2	629.5	630.7	617.2	619.6	620.9	619.6	618.5	597.5	597.5
32.5°	456.1	456.1	472.1	468.5	453.7	457.4	457.4	457.4	456.1	438.9	436.4
35°	302.4	303.7	317.2	314.8	303.7	306.1	306.1	309.9	306.1	296.4	293.9
37.5°	184.5	185.6	191.8	193.0	189.4	190.5	191.8	190.5	193.0	188.1	185.6
40°	107.0	109.4	114.3	115.6	114.3	114.3	115.6	116.8	121.7	115.6	113.2
42.5°	62.7	64.0	66.4	66.4	66.4	66.4	67.6	68.9	70.0	68.9	67.6
45°	35.7	37.0	38.1	38.1	39.4	38.1	39.4	39.4	40.6	39.4	39.4
47.5°	20.9	20.9	22.1	22.1	23.3	22.1	23.3	23.3	23.3	22.1	22.1
50°	12.4	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5	12.4	12.4
52.5°	9.8	9.8	9.8	9.8	9.8	8.6	8.6	8.6	8.6	7.3	7.3
55°	8.6	8.6	8.6	8.6	8.6	8.6	7.3	6.2	6.2	4.9	4.9
57.5°	7.3	8.6	8.6	8.6	8.6	7.3	7.3	6.2	4.9	3.7	3.7
60°	8.6	8.6	8.6	8.6	7.3	7.3	7.3	6.2	4.9	3.7	3.7
62.5°	8.6	8.6	8.6	8.6	8.6	7.3	7.3	6.2	4.9	3.7	3.7
65°	8.6	8.6	8.6	8.6	8.6	7.3	7.3	6.2	4.9	3.7	3.7
67.5°	8.6	8.6	8.6	8.6	8.6	7.3	7.3	6.2	4.9	4.9	3.7
70°	8.6	9.8	9.8	8.6	8.6	8.6	7.3	6.2	6.2	4.9	3.7
72.5°	8.6	9.8	9.8	8.6	8.6	8.6	7.3	6.2	6.2	4.9	3.7
75°	9.8	9.8	9.8	9.8	8.6	8.6	7.3	7.3	6.2	4.9	3.7
77.5°	9.8	9.8	9.8	9.8	8.6	8.6	7.3	7.3	6.2	4.9	3.7
80°	9.8	9.8	9.8	9.8	9.8	8.6	8.6	7.3	6.2	4.9	4.9
82.5°	9.8	9.8	9.8	9.8	9.8	8.6	8.6	7.3	6.2	4.9	4.9
85°	9.8	9.8	9.8	9.8	9.8	8.6	8.6	7.3	6.2	4.9	3.7
87.5°	9.8	9.8	9.8	9.8	8.6	8.6	7.3	7.3	6.2	4.9	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192713

CATALOG NUMBER: LDA6A70935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1203.7	1175.4	1163.2	1182.7	1172.9	1143.5	1149.5	1131.1
5°	718.0	675.0	647.9	660.2	620.9	585.3	585.3	559.4
7.5°	346.7	333.2	325.8	328.3	319.7	308.6	302.4	302.4
10°	243.4	238.6	239.7	239.7	247.2	245.9	249.6	248.3
12.5°	288.9	291.3	292.6	297.5	303.7	303.7	307.4	304.8
15°	370.1	367.7	375.0	376.2	386.1	387.2	392.3	387.2
17.5°	470.9	475.8	483.2	482.0	501.6	502.9	502.9	501.6
20°	606.1	609.8	617.2	619.6	643.1	645.5	654.1	655.3
22.5°	753.6	753.6	757.4	762.3	784.4	785.7	789.3	789.3
25°	804.1	796.8	797.9	804.1	816.3	811.4	815.2	812.7
27.5°	739.0	727.9	725.5	733.9	742.6	729.0	733.9	733.9
30°	600.1	590.1	587.7	596.3	602.5	587.7	592.6	595.0
32.5°	438.9	432.8	431.5	437.7	442.6	430.4	435.3	438.9
35°	296.4	293.9	291.3	292.6	300.0	290.2	295.1	297.5
37.5°	188.1	183.2	184.5	186.9	191.8	185.6	190.5	190.5
40°	115.6	113.2	113.2	115.6	118.1	113.2	115.6	116.8
42.5°	67.6	67.6	67.6	68.9	70.0	67.6	67.6	68.9
45°	39.4	38.1	38.1	39.4	40.6	38.1	39.4	39.4
47.5°	22.1	20.9	20.9	22.1	22.1	20.9	22.1	22.1
50°	12.4	11.1	11.1	12.4	12.4	11.1	11.1	11.1
52.5°	6.2	6.2	6.2	6.2	6.2	6.2	4.9	4.9
55°	3.7	3.7	2.4	2.4	2.4	2.4	2.4	1.3
57.5°	2.4	2.4	1.3	1.3	1.3	1.3	0.0	0.0
60°	2.4	2.4	1.3	1.3	1.3	0.0	0.0	0.0
62.5°	2.4	2.4	1.3	1.3	1.3	0.0	0.0	0.0
65°	2.4	2.4	1.3	1.3	1.3	0.0	0.0	0.0
67.5°	2.4	2.4	1.3	1.3	1.3	0.0	0.0	0.0
70°	3.7	2.4	2.4	1.3	1.3	1.3	0.0	0.0
72.5°	3.7	2.4	2.4	2.4	1.3	1.3	0.0	0.0
75°	3.7	2.4	2.4	2.4	1.3	1.3	0.0	0.0
77.5°	3.7	2.4	2.4	2.4	1.3	1.3	1.3	0.0
80°	3.7	2.4	2.4	2.4	1.3	1.3	1.3	1.3
82.5°	3.7	2.4	2.4	2.4	1.3	1.3	1.3	1.3
85°	3.7	2.4	2.4	2.4	1.3	1.3	1.3	0.0
87.5°	3.7	2.4	2.4	2.4	1.3	1.3	1.3	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)