

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192723

Luminaire Tested: **LDA6A70935D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192723
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26684)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70935D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5067.5 lumens
Efficiency: N/A
Efficacy: 64.9 lumens/watt
Spacing Criteria (0/90/45): 2.21 / 1.07 / 1.54
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192723

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192723

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	61		
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54		
6	77	65	57	51	75	64	57	51	62	56	51	61	55	50	59	54	50	48		
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35		
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	79939	79939	79939
5°	126997	78956	51282
10°	190539	75761	34429
15°	273049	71800	25471
20°	360432	67136	21229
25°	432612	65441	31018
30°	483403	65611	46849
35°	496997	58752	39993
40°	478919	46716	29741
45°	422083	34694	22878
50°	329158	25696	15829
55°	190378	18800	10227
60°	88962	13069	4583
65°	41639	7186	1920
70°	19314	3158	1378
75°	8070	2076	1546
80°	3504	2305	1957
85°	818	3900	3082



TEST NUMBER: P1192723

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.8	3.0
10°-20°	553.5	10.9
20°-30°	1095.8	21.6
30°-40°	1416.8	28.0
40°-50°	1164.2	23.0
50°-60°	538.2	10.6
60°-70°	122.9	2.4
70°-80°	20.0	0.4
80°-90°	5.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1800.1	35.5
0°-40°	3217.0	63.5
0°-60°	4919.4	97.1
0°-90°	5067.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5067.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1458	1458	1458	1458	1458	
5°	2308	1984	1435	1038	932	255
15°	4811	3218	1265	567	449	1405
25°	7152	4003	1082	531	513	3293
35°	7426	3664	878	583	598	4598
45°	5444	2474	448	298	295	4143
55°	1992	963	197	127	107	1872
65°	321	197	55	21	15	368
75°	38	22	10	9	7	51
85°	1	4	6	6	5	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192723

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2
2.5°	1851.7	1823.3	1840.6	1849.2	1804.9	1814.7	1819.7	1785.2	1775.5	1757.0	1702.8
5°	2307.8	2274.6	2288.1	2288.1	2222.9	2226.7	2224.2	2159.1	2123.4	2076.7	1984.4
7.5°	2845.2	2811.9	2814.4	2802.0	2709.8	2703.7	2664.4	2584.4	2514.4	2428.3	2290.5
10°	3422.9	3403.4	3391.0	3360.2	3238.6	3217.7	3159.9	3033.2	2917.6	2786.1	2591.8
12.5°	4101.6	4062.4	4026.7	3977.5	3818.9	3779.5	3698.4	3515.2	3345.6	3161.1	2904.1
15°	4811.1	4780.4	4722.6	4645.2	4442.3	4379.6	4273.8	4027.9	3816.5	3547.2	3217.7
17.5°	5545.2	5488.6	5403.7	5294.3	5049.7	4961.1	4829.5	4514.8	4234.5	3898.7	3500.4
20°	6178.3	6134.1	6017.3	5875.9	5595.5	5477.5	5322.6	4936.5	4593.4	4195.1	3726.6
22.5°	6727.9	6669.0	6525.0	6354.2	6040.6	5894.4	5719.8	5288.2	4870.1	4407.8	3892.7
25°	7152.1	7107.8	6937.0	6737.7	6393.5	6223.8	6030.8	5541.5	5077.9	4570.1	4003.3
27.5°	7497.7	7422.6	7232.1	7007.0	6635.8	6437.8	6233.7	5697.6	5195.9	4652.5	4045.1
30°	7636.6	7559.1	7357.5	7107.8	6714.4	6496.9	6286.5	5714.9	5187.3	4624.2	3994.7
32.5°	7610.7	7523.4	7308.3	7044.0	6641.9	6409.6	6196.8	5602.9	5064.4	4496.4	3858.2
35°	7426.4	7353.7	7131.3	6854.6	6453.7	6209.1	5986.5	5398.8	4859.0	4298.4	3663.9
37.5°	7148.4	7045.2	6837.4	6559.6	6135.4	5907.9	5687.7	5107.5	4579.9	4024.3	3421.8
40°	6692.3	6568.2	6360.3	6118.1	5714.9	5488.6	5288.2	4746.0	4227.0	3708.2	3132.9
42.5°	6118.1	6021.0	5827.9	5578.3	5208.3	4991.9	4812.3	4291.0	3831.2	3350.5	2814.4
45°	5444.3	5350.9	5186.2	4961.1	4626.6	4438.6	4273.8	3810.3	3395.9	2957.0	2473.9
47.5°	4715.2	4623.0	4479.1	4281.2	3982.4	3820.1	3676.3	3296.4	2905.4	2521.8	2097.6
50°	3859.5	3732.8	3654.1	3488.2	3238.6	3100.8	2990.2	2649.6	2360.7	2052.1	1699.2
52.5°	2880.8	2840.3	2727.1	2610.3	2434.5	2332.4	2259.9	2041.0	1801.2	1577.4	1308.3
55°	1991.9	1954.9	1886.0	1814.7	1696.8	1645.2	1591.0	1458.2	1298.3	1145.9	962.7
57.5°	1259.1	1286.1	1241.8	1201.3	1130.0	1111.5	1069.7	992.2	893.8	797.9	683.6
60°	811.4	826.3	797.9	774.6	735.2	720.6	700.9	654.1	595.0	539.8	462.3
62.5°	513.9	521.3	505.3	491.8	469.6	463.6	449.9	422.9	387.2	354.2	305.0
65°	321.0	327.0	315.9	307.4	293.9	295.1	282.8	266.7	245.9	225.0	196.7
67.5°	198.0	201.6	194.3	189.4	180.8	180.8	173.4	163.5	150.0	137.8	119.2
70°	120.5	121.7	116.8	114.3	108.1	107.0	103.2	95.9	87.3	78.7	67.6
72.5°	70.0	71.3	67.6	65.1	61.5	61.5	59.0	55.4	51.6	44.3	38.1
75°	38.1	39.4	37.0	35.7	33.2	34.4	31.9	30.8	27.0	24.6	22.1
77.5°	19.7	20.9	19.7	18.4	18.4	18.4	17.3	16.0	16.0	13.5	13.5
80°	11.1	11.1	11.1	11.1	11.1	9.8	9.8	9.8	9.8	9.8	8.6
82.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	4.9
85°	1.3	1.3	2.4	2.4	2.4	2.4	2.4	2.4	2.4	3.7	3.7
87.5°	0.0	0.0	1.3	1.3	1.3	1.3	1.3	2.4	2.4	2.4	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192723

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2
2.5°	1686.9	1685.7	1629.1	1604.5	1584.9	1554.1	1532.0	1508.6	1487.7	1449.6	1417.7
5°	1937.8	1903.3	1809.8	1750.9	1713.9	1664.7	1610.7	1556.6	1503.7	1434.8	1378.3
7.5°	2200.8	2127.0	1987.0	1888.5	1832.0	1763.1	1672.2	1587.4	1501.2	1406.6	1325.4
10°	2451.7	2331.2	2152.9	2002.9	1925.4	1836.9	1711.5	1593.4	1480.4	1361.0	1260.2
12.5°	2707.4	2535.3	2302.9	2108.6	2010.3	1900.8	1739.8	1593.4	1453.3	1315.6	1196.4
15°	2960.6	2733.3	2444.2	2203.2	2084.0	1953.8	1759.5	1584.9	1420.1	1265.1	1132.4
17.5°	3177.0	2895.5	2547.6	2268.5	2128.3	1980.8	1758.2	1559.0	1375.8	1208.6	1067.3
20°	3345.6	3012.4	2620.1	2301.6	2144.3	1983.2	1738.5	1520.9	1325.4	1150.8	1005.7
22.5°	3459.9	3088.6	2657.1	2307.8	2139.4	1969.7	1707.9	1482.8	1279.9	1105.4	960.3
25°	3531.2	3126.7	2668.0	2299.2	2122.1	1946.3	1679.5	1449.6	1250.5	1081.9	946.8
27.5°	3544.7	3115.6	2646.0	2263.5	2081.6	1904.6	1639.0	1417.7	1224.6	1068.4	946.8
30°	3478.3	3044.3	2570.9	2183.7	2005.4	1832.0	1571.3	1359.9	1179.1	1036.5	925.8
32.5°	3351.7	2912.7	2446.7	2065.6	1892.2	1729.9	1479.1	1277.5	1102.9	971.3	871.7
35°	3168.5	2736.9	2285.6	1916.8	1748.4	1597.1	1350.0	1165.6	999.7	877.9	785.7
37.5°	2946.0	2525.5	2097.6	1747.1	1587.4	1445.9	1209.9	1036.5	882.8	768.4	686.1
40°	2675.5	2296.7	1886.0	1560.3	1407.8	1279.9	1062.4	895.1	750.0	652.8	577.9
42.5°	2392.6	2041.0	1661.1	1351.3	1215.9	1094.3	901.2	751.2	622.2	542.3	483.2
45°	2101.3	1757.0	1425.0	1149.7	1047.6	911.1	732.8	611.1	506.6	447.5	400.8
47.5°	1773.0	1481.5	1175.4	933.2	826.3	734.1	585.3	486.9	419.3	367.7	332.0
50°	1420.1	1187.8	930.8	724.2	635.7	565.6	456.1	388.5	336.9	301.3	274.2
52.5°	1091.8	908.6	700.9	531.2	475.8	422.9	355.3	308.6	271.8	244.7	225.0
55°	811.4	662.8	504.1	393.4	354.2	319.7	279.1	242.2	215.1	196.7	180.8
57.5°	571.7	462.3	354.2	285.3	264.3	242.2	211.5	186.9	168.4	153.7	141.4
60°	382.4	314.8	249.6	209.1	194.3	179.5	159.9	142.6	129.1	119.2	107.0
62.5°	257.0	211.5	174.6	150.0	140.2	130.3	116.8	104.5	94.6	84.8	75.1
65°	164.8	140.2	118.1	102.1	94.6	89.7	80.0	71.3	64.0	55.4	47.9
67.5°	100.8	87.3	73.8	64.0	60.3	56.5	50.5	44.3	39.4	33.2	28.3
70°	59.0	51.6	44.3	38.1	37.0	34.4	29.5	25.9	23.3	19.7	17.3
72.5°	34.4	30.8	25.9	23.3	22.1	19.7	18.4	16.0	13.5	12.4	11.1
75°	19.7	17.3	14.8	13.5	13.5	12.4	11.1	11.1	9.8	9.8	8.6
77.5°	12.4	11.1	9.8	9.8	9.8	8.6	8.6	8.6	8.6	7.3	7.3
80°	8.6	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
82.5°	4.9	4.9	4.9	4.9	4.9	6.2	6.2	6.2	6.2	6.2	7.3
85°	3.7	4.9	4.9	4.9	4.9	4.9	6.2	6.2	6.2	6.2	6.2
87.5°	3.7	4.9	4.9	4.9	4.9	4.9	6.2	6.2	6.2	6.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192723

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2
2.5°	1399.1	1379.6	1319.3	1340.2	1302.1	1271.3	1268.9	1250.5	1218.4	1201.3	1192.6
5°	1335.3	1291.0	1217.2	1222.1	1177.8	1130.0	1104.1	1079.5	1037.8	1011.9	994.6
7.5°	1256.6	1196.4	1109.1	1102.9	1056.2	998.4	961.4	927.1	881.6	848.4	827.4
10°	1174.2	1100.5	998.4	991.0	941.9	879.2	837.3	797.9	751.2	718.0	696.0
12.5°	1098.0	1013.2	911.1	892.7	844.7	780.8	735.2	693.4	647.9	619.6	593.9
15°	1025.4	933.2	825.0	807.8	761.1	697.1	646.8	609.8	566.8	539.8	516.4
17.5°	952.9	858.2	751.2	731.6	687.3	625.8	581.5	542.3	502.9	477.1	456.1
20°	890.2	795.5	690.9	671.4	630.7	571.7	531.2	494.2	458.6	434.0	416.9
22.5°	849.5	757.4	662.8	645.5	607.4	554.5	516.4	484.4	453.7	430.4	416.9
25°	847.1	767.2	682.5	672.5	640.6	596.3	569.3	549.6	531.2	512.8	507.7
27.5°	861.9	796.8	725.5	723.0	697.1	667.6	655.3	649.2	639.3	633.1	641.8
30°	853.3	797.9	737.7	737.7	718.0	697.1	690.9	688.5	682.5	683.6	693.4
32.5°	807.8	757.4	699.6	700.9	688.5	665.2	661.5	660.3	652.8	651.7	659.0
35°	725.5	678.7	630.7	632.0	622.2	600.1	595.0	592.6	582.8	577.9	582.8
37.5°	630.7	592.6	547.1	547.1	537.4	520.1	515.2	510.2	504.1	499.1	499.1
40°	533.6	502.9	466.0	464.7	457.4	440.2	435.3	431.5	425.3	416.9	419.3
42.5°	451.2	422.9	393.4	391.0	386.1	371.3	366.4	361.5	355.3	348.0	348.0
45°	375.0	356.6	330.7	329.6	324.5	312.3	308.6	302.4	297.5	290.2	290.2
47.5°	312.3	297.5	276.7	275.4	271.8	260.7	257.0	252.1	247.2	242.2	242.2
50°	261.9	247.2	229.9	228.6	226.2	217.6	212.7	209.1	205.3	201.6	199.2
52.5°	215.1	202.9	189.4	188.1	185.6	177.0	173.4	171.0	167.2	161.1	161.1
55°	173.4	163.5	151.3	150.0	147.5	140.2	136.5	131.6	126.7	120.5	119.2
57.5°	135.3	126.7	116.8	115.6	111.9	105.7	99.7	94.6	89.7	84.8	82.4
60°	102.1	92.2	83.5	81.1	78.7	70.0	65.1	60.3	55.4	51.6	49.2
62.5°	68.9	62.7	52.9	51.6	49.2	44.3	38.1	35.7	33.2	30.8	29.5
65°	43.0	38.1	33.2	31.9	29.5	25.9	23.3	22.1	20.9	19.7	18.4
67.5°	25.9	23.3	19.7	19.7	18.4	17.3	14.8	14.8	13.5	13.5	12.4
70°	16.0	14.8	13.5	12.4	12.4	12.4	11.1	11.1	11.1	11.1	11.1
72.5°	11.1	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.8	9.8
75°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
77.5°	8.6	8.6	7.3	8.6	8.6	8.6	8.6	7.3	8.6	7.3	7.3
80°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
82.5°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	6.2	6.2	6.2	6.2
85°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	4.9
87.5°	6.2	6.2	6.2	6.2	6.2	4.9	4.9	4.9	4.9	3.7	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192723

CATALOG NUMBER: LDA6A70935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2	1458.2
2.5°	1195.1	1160.7	1174.2	1154.5	1148.4	1143.5	1136.1	1159.4
5°	987.3	950.5	959.0	939.4	930.8	922.2	913.5	931.9
7.5°	815.2	779.5	783.3	766.0	757.4	747.6	739.0	753.6
10°	681.2	647.9	649.2	633.1	624.7	614.7	607.4	618.5
12.5°	579.1	548.4	548.4	536.1	528.7	517.7	511.5	520.1
15°	501.7	474.5	474.5	462.3	456.1	446.3	440.2	448.8
17.5°	442.6	418.0	418.0	409.4	403.3	394.7	389.7	397.2
20°	403.3	382.4	383.6	375.0	370.1	360.2	357.8	363.9
22.5°	406.9	387.2	389.7	383.6	378.8	371.3	368.8	377.5
25°	509.0	494.2	502.9	502.9	505.3	494.2	499.1	512.8
27.5°	654.1	646.8	660.3	655.3	665.2	665.2	670.1	687.3
30°	707.0	700.9	715.5	714.4	724.2	721.7	724.2	740.1
32.5°	668.8	662.8	675.0	673.8	681.2	675.0	676.3	689.8
35°	587.7	581.5	590.1	589.0	593.9	586.5	590.1	597.6
37.5°	501.7	495.5	500.4	499.1	500.4	491.8	496.7	500.4
40°	421.8	414.4	421.8	416.9	418.0	409.4	410.7	415.6
42.5°	352.9	344.2	350.4	350.4	350.4	344.2	345.5	350.4
45°	293.9	287.7	291.3	290.2	291.3	286.4	290.2	295.1
47.5°	243.4	238.6	241.0	239.7	239.7	234.8	236.1	236.1
50°	200.5	195.6	196.7	195.6	191.8	185.6	184.5	185.6
52.5°	158.6	152.4	152.4	150.0	147.5	142.6	142.6	143.8
55°	116.8	111.9	111.9	110.7	108.1	104.5	104.5	107.0
57.5°	78.7	75.1	76.2	75.1	75.1	70.0	72.5	72.5
60°	47.9	45.4	45.4	44.3	41.8	40.6	39.4	41.8
62.5°	28.3	27.0	27.0	25.9	25.9	24.6	24.6	24.6
65°	18.4	17.3	17.3	16.0	16.0	14.8	13.5	14.8
67.5°	12.4	11.1	11.1	11.1	11.1	9.8	9.8	9.8
70°	11.1	9.8	9.8	9.8	9.8	8.6	8.6	8.6
72.5°	9.8	8.6	9.8	8.6	8.6	8.6	8.6	8.6
75°	8.6	8.6	8.6	7.3	7.3	7.3	7.3	7.3
77.5°	7.3	7.3	7.3	7.3	7.3	6.2	6.2	6.2
80°	7.3	6.2	6.2	6.2	6.2	6.2	6.2	6.2
82.5°	6.2	6.2	6.2	6.2	6.2	4.9	4.9	4.9
85°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
87.5°	3.7	3.7	3.7	3.7	3.7	2.4	2.4	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)