

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192724

Luminaire Tested: **LDA6A70935D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192724
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70935D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7110.7 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192724

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192724

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81
4	91	82	75	70	89	80	74	69	78	73	68		76	71	67		74
5	85	74	67	62	83	73	66	61	71	65	61		70	64	60		68
6	79	68	60	55	77	67	60	55	65	59	54		64	58	54		62
7	74	62	55	49	72	61	54	49	60	53	49		59	53	49		57
8	69	57	49	44	67	56	49	44	55	49	44		54	48	44		53
9	64	52	45	40	63	52	45	40	51	44	40		50	44	40		49
10	60	48	41	36	59	48	41	36	47	41	36		46	40	36		45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	73059	73059	73059
5°	200522	67318	27465
10°	439426	55087	10471
15°	671213	41930	12282
20°	777668	31199	19077
25°	848329	25659	30788
30°	947317	23263	31442
35°	963846	15968	21556
40°	980780	7564	10906
45°	982373	3148	4760
50°	830506	1365	1475
55°	267431	937	229
60°	53110	1074	0
65°	5422	1271	0
70°	593	1779	0
75°	0	2351	0
80°	0	3852	410
85°	0	7674	818



TEST NUMBER: P1192724

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.9	2.5
10°-20°	935.6	13.2
20°-30°	1791.4	25.2
30°-40°	2110.6	29.7
40°-50°	1657.8	23.3
50°-60°	404.0	5.7
60°-70°	17.3	0.2
70°-80°	6.5	0.1
80°-90°	6.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2907.9	40.9
0°-40°	5018.5	70.6
0°-60°	7080.3	99.6
0°-90°	7110.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7110.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1333	1333	1333	1333	1333	
5°	3644	2637	1223	640	499	482
15°	11827	6074	739	212	216	3302
25°	14025	7386	424	444	509	6537
35°	14402	4669	239	307	322	9031
45°	12671	1443	41	56	61	9521
55°	2798	53	10	6	2	3330
65°	42	6	10	6	0	111
75°	0	6	11	7	0	0
85°	0	7	12	7	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192724

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	2284.2	2279.3	2246.1	2276.9	2183.4	2179.7	2138.0	2119.4	2065.3	2013.7	1940.0
5°	3643.9	3564.0	3498.8	3501.3	3321.8	3288.6	3195.2	3100.5	2955.4	2820.3	2637.1
7.5°	5554.4	5459.7	5322.0	5264.2	4921.3	4820.5	4627.4	4375.4	4059.5	3744.7	3405.4
10°	7894.0	7908.6	7730.3	7565.7	7046.9	6842.8	6530.5	6033.8	5435.1	4843.8	4242.6
12.5°	10248.2	10238.3	10025.6	9776.1	9136.8	8849.1	8433.6	7814.0	7021.0	6103.9	5163.4
15°	11826.7	11896.8	11807.1	11607.9	11062.1	10732.5	10264.2	9423.3	8456.9	7343.1	6074.4
17.5°	12817.6	12884.0	12852.1	12695.9	12214.1	11862.3	11471.5	10783.0	9665.4	8265.1	6792.4
20°	13330.3	13434.7	13420.1	13250.4	12886.4	12595.1	12163.6	11525.6	10557.9	8905.7	7257.1
22.5°	13672.0	13752.0	13774.1	13582.3	13206.1	12929.4	12613.5	11966.9	11057.1	9296.7	7441.5
25°	14024.9	14166.2	14027.3	13791.4	13445.8	13180.2	12843.4	12223.8	11295.6	9456.5	7386.2
27.5°	14457.6	14525.3	14210.5	13995.4	13611.8	13324.2	12966.4	12372.5	11337.5	9328.6	7070.2
30°	14965.3	14685.0	14465.0	14038.4	13603.3	13322.9	12959.1	12279.2	11117.3	8904.4	6458.0
32.5°	14881.8	14624.8	14375.3	13924.1	13493.8	13215.9	12810.2	11968.2	10597.4	8195.1	5613.4
35°	14402.3	14457.6	14188.4	13814.6	13327.8	13041.3	12598.8	11525.6	9714.6	7216.6	4669.2
37.5°	13997.8	14119.5	13943.8	13598.2	13104.0	12716.8	12119.3	10814.9	8562.6	5974.9	3774.2
40°	13705.2	13744.6	13649.9	13262.6	12668.9	12109.5	11418.6	9538.9	7163.6	4690.1	2978.9
42.5°	13251.5	13356.1	13188.8	12765.9	11866.1	11232.9	10232.3	8064.8	5564.2	3582.4	2242.4
45°	12671.3	12770.8	12564.3	11861.2	10609.6	9681.5	8460.7	6288.4	4116.0	2640.7	1443.3
47.5°	11724.7	11786.1	11386.6	10414.2	8594.7	7720.6	6469.1	4384.1	2651.7	1476.5	702.0
50°	9738.0	9708.5	8884.7	7688.6	5748.7	4831.6	3850.4	2376.4	1191.2	699.6	438.9
52.5°	6276.0	6208.4	5393.4	4305.3	2911.2	2221.5	1669.5	1025.3	620.9	391.0	173.3
55°	2798.1	2772.2	2269.4	1762.9	1191.2	1025.3	783.1	502.9	330.7	136.5	52.9
57.5°	1037.6	1014.2	893.8	749.9	575.3	478.3	379.9	241.0	84.8	45.4	28.3
60°	484.4	483.2	425.3	350.4	243.4	184.3	107.0	56.5	35.7	24.6	16.0
62.5°	154.9	151.3	105.7	77.5	55.4	47.9	38.1	28.3	18.4	13.5	9.8
65°	41.8	41.8	38.1	31.9	25.9	22.1	18.4	13.5	8.6	7.3	6.2
67.5°	16.0	16.0	14.8	13.5	9.8	8.6	7.3	6.2	4.9	6.2	6.2
70°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	4.9	4.9	6.2
72.5°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	4.9	6.2	6.2
75°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	4.9	6.2	6.2
77.5°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	4.9	6.2	6.2
80°	0.0	0.0	1.3	1.3	2.4	2.4	3.7	3.7	4.9	6.2	6.2
82.5°	0.0	0.0	1.3	2.4	2.4	2.4	3.7	4.9	4.9	6.2	7.3
85°	0.0	0.0	1.3	2.4	2.4	3.7	3.7	4.9	4.9	6.2	7.3
87.5°	0.0	0.0	1.3	2.4	2.4	3.7	3.7	4.9	4.9	6.2	7.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192724

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1885.9	1804.8	1692.9	1627.8	1611.7	1577.3	1517.1	1427.3	1353.6	1282.2	1240.4
5°	2482.1	2290.4	2075.3	1924.0	1862.6	1780.2	1633.8	1482.7	1343.8	1223.3	1128.5
7.5°	3114.1	2798.1	2450.1	2169.9	2069.1	1938.8	1700.2	1475.2	1284.7	1117.6	990.9
10°	3742.3	3233.3	2761.2	2355.5	2190.7	2013.7	1699.0	1407.6	1183.9	989.6	849.5
12.5°	4370.5	3639.1	2989.8	2467.4	2253.4	2029.7	1648.6	1304.4	1056.0	858.2	724.2
15°	4950.8	3962.3	3144.8	2505.5	2247.4	1982.9	1546.5	1179.0	922.0	738.8	614.7
17.5°	5383.4	4132.0	3180.5	2447.7	2150.2	1857.6	1390.5	1031.5	794.2	633.1	506.5
20°	5596.1	4159.0	3095.6	2282.9	1982.9	1679.4	1219.5	890.1	684.8	534.8	427.8
22.5°	5596.1	4031.2	2911.2	2076.4	1774.0	1474.1	1054.7	773.3	598.8	465.9	376.2
25°	5383.4	3776.7	2664.1	1838.0	1544.1	1271.2	912.2	686.1	532.3	424.2	349.1
27.5°	4970.5	3425.1	2346.9	1572.4	1317.9	1090.4	799.1	606.1	481.9	382.4	383.5
30°	4402.5	2993.5	1982.9	1292.2	1085.5	896.3	672.5	507.7	386.1	367.5	378.6
32.5°	3745.9	2477.2	1571.1	1002.0	840.9	705.6	511.5	358.9	307.3	309.7	322.1
35°	3072.2	1949.9	1182.7	742.6	625.8	511.5	335.6	236.1	233.5	238.6	247.0
37.5°	2425.6	1459.2	855.6	543.4	420.5	314.8	180.8	162.3	162.3	167.2	172.1
40°	1817.0	1035.2	588.8	322.1	204.0	143.8	114.3	105.7	104.5	105.7	111.9
42.5°	1247.9	655.3	350.4	129.1	98.4	83.5	72.5	66.4	65.1	66.4	70.0
45°	700.7	403.2	136.5	68.9	59.0	52.9	45.4	41.8	40.6	40.6	43.0
47.5°	438.9	159.8	61.4	43.0	36.8	34.4	29.5	27.0	25.9	25.9	27.0
50°	168.4	62.7	38.1	28.3	24.6	22.1	19.7	17.3	16.0	16.0	17.3
52.5°	57.8	36.8	24.6	18.4	16.0	14.8	12.2	11.1	11.1	11.1	11.1
55°	31.9	22.1	14.8	11.1	9.8	9.8	9.8	9.8	9.8	9.8	9.8
57.5°	19.7	13.5	9.8	8.6	8.6	8.6	8.6	8.6	8.6	9.8	9.8
60°	11.1	8.6	7.3	7.3	7.3	7.3	8.6	8.6	8.6	9.8	9.8
62.5°	7.3	7.3	7.3	7.3	7.3	7.3	8.6	8.6	9.8	9.8	9.8
65°	6.2	6.2	6.2	7.3	7.3	7.3	8.6	8.6	9.8	9.8	9.8
67.5°	6.2	6.2	7.3	7.3	7.3	8.6	8.6	9.8	9.8	9.8	9.8
70°	6.2	7.3	7.3	8.6	8.6	8.6	9.8	9.8	9.8	11.1	11.1
72.5°	6.2	7.3	7.3	8.6	8.6	8.6	9.8	9.8	11.1	11.1	11.1
75°	7.3	7.3	7.3	8.6	8.6	8.6	9.8	11.1	11.1	11.1	11.1
77.5°	7.3	7.3	8.6	8.6	8.6	9.8	9.8	11.1	11.1	11.1	11.1
80°	7.3	7.3	8.6	8.6	9.8	9.8	11.1	11.1	11.1	12.2	12.2
82.5°	7.3	7.3	8.6	9.8	9.8	9.8	11.1	11.1	12.2	12.2	12.2
85°	7.3	8.6	8.6	9.8	9.8	9.8	11.1	11.1	12.2	12.2	12.2
87.5°	7.3	8.6	8.6	9.8	9.8	9.8	11.1	11.1	12.2	12.2	12.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192724

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	1185.2	1133.5	1081.9	1043.8	1025.3	1006.9	966.3	913.4	891.2	859.3	840.9
5°	1032.7	945.5	876.6	831.0	804.0	768.3	721.7	669.9	640.5	607.3	585.3
7.5°	875.3	773.3	706.9	665.1	638.0	593.7	534.8	473.4	437.7	400.8	375.0
10°	737.7	640.5	565.6	517.5	483.2	431.5	372.6	329.4	298.8	266.7	241.0
12.5°	615.9	511.5	431.5	391.0	367.5	318.4	269.2	221.3	202.9	196.7	196.7
15°	499.1	404.5	336.9	302.4	277.8	225.0	215.1	212.7	211.5	210.2	212.7
17.5°	406.9	327.0	255.7	238.6	236.1	234.8	236.1	236.1	237.3	241.0	247.0
20°	341.8	268.0	263.1	264.3	264.3	269.2	275.4	280.3	285.1	291.3	302.4
22.5°	303.7	302.4	311.0	312.3	318.4	325.8	336.9	344.2	356.5	362.7	378.6
25°	350.4	358.9	375.0	379.9	389.7	402.1	419.2	429.1	443.8	451.2	469.6
27.5°	397.0	410.7	430.2	436.4	445.0	464.7	477.0	485.6	492.9	498.0	509.0
30°	393.4	405.6	425.3	426.6	438.9	452.4	459.9	467.2	472.1	470.8	477.0
32.5°	333.2	344.2	362.7	362.7	376.2	387.2	391.0	397.0	397.0	397.0	399.6
35°	255.7	263.1	275.4	279.1	290.2	297.5	300.0	307.3	307.3	304.8	304.8
37.5°	177.0	186.9	195.4	197.9	205.3	210.2	216.4	217.6	215.1	216.4	216.4
40°	115.6	121.7	127.8	129.1	135.2	138.9	145.1	145.1	146.2	145.1	147.5
42.5°	71.3	76.2	80.0	82.4	84.8	87.3	91.0	92.2	93.5	92.2	94.6
45°	44.3	46.7	49.2	50.5	51.6	52.9	56.5	56.5	56.5	56.5	57.8
47.5°	27.0	28.3	29.5	29.5	30.8	31.9	33.2	33.2	33.2	33.2	34.4
50°	16.0	17.3	17.3	17.3	18.4	18.4	19.7	19.7	19.7	18.4	19.7
52.5°	11.1	11.1	11.1	11.1	11.1	11.1	11.1	11.1	11.1	9.8	11.1
55°	9.8	9.8	8.6	8.6	8.6	8.6	8.6	7.3	6.2	6.2	4.9
57.5°	8.6	8.6	8.6	8.6	8.6	7.3	7.3	6.2	6.2	4.9	3.7
60°	8.6	8.6	8.6	8.6	8.6	7.3	7.3	6.2	4.9	4.9	3.7
62.5°	9.8	8.6	8.6	8.6	8.6	7.3	7.3	6.2	4.9	4.9	3.7
65°	9.8	9.8	8.6	8.6	8.6	7.3	7.3	6.2	6.2	4.9	3.7
67.5°	9.8	9.8	9.8	8.6	9.8	8.6	7.3	7.3	6.2	4.9	4.9
70°	11.1	9.8	9.8	9.8	9.8	8.6	8.6	7.3	6.2	4.9	4.9
72.5°	11.1	11.1	9.8	9.8	9.8	8.6	8.6	7.3	6.2	6.2	4.9
75°	11.1	11.1	9.8	9.8	9.8	8.6	8.6	7.3	7.3	6.2	4.9
77.5°	11.1	11.1	11.1	9.8	9.8	9.8	8.6	8.6	7.3	6.2	4.9
80°	11.1	11.1	11.1	11.1	11.1	9.8	9.8	8.6	7.3	6.2	4.9
82.5°	12.2	11.1	11.1	11.1	11.1	9.8	9.8	8.6	7.3	6.2	6.2
85°	12.2	12.2	11.1	11.1	11.1	9.8	9.8	8.6	7.3	7.3	6.2
87.5°	12.2	11.1	11.1	11.1	11.1	9.8	9.8	8.6	7.3	6.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192724

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7	1332.7
2.5°	822.5	812.6	812.6	795.5	792.9	779.4	790.4	783.1
5°	560.7	544.6	539.7	522.6	516.4	500.4	505.3	499.1
7.5°	352.9	336.9	331.9	319.7	312.3	300.0	301.3	297.5
10°	215.1	200.5	196.7	193.0	189.4	188.1	189.4	188.1
12.5°	195.4	194.3	191.8	193.0	190.5	191.8	193.0	191.8
15°	212.7	215.1	212.7	214.0	212.7	215.1	216.4	216.4
17.5°	249.6	254.5	252.1	255.7	254.5	260.6	260.6	260.6
20°	306.1	314.8	312.3	317.2	317.2	324.5	324.5	327.0
22.5°	384.8	395.9	394.6	405.6	403.2	411.8	411.8	414.3
25°	479.4	490.5	491.8	499.1	498.0	506.5	506.5	509.0
27.5°	518.8	525.0	523.7	527.4	528.6	533.5	537.2	534.8
30°	486.9	491.8	490.5	492.9	492.9	496.7	500.4	496.7
32.5°	409.4	413.1	413.1	418.0	414.3	415.6	421.6	418.0
35°	313.5	315.9	313.5	315.9	317.2	317.2	323.4	322.1
37.5°	223.7	225.0	225.0	228.6	225.0	225.0	231.1	232.4
40°	150.0	151.3	150.0	154.9	152.4	152.4	156.2	152.4
42.5°	95.9	97.1	95.9	99.7	97.1	99.7	100.8	102.1
45°	59.0	59.0	57.8	60.3	59.0	60.3	61.4	61.4
47.5°	34.4	34.4	33.2	35.7	34.4	34.4	34.4	35.7
50°	18.4	18.4	18.4	19.7	18.4	18.4	18.4	17.3
52.5°	9.8	9.8	8.6	9.8	8.6	8.6	8.6	8.6
55°	4.9	3.7	3.7	3.7	2.4	2.4	2.4	2.4
57.5°	3.7	2.4	2.4	1.3	1.3	1.3	0.0	0.0
60°	2.4	2.4	1.3	1.3	0.0	0.0	0.0	0.0
62.5°	2.4	2.4	1.3	1.3	0.0	0.0	0.0	0.0
65°	2.4	2.4	1.3	1.3	0.0	0.0	0.0	0.0
67.5°	3.7	2.4	2.4	1.3	1.3	0.0	0.0	0.0
70°	3.7	2.4	2.4	1.3	1.3	0.0	0.0	0.0
72.5°	3.7	2.4	2.4	2.4	1.3	1.3	0.0	0.0
75°	3.7	3.7	2.4	2.4	1.3	1.3	0.0	0.0
77.5°	4.9	3.7	2.4	2.4	1.3	1.3	0.0	0.0
80°	4.9	3.7	2.4	2.4	2.4	1.3	1.3	1.3
82.5°	4.9	3.7	3.7	2.4	2.4	1.3	1.3	1.3
85°	4.9	3.7	3.7	2.4	2.4	1.3	1.3	1.3
87.5°	4.9	3.7	3.7	2.4	2.4	1.3	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)