

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192729

Luminaire Tested: **LDA6A70935D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192729
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26685)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70935D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5362.5 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 2.12 / 1.05 / 1.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192729

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192729

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	76	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55		
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44		
8	67	55	47	42	65	54	47	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	43	38	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	94905	94905	94905
5°	152498	93033	59338
10°	225514	89104	39829
15°	307300	84297	29586
20°	380081	79544	28043
25°	440336	78307	46037
30°	480435	75024	46077
35°	493772	64842	36038
40°	480844	51031	28074
45°	435991	37748	22119
50°	343520	27888	15002
55°	204819	19861	8573
60°	104750	13212	3234
65°	50083	7018	1440
70°	23642	3158	1378
75°	9616	2076	1546
80°	4672	2305	1547
85°	2327	3900	2327

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192729

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.7	3.3
10°-20°	627.8	11.7
20°-30°	1181.8	22.0
30°-40°	1439.1	26.8
40°-50°	1197.9	22.3
50°-60°	573.7	10.7
60°-70°	137.8	2.6
70°-80°	21.7	0.4
80°-90°	5.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1987.3	37.1
0°-40°	3426.4	63.9
0°-60°	5197.9	96.9
0°-90°	5362.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5362.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1731	1731	1731	1731	1731	
5°	2771	2351	1691	1230	1078	304
15°	5415	3679	1485	674	521	1552
25°	7280	4300	1295	734	761	3344
35°	7378	3776	969	564	538	4572
45°	5624	2524	487	300	285	4258
55°	2143	1041	208	117	90	2019
65°	386	225	54	17	11	442
75°	45	23	10	9	7	62
85°	4	4	6	5	4	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192729

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2
2.5°	2238.9	2160.3	2184.8	2180.0	2174.9	2149.2	2130.8	2114.7	2074.1	2074.1	2022.5
5°	2771.2	2679.1	2702.4	2685.3	2663.1	2623.7	2588.0	2547.5	2472.6	2440.5	2350.8
7.5°	3379.9	3275.4	3296.2	3261.9	3215.1	3162.2	3104.4	3028.2	2909.0	2836.4	2697.5
10°	4051.2	3902.3	3914.7	3863.1	3785.6	3714.3	3659.0	3513.9	3344.3	3223.8	3029.5
12.5°	4686.9	4556.5	4560.2	4487.6	4375.7	4288.4	4204.9	4013.1	3786.9	3614.7	3358.9
15°	5414.6	5254.9	5216.8	5118.4	4972.0	4865.1	4750.7	4508.6	4224.6	3997.1	3678.6
17.5°	6001.2	5836.4	5811.8	5719.6	5510.6	5381.4	5237.6	4964.7	4604.5	4321.7	3930.7
20°	6515.1	6351.6	6309.8	6190.4	5950.7	5803.2	5629.9	5307.7	4914.2	4566.4	4124.9
22.5°	6935.6	6756.1	6697.0	6549.5	6282.7	6116.7	5905.3	5553.6	5114.7	4726.2	4240.6
25°	7279.8	7075.8	7000.7	6833.5	6533.5	6350.3	6118.0	5724.5	5246.3	4817.2	4299.5
27.5°	7499.8	7295.8	7213.4	7021.6	6684.8	6488.1	6234.7	5809.4	5293.0	4829.4	4287.3
30°	7589.7	7378.2	7284.7	7067.2	6704.4	6496.6	6232.3	5772.4	5232.7	4741.0	4183.9
32.5°	7534.3	7326.6	7222.0	6985.9	6608.6	6384.7	6120.4	5629.9	5074.1	4565.1	4004.4
35°	7378.2	7172.8	7064.7	6812.6	6419.2	6185.5	5922.4	5414.6	4852.8	4332.7	3775.8
37.5°	7108.9	6914.7	6790.5	6540.9	6145.0	5906.4	5645.9	5133.1	4558.9	4069.6	3511.4
40°	6719.2	6534.8	6411.7	6145.0	5771.3	5530.3	5284.4	4764.3	4223.3	3746.3	3207.8
42.5°	6222.5	6052.8	5934.8	5675.3	5318.7	5081.5	4856.4	4357.3	3842.1	3388.4	2879.5
45°	5623.7	5476.2	5360.6	5145.5	4793.7	4568.8	4365.9	3913.4	3413.0	2996.3	2524.2
47.5°	4919.1	4797.5	4685.6	4490.0	4173.0	3960.1	3792.9	3378.6	2954.4	2562.3	2160.3
50°	4027.9	3940.6	3853.2	3650.4	3426.7	3240.9	3119.2	2750.4	2407.3	2100.0	1766.8
52.5°	3036.8	2983.9	2922.5	2777.4	2627.4	2519.2	2411.0	2130.8	1873.8	1645.0	1385.6
55°	2143.0	2116.0	2067.9	2009.0	1894.7	1820.9	1727.4	1584.8	1385.6	1231.9	1041.4
57.5°	1448.3	1441.0	1407.8	1372.1	1309.4	1284.8	1206.2	1114.0	1002.0	887.7	752.5
60°	955.4	939.3	931.9	912.2	864.4	844.7	816.3	757.4	688.5	608.5	525.0
62.5°	614.7	606.1	600.1	591.4	561.8	561.8	533.6	506.6	455.0	405.8	351.6
65°	386.1	378.6	377.5	371.3	360.2	355.3	334.5	314.8	290.2	263.1	225.0
67.5°	248.3	237.3	231.1	227.5	220.0	211.5	204.0	195.4	175.9	159.9	135.3
70°	147.5	137.8	136.5	137.8	129.1	127.8	120.5	114.3	100.8	91.0	76.2
72.5°	83.5	78.7	77.5	77.5	72.5	71.3	66.4	62.7	55.4	47.9	41.8
75°	45.4	41.8	41.8	41.8	39.4	38.1	35.7	34.4	29.5	27.0	23.3
77.5°	25.9	24.6	24.6	23.3	22.1	20.9	19.7	19.7	17.3	16.0	14.8
80°	14.8	14.8	14.8	14.8	13.5	13.5	12.4	12.4	11.1	11.1	9.8
82.5°	8.6	8.6	8.6	8.6	8.6	8.6	7.3	7.3	7.3	7.3	6.2
85°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
87.5°	0.0	0.0	1.3	1.3	1.3	1.3	1.3	2.4	2.4	2.4	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192729

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2
2.5°	1999.2	1962.2	1959.8	1905.7	1871.2	1843.0	1822.0	1796.3	1738.5	1706.6	1683.1
5°	2288.1	2211.9	2172.5	2074.1	2020.0	1972.2	1913.1	1851.7	1756.9	1690.6	1636.4
7.5°	2588.0	2461.5	2377.8	2231.6	2157.8	2082.7	1983.2	1883.6	1754.5	1655.0	1572.6
10°	2867.2	2687.7	2554.8	2358.1	2262.2	2163.8	2023.8	1889.8	1728.7	1600.7	1492.6
12.5°	3141.4	2905.3	2722.1	2472.6	2355.7	2234.0	2054.4	1886.0	1696.7	1543.1	1416.4
15°	3403.2	3106.9	2873.3	2572.1	2435.6	2289.4	2074.1	1875.0	1659.8	1485.3	1341.3
17.5°	3612.3	3260.6	2980.3	2633.6	2479.9	2314.0	2066.8	1843.0	1609.4	1423.7	1266.4
20°	3756.1	3358.9	3039.3	2658.2	2489.7	2311.4	2038.5	1798.7	1556.6	1363.5	1203.7
22.5°	3833.6	3403.2	3055.2	2650.7	2475.0	2288.1	2004.1	1758.2	1514.7	1321.8	1169.2
25°	3861.8	3407.0	3038.1	2618.8	2441.8	2251.1	1963.5	1720.1	1481.5	1294.6	1152.1
27.5°	3828.6	3355.3	2975.4	2552.4	2372.9	2184.8	1898.4	1666.0	1432.4	1255.3	1121.3
30°	3715.6	3234.8	2852.5	2434.3	2258.6	2077.9	1795.0	1566.4	1352.4	1185.2	1057.3
32.5°	3535.9	3057.7	2679.1	2272.1	2102.4	1929.0	1658.5	1441.0	1241.8	1084.4	970.0
35°	3313.5	2846.3	2477.5	2082.7	1923.0	1759.3	1502.4	1297.2	1110.3	968.9	857.0
37.5°	3061.4	2611.5	2254.9	1892.2	1729.9	1576.2	1326.7	1150.8	971.3	842.2	740.1
40°	2778.7	2342.2	2017.6	1664.7	1522.1	1381.9	1150.8	990.9	827.4	713.1	624.7
42.5°	2476.2	2069.2	1769.3	1452.1	1309.4	1181.6	973.8	829.8	684.8	590.1	520.1
45°	2155.4	1796.3	1508.6	1224.6	1095.4	984.9	795.5	665.2	559.4	486.9	434.0
47.5°	1819.6	1502.4	1246.7	999.5	885.2	789.3	636.9	537.2	453.7	400.8	360.2
50°	1481.5	1198.7	995.9	785.7	687.3	611.0	498.0	429.1	367.7	327.0	296.4
52.5°	1158.1	927.1	762.3	592.6	517.7	464.7	388.5	340.5	293.9	263.1	239.7
55°	855.7	698.4	556.9	430.4	386.1	352.9	298.8	264.3	231.1	207.8	190.5
57.5°	618.5	500.4	397.2	315.9	286.4	264.3	225.0	201.6	178.3	161.1	147.5
60°	434.0	345.5	280.3	231.1	210.2	195.4	167.2	152.4	135.3	120.5	107.0
62.5°	285.3	232.4	195.4	163.5	151.3	140.2	120.5	109.4	94.6	84.8	72.5
65°	185.6	152.4	130.3	109.4	99.7	94.6	81.1	72.5	62.7	54.1	46.7
67.5°	113.2	94.6	82.4	68.9	64.0	59.0	50.5	44.3	38.1	31.9	28.3
70°	62.7	55.4	47.9	40.6	37.0	34.4	29.5	27.0	22.1	19.7	16.0
72.5°	37.0	31.9	28.3	23.3	22.1	20.9	17.3	16.0	13.5	12.4	11.1
75°	22.1	18.4	17.3	14.8	13.5	13.5	12.4	11.1	9.8	9.8	8.6
77.5°	13.5	12.4	11.1	9.8	9.8	9.8	8.6	8.6	8.6	7.3	7.3
80°	8.6	8.6	8.6	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
82.5°	6.2	6.2	6.2	4.9	6.2	4.9	6.2	6.2	6.2	6.2	6.2
85°	3.7	3.7	4.9	4.9	4.9	4.9	4.9	6.2	6.2	6.2	6.2
87.5°	3.7	3.7	4.9	4.9	4.9	4.9	4.9	6.2	6.2	6.2	4.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192729

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2
2.5°	1656.1	1610.7	1577.4	1552.9	1561.5	1518.5	1504.8	1458.2	1441.0	1441.0	1416.4
5°	1581.2	1508.6	1452.1	1416.4	1413.9	1352.4	1320.5	1261.5	1229.5	1206.2	1182.7
7.5°	1491.3	1398.0	1322.9	1279.9	1267.6	1195.1	1152.1	1093.0	1045.1	1014.3	986.0
10°	1395.5	1283.5	1198.7	1149.5	1131.1	1052.4	995.9	941.7	890.1	858.2	828.7
12.5°	1303.2	1181.6	1088.1	1037.6	1014.3	933.2	875.4	818.8	769.6	736.5	706.9
15°	1218.4	1089.4	990.9	940.6	914.7	834.9	777.1	721.7	673.8	643.1	616.0
17.5°	1138.6	1007.0	908.6	859.5	831.1	757.4	702.0	647.9	605.0	576.6	552.0
20°	1078.3	947.9	857.0	813.9	785.7	716.8	668.8	622.1	586.4	565.6	542.3
22.5°	1052.4	931.9	854.4	815.2	795.5	740.1	706.9	673.8	650.4	646.7	632.0
25°	1048.7	943.0	879.0	846.0	833.6	791.7	772.2	751.2	733.9	739.0	741.4
27.5°	1032.7	934.4	881.6	853.3	843.4	809.0	794.2	774.6	762.3	768.4	770.9
30°	977.4	886.5	837.3	813.9	804.1	769.6	757.4	735.2	725.5	726.6	725.5
32.5°	891.4	805.3	759.8	739.0	727.9	697.1	683.6	663.9	649.2	647.9	645.5
35°	786.9	709.3	667.6	649.2	638.2	612.3	600.1	581.5	564.4	563.1	560.7
37.5°	679.9	611.0	575.5	559.4	549.6	528.7	513.9	501.6	490.6	485.6	484.4
40°	576.6	515.2	489.3	477.0	469.6	447.5	440.2	427.8	419.3	414.3	413.1
42.5°	479.6	436.4	415.6	404.5	398.3	382.4	373.7	363.9	355.3	350.4	349.1
45°	406.9	371.3	351.6	343.1	338.1	323.4	317.2	307.4	300.0	296.4	295.1
47.5°	339.4	311.0	297.5	287.7	286.4	274.2	265.6	258.3	250.8	247.2	245.9
50°	277.8	254.5	243.4	237.3	236.1	223.7	217.6	211.5	205.3	201.6	199.2
52.5°	228.6	206.5	199.2	190.5	189.4	178.3	173.4	167.2	161.1	156.2	152.4
55°	180.8	163.5	156.2	148.8	147.5	135.3	130.3	122.9	116.8	111.9	107.0
57.5°	137.8	124.2	116.8	109.4	108.1	99.7	91.0	84.8	78.7	72.5	68.9
60°	100.8	87.3	78.7	75.1	71.3	62.7	56.5	51.6	46.7	43.0	39.4
62.5°	66.4	56.5	50.5	45.4	43.0	37.0	33.2	29.5	27.0	25.9	24.6
65°	40.6	34.4	29.5	27.0	27.0	23.3	20.9	18.4	17.3	17.3	16.0
67.5°	24.6	20.9	18.4	17.3	16.0	14.8	13.5	13.5	12.4	12.4	11.1
70°	14.8	13.5	12.4	11.1	11.1	11.1	11.1	11.1	9.8	9.8	9.8
72.5°	11.1	9.8	9.8	9.8	9.8	9.8	9.8	9.8	8.6	8.6	8.6
75°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6	7.3
77.5°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
80°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	6.2	6.2	6.2
82.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
85°	6.2	6.2	6.2	6.2	6.2	6.2	4.9	4.9	4.9	4.9	4.9
87.5°	6.2	4.9	4.9	4.9	4.9	4.9	3.7	3.7	3.7	3.7	2.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192729

CATALOG NUMBER: LDA6A70935D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2	1731.2
2.5°	1404.0	1413.9	1399.1	1389.4	1379.4	1386.9	1352.4	1337.7
5°	1160.6	1149.5	1142.2	1133.5	1118.9	1121.3	1091.8	1078.3
7.5°	960.3	952.8	934.4	924.6	909.8	909.8	882.8	871.7
10°	801.7	790.6	773.3	764.7	751.2	740.1	726.6	715.5
12.5°	681.2	668.8	654.1	646.7	633.1	624.7	611.0	613.6
15°	591.4	579.1	565.6	558.2	547.1	538.5	527.4	521.3
17.5°	528.7	517.7	506.6	499.1	490.6	483.2	473.4	472.1
20°	523.7	515.2	509.0	504.1	496.7	491.8	486.9	480.7
22.5°	627.1	628.2	629.5	629.5	630.7	630.7	632.0	619.6
25°	740.1	753.6	753.6	757.4	768.4	768.4	766.0	761.1
27.5°	769.6	783.3	779.5	782.0	793.0	795.5	786.9	788.1
30°	720.4	732.8	725.5	726.6	733.9	733.9	723.0	727.9
32.5°	638.2	645.5	635.6	635.6	641.8	640.6	633.1	633.1
35°	550.9	554.5	545.9	549.6	549.6	545.9	538.5	538.5
37.5°	475.8	477.0	468.5	469.6	469.6	466.0	458.6	458.6
40°	404.5	408.2	400.8	403.2	400.8	397.2	393.4	392.3
42.5°	341.8	344.2	338.1	341.8	340.5	340.5	339.4	340.5
45°	287.7	290.2	285.3	287.7	288.9	287.7	284.0	285.3
47.5°	238.6	241.0	241.0	238.6	237.3	231.1	227.5	227.5
50°	193.0	191.8	190.5	186.9	183.2	179.5	175.9	175.9
52.5°	145.1	142.6	141.4	137.8	136.5	132.7	132.7	129.1
55°	99.7	98.4	98.4	94.6	94.6	91.0	89.7	89.7
57.5°	62.7	60.3	61.5	59.0	57.8	54.1	54.1	52.9
60°	35.7	34.4	34.4	33.2	31.9	29.5	29.5	29.5
62.5°	23.3	22.1	22.1	20.9	20.9	19.7	19.7	18.4
65°	14.8	13.5	13.5	12.4	12.4	11.1	11.1	11.1
67.5°	11.1	9.8	9.8	9.8	9.8	9.8	8.6	8.6
70°	9.8	9.8	8.6	8.6	8.6	8.6	8.6	8.6
72.5°	8.6	8.6	8.6	8.6	7.3	7.3	7.3	7.3
75°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
77.5°	7.3	6.2	6.2	6.2	6.2	6.2	6.2	6.2
80°	6.2	6.2	6.2	6.2	6.2	6.2	4.9	4.9
82.5°	6.2	4.9	4.9	4.9	4.9	4.9	4.9	4.9
85°	4.9	3.7	3.7	3.7	3.7	3.7	3.7	3.7
87.5°	2.4	2.4	2.4	2.4	1.3	1.3	1.3	1.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)