

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192749

Luminaire Tested: **LDA6A70950D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192749
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26689)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70950D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6063.3 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 2.34 / 0.96 / 1.3
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192749

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192749

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	51	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	61	50	43	38	49	43	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	94620	94620	94620
5°	184993	89940	32809
10°	311378	77231	7276
15°	474191	58479	11952
20°	685225	47371	133257
25°	1019781	76631	38518
30°	1177871	26238	7609
35°	1178248	5869	4116
40°	963033	3278	2526
45°	729254	2140	1620
50°	484300	1458	1109
55°	77856	1242	879
60°	4868	1305	724
65°	1544	1686	856
70°	833	1907	1058
75°	530	2224	1398
80°	442	3315	2084
85°	881	6604	2390



TEST NUMBER: P1192749

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.2	3.0
10°-20°	770.3	12.7
20°-30°	1813.5	29.9
30°-40°	1910.7	31.5
40°-50°	1191.4	19.6
50°-60°	171.2	2.8
60°-70°	11.0	0.2
70°-80°	8.6	0.1
80°-90°	6.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2764.0	45.6
0°-40°	4674.7	77.1
0°-60°	6037.3	99.6
0°-90°	6063.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6063.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1726	1726	1726	1726	1726	
5°	3362	2721	1634	848	596	390
15°	8355	4729	1030	179	211	2488
25°	16859	5670	1267	917	637	7586
35°	17606	4153	88	81	62	10620
45°	9406	1149	28	30	21	7362
55°	815	21	13	14	9	1464
65°	12	9	13	10	7	17
75°	2	7	10	10	7	3
85°	1	7	10	8	4	1
90°	0	0	0	0	0	

TEST NUMBER: P1192749

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	2519.6	2502.7	2508.0	2468.5	2416.4	2439.8	2381.0	2382.3	2345.6	2253.0	2212.4
5°	3361.7	3359.0	3355.1	3283.2	3190.4	3200.9	3114.5	3081.9	2987.7	2824.2	2721.1
7.5°	4407.7	4409.0	4389.4	4214.3	4110.9	4104.4	3968.4	3870.3	3695.0	3437.5	3249.3
10°	5593.7	5630.4	5594.9	5325.5	5133.3	5136.0	4891.5	4703.3	4422.2	4046.7	3778.7
12.5°	6986.1	6991.4	6936.5	6582.2	6289.3	6266.9	5938.8	5579.3	5151.6	4661.4	4271.7
15°	8355.2	8391.8	8321.1	7884.4	7476.5	7415.0	6996.6	6521.9	5991.2	5265.4	4729.3
17.5°	9873.1	9815.7	9628.6	9003.7	8513.3	8423.2	7973.3	7352.3	6674.9	5797.7	5094.2
20°	11745.7	11765.2	11369.1	10435.5	9606.5	9254.8	8733.0	8053.1	7208.6	6188.6	5337.4
22.5°	14421.0	14314.9	13465.0	11954.9	10708.7	10239.4	9495.4	8557.8	7607.2	6485.4	5519.1
25°	16859.4	16580.8	15797.7	13720.0	11769.2	11188.6	10418.4	8988.0	7938.0	6705.0	5669.6
27.5°	18259.8	18135.5	17247.7	15151.8	12625.6	11808.3	10724.4	9304.5	8134.3	6813.6	5712.6
30°	18607.5	18629.8	17840.1	15626.4	12828.2	11894.8	10774.2	9295.3	8002.2	6620.0	5464.2
32.5°	18518.7	18398.4	17411.2	15102.2	12288.2	11438.3	10287.7	8879.5	7476.5	6043.3	4845.8
35°	17606.0	17429.6	16214.7	13738.4	11371.7	10545.2	9501.9	8198.2	6742.9	5308.7	4152.8
37.5°	15869.6	15665.6	14263.9	12101.2	10272.0	9572.5	8670.4	7439.8	6001.6	4623.4	3543.4
40°	13457.2	13203.6	12032.1	10532.2	9090.0	8601.0	7838.7	6574.3	5232.9	3975.0	2981.3
42.5°	11201.7	11080.1	10376.7	9090.0	8118.6	7646.5	6877.7	5701.0	4466.6	3312.1	2207.2
45°	9406.4	9325.4	8858.6	8041.4	7055.6	6613.5	5889.2	4741.2	3398.3	2230.7	1149.3
47.5°	8233.5	8027.0	7570.7	6712.9	5617.1	5066.7	4376.4	3123.7	1916.9	988.5	353.1
50°	5678.6	5698.3	5183.0	4237.8	3305.4	2839.9	2345.6	1437.0	634.1	215.8	61.5
52.5°	2990.3	2769.3	2407.1	1797.8	1251.2	954.6	696.9	287.8	115.0	43.3	32.8
55°	814.6	715.3	571.4	404.0	218.3	153.0	100.7	53.6	38.0	30.1	20.9
57.5°	79.7	75.8	69.3	56.3	48.5	44.4	40.6	32.8	26.2	18.2	13.0
60°	44.4	43.3	40.6	35.3	31.4	28.7	26.2	22.3	15.7	11.9	10.5
62.5°	24.9	23.5	22.3	19.6	17.1	15.7	15.7	13.0	10.5	9.2	9.2
65°	11.9	11.9	11.9	11.9	11.9	10.5	9.2	9.2	9.2	9.2	9.2
67.5°	9.2	9.2	9.2	7.8	7.8	7.8	7.8	7.8	7.8	6.6	7.8
70°	5.2	5.2	6.6	5.2	5.2	5.2	5.2	5.2	5.2	5.2	6.6
72.5°	2.5	3.8	3.8	3.8	3.8	3.8	3.8	3.8	5.2	5.2	6.6
75°	2.5	2.5	2.5	2.5	3.8	3.8	3.8	3.8	5.2	5.2	6.6
77.5°	2.5	2.5	2.5	2.5	2.5	2.5	3.8	3.8	5.2	5.2	6.6
80°	1.4	1.4	1.4	2.5	2.5	2.5	2.5	3.8	5.2	5.2	6.6
82.5°	1.4	1.4	1.4	1.4	2.5	2.5	2.5	3.8	5.2	5.2	6.6
85°	1.4	1.4	1.4	1.4	2.5	2.5	2.5	3.8	3.8	5.2	6.6
87.5°	0.0	0.0	1.4	1.4	2.5	2.5	2.5	3.8	3.8	5.2	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192749

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	2170.6	2106.4	2042.4	1978.4	1975.7	1937.8	1881.6	1807.0	1745.5	1693.3	1642.4
5°	2617.7	2485.6	2353.6	2221.5	2182.3	2114.3	1992.7	1855.5	1737.7	1634.4	1535.1
7.5°	3066.2	2844.0	2634.7	2428.1	2345.6	2242.4	2052.9	1854.1	1684.1	1532.4	1384.7
10°	3466.2	3143.4	2849.2	2558.9	2439.8	2305.2	2050.2	1797.8	1582.0	1387.4	1199.1
12.5°	3835.0	3385.2	3012.5	2646.4	2484.2	2320.9	2009.6	1708.9	1451.3	1218.7	1001.5
15°	4159.3	3607.6	3127.7	2685.7	2487.0	2290.8	1924.7	1586.1	1297.0	1030.4	795.0
17.5°	4390.8	3718.6	3165.4	2650.4	2418.9	2199.3	1799.2	1437.0	1125.8	847.3	619.7
20°	4531.9	3764.4	3145.9	2584.9	2339.3	2111.6	1706.3	1354.6	1052.5	812.0	657.7
22.5°	4624.8	3808.8	3153.8	2583.8	2337.9	2123.5	1745.5	1416.1	1170.2	1040.8	1022.4
25°	4724.1	3871.6	3211.2	2642.5	2413.7	2215.0	1848.9	1527.1	1321.8	1266.9	1274.9
27.5°	4718.8	3844.2	3156.4	2591.5	2350.9	2149.6	1720.7	1314.0	1122.0	967.6	911.4
30°	4437.9	3526.5	2782.5	2149.6	1865.9	1618.8	1053.8	685.0	473.3	414.5	355.6
32.5°	3780.1	2857.0	2080.3	1486.7	1167.7	872.1	414.5	219.6	186.9	156.8	142.5
35°	3143.4	2277.8	1555.9	898.4	567.5	351.7	149.1	98.1	92.9	87.7	87.7
37.5°	2598.1	1788.7	1005.6	379.3	207.9	126.8	72.0	65.3	62.8	61.5	61.5
40°	2032.0	1166.4	435.4	125.4	66.7	57.6	51.0	48.5	47.1	45.8	47.1
42.5°	1199.1	469.5	126.8	47.1	44.4	41.9	38.0	36.6	36.6	35.3	36.6
45°	408.0	121.6	41.9	33.9	31.4	31.4	28.7	28.7	28.7	27.6	30.1
47.5°	105.9	38.0	27.6	24.9	23.5	23.5	22.3	22.3	22.3	22.3	23.5
50°	36.6	24.9	19.6	18.2	17.1	18.2	17.1	17.1	17.1	17.1	18.2
52.5°	22.3	17.1	14.4	14.4	14.4	14.4	14.4	14.4	14.4	14.4	14.4
55°	14.4	13.0	11.9	11.9	11.9	11.9	11.9	13.0	13.0	13.0	13.0
57.5°	11.9	10.5	10.5	10.5	10.5	10.5	11.9	10.5	10.5	11.9	13.0
60°	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	11.9	11.9	13.0
62.5°	9.2	10.5	10.5	10.5	10.5	10.5	10.5	11.9	11.9	11.9	13.0
65°	9.2	9.2	9.2	10.5	10.5	10.5	11.9	11.9	11.9	13.0	13.0
67.5°	7.8	7.8	9.2	9.2	10.5	10.5	10.5	11.9	11.9	11.9	13.0
70°	7.8	7.8	7.8	9.2	9.2	9.2	9.2	10.5	10.5	11.9	11.9
72.5°	6.6	7.8	7.8	9.2	9.2	9.2	9.2	10.5	10.5	10.5	11.9
75°	6.6	7.8	7.8	9.2	9.2	9.2	9.2	9.2	10.5	10.5	11.9
77.5°	6.6	7.8	7.8	9.2	9.2	9.2	9.2	10.5	10.5	10.5	11.9
80°	6.6	7.8	7.8	9.2	9.2	9.2	9.2	10.5	10.5	10.5	10.5
82.5°	6.6	7.8	7.8	9.2	9.2	9.2	9.2	10.5	10.5	10.5	10.5
85°	6.6	7.8	7.8	9.2	9.2	9.2	9.2	9.2	10.5	10.5	10.5
87.5°	6.6	7.8	7.8	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192749

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1571.6	1549.5	1471.0	1460.5	1447.5	1383.3	1357.3	1312.7	1250.1	1231.7	1209.5
5°	1418.7	1345.4	1230.3	1199.1	1165.0	1064.3	1002.9	929.6	848.5	804.1	762.2
7.5°	1223.9	1122.0	969.0	907.5	869.4	759.7	661.6	563.5	444.6	376.6	333.5
10°	1006.7	866.9	707.4	636.8	585.7	426.2	333.5	290.3	249.7	216.9	188.2
12.5°	788.4	630.2	449.8	368.8	328.2	272.1	221.0	167.3	149.1	147.8	142.5
15°	578.0	401.3	303.3	273.2	244.5	175.2	173.9	173.9	179.2	183.0	184.4
17.5°	426.2	353.1	277.3	258.9	272.1	282.5	300.8	328.2	350.4	413.2	400.1
20°	624.9	619.7	676.0	747.9	798.9	907.5	1044.8	1200.3	1362.4	1542.8	1680.2
22.5°	1072.1	1203.0	1305.0	1391.2	1437.0	1559.9	1668.4	1722.0	1753.4	1737.7	1715.5
25°	1310.2	1357.3	1325.9	1295.8	1299.7	1188.6	1107.6	1004.2	916.6	836.9	789.8
27.5°	783.2	716.5	622.4	557.0	543.9	469.5	414.5	356.9	339.9	287.8	265.4
30°	282.5	262.7	232.6	209.2	206.5	186.9	175.2	162.1	160.8	149.1	142.5
32.5°	128.1	128.1	117.7	120.2	117.7	113.8	112.4	108.6	108.6	104.5	102.0
35°	83.7	85.0	83.7	83.7	82.4	82.4	82.4	79.7	81.0	78.5	74.5
37.5°	61.5	62.8	60.1	61.5	61.5	61.5	61.5	60.1	58.8	56.3	54.9
40°	47.1	47.1	47.1	47.1	47.1	47.1	47.1	45.8	45.8	44.4	41.9
42.5°	36.6	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0	36.6	36.6
45°	30.1	31.4	30.1	31.4	31.4	31.4	30.1	30.1	30.1	28.7	27.6
47.5°	23.5	23.5	22.3	22.3	22.3	22.3	22.3	22.3	22.3	22.3	20.9
50°	18.2	18.2	18.2	18.2	18.2	18.2	19.6	18.2	18.2	18.2	18.2
52.5°	14.4	15.7	15.7	17.1	17.1	17.1	17.1	17.1	15.7	15.7	14.4
55°	13.0	14.4	14.4	15.7	15.7	15.7	15.7	14.4	14.4	14.4	13.0
57.5°	13.0	14.4	14.4	14.4	14.4	14.4	14.4	13.0	13.0	11.9	11.9
60°	13.0	13.0	13.0	14.4	14.4	13.0	13.0	11.9	11.9	10.5	10.5
62.5°	13.0	13.0	13.0	14.4	14.4	13.0	13.0	11.9	10.5	10.5	9.2
65°	13.0	14.4	13.0	14.4	14.4	13.0	13.0	11.9	10.5	10.5	9.2
67.5°	13.0	14.4	14.4	14.4	13.0	13.0	13.0	11.9	10.5	10.5	9.2
70°	11.9	13.0	13.0	13.0	13.0	13.0	11.9	11.9	10.5	10.5	9.2
72.5°	11.9	13.0	11.9	13.0	13.0	11.9	11.9	11.9	10.5	10.5	9.2
75°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	10.5	10.5	9.2	9.2
77.5°	11.9	11.9	11.9	11.9	11.9	11.9	10.5	10.5	10.5	9.2	9.2
80°	11.9	11.9	11.9	11.9	11.9	11.9	10.5	10.5	9.2	9.2	7.8
82.5°	10.5	11.9	11.9	11.9	11.9	11.9	10.5	10.5	9.2	9.2	7.8
85°	10.5	10.5	10.5	10.5	10.5	10.5	9.2	9.2	7.8	6.6	6.6
87.5°	9.2	10.5	9.2	9.2	9.2	9.2	7.8	6.6	5.2	5.2	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192749

CATALOG NUMBER: LDA6A70950D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0	1726.0
2.5°	1174.1	1141.5	1142.9	1148.1	1115.3	1098.2	1094.4	1077.3
5°	706.1	668.2	661.6	656.3	610.6	592.4	578.0	596.2
7.5°	303.3	288.9	286.4	282.5	261.6	251.1	245.9	251.1
10°	150.3	141.1	142.5	143.8	137.3	133.4	132.1	130.7
12.5°	149.1	147.8	149.1	149.1	150.3	147.8	149.1	149.1
15°	193.5	193.5	197.4	200.1	206.5	205.3	207.9	210.6
17.5°	482.5	457.6	470.8	470.8	529.6	477.3	521.8	481.2
20°	1895.9	1984.8	2075.1	2150.9	2228.1	2251.6	2297.4	2284.2
22.5°	1681.5	1692.0	1678.9	1664.5	1660.6	1664.5	1593.9	1604.3
25°	721.8	716.5	695.6	673.4	679.8	685.0	660.3	636.8
27.5°	247.1	240.7	234.0	228.8	226.3	222.2	214.4	209.2
30°	140.0	135.9	133.4	132.1	129.5	126.8	122.9	120.2
32.5°	100.7	98.1	96.7	95.4	92.9	90.2	86.3	85.0
35°	74.5	72.0	70.6	69.3	66.7	64.0	62.8	61.5
37.5°	54.9	52.3	52.3	52.3	48.5	45.8	44.4	43.3
40°	41.9	40.6	40.6	40.6	38.0	36.6	35.3	35.3
42.5°	36.6	35.3	35.3	35.3	32.8	31.4	31.4	30.1
45°	27.6	26.2	26.2	24.9	23.5	23.5	22.3	20.9
47.5°	20.9	19.6	19.6	19.6	18.2	17.1	17.1	15.7
50°	17.1	17.1	15.7	17.1	14.4	14.4	14.4	13.0
52.5°	14.4	14.4	13.0	13.0	11.9	11.9	11.9	10.5
55°	13.0	11.9	11.9	11.9	10.5	10.5	10.5	9.2
57.5°	10.5	10.5	9.2	9.2	7.8	7.8	7.8	7.8
60°	9.2	9.2	7.8	7.8	6.6	6.6	6.6	6.6
62.5°	9.2	7.8	7.8	7.8	6.6	6.6	6.6	6.6
65°	9.2	7.8	7.8	7.8	6.6	6.6	6.6	6.6
67.5°	9.2	7.8	7.8	7.8	6.6	6.6	6.6	6.6
70°	9.2	9.2	7.8	7.8	7.8	6.6	6.6	6.6
72.5°	9.2	9.2	7.8	7.8	7.8	7.8	6.6	6.6
75°	7.8	7.8	7.8	7.8	6.6	6.6	6.6	6.6
77.5°	7.8	7.8	7.8	7.8	6.6	6.6	6.6	6.6
80°	7.8	7.8	6.6	6.6	6.6	6.6	6.6	6.6
82.5°	7.8	6.6	6.6	6.6	6.6	5.2	5.2	5.2
85°	5.2	5.2	5.2	5.2	3.8	3.8	3.8	3.8
87.5°	3.8	2.5	2.5	2.5	1.4	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)