

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204983

Luminaire Tested: **LE_6B15D010 EC6B10209035 6LBCS1MMS**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204983
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209035 6LBCS1MMS
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE METALLIC SILVER TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1632.8 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204983

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBCS1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P204983

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBCS1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	105	101	98		100	98	95		97	94	92		93	91	90
2	102	95	89	84		99	93	88	83		90	85	81		86	83	79		83	80	78
3	94	85	77	72		92	83	76	71		80	74	70		77	73	69		75	71	67
4	87	76	68	62		84	74	67	61		72	66	61		70	64	60		68	63	59
5	80	68	60	54		78	67	59	54		65	58	53		63	57	53		61	56	52
6	74	62	54	48		72	61	53	47		59	52	47		58	51	47		56	51	46
7	69	56	48	42		67	56	48	42		54	47	42		53	46	42		51	46	41
8	64	52	44	38		63	51	43	38		50	43	38		48	42	38		47	42	37
9	60	48	40	35		59	47	40	34		46	39	34		45	39	34		44	38	34
10	57	44	36	31		55	43	36	31		43	36	31		42	35	31		41	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204983

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBCS1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.7	4.3
10°-20°	198.3	12.1
20°-30°	289.6	17.7
30°-40°	331.2	20.3
40°-50°	318.3	19.5
50°-60°	245.8	15.1
60°-70°	137.2	8.4
70°-80°	40.0	2.4
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	558.6	34.2
0°-40°	889.8	54.5
0°-60°	1453.9	89.0
0°-90°	1632.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1632.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	750	
5°	744	71
15°	703	198
25°	630	290
35°	530	331
45°	415	318
55°	276	246
65°	137	137
75°	35	40
85°	1	2
90°	0	



TEST NUMBER: P204983

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBCS1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	749.9
2.5°	749.9
5°	743.5
7.5°	740.4
10°	729.8
12.5°	717.1
15°	703.4
17.5°	689.6
20°	669.6
22.5°	653.8
25°	629.5
27.5°	605.1
30°	580.9
32.5°	556.6
35°	530.1
37.5°	503.8
40°	473.1
42.5°	445.6
45°	415.0
47.5°	380.2
50°	347.5
52.5°	311.5
55°	275.6
57.5°	238.6
60°	203.9
62.5°	169.0
65°	137.2
67.5°	107.8
70°	80.2
72.5°	56.0
75°	34.9
77.5°	18.0
80°	6.4
82.5°	2.1
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)