

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192757

Luminaire Tested: **LDA6A70950D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192757
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26684)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70950D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5389.8 lumens
Efficiency: N/A
Efficacy: 69.0 lumens/watt
Spacing Criteria (0/90/45): 2.21 / 1.07 / 1.54
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192757

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192757

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	61		
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54		
6	77	65	57	51	75	64	57	51	62	56	51	61	55	50	59	54	50	48		
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35		
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	85026	85026	85026
5°	135070	83981	54545
10°	202663	80582	36611
15°	290416	76374	27094
20°	383353	71412	22577
25°	460133	69609	32984
30°	514149	69789	49830
35°	528605	62493	42530
40°	509376	49686	31638
45°	448930	36903	24336
50°	350095	27317	16835
55°	202478	19995	10877
60°	94620	13902	4868
65°	44259	7653	2037
70°	20532	3350	1475
75°	8599	2224	1652
80°	3757	2462	2084
85°	881	4151	3271



TEST NUMBER: P1192757

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.4	3.0
10°-20°	588.7	10.9
20°-30°	1165.5	21.6
30°-40°	1507.0	28.0
40°-50°	1238.3	23.0
50°-60°	572.4	10.6
60°-70°	130.7	2.4
70°-80°	21.4	0.4
80°-90°	5.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1914.6	35.5
0°-40°	3421.6	63.5
0°-60°	5232.3	97.1
0°-90°	5389.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5389.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1551	1551	1551	1551	1551	
5°	2454	2111	1526	1104	991	271
15°	5117	3422	1346	603	477	1495
25°	7607	4258	1151	565	545	3503
35°	7899	3897	934	620	636	4890
45°	5791	2631	476	316	314	4407
55°	2118	1024	209	135	114	1991
65°	341	209	59	22	16	391
75°	41	24	10	9	8	54
85°	1	4	7	7	5	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192757

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0
2.5°	1969.4	1939.3	1957.7	1966.8	1919.7	1930.2	1935.4	1898.8	1888.3	1868.8	1811.2
5°	2454.5	2419.2	2433.7	2433.7	2364.3	2368.3	2365.7	2296.3	2258.5	2208.6	2110.7
7.5°	3026.1	2990.8	2993.3	2980.3	2882.3	2875.7	2833.8	2748.8	2674.3	2582.7	2436.3
10°	3640.7	3619.8	3606.6	3574.1	3444.6	3422.2	3360.8	3226.2	3103.3	2963.3	2756.6
12.5°	4362.6	4320.8	4282.7	4230.4	4061.7	4020.0	3933.6	3738.8	3558.4	3362.1	3088.8
15°	5117.1	5084.5	5023.0	4940.6	4724.8	4658.2	4545.6	4284.1	4059.2	3772.8	3422.2
17.5°	5897.8	5837.6	5747.5	5631.1	5370.9	5276.6	5136.7	4802.0	4503.8	4146.8	3723.2
20°	6571.2	6524.2	6400.1	6249.6	5951.4	5826.0	5661.1	5250.4	4885.6	4461.9	3963.8
22.5°	7155.8	7093.1	6940.1	6758.3	6424.9	6269.2	6083.5	5624.5	5179.9	4688.2	4140.2
25°	7607.1	7560.0	7378.1	7166.3	6800.1	6619.7	6414.4	5893.9	5400.9	4860.8	4258.0
27.5°	7974.5	7894.7	7692.0	7452.7	7057.8	6847.3	6630.2	6060.0	5526.4	4948.4	4302.4
30°	8122.3	8039.8	7825.4	7560.0	7141.5	6910.0	6686.5	6078.3	5517.3	4918.4	4248.8
32.5°	8094.7	8002.0	7773.1	7492.0	7064.3	6817.2	6590.9	5959.3	5386.6	4782.4	4103.6
35°	7898.7	7821.5	7584.8	7290.6	6864.2	6604.0	6367.3	5742.2	5168.1	4571.8	3897.1
37.5°	7603.0	7493.3	7272.2	6976.7	6525.5	6283.6	6049.5	5432.3	4871.3	4280.2	3639.4
40°	7117.9	6985.9	6764.8	6507.3	6078.3	5837.6	5624.5	5047.8	4496.0	3944.0	3332.1
42.5°	6507.3	6403.9	6198.6	5933.2	5539.6	5309.4	5118.5	4563.9	4074.9	3563.6	2993.3
45°	5790.6	5691.2	5516.0	5276.6	4921.1	4721.0	4545.6	4052.6	3611.9	3145.2	2631.2
47.5°	5015.1	4917.0	4764.0	4553.4	4235.6	4063.1	3910.1	3506.0	3090.2	2682.2	2231.0
50°	4105.0	3970.2	3886.6	3710.0	3444.6	3298.2	3180.4	2818.1	2510.8	2182.6	1807.3
52.5°	3063.9	3020.9	2900.5	2776.4	2589.3	2480.7	2403.5	2170.8	1915.9	1677.7	1391.4
55°	2118.5	2079.3	2006.1	1930.2	1804.6	1749.7	1692.2	1551.0	1380.9	1218.8	1024.0
57.5°	1339.1	1367.9	1320.8	1277.6	1201.7	1182.2	1137.8	1055.4	950.7	848.6	727.1
60°	863.0	878.7	848.6	823.9	782.0	766.3	745.4	695.7	632.8	574.1	491.7
62.5°	546.6	554.5	537.5	523.1	499.5	493.1	478.5	449.8	412.0	376.6	324.4
65°	341.2	347.9	336.0	326.9	312.5	313.9	300.8	283.8	261.6	239.3	209.2
67.5°	210.6	214.4	206.6	201.4	192.2	192.2	184.4	173.9	159.5	146.4	126.8
70°	128.1	129.5	124.3	121.6	115.1	113.8	109.9	102.0	92.9	83.7	72.0
72.5°	74.5	75.8	72.0	69.3	65.3	65.3	62.8	59.0	54.9	47.1	40.6
75°	40.6	41.9	39.2	38.0	35.3	36.6	33.9	32.8	28.7	26.2	23.5
77.5°	20.9	22.3	20.9	19.6	19.6	19.6	18.2	17.1	17.1	14.4	14.4
80°	11.9	11.9	11.9	11.9	11.9	10.5	10.5	10.5	10.5	10.5	9.2
82.5°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	5.2
85°	1.4	1.4	2.5	2.5	2.5	2.5	2.5	2.5	2.5	3.8	3.8
87.5°	0.0	0.0	1.4	1.4	1.4	1.4	1.4	2.5	2.5	2.5	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192757

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0
2.5°	1794.1	1793.0	1732.6	1706.6	1685.7	1653.0	1629.5	1604.5	1582.4	1541.8	1507.8
5°	2061.0	2024.3	1924.9	1862.2	1823.0	1770.6	1713.1	1655.7	1599.4	1526.1	1466.0
7.5°	2340.8	2262.3	2113.3	2008.8	1948.4	1875.3	1778.6	1688.2	1596.7	1496.0	1409.8
10°	2607.7	2479.5	2289.9	2130.3	2047.9	1953.7	1820.3	1694.8	1574.5	1447.6	1340.4
12.5°	2879.6	2696.5	2449.3	2242.8	2138.1	2021.8	1850.4	1694.8	1545.8	1399.3	1272.3
15°	3149.0	2907.1	2599.8	2343.4	2216.6	2077.9	1871.3	1685.7	1510.4	1345.7	1204.4
17.5°	3379.2	3079.6	2709.6	2412.8	2263.7	2106.7	1870.1	1658.2	1463.3	1285.5	1135.1
20°	3558.4	3203.9	2786.8	2448.1	2280.6	2109.3	1849.1	1617.6	1409.8	1224.1	1069.7
22.5°	3679.9	3284.9	2826.0	2454.5	2275.4	2095.0	1816.4	1577.2	1361.4	1175.6	1021.3
25°	3755.8	3325.5	2837.8	2445.5	2257.1	2070.2	1786.3	1541.8	1330.0	1150.8	1006.9
27.5°	3770.1	3313.9	2814.2	2407.6	2214.0	2025.6	1743.1	1507.8	1302.6	1136.4	1006.9
30°	3699.5	3237.8	2734.5	2322.5	2132.8	1948.4	1671.2	1446.3	1254.1	1102.5	984.8
32.5°	3564.8	3098.1	2602.4	2197.0	2012.6	1840.1	1573.2	1358.8	1173.0	1033.0	927.2
35°	3370.0	2911.0	2431.1	2038.8	1859.6	1698.7	1435.8	1239.8	1063.1	933.8	835.6
37.5°	3133.3	2686.0	2231.0	1858.3	1688.2	1538.0	1286.9	1102.5	939.0	817.2	729.7
40°	2845.6	2442.9	2006.1	1659.5	1497.3	1361.4	1129.9	952.0	797.7	694.3	614.6
42.5°	2544.9	2170.8	1766.8	1437.2	1293.2	1164.0	958.6	799.0	661.8	576.7	514.0
45°	2234.9	1868.8	1515.7	1222.7	1114.2	969.1	779.5	649.9	538.8	476.0	426.4
47.5°	1885.8	1575.8	1250.2	992.6	878.7	780.6	622.4	517.9	446.0	391.0	353.1
50°	1510.4	1263.2	990.0	770.3	676.1	601.4	485.2	413.2	358.3	320.3	291.6
52.5°	1161.3	966.4	745.4	565.0	506.1	449.8	377.9	328.2	289.1	260.2	239.3
55°	863.0	704.8	536.1	418.4	376.6	340.1	296.8	257.7	228.8	209.2	192.2
57.5°	608.1	491.7	376.6	303.5	281.1	257.7	225.0	198.7	179.2	163.5	150.5
60°	406.7	334.9	265.4	222.4	206.6	190.9	170.0	151.6	137.3	126.8	113.8
62.5°	273.4	225.0	185.7	159.5	149.1	138.6	124.3	111.1	100.7	90.2	79.7
65°	175.2	149.1	125.4	108.6	100.7	95.4	85.0	75.8	68.0	59.0	51.0
67.5°	107.2	92.9	78.5	68.0	64.0	60.1	53.7	47.1	41.9	35.3	30.1
70°	62.8	54.9	47.1	40.6	39.2	36.6	31.4	27.6	24.9	20.9	18.2
72.5°	36.6	32.8	27.6	24.9	23.5	20.9	19.6	17.1	14.4	13.0	11.9
75°	20.9	18.2	15.7	14.4	14.4	13.0	11.9	11.9	10.5	10.5	9.2
77.5°	13.0	11.9	10.5	10.5	10.5	9.2	9.2	9.2	9.2	7.8	7.8
80°	9.2	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8
82.5°	5.2	5.2	5.2	5.2	5.2	6.6	6.6	6.6	6.6	6.6	7.8
85°	3.8	5.2	5.2	5.2	5.2	5.2	6.6	6.6	6.6	6.6	6.6
87.5°	3.8	5.2	5.2	5.2	5.2	5.2	6.6	6.6	6.6	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192757

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0
2.5°	1488.1	1467.2	1403.2	1425.3	1384.9	1352.2	1349.5	1330.0	1295.9	1277.6	1268.5
5°	1420.2	1373.1	1294.6	1299.9	1252.8	1201.7	1174.4	1148.3	1103.6	1076.3	1057.9
7.5°	1336.5	1272.3	1179.7	1173.0	1123.4	1061.9	1022.6	985.9	937.7	902.4	880.0
10°	1248.8	1170.3	1061.9	1054.0	1001.6	935.0	890.6	848.6	799.0	763.8	740.1
12.5°	1167.8	1077.5	969.1	949.5	898.4	830.4	782.0	737.6	689.1	659.0	631.7
15°	1090.6	992.6	877.6	859.1	809.5	741.4	688.0	648.5	602.8	574.1	549.3
17.5°	1013.5	912.8	799.0	778.1	731.0	665.6	618.5	576.7	534.8	507.4	485.2
20°	946.8	846.1	734.9	714.0	670.9	608.1	565.0	525.6	487.9	461.7	443.2
22.5°	903.6	805.6	704.8	686.6	646.0	589.8	549.3	515.2	482.6	457.8	443.2
25°	901.1	816.1	725.7	715.3	681.3	634.2	605.5	584.6	565.0	545.3	540.0
27.5°	916.8	847.3	771.5	769.0	741.4	710.0	697.0	690.5	680.0	673.4	682.7
30°	907.6	848.6	784.7	784.7	763.8	741.4	734.9	732.4	725.7	727.1	737.6
32.5°	859.1	805.6	744.1	745.4	732.4	707.5	703.7	702.3	694.3	693.2	701.0
35°	771.5	721.9	670.9	672.3	661.8	638.1	632.8	630.3	619.8	614.6	619.8
37.5°	670.9	630.3	581.9	581.9	571.4	553.2	548.0	542.7	536.1	530.9	530.9
40°	567.5	534.8	495.6	494.2	486.5	468.2	463.0	459.0	452.5	443.2	446.0
42.5°	479.9	449.8	418.4	415.9	410.7	395.0	389.7	384.5	377.9	370.1	370.1
45°	398.8	379.3	351.7	350.6	345.3	332.2	328.2	321.7	316.5	308.7	308.7
47.5°	332.2	316.5	294.3	293.0	289.1	277.3	273.4	268.1	262.9	257.7	257.7
50°	278.6	262.9	244.5	243.2	240.7	231.5	226.3	222.4	218.3	214.4	212.0
52.5°	228.8	215.8	201.4	200.1	197.4	188.2	184.4	181.7	177.8	171.4	171.4
55°	184.4	173.9	160.9	159.5	156.8	149.1	145.2	140.0	134.8	128.1	126.8
57.5°	143.8	134.8	124.3	122.9	119.1	112.4	105.9	100.7	95.4	90.2	87.7
60°	108.6	98.1	89.0	86.3	83.7	74.5	69.3	64.0	59.0	54.9	52.3
62.5°	73.3	66.7	56.3	54.9	52.3	47.1	40.6	38.0	35.3	32.8	31.4
65°	45.8	40.6	35.3	33.9	31.4	27.6	24.9	23.5	22.3	20.9	19.6
67.5°	27.6	24.9	20.9	20.9	19.6	18.2	15.7	15.7	14.4	14.4	13.0
70°	17.1	15.7	14.4	13.0	13.0	13.0	11.9	11.9	11.9	11.9	11.9
72.5°	11.9	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5	10.5
75°	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2	9.2
77.5°	9.2	9.2	7.8	9.2	9.2	9.2	9.2	7.8	9.2	7.8	7.8
80°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8	7.8
82.5°	7.8	7.8	7.8	7.8	7.8	7.8	7.8	6.6	6.6	6.6	6.6
85°	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	6.6	5.2
87.5°	6.6	6.6	6.6	6.6	6.6	5.2	5.2	5.2	5.2	3.8	3.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192757

CATALOG NUMBER: LDA6A70950D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0	1551.0
2.5°	1271.2	1234.5	1248.8	1227.9	1221.4	1216.2	1208.4	1233.1
5°	1050.1	1010.8	1020.0	999.1	990.0	980.7	971.6	991.2
7.5°	867.0	829.1	832.9	814.7	805.6	795.2	785.8	801.5
10°	724.4	689.1	690.5	673.4	664.2	653.8	646.0	657.7
12.5°	616.0	583.2	583.2	570.2	562.3	550.5	544.0	553.2
15°	533.6	504.7	504.7	491.7	485.2	474.7	468.2	477.4
17.5°	470.8	444.6	444.6	435.4	428.9	419.7	414.5	422.3
20°	428.9	406.7	408.0	398.8	393.6	383.1	380.6	387.0
22.5°	432.7	412.0	414.5	408.0	402.7	395.0	392.3	401.5
25°	541.3	525.6	534.8	534.8	537.5	525.6	530.9	545.3
27.5°	695.7	688.0	702.3	697.0	707.5	707.5	712.7	731.0
30°	751.9	745.4	761.1	759.8	770.3	767.6	770.3	787.2
32.5°	711.4	704.8	718.0	716.7	724.4	718.0	719.2	733.7
35°	625.1	618.5	627.6	626.5	631.7	623.8	627.6	635.5
37.5°	533.6	527.0	532.3	530.9	532.3	523.1	528.3	532.3
40°	448.4	440.8	448.4	443.2	444.6	435.4	436.8	442.1
42.5°	375.3	366.1	372.6	372.6	372.6	366.1	367.4	372.6
45°	312.5	306.0	309.8	308.7	309.8	304.6	308.7	313.9
47.5°	258.9	253.7	256.4	255.0	255.0	249.7	251.1	251.1
50°	213.1	207.9	209.2	207.9	203.9	197.4	196.2	197.4
52.5°	168.7	162.1	162.1	159.5	156.8	151.6	151.6	153.0
55°	124.3	119.1	119.1	117.7	115.1	111.1	111.1	113.8
57.5°	83.7	79.7	81.0	79.7	79.7	74.5	77.2	77.2
60°	51.0	48.5	48.5	47.1	44.4	43.3	41.9	44.4
62.5°	30.1	28.7	28.7	27.6	27.6	26.2	26.2	26.2
65°	19.6	18.2	18.2	17.1	17.1	15.7	14.4	15.7
67.5°	13.0	11.9	11.9	11.9	11.9	10.5	10.5	10.5
70°	11.9	10.5	10.5	10.5	10.5	9.2	9.2	9.2
72.5°	10.5	9.2	10.5	9.2	9.2	9.2	9.2	9.2
75°	9.2	9.2	9.2	7.8	7.8	7.8	7.8	7.8
77.5°	7.8	7.8	7.8	7.8	7.8	6.6	6.6	6.6
80°	7.8	6.6	6.6	6.6	6.6	6.6	6.6	6.6
82.5°	6.6	6.6	6.6	6.6	6.6	5.2	5.2	5.2
85°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
87.5°	3.8	3.8	3.8	3.8	3.8	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)