

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192758

Luminaire Tested: **LDA6A70950D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192758
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70950D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7563.0 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192758

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192758

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	103	110	107	104	102		103	100	98		99	97	95		95	94	93
2	105	99	94	90	103	97	93	89		94	90	87		91	88	85		88	85	83
3	98	90	84	79	96	88	83	78		86	81	77		83	79	76		81	77	74
4	91	82	75	70	89	80	74	69		78	73	68		76	71	67		74	70	67
5	85	74	67	62	83	73	66	61		71	65	61		70	64	60		68	63	60
6	79	68	60	55	77	67	60	55		65	59	54		64	58	54		62	57	54
7	74	62	55	49	72	61	54	49		60	53	49		59	53	49		57	52	48
8	69	57	49	44	67	56	49	44		55	49	44		54	48	44		53	47	44
9	64	52	45	40	63	52	45	40		51	44	40		50	44	40		49	43	39
10	60	48	41	36	59	48	41	36		47	41	36		46	40	36		45	40	36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	77702	77702	77702
5°	213278	71593	29215
10°	467365	58599	11139
15°	713903	44597	13065
20°	827122	33183	20296
25°	902278	27292	32742
30°	1007573	24744	33436
35°	1025154	16978	22928
40°	1043154	8044	11600
45°	1044860	3357	5063
50°	883331	1458	1552
55°	284434	1004	239
60°	56487	1151	0
65°	5759	1362	0
70°	609	1907	0
75°	0	2521	0
80°	0	4104	442
85°	0	8177	881

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192758

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	192.4	2.5
10°-20°	995.1	13.2
20°-30°	1905.4	25.2
30°-40°	2244.8	29.7
40°-50°	1763.2	23.3
50°-60°	429.7	5.7
60°-70°	18.4	0.2
70°-80°	7.0	0.1
80°-90°	6.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3092.9	40.9
0°-40°	5337.7	70.6
0°-60°	7530.7	99.6
0°-90°	7563.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7563.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1417	1417	1417	1417	1417	
5°	3876	2805	1301	681	531	512
15°	12579	6461	786	225	230	3512
25°	14917	7856	451	472	541	6953
35°	15318	4966	254	327	343	9605
45°	13477	1535	43	60	65	10126
55°	2976	56	10	7	2	3542
65°	44	7	10	7	0	118
75°	0	7	12	8	0	0
85°	0	8	13	8	1	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192758

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4
2.5°	2429.5	2424.3	2388.9	2421.6	2322.3	2318.3	2273.9	2254.3	2196.7	2141.8	2063.4
5°	3875.7	3790.7	3721.3	3724.0	3533.1	3497.7	3398.3	3297.7	3143.4	2999.7	2804.8
7.5°	5907.6	5806.9	5660.5	5599.0	5234.2	5127.0	4921.8	4653.7	4317.6	3982.9	3622.0
10°	8395.9	8411.6	8222.0	8046.9	7495.1	7278.0	6946.0	6417.5	5780.7	5152.0	4512.5
12.5°	10899.9	10889.5	10663.3	10397.9	9718.0	9412.0	8970.0	8311.0	7467.5	6492.2	5491.8
15°	12578.9	12653.4	12558.0	12346.3	11765.5	11415.1	10917.0	10022.6	8994.9	7810.2	6460.8
17.5°	13632.8	13703.4	13669.4	13503.5	12990.7	12616.8	12201.1	11468.8	10280.2	8790.9	7224.4
20°	14178.0	14289.2	14273.6	14093.1	13706.1	13396.2	12937.3	12258.6	11229.6	9472.1	7718.7
22.5°	14541.6	14626.6	14650.2	14446.2	14046.0	13751.8	13415.8	12728.0	11760.3	9888.0	7914.8
25°	14916.8	15067.3	14919.5	14668.5	14300.9	14018.7	13660.3	13001.2	12014.1	10057.8	7856.0
27.5°	15377.1	15449.1	15114.4	14885.5	14477.6	14171.7	13791.0	13159.4	12058.5	9921.9	7519.8
30°	15917.2	15619.1	15385.0	14931.3	14468.4	14170.3	13783.2	13060.2	11824.5	9470.9	6868.8
32.5°	15828.3	15555.0	15289.5	14809.6	14352.0	14056.4	13625.0	12729.2	11271.3	8716.2	5970.4
35°	15318.4	15377.1	15090.7	14693.2	14175.5	13870.9	13400.1	12258.6	10332.6	7675.5	4966.2
37.5°	14888.1	15017.6	14830.5	14463.1	13937.5	13525.6	12890.2	11502.8	9107.3	6354.9	4014.3
40°	14576.8	14618.8	14518.1	14106.1	13474.6	12879.7	12144.8	10145.5	7619.4	4988.5	3168.4
42.5°	14094.5	14205.6	14027.7	13577.9	12620.8	11947.4	10883.1	8577.8	5918.0	3810.4	2385.0
45°	13477.3	13583.1	13363.5	12615.6	11284.4	10297.1	8998.7	6688.2	4377.7	2808.6	1535.1
47.5°	12470.3	12535.7	12110.8	11076.6	9141.3	8211.5	6880.5	4662.7	2820.5	1570.4	746.7
50°	10357.4	10326.0	9450.0	8177.6	6114.3	5138.7	4095.4	2527.5	1266.9	744.0	466.8
52.5°	6675.2	6603.3	5736.3	4579.1	3096.4	2362.9	1775.7	1090.5	660.3	415.8	184.4
55°	2976.0	2948.6	2413.8	1875.0	1266.9	1090.5	832.9	534.8	351.7	145.2	56.3
57.5°	1103.6	1078.7	950.7	797.7	611.9	508.7	404.0	256.4	90.2	48.5	30.1
60°	515.2	513.9	452.4	372.6	258.9	196.2	113.8	60.1	38.0	26.2	17.1
62.5°	164.8	160.8	112.4	82.4	58.8	51.0	40.6	30.1	19.6	14.4	10.5
65°	44.4	44.4	40.6	33.9	27.6	23.5	19.6	14.4	9.2	7.8	6.6
67.5°	17.1	17.1	15.7	14.4	10.5	9.2	7.8	6.6	5.2	6.6	6.6
70°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	5.2	5.2	6.6
72.5°	0.0	0.0	1.4	1.4	2.5	2.5	3.8	3.8	5.2	6.6	6.6
75°	0.0	0.0	1.4	1.4	2.5	2.5	3.8	3.8	5.2	6.6	6.6
77.5°	0.0	0.0	1.4	1.4	2.5	2.5	3.8	3.8	5.2	6.6	6.6
80°	0.0	0.0	1.4	1.4	2.5	2.5	3.8	3.8	5.2	6.6	6.6
82.5°	0.0	0.0	1.4	2.5	2.5	2.5	3.8	5.2	5.2	6.6	7.8
85°	0.0	0.0	1.4	2.5	2.5	3.8	3.8	5.2	5.2	6.6	7.8
87.5°	0.0	0.0	1.4	2.5	2.5	3.8	3.8	5.2	5.2	6.6	7.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192758

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4
2.5°	2005.8	1919.6	1800.6	1731.2	1714.2	1677.6	1613.7	1518.1	1439.7	1363.9	1319.3
5°	2639.9	2436.0	2207.2	2046.4	1980.9	1893.4	1737.7	1577.0	1429.3	1301.0	1200.5
7.5°	3312.1	2976.0	2606.0	2307.9	2200.6	2062.1	1808.4	1569.0	1366.5	1188.6	1053.8
10°	3980.2	3439.0	2936.9	2505.4	2330.1	2141.8	1807.1	1497.1	1259.2	1052.7	903.6
12.5°	4648.4	3870.5	3180.0	2624.2	2396.8	2158.8	1753.4	1387.4	1123.3	912.7	770.2
15°	5265.6	4214.3	3344.7	2664.8	2390.2	2109.1	1644.9	1253.9	980.7	785.8	653.8
17.5°	5725.9	4394.7	3382.8	2603.3	2286.9	1975.7	1478.9	1097.1	844.7	673.4	538.7
20°	5952.1	4423.4	3292.4	2428.2	2109.1	1786.2	1297.2	946.6	728.3	568.8	455.1
22.5°	5952.1	4287.5	3096.4	2208.5	1886.9	1567.9	1122.0	822.5	636.8	495.6	400.2
25°	5725.9	4016.9	2833.5	1954.9	1642.4	1352.1	970.2	729.7	566.2	451.2	371.3
27.5°	5286.5	3643.0	2496.1	1672.4	1401.7	1159.9	849.9	644.7	512.5	406.6	408.0
30°	4682.5	3184.1	2109.1	1374.2	1154.7	953.3	715.3	540.0	410.5	390.9	402.7
32.5°	3984.2	2634.7	1671.1	1065.7	894.4	750.6	543.9	381.8	326.9	329.5	342.6
35°	3267.6	2073.8	1257.9	789.8	665.5	543.9	356.9	251.1	248.4	253.7	262.7
37.5°	2579.8	1552.2	910.1	578.0	447.2	334.7	192.2	172.5	172.5	177.8	183.0
40°	1932.6	1100.9	626.3	342.6	216.9	153.0	121.6	112.4	111.1	112.4	119.1
42.5°	1327.2	696.9	372.6	137.3	104.5	89.0	77.2	70.6	69.3	70.6	74.5
45°	745.4	428.9	145.2	73.3	62.8	56.3	48.5	44.4	43.3	43.3	45.8
47.5°	466.8	170.0	65.3	45.8	39.2	36.6	31.4	28.7	27.6	27.6	28.7
50°	179.2	66.7	40.6	30.1	26.2	23.5	20.9	18.2	17.1	17.1	18.2
52.5°	61.5	39.2	26.2	19.6	17.1	15.7	13.0	11.9	11.9	11.9	11.9
55°	33.9	23.5	15.7	11.9	10.5	10.5	10.5	10.5	10.5	10.5	10.5
57.5°	20.9	14.4	10.5	9.2	9.2	9.2	9.2	9.2	9.2	10.5	10.5
60°	11.9	9.2	7.8	7.8	7.8	7.8	9.2	9.2	9.2	10.5	10.5
62.5°	7.8	7.8	7.8	7.8	7.8	7.8	9.2	9.2	10.5	10.5	10.5
65°	6.6	6.6	6.6	7.8	7.8	7.8	9.2	9.2	10.5	10.5	10.5
67.5°	6.6	6.6	7.8	7.8	7.8	9.2	9.2	10.5	10.5	10.5	10.5
70°	6.6	7.8	7.8	9.2	9.2	9.2	10.5	10.5	10.5	11.9	11.9
72.5°	6.6	7.8	7.8	9.2	9.2	9.2	10.5	10.5	11.9	11.9	11.9
75°	7.8	7.8	7.8	9.2	9.2	9.2	10.5	11.9	11.9	11.9	11.9
77.5°	7.8	7.8	9.2	9.2	9.2	10.5	10.5	11.9	11.9	11.9	11.9
80°	7.8	7.8	9.2	9.2	10.5	10.5	11.9	11.9	11.9	13.0	13.0
82.5°	7.8	7.8	9.2	10.5	10.5	10.5	11.9	11.9	13.0	13.0	13.0
85°	7.8	9.2	9.2	10.5	10.5	10.5	11.9	11.9	13.0	13.0	13.0
87.5°	7.8	9.2	9.2	10.5	10.5	10.5	11.9	11.9	13.0	13.0	13.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192758

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4
2.5°	1260.6	1205.7	1150.7	1110.1	1090.5	1070.9	1027.7	971.5	948.0	914.1	894.4
5°	1098.4	1005.6	932.3	884.0	855.1	817.2	767.5	712.6	681.2	645.9	622.4
7.5°	930.9	822.5	751.9	707.4	678.6	631.6	568.8	503.4	465.5	426.2	398.8
10°	784.6	681.2	601.4	550.5	513.9	459.0	396.1	350.4	317.8	283.7	256.4
12.5°	655.2	543.9	459.0	415.8	390.9	338.7	286.4	235.4	215.8	209.2	209.2
15°	530.9	430.2	358.3	321.7	295.5	239.3	228.8	226.3	225.0	223.6	226.3
17.5°	432.7	347.9	272.1	253.7	251.1	249.7	251.1	251.1	252.4	256.4	262.7
20°	363.6	285.1	279.8	281.1	281.1	286.4	293.0	298.2	303.5	309.8	321.7
22.5°	323.0	321.7	330.8	332.2	338.7	346.5	358.3	366.1	379.3	385.7	402.7
25°	372.6	381.8	398.8	404.0	414.5	427.5	446.0	456.2	472.0	479.9	499.5
27.5°	422.3	436.7	457.6	464.2	473.3	494.2	507.3	516.6	524.3	529.6	541.3
30°	418.4	431.5	452.4	453.8	466.8	481.2	489.0	496.9	502.2	500.9	507.3
32.5°	354.4	366.1	385.7	385.7	400.2	411.8	415.8	422.3	422.3	422.3	425.0
35°	272.1	279.8	293.0	296.8	308.6	316.5	319.0	326.9	326.9	324.3	324.3
37.5°	188.2	198.7	207.9	210.6	218.3	223.6	230.2	231.5	228.8	230.2	230.2
40°	122.9	129.5	135.9	137.3	143.8	147.8	154.3	154.3	155.5	154.3	156.8
42.5°	75.8	81.0	85.0	87.7	90.2	92.9	96.7	98.1	99.4	98.1	100.7
45°	47.1	49.6	52.3	53.6	54.9	56.3	60.1	60.1	60.1	60.1	61.5
47.5°	28.7	30.1	31.4	31.4	32.8	33.9	35.3	35.3	35.3	35.3	36.6
50°	17.1	18.2	18.2	18.2	19.6	19.6	20.9	20.9	20.9	19.6	20.9
52.5°	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	11.9	10.5	11.9
55°	10.5	10.5	9.2	9.2	9.2	9.2	9.2	7.8	6.6	6.6	5.2
57.5°	9.2	9.2	9.2	9.2	9.2	7.8	7.8	6.6	6.6	5.2	3.8
60°	9.2	9.2	9.2	9.2	9.2	7.8	7.8	6.6	5.2	5.2	3.8
62.5°	10.5	9.2	9.2	9.2	9.2	7.8	7.8	6.6	5.2	5.2	3.8
65°	10.5	10.5	9.2	9.2	9.2	7.8	7.8	6.6	6.6	5.2	3.8
67.5°	10.5	10.5	10.5	9.2	10.5	9.2	7.8	7.8	6.6	5.2	5.2
70°	11.9	10.5	10.5	10.5	10.5	9.2	9.2	7.8	6.6	5.2	5.2
72.5°	11.9	11.9	10.5	10.5	10.5	9.2	9.2	7.8	6.6	6.6	5.2
75°	11.9	11.9	10.5	10.5	10.5	9.2	9.2	7.8	7.8	6.6	5.2
77.5°	11.9	11.9	11.9	10.5	10.5	10.5	9.2	9.2	7.8	6.6	5.2
80°	11.9	11.9	11.9	11.9	11.9	10.5	10.5	9.2	7.8	6.6	5.2
82.5°	13.0	11.9	11.9	11.9	11.9	10.5	10.5	9.2	7.8	6.6	6.6
85°	13.0	13.0	11.9	11.9	11.9	10.5	10.5	9.2	7.8	7.8	6.6
87.5°	13.0	11.9	11.9	11.9	11.9	10.5	10.5	9.2	7.8	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192758

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4	1417.4
2.5°	874.7	864.2	864.2	846.0	843.4	829.0	840.7	832.9
5°	596.2	579.2	574.0	555.7	549.1	532.3	537.5	530.9
7.5°	375.2	358.3	353.1	339.9	332.2	319.0	320.3	316.5
10°	228.8	213.1	209.2	205.3	201.4	200.1	201.4	200.1
12.5°	207.9	206.5	203.9	205.3	202.6	203.9	205.3	203.9
15°	226.3	228.8	226.3	227.4	226.3	228.8	230.2	230.2
17.5°	265.4	270.7	268.0	272.1	270.7	277.3	277.3	277.3
20°	325.5	334.7	332.2	337.4	337.4	345.2	345.2	347.9
22.5°	409.3	421.0	419.7	431.5	428.9	438.0	438.0	440.8
25°	509.9	521.8	523.0	530.9	529.6	538.7	538.7	541.3
27.5°	551.8	558.3	557.0	561.0	562.3	567.5	571.4	568.8
30°	517.7	523.0	521.8	524.3	524.3	528.2	532.3	528.2
32.5°	435.4	439.4	439.4	444.6	440.8	441.9	448.4	444.6
35°	333.5	336.0	333.5	336.0	337.4	337.4	343.9	342.6
37.5°	238.0	239.3	239.3	243.2	239.3	239.3	245.9	247.2
40°	159.5	160.8	159.5	164.8	162.1	162.1	166.0	162.1
42.5°	102.0	103.4	102.0	105.9	103.4	105.9	107.2	108.6
45°	62.8	62.8	61.5	64.0	62.8	64.0	65.3	65.3
47.5°	36.6	36.6	35.3	38.0	36.6	36.6	36.6	38.0
50°	19.6	19.6	19.6	20.9	19.6	19.6	19.6	18.2
52.5°	10.5	10.5	9.2	10.5	9.2	9.2	9.2	9.2
55°	5.2	3.8	3.8	3.8	2.5	2.5	2.5	2.5
57.5°	3.8	2.5	2.5	1.4	1.4	1.4	0.0	0.0
60°	2.5	2.5	1.4	1.4	0.0	0.0	0.0	0.0
62.5°	2.5	2.5	1.4	1.4	0.0	0.0	0.0	0.0
65°	2.5	2.5	1.4	1.4	0.0	0.0	0.0	0.0
67.5°	3.8	2.5	2.5	1.4	1.4	0.0	0.0	0.0
70°	3.8	2.5	2.5	1.4	1.4	0.0	0.0	0.0
72.5°	3.8	2.5	2.5	2.5	1.4	1.4	0.0	0.0
75°	3.8	3.8	2.5	2.5	1.4	1.4	0.0	0.0
77.5°	5.2	3.8	2.5	2.5	1.4	1.4	0.0	0.0
80°	5.2	3.8	2.5	2.5	2.5	1.4	1.4	1.4
82.5°	5.2	3.8	3.8	2.5	2.5	1.4	1.4	1.4
85°	5.2	3.8	3.8	2.5	2.5	1.4	1.4	1.4
87.5°	5.2	3.8	3.8	2.5	2.5	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)