

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192760

Luminaire Tested: **LDA6A70950D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192760
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A70950D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7028.2 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192760

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192760

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	103	110	107	104	102		103	100	98			99	97	95			95
2	105	99	94	90	103	97	93	89		94	90	87			91	88	85			88
3	98	90	84	79	96	88	83	78		86	81	77			83	79	76			81
4	91	82	75	70	89	80	74	69		78	73	68			76	71	67			74
5	85	74	67	62	83	73	67	61		71	65	61			70	64	60			68
6	79	68	60	55	77	67	60	55		65	59	54			64	58	54			62
7	74	62	55	49	72	61	54	49		60	54	49			59	53	49			57
8	69	57	50	44	67	56	49	44		55	49	44			54	48	44			53
9	64	52	45	40	63	52	45	40		51	44	40			50	44	40			49
10	60	48	41	37	59	48	41	36		47	41	36			46	40	36			45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	75060	75060	75060
5°	199180	69579	26623
10°	434784	56267	7932
15°	656281	41113	6901
20°	763393	28224	10833
25°	841899	30449	72143
30°	931472	22928	22434
35°	945308	11725	8392
40°	967048	4773	4029
45°	975171	2946	2434
50°	821474	2004	1552
55°	271331	1376	879
60°	53340	1305	570
65°	6291	1686	675
70°	1683	1907	833
75°	297	2521	1398
80°	0	4104	2084
85°	0	8177	3271

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192760

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.2	2.6
10°-20°	920.0	13.1
20°-30°	1816.0	25.8
30°-40°	2048.4	29.1
40°-50°	1626.2	23.1
50°-60°	397.6	5.7
60°-70°	21.3	0.3
70°-80°	9.1	0.1
80°-90°	7.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2918.2	41.5
0°-40°	4966.6	70.7
0°-60°	6990.4	99.5
0°-90°	7028.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7028.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1369	1369	1369	1369	1369	
5°	3620	2712	1264	636	484	478
15°	11564	6146	724	142	122	3244
25°	13919	7450	503	912	1193	6447
35°	14125	4742	175	139	125	8883
45°	12578	1478	38	39	31	9427
55°	2839	64	14	14	9	3330
65°	48	12	13	10	5	118
75°	1	7	12	10	7	3
85°	0	7	13	9	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192760

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	2376.0	2330.2	2351.2	2318.5	2225.6	2196.9	2220.3	2185.0	2079.2	2038.6	1996.8
5°	3619.5	3579.0	3592.2	3517.5	3343.6	3283.5	3279.6	3172.3	2957.9	2837.6	2712.0
7.5°	5488.3	5432.0	5416.3	5237.1	4902.4	4776.8	4715.4	4451.3	4047.3	3760.8	3479.7
10°	7810.6	7865.5	7809.3	7519.0	6993.3	6757.9	6608.8	6109.4	5381.1	4835.7	4310.0
12.5°	10139.5	10173.5	10067.6	9706.7	9038.5	8756.1	8536.3	7896.9	6937.1	6011.2	5226.7
15°	11563.6	11724.4	11625.0	11372.7	10854.8	10512.2	10314.8	9524.8	8316.7	7299.2	6146.0
17.5°	12578.4	12727.3	12645.0	12438.4	11853.8	11577.9	11449.9	10799.9	9484.4	8191.0	6833.7
20°	13085.6	13267.5	13192.8	12958.8	12529.9	12299.8	12144.2	11510.0	10323.9	8854.1	7292.7
22.5°	13429.5	13631.0	13549.8	13336.6	12900.1	12631.8	12558.7	11958.4	10763.3	9251.6	7487.6
25°	13918.6	14087.3	13858.5	13595.7	13164.1	12881.6	12837.2	12224.0	10973.9	9401.9	7449.7
27.5°	14269.1	14469.2	14080.9	13814.0	13320.9	13024.1	12966.7	12390.0	10993.4	9283.0	7142.4
30°	14715.0	14585.6	14244.3	13857.2	13331.4	13015.0	12941.8	12293.1	10797.2	8845.0	6541.0
32.5°	14538.5	14507.1	14165.8	13710.7	13220.4	12901.2	12803.2	11995.2	10258.6	8089.0	5689.5
35°	14125.3	14224.6	13939.5	13657.1	13047.7	12715.7	12579.5	11555.8	9446.5	7116.2	4741.6
37.5°	13883.3	13946.1	13765.6	13420.5	12816.2	12379.6	12121.9	10816.8	8383.3	5889.6	3827.5
40°	13513.3	13672.8	13498.8	13102.6	12405.6	11806.8	11358.2	9481.8	6982.9	4643.5	2993.2
42.5°	13107.8	13250.4	13084.4	12609.8	11625.0	10822.0	10076.7	7912.6	5467.3	3547.8	2245.2
45°	12578.4	12706.5	12408.3	11669.5	10275.4	9167.9	8423.9	6214.0	4123.1	2606.1	1477.7
47.5°	11623.8	11589.7	11167.3	10019.3	8302.3	7309.7	6444.0	4451.3	2740.8	1476.4	734.9
50°	9632.1	9314.4	8693.3	7360.7	5571.9	4499.6	3908.6	2297.5	1243.6	715.3	461.7
52.5°	6238.9	5884.4	5315.5	4085.0	2675.4	2147.2	1722.2	1038.3	648.5	404.0	181.7
55°	2838.9	2587.7	2224.4	1650.3	1148.1	954.6	808.2	525.6	347.9	150.5	64.0
57.5°	1081.4	997.8	886.5	707.5	530.9	459.0	380.6	252.4	108.6	56.3	38.0
60°	486.5	451.2	414.5	324.4	227.4	163.5	124.3	68.0	45.8	32.8	24.9
62.5°	166.0	138.6	115.0	82.4	61.5	53.7	47.1	38.0	27.6	22.3	17.1
65°	48.5	47.1	44.4	39.2	31.4	28.7	27.6	22.3	17.1	14.4	11.9
67.5°	23.5	22.3	20.9	19.6	15.7	14.4	14.4	13.0	10.5	9.2	7.8
70°	10.5	10.5	9.2	9.2	7.8	7.8	7.8	6.6	6.6	6.6	6.6
72.5°	5.2	5.2	5.2	3.8	3.8	3.8	3.8	5.2	5.2	6.6	6.6
75°	1.4	2.5	2.5	2.5	2.5	3.8	3.8	5.2	5.2	6.6	6.6
77.5°	1.4	1.4	1.4	2.5	2.5	2.5	3.8	5.2	5.2	6.6	6.6
80°	0.0	1.4	1.4	2.5	2.5	2.5	3.8	3.8	5.2	6.6	6.6
82.5°	0.0	1.4	1.4	2.5	2.5	2.5	3.8	3.8	5.2	6.6	6.6
85°	0.0	0.0	1.4	1.4	2.5	2.5	3.8	3.8	5.2	6.6	6.6
87.5°	0.0	0.0	1.4	1.4	2.5	2.5	3.8	3.8	5.2	6.6	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192760

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1894.8	1867.2	1758.8	1675.1	1635.9	1633.2	1545.5	1492.1	1397.9	1324.6	1255.3
5°	2491.0	2369.4	2149.8	1975.8	1892.3	1849.0	1676.5	1552.2	1390.1	1264.4	1140.3
7.5°	3097.8	2866.3	2557.7	2227.0	2091.0	2007.2	1740.4	1541.7	1325.9	1150.8	996.4
10°	3718.9	3310.9	2850.6	2413.8	2217.8	2076.5	1734.0	1464.5	1216.2	1010.8	842.1
12.5°	4366.2	3722.9	3082.1	2535.6	2276.6	2091.0	1675.1	1352.1	1081.4	863.0	702.3
15°	4911.6	4042.0	3228.6	2564.3	2258.4	2033.4	1549.6	1209.5	937.6	724.4	578.0
17.5°	5332.6	4221.2	3256.1	2493.7	2156.3	1905.3	1387.4	1052.7	785.8	597.6	452.4
20°	5544.4	4248.5	3169.7	2326.4	1971.9	1713.1	1203.0	893.2	659.0	483.8	359.6
22.5°	5560.2	4120.4	2981.4	2110.6	1769.4	1506.4	1051.3	770.2	578.0	434.1	341.2
25°	5356.1	3873.3	2729.1	1889.6	1561.2	1324.6	942.8	738.8	581.9	503.4	462.8
27.5°	4969.0	3530.7	2451.8	1668.5	1382.2	1199.1	898.4	738.8	630.3	568.9	583.2
30°	4432.9	3093.9	2066.2	1367.8	1124.6	965.0	706.2	553.2	434.1	362.2	349.2
32.5°	3737.2	2531.6	1601.8	1010.8	819.8	695.7	477.4	346.5	279.8	273.2	265.4
35°	3075.6	1999.5	1216.2	746.7	604.1	491.7	304.6	203.9	185.7	175.2	167.3
37.5°	2429.5	1495.9	873.5	542.7	414.5	312.5	156.8	132.1	115.0	104.7	95.4
40°	1826.8	1074.9	615.9	328.2	217.2	134.8	94.2	81.0	72.0	66.7	64.0
42.5°	1292.0	715.3	381.8	138.6	103.4	85.0	65.3	57.6	52.3	49.6	47.1
45°	750.6	444.6	154.3	81.0	65.3	58.8	48.5	43.3	40.6	38.0	36.6
47.5°	469.5	179.2	79.7	52.3	45.8	41.9	35.3	33.9	31.4	30.1	30.1
50°	189.6	79.7	49.6	36.6	32.8	31.4	27.6	26.2	23.5	23.5	23.5
52.5°	72.0	47.1	33.9	26.2	23.5	22.3	19.6	19.6	18.2	18.2	18.2
55°	41.9	31.4	23.5	18.2	17.1	17.1	15.7	15.7	14.4	14.4	14.4
57.5°	27.6	20.9	17.1	13.0	13.0	13.0	11.9	11.9	11.9	11.9	11.9
60°	18.2	14.4	11.9	10.5	10.5	10.5	10.5	11.9	11.9	11.9	11.9
62.5°	13.0	11.9	10.5	10.5	10.5	10.5	10.5	11.9	11.9	11.9	13.0
65°	10.5	9.2	9.2	9.2	9.2	10.5	10.5	11.9	11.9	13.0	13.0
67.5°	7.8	7.8	7.8	7.8	9.2	9.2	10.5	11.9	11.9	11.9	13.0
70°	6.6	7.8	7.8	9.2	9.2	9.2	10.5	10.5	11.9	11.9	13.0
72.5°	6.6	7.8	7.8	9.2	9.2	9.2	10.5	11.9	11.9	11.9	13.0
75°	6.6	7.8	7.8	9.2	9.2	9.2	10.5	11.9	11.9	11.9	13.0
77.5°	7.8	7.8	9.2	9.2	9.2	10.5	10.5	11.9	11.9	13.0	13.0
80°	7.8	7.8	9.2	9.2	9.2	10.5	10.5	11.9	11.9	13.0	13.0
82.5°	7.8	7.8	9.2	9.2	9.2	10.5	10.5	11.9	11.9	13.0	13.0
85°	7.8	7.8	9.2	9.2	9.2	10.5	10.5	11.9	11.9	13.0	13.0
87.5°	7.8	7.8	9.2	9.2	9.2	10.5	10.5	11.9	11.9	11.9	13.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192760

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	1221.4	1161.3	1095.7	1074.9	1054.0	1013.5	988.5	944.1	911.5	878.7	852.6
5°	1057.9	962.5	882.6	848.6	816.0	759.7	720.5	673.4	635.5	602.8	572.7
7.5°	887.8	778.1	698.3	664.2	631.6	570.1	520.4	461.7	417.0	380.6	350.4
10°	731.0	626.3	540.0	499.5	461.7	397.5	350.4	303.5	265.4	234.0	206.6
12.5°	595.1	482.6	395.0	364.9	328.2	275.9	231.5	180.5	158.2	149.1	142.5
15°	461.7	360.9	287.8	260.2	227.4	177.8	158.2	149.1	142.5	138.6	133.4
17.5°	351.7	268.1	196.2	177.8	167.3	156.8	151.6	145.2	141.1	140.0	135.9
20°	275.9	202.6	184.4	179.2	179.2	176.5	172.5	172.5	171.2	175.2	175.2
22.5°	283.7	283.7	299.4	298.2	319.2	339.9	355.6	406.6	435.4	496.9	538.8
25°	495.6	542.7	597.6	614.6	655.2	715.3	778.1	856.4	911.5	970.2	993.7
27.5°	618.5	626.3	618.5	638.1	611.9	596.2	601.4	610.6	610.6	614.6	630.3
30°	366.1	384.5	401.3	414.5	408.0	401.3	398.8	379.3	379.3	371.3	364.9
32.5°	248.4	245.9	243.2	248.4	243.2	243.2	239.3	240.7	232.6	227.4	225.0
35°	170.0	162.1	153.0	154.3	149.1	147.8	143.8	143.8	138.6	135.9	134.8
37.5°	94.2	94.2	90.2	91.5	90.2	90.2	90.2	91.5	90.2	90.2	91.5
40°	64.0	64.0	62.8	64.0	62.8	64.0	65.3	65.3	65.3	65.3	64.0
42.5°	48.5	48.5	47.1	48.5	47.1	48.5	49.6	49.6	49.6	49.6	49.6
45°	38.0	38.0	38.0	38.0	38.0	38.0	38.0	39.2	39.2	38.0	38.0
47.5°	30.1	31.4	30.1	30.1	30.1	30.1	31.4	31.4	30.1	30.1	30.1
50°	24.9	24.9	23.5	23.5	23.5	23.5	23.5	23.5	23.5	23.5	23.5
52.5°	19.6	18.2	18.2	17.1	17.1	17.1	17.1	17.1	17.1	17.1	15.7
55°	14.4	14.4	13.0	13.0	13.0	14.4	14.4	14.4	14.4	13.0	13.0
57.5°	13.0	13.0	13.0	11.9	11.9	13.0	13.0	11.9	11.9	11.9	10.5
60°	11.9	13.0	11.9	11.9	11.9	11.9	11.9	10.5	10.5	10.5	9.2
62.5°	13.0	13.0	11.9	11.9	11.9	11.9	10.5	10.5	10.5	9.2	9.2
65°	13.0	13.0	13.0	11.9	11.9	11.9	11.9	10.5	10.5	9.2	9.2
67.5°	13.0	13.0	13.0	13.0	11.9	11.9	11.9	10.5	10.5	10.5	9.2
70°	13.0	13.0	13.0	13.0	13.0	11.9	11.9	11.9	10.5	10.5	9.2
72.5°	13.0	13.0	13.0	11.9	11.9	11.9	11.9	11.9	10.5	10.5	9.2
75°	13.0	13.0	13.0	11.9	11.9	11.9	11.9	10.5	10.5	10.5	9.2
77.5°	13.0	13.0	13.0	11.9	11.9	11.9	11.9	10.5	10.5	10.5	9.2
80°	13.0	13.0	13.0	11.9	11.9	11.9	11.9	10.5	10.5	10.5	9.2
82.5°	13.0	13.0	13.0	11.9	11.9	11.9	11.9	10.5	10.5	9.2	9.2
85°	13.0	13.0	11.9	11.9	11.9	11.9	10.5	10.5	9.2	9.2	7.8
87.5°	11.9	11.9	11.9	11.9	10.5	10.5	10.5	9.2	7.8	7.8	6.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192760

CATALOG NUMBER: LDA6A70950D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2	1369.2
2.5°	821.2	816.0	812.0	819.8	817.2	784.6	788.5	787.2
5°	538.8	527.0	517.9	521.8	511.3	496.9	486.5	483.8
7.5°	320.3	307.3	299.4	291.6	288.9	270.7	262.9	268.1
10°	176.5	158.2	156.8	153.0	147.8	143.8	141.1	142.5
12.5°	135.9	134.8	132.1	130.7	128.1	126.8	125.4	124.3
15°	129.5	128.1	126.8	125.4	124.3	122.9	121.6	121.6
17.5°	133.4	133.4	132.1	130.7	130.7	132.1	130.7	129.5
20°	173.9	173.9	176.5	180.5	180.5	184.4	189.6	185.7
22.5°	564.8	593.7	629.0	639.5	701.0	750.6	842.1	801.5
25°	1033.0	1098.4	1114.2	1136.4	1170.3	1187.4	1170.3	1192.7
27.5°	627.6	649.9	652.5	653.8	661.6	660.4	643.3	653.8
30°	364.9	372.6	370.1	368.8	366.1	351.7	349.2	354.4
32.5°	228.8	226.3	225.0	223.6	223.6	215.8	219.6	217.2
35°	130.7	134.8	133.4	132.1	128.1	126.8	126.8	125.4
37.5°	87.7	89.0	87.7	86.3	83.7	82.4	81.0	79.7
40°	62.8	64.0	62.8	61.5	60.1	58.8	57.6	56.3
42.5°	47.1	48.5	47.1	47.1	44.4	43.3	41.9	40.6
45°	36.6	35.3	35.3	35.3	33.9	32.8	31.4	31.4
47.5°	30.1	30.1	30.1	28.7	27.6	27.6	27.6	26.2
50°	22.3	23.5	22.3	22.3	20.9	19.6	19.6	18.2
52.5°	15.7	15.7	14.4	14.4	13.0	11.9	11.9	11.9
55°	11.9	11.9	11.9	10.5	10.5	9.2	9.2	9.2
57.5°	10.5	9.2	9.2	9.2	7.8	7.8	6.6	6.6
60°	9.2	7.8	7.8	6.6	6.6	5.2	5.2	5.2
62.5°	7.8	6.6	6.6	6.6	5.2	5.2	5.2	5.2
65°	7.8	6.6	6.6	6.6	5.2	5.2	5.2	5.2
67.5°	7.8	7.8	6.6	6.6	6.6	5.2	5.2	5.2
70°	7.8	7.8	7.8	6.6	6.6	6.6	5.2	5.2
72.5°	9.2	7.8	7.8	7.8	6.6	6.6	6.6	6.6
75°	9.2	7.8	7.8	7.8	6.6	6.6	6.6	6.6
77.5°	9.2	7.8	7.8	7.8	6.6	6.6	6.6	6.6
80°	7.8	7.8	7.8	6.6	6.6	6.6	6.6	6.6
82.5°	7.8	7.8	7.8	7.8	6.6	6.6	6.6	6.6
85°	7.8	6.6	6.6	6.6	5.2	5.2	5.2	5.2
87.5°	6.6	5.2	5.2	3.8	3.8	3.8	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)