

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203848

Luminaire Tested: **LE_6B15D010 EC6B10209035 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203848
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209035 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 798.6 lumens
Efficiency: N/A
Efficacy: 55.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203848

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBNGPH1

Luminous Intensity Polar Plot






TEST NUMBER: P203848

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	111	108	106	111	109	106	104		105	103	101			101	100	98			94
2	108	103	99	96	106	101	98	95		98	95	93			95	93	91			87
3	103	96	91	87	101	95	90	87		92	88	85			90	87	84			81
4	97	90	84	80	96	89	84	80		87	82	79			85	81	78			76
5	93	84	78	74	91	83	78	74		81	77	73			80	76	73			70
6	88	79	73	69	86	78	73	69		77	72	68			75	71	68			66
7	84	74	68	64	82	74	68	64		72	67	64			71	67	63			62
8	79	70	64	60	78	69	64	60		68	63	60			67	63	59			58
9	76	66	60	56	75	66	60	56		65	60	56			64	59	56			54
10	72	63	57	53	71	62	57	53		61	56	53			61	56	53			51

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203848

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	11.0
10°-20°	216.7	27.1
20°-30°	262.6	32.9
30°-40°	178.9	22.4
40°-50°	42.6	5.3
50°-60°	6.7	0.8
60°-70°	2.5	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	567.1	71.0
0°-40°	746.1	93.4
0°-60°	795.3	99.6
0°-90°	798.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	798.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	971	
5°	943	88
15°	776	217
25°	574	263
35°	286	179
45°	46	43
55°	7	7
65°	2	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203848

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	970.6
2.5°	965.1
5°	943.2
7.5°	914.1
10°	872.2
12.5°	824.9
15°	775.8
17.5°	724.8
20°	673.8
22.5°	622.8
25°	573.6
27.5°	528.1
30°	462.5
32.5°	377.0
35°	285.9
37.5°	204.0
40°	134.8
42.5°	83.8
45°	45.5
47.5°	23.6
50°	12.8
52.5°	9.1
55°	7.2
57.5°	5.5
60°	3.6
62.5°	3.6
65°	1.9
67.5°	1.9
70°	1.9
72.5°	1.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)