

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192764

Luminaire Tested: **LDA6A75927D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192764
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75927D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5854.0 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192764

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192764

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	90601	90601	90601
5°	175550	86336	29116
10°	298258	75555	13081
15°	459605	60267	20789
20°	665320	39221	36164
25°	976151	37847	46503
30°	1135010	35854	35632
35°	1148815	18993	18832
40°	951139	7163	7908
45°	718346	2434	2876
50°	491481	887	887
55°	68366	774	105
60°	1787	767	0
65°	441	1051	0
70°	176	1298	0
75°	0	1716	0
80°	0	2936	347
85°	0	5850	0



TEST NUMBER: P1192764

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.4	3.0
10°-20°	732.9	12.5
20°-30°	1671.9	28.6
30°-40°	1934.8	33.1
40°-50°	1166.8	19.9
50°-60°	158.5	2.7
60°-70°	5.1	0.1
70°-80°	5.5	0.1
80°-90°	5.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2578.2	44.0
0°-40°	4512.9	77.1
0°-60°	5838.2	99.7
0°-90°	5854.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5854.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1653	1653	1653	1653	1653	
5°	3190	2612	1569	858	529	371
15°	8098	4552	1062	327	366	2397
25°	16138	5394	626	752	769	7303
35°	17166	4112	284	290	281	10345
45°	9266	1120	31	38	37	7245
55°	715	8	8	6	1	1402
65°	3	5	8	5	0	5
75°	0	6	8	6	0	0
85°	0	6	9	6	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P1192764

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7
2.5°	2389.9	2367.9	2377.2	2352.8	2291.1	2278.4	2277.3	2261.0	2208.6	2167.9	2119.1
5°	3190.1	3189.0	3194.8	3142.6	3034.4	3000.7	2984.4	2944.7	2818.1	2720.3	2612.2
7.5°	4189.2	4182.2	4175.2	4079.9	3910.1	3845.0	3803.0	3660.0	3485.5	3312.3	3119.2
10°	5358.0	5354.6	5327.8	5160.3	4888.2	4768.4	4686.9	4460.2	4179.9	3933.4	3605.3
12.5°	6715.3	6683.9	6636.2	6390.8	6017.5	5887.3	5708.1	5348.8	4918.5	4540.4	4082.3
15°	8098.2	8052.8	7967.8	7652.6	7189.9	6967.6	6745.6	6272.2	5688.4	5139.3	4552.1
17.5°	9450.7	9400.8	9201.9	8666.8	8214.4	7943.4	7696.9	7046.7	6360.6	5654.6	4910.3
20°	11404.5	11223.2	10876.6	10033.4	9192.5	8704.1	8415.7	7728.3	6879.2	6057.0	5165.0
22.5°	14014.4	13612.0	12873.6	11503.5	10302.1	9597.2	9125.1	8211.0	7252.6	6319.9	5321.9
25°	16138.1	15955.5	15115.9	13166.6	11291.7	10461.4	9804.4	8594.7	7524.8	6495.5	5394.0
27.5°	17507.0	17461.7	16502.0	14543.7	12100.1	11010.3	10276.5	8848.3	7656.2	6532.7	5359.2
30°	17930.4	18001.2	17080.1	15011.1	12333.8	11120.8	10318.3	8851.7	7555.1	6364.0	5135.9
32.5°	17899.0	17902.4	16773.1	14607.5	11953.6	10799.9	9969.4	8557.6	7181.6	5941.8	4711.3
35°	17166.2	16986.0	15708.9	13367.7	11068.6	10050.8	9278.6	7987.7	6566.4	5306.8	4112.4
37.5°	15557.8	15321.6	13833.0	11780.3	10020.7	9079.7	8456.4	7239.7	5833.7	4628.8	3493.8
40°	13291.0	12956.1	11727.9	10304.4	8873.8	8166.7	7643.3	6403.7	5049.8	3963.5	2913.3
42.5°	11021.9	10858.0	10046.2	8889.0	7909.7	7244.4	6697.9	5527.8	4296.3	3307.6	2179.5
45°	9265.7	9125.1	8579.6	7816.6	6856.1	6248.9	5722.1	4614.8	3337.9	2219.0	1120.0
47.5°	7986.5	7872.5	7350.2	6549.0	5495.3	4831.2	4288.0	3026.2	1891.1	958.4	280.3
50°	5762.8	5646.4	5134.8	4206.6	3255.4	2699.3	2308.7	1351.4	536.1	194.3	29.1
52.5°	2824.9	2729.6	2381.9	1782.9	1196.8	860.6	629.2	253.5	61.7	21.0	14.0
55°	715.3	657.0	547.8	344.2	168.6	101.2	65.1	23.3	15.1	11.7	8.1
57.5°	40.7	39.5	36.1	26.7	19.7	17.4	15.1	11.7	8.1	7.0	5.7
60°	16.3	15.1	14.0	11.7	9.3	8.1	8.1	5.7	4.7	4.7	4.7
62.5°	7.0	7.0	7.0	5.7	4.7	4.7	4.7	3.4	4.7	4.7	4.7
65°	3.4	3.4	3.4	2.3	2.3	2.3	3.4	3.4	3.4	4.7	4.7
67.5°	2.3	1.1	1.1	1.1	2.3	2.3	2.3	3.4	3.4	4.7	4.7
70°	1.1	1.1	1.1	1.1	2.3	2.3	2.3	3.4	3.4	4.7	5.7
72.5°	0.0	1.1	1.1	1.1	2.3	2.3	2.3	3.4	3.4	4.7	5.7
75°	0.0	1.1	1.1	1.1	2.3	2.3	2.3	3.4	4.7	4.7	5.7
77.5°	0.0	1.1	1.1	1.1	2.3	2.3	2.3	3.4	4.7	4.7	5.7
80°	0.0	1.1	1.1	1.1	2.3	2.3	2.3	3.4	4.7	4.7	5.7
82.5°	0.0	0.0	1.1	1.1	2.3	2.3	2.3	3.4	4.7	4.7	5.7
85°	0.0	0.0	1.1	1.1	2.3	2.3	2.3	3.4	4.7	4.7	5.7
87.5°	0.0	0.0	1.1	1.1	2.3	2.3	2.3	3.4	3.4	4.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192764

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7
2.5°	2056.3	2014.3	1952.8	1912.1	1872.4	1835.3	1773.6	1738.6	1675.9	1617.7	1567.7
5°	2481.9	2377.2	2250.4	2142.2	2072.4	2003.9	1879.4	1787.6	1672.4	1568.9	1473.5
7.5°	2912.2	2727.3	2519.1	2341.1	2233.0	2127.2	1941.1	1792.3	1629.4	1481.8	1341.0
10°	3302.9	3025.1	2730.7	2476.0	2329.5	2192.3	1946.9	1749.2	1539.9	1357.3	1180.4
12.5°	3665.8	3285.5	2901.7	2569.1	2387.8	2222.6	1922.5	1680.5	1431.7	1215.4	1009.5
15°	3989.2	3500.8	3026.2	2622.6	2409.8	2214.3	1865.5	1584.0	1303.7	1061.9	801.3
17.5°	4234.6	3634.4	3080.9	2614.5	2370.2	2152.8	1767.9	1463.1	1167.7	874.6	580.3
20°	4383.4	3691.4	3069.2	2551.7	2285.4	2055.0	1651.5	1331.6	1003.7	672.3	511.7
22.5°	4446.2	3686.8	3014.5	2457.5	2180.6	1948.1	1539.9	1203.7	831.6	608.2	533.8
25°	4456.6	3639.1	2937.7	2353.9	2077.1	1845.7	1427.1	1058.3	722.3	625.7	597.8
27.5°	4376.4	3527.5	2793.5	2205.2	1931.8	1692.2	1258.5	840.9	678.0	623.3	642.0
30°	4139.1	3272.8	2538.8	1943.5	1679.4	1439.8	899.0	659.4	562.9	566.4	571.1
32.5°	3721.7	2849.5	2129.5	1560.7	1272.3	949.0	559.4	440.7	428.0	428.0	425.6
35°	3164.6	2331.8	1671.2	987.4	632.6	456.0	289.5	290.8	285.0	283.8	282.7
37.5°	2588.9	1840.0	1058.3	408.2	274.4	190.7	170.9	173.3	170.9	174.5	172.2
40°	2041.1	1136.3	386.2	130.2	96.5	93.1	95.4	97.7	97.7	100.1	100.1
42.5°	1186.3	376.9	101.2	52.4	52.4	50.0	51.1	53.5	54.7	55.8	54.7
45°	352.5	77.9	32.6	29.1	29.1	28.0	28.0	29.1	30.3	31.4	31.4
47.5°	55.8	22.1	18.6	16.3	16.3	16.3	16.3	16.3	17.4	17.4	18.6
50°	17.4	14.0	11.7	10.4	10.4	9.3	9.3	10.4	10.4	10.4	11.7
52.5°	10.4	8.1	8.1	7.0	8.1	8.1	7.0	8.1	8.1	8.1	9.3
55°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	8.1	8.1	8.1
57.5°	5.7	5.7	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
60°	5.7	5.7	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	8.1
62.5°	5.7	5.7	7.0	7.0	7.0	7.0	7.0	7.0	8.1	8.1	8.1
65°	5.7	5.7	7.0	7.0	7.0	7.0	7.0	8.1	8.1	8.1	8.1
67.5°	5.7	7.0	7.0	7.0	7.0	8.1	8.1	8.1	8.1	8.1	8.1
70°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
72.5°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
75°	7.0	7.0	7.0	8.1	8.1	8.1	8.1	8.1	8.1	8.1	9.3
77.5°	7.0	7.0	8.1	8.1	8.1	8.1	8.1	8.1	9.3	9.3	9.3
80°	7.0	7.0	8.1	8.1	8.1	8.1	8.1	9.3	9.3	9.3	9.3
82.5°	7.0	7.0	8.1	8.1	8.1	8.1	8.1	9.3	9.3	9.3	9.3
85°	7.0	7.0	8.1	8.1	8.1	8.1	8.1	9.3	9.3	9.3	9.3
87.5°	7.0	7.0	8.1	8.1	8.1	8.1	8.1	9.3	9.3	9.3	9.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192764

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7
2.5°	1524.7	1471.2	1445.7	1409.7	1384.0	1327.0	1303.7	1264.2	1231.6	1178.1	1181.7
5°	1392.1	1290.9	1222.4	1168.8	1131.6	1040.9	980.4	916.4	858.3	786.2	759.5
7.5°	1208.4	1083.9	979.2	915.3	867.6	746.7	612.9	508.2	429.2	372.2	350.1
10°	1024.6	863.0	696.7	597.8	529.1	412.9	353.5	325.7	300.1	268.7	247.7
12.5°	810.6	580.3	429.2	389.6	361.8	323.4	285.0	254.7	260.5	261.7	269.8
15°	553.5	417.6	369.9	343.1	312.8	290.8	303.5	311.7	326.8	327.9	338.5
17.5°	450.0	391.9	353.5	352.5	354.8	367.5	387.3	397.8	417.6	422.2	437.3
20°	450.0	416.3	449.0	449.0	454.7	472.1	497.8	512.8	535.1	543.1	561.8
22.5°	512.8	536.1	576.9	581.5	583.8	602.5	635.0	650.2	675.7	680.4	700.1
25°	625.7	646.6	683.9	687.3	688.4	702.4	726.8	735.1	752.5	743.1	754.8
27.5°	661.7	671.0	694.3	696.7	690.8	696.7	706.0	706.0	711.7	693.1	696.7
30°	581.5	583.8	595.5	596.6	583.8	586.2	587.3	586.2	584.9	565.2	565.2
32.5°	431.6	431.6	446.6	443.1	429.2	432.6	432.6	432.6	431.6	415.2	412.9
35°	286.1	287.3	300.1	297.8	287.3	289.5	289.5	293.1	289.5	280.3	278.0
37.5°	174.5	175.6	181.4	182.6	179.2	180.3	181.4	180.3	182.6	177.9	175.6
40°	101.2	103.5	108.2	109.2	108.2	108.2	109.2	110.5	115.2	109.2	107.1
42.5°	59.4	60.5	62.8	62.8	62.8	62.8	64.0	65.1	66.4	65.1	64.0
45°	33.7	35.0	36.1	36.1	37.1	36.1	37.1	37.1	38.4	37.1	37.1
47.5°	19.7	19.7	21.0	21.0	22.1	21.0	22.1	22.1	22.1	21.0	21.0
50°	11.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7	12.7	11.7	11.7
52.5°	9.3	9.3	9.3	9.3	9.3	8.1	8.1	8.1	8.1	7.0	7.0
55°	8.1	8.1	8.1	8.1	8.1	8.1	7.0	5.7	5.7	4.7	4.7
57.5°	7.0	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	3.4	3.4
60°	8.1	8.1	8.1	8.1	7.0	7.0	7.0	5.7	4.7	3.4	3.4
62.5°	8.1	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	3.4	3.4
65°	8.1	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	3.4	3.4
67.5°	8.1	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	4.7	3.4
70°	8.1	9.3	9.3	8.1	8.1	8.1	7.0	5.7	5.7	4.7	3.4
72.5°	8.1	9.3	9.3	8.1	8.1	8.1	7.0	5.7	5.7	4.7	3.4
75°	9.3	9.3	9.3	9.3	8.1	8.1	7.0	7.0	5.7	4.7	3.4
77.5°	9.3	9.3	9.3	9.3	8.1	8.1	7.0	7.0	5.7	4.7	3.4
80°	9.3	9.3	9.3	9.3	9.3	8.1	8.1	7.0	5.7	4.7	4.7
82.5°	9.3	9.3	9.3	9.3	9.3	8.1	8.1	7.0	5.7	4.7	4.7
85°	9.3	9.3	9.3	9.3	9.3	8.1	8.1	7.0	5.7	4.7	3.4
87.5°	9.3	9.3	9.3	9.3	8.1	8.1	7.0	7.0	5.7	4.7	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192764

CATALOG NUMBER: LDA6A75927D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7	1652.7
2.5°	1138.6	1111.9	1100.3	1118.9	1109.6	1081.6	1087.4	1069.9
5°	679.3	638.5	612.9	624.6	587.3	553.5	553.5	529.1
7.5°	327.9	315.2	308.2	310.5	302.4	291.8	286.1	286.1
10°	230.3	225.6	226.7	226.7	233.7	232.6	236.1	235.0
12.5°	273.4	275.7	276.8	281.4	287.3	287.3	290.8	288.4
15°	350.1	347.8	354.8	355.9	365.2	366.3	370.9	366.3
17.5°	445.4	450.0	457.0	456.0	474.4	475.7	475.7	474.4
20°	573.4	576.9	583.8	586.2	608.2	610.6	618.7	619.9
22.5°	713.0	713.0	716.4	721.1	742.0	743.1	746.7	746.7
25°	760.5	753.7	754.8	760.5	772.2	767.5	771.1	768.8
27.5°	699.0	688.4	686.3	694.3	702.4	689.7	694.3	694.3
30°	567.5	558.2	555.9	564.1	569.9	555.9	560.5	562.9
32.5°	415.2	409.3	408.2	414.0	418.7	407.0	411.7	415.2
35°	280.3	278.0	275.7	276.8	283.8	274.4	279.1	281.4
37.5°	177.9	173.3	174.5	176.8	181.4	175.6	180.3	180.3
40°	109.2	107.1	107.1	109.2	111.6	107.1	109.2	110.5
42.5°	64.0	64.0	64.0	65.1	66.4	64.0	64.0	65.1
45°	37.1	36.1	36.1	37.1	38.4	36.1	37.1	37.1
47.5°	21.0	19.7	19.7	21.0	21.0	19.7	21.0	21.0
50°	11.7	10.4	10.4	11.7	11.7	10.4	10.4	10.4
52.5°	5.7	5.7	5.7	5.7	5.7	5.7	4.7	4.7
55°	3.4	3.4	2.3	2.3	2.3	2.3	2.3	1.1
57.5°	2.3	2.3	1.1	1.1	1.1	1.1	0.0	0.0
60°	2.3	2.3	1.1	1.1	1.1	0.0	0.0	0.0
62.5°	2.3	2.3	1.1	1.1	1.1	0.0	0.0	0.0
65°	2.3	2.3	1.1	1.1	1.1	0.0	0.0	0.0
67.5°	2.3	2.3	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.4	2.3	2.3	1.1	1.1	1.1	0.0	0.0
72.5°	3.4	2.3	2.3	2.3	1.1	1.1	0.0	0.0
75°	3.4	2.3	2.3	2.3	1.1	1.1	0.0	0.0
77.5°	3.4	2.3	2.3	2.3	1.1	1.1	1.1	0.0
80°	3.4	2.3	2.3	2.3	1.1	1.1	1.1	1.1
82.5°	3.4	2.3	2.3	2.3	1.1	1.1	1.1	1.1
85°	3.4	2.3	2.3	2.3	1.1	1.1	1.1	0.0
87.5°	3.4	2.3	2.3	2.3	1.1	1.1	1.1	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)