

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204674

Luminaire Tested: **LE_6B15D010 EC6B10209035 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204674
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209035 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1781.7 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204674

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204674

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86						
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74						
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63						
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54						
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47						
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42						
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37						
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33						
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30						
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27						

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204674

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.0	3.8
10°-20°	193.9	10.9
20°-30°	292.0	16.4
30°-40°	347.5	19.5
40°-50°	346.8	19.5
50°-60°	282.1	15.8
60°-70°	173.5	9.7
70°-80°	67.2	3.8
80°-90°	10.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	553.9	31.1
0°-40°	901.4	50.6
0°-60°	1530.2	85.9
0°-90°	1781.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1781.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	718	
5°	716	68
15°	688	194
25°	636	292
35°	556	347
45°	451	347
55°	316	282
65°	174	174
75°	61	67
85°	8	11
90°	0	



TEST NUMBER: P204674

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	717.9
2.5°	719.0
5°	715.8
7.5°	711.5
10°	706.2
12.5°	696.8
15°	688.4
17.5°	675.6
20°	661.9
22.5°	649.2
25°	635.5
27.5°	616.5
30°	597.5
32.5°	579.6
35°	556.4
37.5°	531.0
40°	507.8
42.5°	479.2
45°	450.8
47.5°	420.1
50°	387.5
52.5°	353.6
55°	315.6
57.5°	278.8
60°	242.9
62.5°	208.0
65°	174.2
67.5°	142.5
70°	113.0
72.5°	85.5
75°	61.2
77.5°	40.1
80°	24.2
82.5°	14.8
85°	8.5
87.5°	4.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)