

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192769

Luminaire Tested: **LDA6A75927D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192769
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75927D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6395.9 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.47 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192769

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192769

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	63246	63246	63246
5°	162244	57533	17918
10°	316249	44215	8606
15°	567710	30029	11555
20°	842879	22799	19065
25°	958053	18781	29899
30°	1038546	20541	28125
35°	1093924	13311	17433
40°	1117587	5904	8487
45°	1009392	2256	3155
50°	664456	887	887
55°	181958	774	0
60°	36346	888	0
65°	2555	1206	0
70°	369	1491	0
75°	0	2203	0
80°	0	3283	347
85°	0	6542	692

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192769

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.3	2.2
10°-20°	750.8	11.7
20°-30°	1701.7	26.6
30°-40°	2042.6	31.9
40°-50°	1439.6	22.5
50°-60°	297.0	4.6
60°-70°	10.5	0.2
70°-80°	6.2	0.1
80°-90°	6.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2593.8	40.6
0°-40°	4636.5	72.5
0°-60°	6373.1	99.6
0°-90°	6395.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6395.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1154	1154	1154	1154	1154	
5°	2948	2148	1046	435	326	363
15°	10003	4401	529	188	204	2969
25°	15839	5323	310	435	494	7310
35°	16346	3728	199	260	260	10162
45°	13020	1278	29	40	41	9576
55°	1904	26	8	6	0	2509
65°	20	6	9	6	0	59
75°	0	6	10	7	0	0
85°	0	7	10	7	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192769

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7
2.5°	1966.6	1907.3	1930.6	1862.0	1846.8	1834.1	1846.8	1772.4	1730.6	1677.1	1634.1
5°	2948.3	2877.3	2893.6	2773.8	2719.1	2681.9	2674.9	2521.4	2406.3	2279.4	2148.1
7.5°	4104.2	4036.7	4027.4	3841.4	3728.6	3664.7	3637.8	3418.1	3219.2	2993.5	2747.1
10°	5681.2	5527.8	5480.1	5210.3	4995.1	4859.0	4691.6	4340.4	3991.4	3650.7	3336.6
12.5°	7516.5	7432.8	7314.2	6838.5	6461.6	6268.6	6018.6	5469.6	4941.6	4378.8	3853.1
15°	10003.0	9705.4	9502.9	8815.5	8208.5	7910.8	7545.6	6705.9	5908.1	5195.1	4400.8
17.5°	12432.5	12276.7	11960.4	11068.4	10133.3	9663.4	9119.2	7978.2	6851.2	5837.1	4867.2
20°	14448.1	14301.5	13941.0	13100.1	12062.7	11369.6	10684.6	9119.2	7646.7	6348.8	5178.8
22.5°	15413.3	15320.2	15026.0	14306.2	13422.3	12762.9	12026.6	10090.3	8235.3	6683.9	5320.8
25°	15838.9	15795.9	15606.3	15038.8	14206.1	13646.7	12951.3	10777.6	8601.5	6839.6	5323.0
27.5°	16270.5	16278.6	15859.9	15411.0	14621.4	14084.0	13414.0	11082.2	8667.9	6752.4	5148.6
30°	16406.5	16320.5	16135.6	15491.3	14741.2	14170.1	13451.3	10941.6	8395.8	6394.2	4800.9
32.5°	16350.7	16317.0	16113.4	15431.9	14537.6	13908.4	13091.9	10383.4	7858.4	5882.5	4307.8
35°	16346.0	16283.2	15816.9	15231.9	14130.6	13353.6	12277.9	9480.8	7097.9	5208.0	3727.5
37.5°	16050.6	15894.7	15544.8	14756.3	13304.8	12319.7	11113.6	8378.2	6167.5	4450.9	3151.7
40°	15616.9	15407.5	14946.9	13753.8	11874.3	10739.3	9562.2	7125.7	5182.4	3704.2	2540.1
42.5°	14710.9	14394.5	13743.2	12102.3	9968.1	8944.7	7965.5	5857.0	4226.3	3018.1	1938.8
45°	13019.8	12587.1	11706.8	9905.4	8052.7	7217.7	6430.2	4712.4	3383.1	2238.7	1278.2
47.5°	10464.7	10063.6	9262.2	7885.1	6315.1	5609.3	4981.1	3505.3	2293.4	1296.7	610.6
50°	7791.0	7446.7	6821.1	5480.1	4239.2	3684.4	3147.1	1991.0	1074.6	616.3	253.5
52.5°	4648.6	4477.6	3922.8	3038.9	2093.4	1803.8	1447.9	843.2	541.9	223.3	68.7
55°	1903.8	1757.3	1549.1	1243.2	910.7	772.2	660.6	416.3	168.6	46.5	25.6
57.5°	860.6	828.0	733.8	576.9	418.7	351.2	237.3	79.1	37.1	23.3	15.1
60°	331.5	298.8	255.8	138.5	59.4	50.0	40.7	26.7	18.6	12.7	9.3
62.5°	47.7	45.4	40.7	32.6	25.6	23.3	19.7	14.0	10.4	8.1	7.0
65°	19.7	19.7	17.4	14.0	11.7	10.4	9.3	7.0	5.7	5.7	5.7
67.5°	8.1	8.1	7.0	5.7	4.7	4.7	4.7	3.4	4.7	4.7	5.7
70°	2.3	2.3	2.3	2.3	2.3	2.3	3.4	3.4	4.7	4.7	5.7
72.5°	0.0	0.0	1.1	1.1	2.3	2.3	2.3	3.4	4.7	5.7	5.7
75°	0.0	0.0	1.1	1.1	2.3	2.3	2.3	3.4	4.7	5.7	5.7
77.5°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
80°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	7.0
82.5°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	7.0
85°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	7.0
87.5°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	7.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192769

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7
2.5°	1596.8	1522.3	1501.5	1436.4	1381.7	1355.0	1321.2	1245.6	1188.5	1113.0	1067.6
5°	2056.1	1915.5	1803.8	1667.8	1578.3	1520.0	1429.4	1290.9	1179.4	1045.5	950.1
7.5°	2552.8	2295.8	2094.5	1870.1	1741.0	1639.8	1485.2	1286.3	1122.3	944.4	796.6
10°	3031.9	2648.2	2331.8	2009.7	1839.8	1699.2	1486.3	1236.2	1018.8	794.3	638.5
12.5°	3454.1	2958.7	2513.3	2099.2	1888.8	1713.2	1446.8	1146.7	883.9	653.6	516.4
15°	3806.6	3199.4	2641.2	2132.9	1892.2	1682.9	1364.3	1018.8	733.8	529.1	432.6
17.5°	4074.0	3326.2	2680.7	2092.2	1824.7	1596.8	1237.5	857.2	595.5	449.0	364.0
20°	4212.3	3350.6	2623.8	1981.7	1700.3	1466.5	1071.2	695.4	504.7	390.8	304.7
22.5°	4229.9	3281.9	2487.7	1823.6	1543.3	1308.3	887.3	580.3	450.0	345.5	268.7
25°	4126.4	3133.1	2293.4	1644.5	1371.1	1127.0	722.2	519.8	409.3	310.5	309.4
27.5°	3905.4	2877.3	2060.8	1436.4	1163.0	916.4	612.9	469.8	365.2	329.1	350.1
30°	3593.7	2549.4	1774.7	1173.4	908.3	704.8	516.4	387.3	321.1	324.5	341.9
32.5°	3171.5	2142.2	1438.6	859.5	650.0	530.4	387.3	264.0	266.4	267.4	282.7
35°	2641.2	1717.8	1074.6	577.9	457.0	373.3	218.7	194.3	197.7	198.9	209.3
37.5°	2116.7	1320.0	714.1	384.9	287.3	196.6	136.1	130.2	132.6	131.5	143.1
40°	1621.2	920.0	428.0	190.7	110.5	91.8	83.8	80.2	81.4	82.5	89.5
42.5°	1148.0	499.0	211.7	72.1	58.1	53.5	50.0	47.7	48.8	48.8	53.5
45°	582.6	236.1	72.1	39.5	36.1	32.6	30.3	29.1	29.1	29.1	31.4
47.5°	252.4	77.9	33.7	24.4	22.1	21.0	18.6	17.4	17.4	17.4	18.6
50°	79.1	31.4	21.0	16.3	14.0	12.7	11.7	11.7	11.7	10.4	11.7
52.5°	29.1	19.7	14.0	10.4	9.3	9.3	9.3	8.1	9.3	8.1	9.3
55°	17.4	12.7	9.3	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
57.5°	11.7	9.3	8.1	8.1	7.0	7.0	8.1	8.1	8.1	8.1	8.1
60°	8.1	8.1	7.0	7.0	7.0	7.0	8.1	8.1	8.1	8.1	8.1
62.5°	7.0	7.0	7.0	7.0	7.0	7.0	8.1	8.1	8.1	8.1	9.3
65°	5.7	7.0	7.0	7.0	7.0	7.0	8.1	8.1	9.3	9.3	9.3
67.5°	5.7	7.0	7.0	8.1	8.1	8.1	8.1	9.3	9.3	9.3	9.3
70°	7.0	7.0	8.1	8.1	8.1	8.1	9.3	9.3	9.3	9.3	10.4
72.5°	7.0	7.0	8.1	8.1	8.1	8.1	9.3	9.3	10.4	10.4	10.4
75°	7.0	8.1	8.1	8.1	8.1	9.3	9.3	9.3	10.4	10.4	10.4
77.5°	7.0	8.1	8.1	9.3	9.3	9.3	9.3	10.4	10.4	10.4	10.4
80°	7.0	8.1	8.1	9.3	9.3	9.3	10.4	10.4	10.4	10.4	11.7
82.5°	7.0	8.1	8.1	9.3	9.3	9.3	10.4	10.4	10.4	10.4	11.7
85°	8.1	8.1	9.3	9.3	9.3	9.3	10.4	10.4	10.4	10.4	11.7
87.5°	8.1	8.1	9.3	9.3	9.3	9.3	10.4	10.4	11.7	10.4	11.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192769

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7
2.5°	1007.2	939.7	893.3	875.7	842.0	788.5	757.1	728.1	673.4	661.7	631.6
5°	840.9	732.7	656.0	626.9	588.5	543.1	499.0	469.8	435.0	421.0	400.0
7.5°	662.9	554.8	488.4	465.3	438.4	401.2	361.6	332.6	296.5	278.0	260.5
10°	521.1	440.7	384.9	361.6	333.8	294.2	253.5	215.2	183.7	163.9	160.5
12.5°	423.3	357.1	297.8	273.4	240.7	201.2	172.2	170.9	168.6	167.5	169.9
15°	346.5	282.7	219.7	193.0	183.7	182.6	186.0	189.6	188.3	191.9	194.3
17.5°	285.0	216.3	202.3	203.6	204.7	208.2	214.0	223.3	224.4	230.3	235.0
20°	232.6	229.1	235.0	239.6	243.0	250.0	262.8	274.4	278.0	286.1	295.4
22.5°	264.0	274.4	287.3	293.1	297.8	310.5	324.5	343.1	350.1	360.5	373.3
25°	318.7	336.1	355.9	362.9	369.9	390.8	407.0	429.2	435.0	447.7	460.6
27.5°	364.0	382.6	403.6	412.9	418.7	439.6	453.6	467.5	467.5	474.4	483.8
30°	357.1	372.2	389.6	396.6	398.9	414.0	428.0	432.6	430.3	433.7	440.7
32.5°	296.5	308.2	322.1	327.9	330.2	340.8	352.5	352.5	351.2	351.2	355.9
35°	219.7	228.0	235.0	240.7	244.3	251.3	261.7	260.5	260.5	258.1	261.7
37.5°	147.6	152.3	160.5	162.9	163.9	168.6	176.8	176.8	174.5	175.6	177.9
40°	89.5	95.4	100.1	101.2	103.5	107.1	112.8	112.8	112.8	112.8	113.9
42.5°	53.5	57.0	60.5	60.5	61.7	66.4	68.7	68.7	68.7	68.7	69.8
45°	31.4	32.6	35.0	36.1	36.1	38.4	39.5	39.5	39.5	39.5	40.7
47.5°	18.6	19.7	19.7	21.0	21.0	22.1	23.3	23.3	22.1	22.1	22.1
50°	11.7	11.7	11.7	11.7	12.7	12.7	12.7	12.7	12.7	12.7	11.7
52.5°	9.3	9.3	9.3	9.3	8.1	8.1	8.1	8.1	7.0	7.0	5.7
55°	8.1	8.1	8.1	8.1	8.1	7.0	7.0	7.0	5.7	4.7	3.4
57.5°	8.1	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	4.7	3.4
60°	8.1	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	4.7	3.4
62.5°	9.3	9.3	8.1	8.1	8.1	7.0	7.0	5.7	5.7	4.7	3.4
65°	9.3	9.3	8.1	8.1	8.1	8.1	7.0	7.0	5.7	4.7	3.4
67.5°	9.3	9.3	9.3	9.3	8.1	8.1	8.1	7.0	5.7	4.7	3.4
70°	10.4	10.4	9.3	9.3	9.3	8.1	8.1	7.0	5.7	5.7	4.7
72.5°	10.4	10.4	9.3	9.3	9.3	9.3	8.1	7.0	7.0	5.7	4.7
75°	10.4	10.4	10.4	10.4	9.3	9.3	8.1	8.1	7.0	5.7	4.7
77.5°	10.4	10.4	10.4	10.4	9.3	9.3	9.3	8.1	7.0	5.7	4.7
80°	10.4	10.4	10.4	10.4	10.4	9.3	9.3	8.1	7.0	5.7	4.7
82.5°	11.7	11.7	10.4	10.4	10.4	9.3	9.3	8.1	7.0	5.7	5.7
85°	11.7	11.7	10.4	10.4	10.4	9.3	9.3	8.1	7.0	7.0	5.7
87.5°	11.7	11.7	10.4	10.4	10.4	9.3	9.3	8.1	7.0	7.0	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192769

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7	1153.7
2.5°	612.9	577.9	566.4	574.5	565.2	558.2	548.9	544.2
5°	383.8	358.2	350.1	352.5	344.2	337.2	327.9	325.6
7.5°	236.1	211.7	202.3	202.3	193.0	184.9	179.2	175.6
10°	158.2	153.5	154.6	155.9	154.6	155.9	152.3	154.6
12.5°	169.9	167.5	169.9	170.9	170.9	173.3	168.6	172.2
15°	197.7	195.3	198.9	201.2	201.2	204.7	200.0	203.6
17.5°	242.0	240.7	246.6	249.0	250.0	255.8	250.0	254.7
20°	305.8	304.7	312.8	316.4	315.2	326.8	318.7	326.8
22.5°	388.5	386.2	397.7	401.2	402.3	417.6	410.6	416.3
25°	471.0	473.4	479.1	485.0	486.1	499.0	488.4	494.3
27.5°	488.4	485.0	488.4	495.4	496.7	502.4	493.1	497.8
30°	442.0	436.1	437.3	445.4	447.7	450.0	442.0	444.3
32.5°	359.4	350.1	350.1	358.2	360.5	364.0	350.1	355.9
35°	265.1	257.0	257.0	262.8	264.0	266.4	255.8	260.5
37.5°	181.4	174.5	176.8	179.2	180.3	182.6	181.4	180.3
40°	116.2	111.6	115.2	115.2	116.2	117.5	117.5	118.6
42.5°	71.0	67.4	69.8	69.8	71.0	71.0	71.0	72.1
45°	40.7	39.5	39.5	40.7	40.7	40.7	39.5	40.7
47.5°	22.1	21.0	22.1	22.1	22.1	22.1	22.1	22.1
50°	11.7	10.4	10.4	10.4	10.4	10.4	10.4	10.4
52.5°	5.7	4.7	4.7	4.7	3.4	4.7	3.4	3.4
55°	3.4	2.3	2.3	2.3	1.1	1.1	0.0	0.0
57.5°	2.3	1.1	1.1	1.1	0.0	0.0	0.0	0.0
60°	2.3	1.1	1.1	1.1	0.0	0.0	0.0	0.0
62.5°	2.3	1.1	1.1	1.1	0.0	0.0	0.0	0.0
65°	2.3	1.1	1.1	1.1	0.0	0.0	0.0	0.0
67.5°	3.4	2.3	1.1	1.1	1.1	0.0	0.0	0.0
70°	3.4	2.3	2.3	1.1	1.1	0.0	0.0	0.0
72.5°	3.4	2.3	2.3	2.3	1.1	1.1	0.0	0.0
75°	3.4	2.3	2.3	2.3	1.1	1.1	0.0	0.0
77.5°	3.4	3.4	2.3	2.3	1.1	1.1	1.1	0.0
80°	4.7	3.4	2.3	2.3	2.3	1.1	1.1	1.1
82.5°	4.7	3.4	2.3	2.3	2.3	1.1	1.1	1.1
85°	4.7	3.4	3.4	2.3	2.3	1.1	1.1	1.1
87.5°	4.7	3.4	3.4	2.3	2.3	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)