

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192771

Luminaire Tested: **LDA6A75927D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192771
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26690)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75927D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5941.2 lumens
Efficiency: N/A
Efficacy: 68.4 lumens/watt
Spacing Criteria (0/90/45): 2.55 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192771

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192771

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	75	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65		
5	85	74	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	59864	59864	59864
5°	154556	55486	17345
10°	293198	42334	5828
15°	524254	27526	5812
20°	781169	18721	10583
25°	891324	23360	66476
30°	963920	19509	19883
35°	1012546	9496	6231
40°	1028563	3414	3156
45°	916390	2256	1892
50°	588552	1586	1288
55°	154948	1118	669
60°	34559	1140	515
65°	3321	1349	610
70°	1122	1667	753
75°	233	2203	1207
80°	0	3694	1799
85°	0	6542	2956



TEST NUMBER: P1192771

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	132.6	2.2
10°-20°	692.1	11.6
20°-30°	1623.9	27.3
30°-40°	1867.9	31.4
40°-50°	1326.8	22.3
50°-60°	269.8	4.5
60°-70°	13.5	0.2
70°-80°	8.0	0.1
80°-90°	6.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2448.6	41.2
0°-40°	4316.5	72.7
0°-60°	5913.1	99.5
0°-90°	5941.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5941.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1092	1092	1092	1092	1092	
5°	2809	2032	1008	404	315	342
15°	9237	4153	485	109	102	2771
25°	14736	5002	386	843	1099	6791
35°	15130	3512	142	105	93	9399
45°	11820	1249	29	31	24	8711
55°	1621	33	12	12	7	2186
65°	26	9	10	9	5	62
75°	1	6	10	9	6	3
85°	0	6	10	8	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192771

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0
2.5°	1881.6	1824.7	1796.8	1795.5	1714.2	1741.0	1714.2	1693.3	1617.6	1586.2	1534.0
5°	2808.6	2738.8	2682.9	2658.5	2518.9	2488.8	2474.8	2403.8	2245.7	2153.7	2031.7
7.5°	3901.7	3828.5	3736.5	3663.3	3461.0	3403.9	3366.8	3244.7	3010.9	2826.0	2598.0
10°	5267.1	5224.0	5075.1	4940.2	4633.2	4514.6	4402.9	4118.0	3812.2	3441.2	3146.9
12.5°	7105.6	7004.5	6739.3	6469.4	5988.0	5811.3	5626.4	5170.4	4702.9	4121.4	3635.3
15°	9237.3	9151.2	8743.1	8303.5	7618.5	7327.7	7038.2	6320.7	5602.0	4852.9	4152.8
17.5°	11691.1	11528.4	11122.5	10379.3	9421.1	8964.1	8424.4	7510.3	6473.0	5455.4	4585.5
20°	13390.3	13293.6	12950.6	12237.6	11146.9	10543.3	9873.5	8618.6	7199.8	5938.1	4869.2
22.5°	14319.4	14222.9	13965.9	13336.7	12442.5	11836.6	11058.5	9515.3	7748.7	6262.4	5003.0
25°	14735.7	14673.0	14532.2	14019.3	13191.4	12645.9	11909.7	10135.0	8091.8	6410.2	5001.8
27.5°	15120.7	15137.0	14789.2	14367.1	13604.3	13056.5	12358.7	10414.2	8159.3	6335.8	4841.4
30°	15227.6	15186.9	15034.6	14440.3	13729.8	13133.2	12385.4	10266.5	7896.5	6006.6	4522.7
32.5°	15161.4	15162.5	15019.5	14388.0	13553.0	12885.5	12044.6	9737.4	7384.7	5490.2	4027.3
35°	15130.0	15119.4	14748.5	14193.9	13133.2	12348.1	11288.8	8888.4	6675.3	4830.8	3512.1
37.5°	14818.3	14755.5	14488.0	13735.6	12348.1	11344.5	10203.7	7849.9	5802.0	4144.7	2984.2
40°	14372.9	14293.8	13858.8	12779.7	11006.1	9886.2	8752.4	6674.2	4887.9	3462.1	2395.7
42.5°	13460.0	13329.7	12670.3	11238.7	9278.0	8236.0	7296.3	5497.2	3995.9	2810.9	1839.8
45°	11820.2	11607.3	10694.5	9198.9	7489.3	6671.9	5877.5	4406.4	3199.3	2093.3	1249.0
47.5°	9490.9	9258.3	8430.3	7228.9	5863.7	5200.7	4526.3	3244.7	2164.3	1219.9	626.9
50°	6901.0	6740.4	6009.0	4996.0	3877.3	3321.4	2803.9	1809.5	1038.6	589.6	257.0
52.5°	3976.1	3861.0	3351.6	2629.4	1907.3	1596.8	1283.9	789.6	529.1	233.7	82.5
55°	1621.2	1554.8	1331.6	1128.1	846.6	731.5	610.6	394.3	177.9	55.8	32.6
57.5°	793.2	784.9	654.7	524.5	386.2	311.7	235.0	79.1	43.0	28.0	21.0
60°	315.2	303.5	208.2	120.9	67.4	54.7	46.5	32.6	24.4	18.6	15.1
62.5°	54.7	53.5	45.4	38.4	31.4	28.0	25.6	19.7	16.3	12.7	11.7
65°	25.6	25.6	23.3	21.0	17.4	16.3	15.1	12.7	10.4	9.3	9.3
67.5°	12.7	12.7	11.7	10.4	9.3	9.3	8.1	8.1	7.0	7.0	7.0
70°	7.0	7.0	7.0	5.7	5.7	5.7	5.7	5.7	4.7	5.7	5.7
72.5°	4.7	4.7	4.7	3.4	2.3	3.4	3.4	3.4	4.7	5.7	5.7
75°	1.1	1.1	1.1	2.3	2.3	2.3	3.4	3.4	4.7	5.7	5.7
77.5°	1.1	1.1	1.1	1.1	2.3	2.3	2.3	3.4	4.7	5.7	5.7
80°	0.0	1.1	1.1	1.1	2.3	2.3	2.3	3.4	4.7	5.7	5.7
82.5°	0.0	0.0	1.1	1.1	2.3	2.3	2.3	3.4	4.7	5.7	5.7
85°	0.0	0.0	1.1	1.1	2.3	2.3	2.3	3.4	4.7	5.7	5.7
87.5°	0.0	0.0	1.1	1.1	2.3	2.3	2.3	3.4	4.7	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192771

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0
2.5°	1510.7	1450.2	1410.6	1340.8	1311.8	1299.0	1235.0	1173.4	1114.1	1071.0	1004.8
5°	1938.6	1842.1	1694.4	1556.0	1495.6	1457.2	1331.6	1215.2	1104.8	1008.3	893.1
7.5°	2399.1	2200.3	1968.8	1746.7	1642.1	1572.4	1378.1	1208.3	1050.2	903.7	746.6
10°	2841.1	2528.2	2191.0	1873.5	1731.7	1626.9	1373.4	1156.0	950.1	760.5	591.9
12.5°	3217.9	2813.1	2365.4	1953.7	1768.8	1635.1	1330.4	1065.3	815.2	611.7	465.1
15°	3535.4	3031.7	2480.5	1980.5	1758.4	1600.2	1246.6	940.8	667.6	485.0	375.6
17.5°	3758.7	3137.6	2507.3	1935.1	1685.2	1502.6	1120.0	781.5	524.5	391.9	296.5
20°	3889.0	3151.6	2442.2	1824.7	1557.1	1364.1	960.5	614.0	425.6	320.9	230.3
22.5°	3908.7	3083.0	2314.3	1675.9	1409.5	1223.5	800.2	514.1	387.3	300.1	225.6
25°	3813.3	2946.9	2148.0	1530.4	1275.7	1085.0	692.0	519.8	435.0	386.2	401.2
27.5°	3628.3	2722.5	1957.3	1381.5	1136.1	943.1	653.6	544.2	474.4	482.7	510.5
30°	3344.6	2406.1	1682.9	1129.2	869.9	718.7	519.8	391.9	325.6	308.2	309.4
32.5°	2927.2	2009.5	1321.1	783.9	584.9	485.0	329.1	218.7	219.7	203.6	202.3
35°	2450.4	1617.6	988.5	525.7	404.7	337.2	194.3	153.5	147.6	141.9	133.8
37.5°	1978.1	1250.2	658.3	359.3	258.1	187.3	97.7	80.2	74.4	69.8	69.8
40°	1506.0	874.6	407.0	188.3	104.7	76.8	58.1	48.8	47.7	47.7	46.5
42.5°	1093.1	516.4	221.0	74.4	58.1	51.1	40.7	36.1	36.1	36.1	36.1
45°	581.5	262.8	84.8	46.5	38.4	36.1	30.3	28.0	28.0	29.1	29.1
47.5°	268.7	98.8	43.0	31.4	26.7	26.7	23.3	22.1	22.1	23.3	23.3
50°	96.5	40.7	28.0	22.1	19.7	21.0	18.6	17.4	18.6	18.6	18.6
52.5°	37.1	25.6	19.7	17.4	15.1	16.3	14.0	14.0	15.1	15.1	15.1
55°	23.3	18.6	15.1	12.7	11.7	12.7	11.7	11.7	11.7	11.7	11.7
57.5°	16.3	14.0	11.7	10.4	9.3	10.4	10.4	10.4	10.4	10.4	10.4
60°	12.7	10.4	9.3	9.3	9.3	9.3	9.3	9.3	9.3	10.4	10.4
62.5°	10.4	9.3	9.3	9.3	9.3	9.3	9.3	9.3	10.4	10.4	10.4
65°	9.3	8.1	9.3	9.3	8.1	9.3	9.3	9.3	10.4	10.4	11.7
67.5°	7.0	7.0	7.0	8.1	8.1	8.1	9.3	9.3	10.4	10.4	10.4
70°	7.0	7.0	8.1	8.1	8.1	8.1	9.3	9.3	10.4	10.4	10.4
72.5°	7.0	7.0	8.1	8.1	8.1	9.3	9.3	9.3	10.4	10.4	10.4
75°	7.0	7.0	8.1	8.1	8.1	9.3	9.3	9.3	10.4	10.4	10.4
77.5°	7.0	7.0	8.1	8.1	8.1	9.3	9.3	10.4	10.4	10.4	10.4
80°	7.0	8.1	8.1	9.3	9.3	9.3	9.3	10.4	10.4	11.7	11.7
82.5°	7.0	8.1	8.1	9.3	9.3	9.3	9.3	10.4	10.4	11.7	11.7
85°	7.0	8.1	8.1	9.3	9.3	9.3	9.3	10.4	10.4	10.4	10.4
87.5°	7.0	8.1	8.1	9.3	9.3	9.3	9.3	9.3	10.4	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192771

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0
2.5°	960.5	903.7	846.6	818.7	794.3	759.5	715.2	679.1	640.7	621.0	575.6
5°	802.5	704.8	622.2	582.6	552.5	510.5	465.1	432.6	403.6	387.3	358.2
7.5°	621.0	527.9	456.0	425.6	403.6	361.6	327.9	294.2	264.0	242.0	212.7
10°	480.3	408.2	348.9	319.8	295.4	251.1	210.6	179.0	146.5	124.5	115.2
12.5°	381.5	314.1	253.5	224.4	198.9	153.5	123.2	117.5	111.6	109.2	105.8
15°	293.1	231.4	167.5	138.5	127.9	122.1	115.2	113.9	109.2	109.2	105.8
17.5°	219.7	151.2	127.9	125.6	124.5	122.1	118.6	117.5	116.2	116.2	115.2
20°	158.2	146.5	143.0	145.3	146.5	148.9	147.6	147.6	152.3	162.9	160.5
22.5°	222.1	240.7	260.5	267.4	293.1	318.6	341.9	370.9	439.6	518.7	537.2
25°	439.6	495.4	546.6	574.5	616.3	673.4	728.1	795.5	843.2	882.7	928.1
27.5°	546.6	567.5	559.4	562.9	558.2	550.1	552.5	566.3	559.4	538.5	546.6
30°	323.2	339.6	330.2	334.9	322.1	322.1	318.6	325.6	320.9	312.8	310.5
32.5°	210.6	219.7	218.7	218.7	214.0	211.7	203.6	201.2	193.0	177.9	174.5
35°	126.8	120.9	115.2	111.6	109.2	109.2	108.2	108.2	104.7	101.2	100.1
37.5°	68.7	69.8	69.8	69.8	69.8	72.1	70.9	70.9	70.9	68.7	68.7
40°	47.7	50.0	50.0	50.0	51.1	51.1	51.1	52.4	51.1	51.1	51.1
42.5°	37.1	38.4	37.1	37.1	38.4	38.4	38.4	39.5	39.5	39.5	38.4
45°	30.3	30.3	29.1	30.3	30.3	31.4	31.4	31.4	31.4	30.3	30.3
47.5°	24.4	24.4	24.4	24.4	25.6	25.6	25.6	25.6	25.6	25.6	25.6
50°	19.7	19.7	19.7	21.0	21.0	21.0	19.7	21.0	21.0	21.0	19.7
52.5°	15.1	15.1	15.1	15.1	15.1	14.0	14.0	14.0	14.0	14.0	12.7
55°	11.7	11.7	11.7	11.7	11.7	12.7	11.7	12.7	11.7	11.7	10.4
57.5°	10.4	10.4	10.4	10.4	11.7	11.7	10.4	10.4	10.4	9.3	9.3
60°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	9.3	8.1	8.1
62.5°	11.7	11.7	10.4	10.4	10.4	10.4	9.3	9.3	9.3	8.1	8.1
65°	11.7	11.7	10.4	11.7	11.7	10.4	10.4	9.3	9.3	8.1	8.1
67.5°	11.7	11.7	11.7	11.7	11.7	11.7	10.4	10.4	9.3	9.3	8.1
70°	11.7	11.7	11.7	11.7	11.7	11.7	10.4	10.4	9.3	9.3	8.1
72.5°	11.7	11.7	11.7	11.7	11.7	11.7	10.4	10.4	10.4	9.3	8.1
75°	11.7	11.7	11.7	11.7	11.7	10.4	10.4	10.4	9.3	9.3	8.1
77.5°	11.7	11.7	11.7	11.7	11.7	10.4	10.4	10.4	9.3	9.3	8.1
80°	11.7	11.7	11.7	11.7	11.7	11.7	10.4	10.4	9.3	9.3	8.1
82.5°	11.7	11.7	11.7	11.7	11.7	10.4	10.4	10.4	9.3	9.3	8.1
85°	11.7	10.4	10.4	10.4	10.4	10.4	9.3	9.3	8.1	8.1	7.0
87.5°	10.4	10.4	10.4	10.4	10.4	9.3	9.3	8.1	7.0	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192771

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0	1092.0
2.5°	575.6	565.2	560.5	552.5	545.5	541.9	529.1	544.2
5°	352.3	339.6	336.1	329.1	320.9	316.4	307.1	315.2
7.5°	201.2	186.0	179.0	173.3	165.2	158.2	150.0	154.6
10°	112.8	108.2	109.2	105.8	104.7	103.5	102.4	104.7
12.5°	104.7	101.2	102.4	100.1	98.8	98.8	97.7	98.8
15°	105.8	102.4	104.7	102.4	101.2	101.2	100.1	102.4
17.5°	115.2	112.8	115.2	112.8	113.9	112.8	113.9	115.2
20°	161.6	165.2	172.2	167.5	170.9	175.6	181.4	181.4
22.5°	568.6	643.1	652.4	689.7	784.9	781.5	845.4	847.7
25°	993.2	997.8	1039.6	1025.7	1026.9	1075.7	1071.0	1099.0
27.5°	570.9	569.9	577.9	562.9	567.5	570.9	558.2	573.3
30°	318.6	312.8	316.4	308.2	308.2	310.5	307.1	314.1
32.5°	176.7	172.2	172.2	166.3	165.2	163.9	160.5	163.9
35°	101.2	97.7	98.8	96.5	94.2	93.1	91.8	93.1
37.5°	69.8	67.4	68.7	66.4	64.0	62.8	61.7	62.8
40°	51.1	50.0	50.0	47.7	46.5	45.4	44.1	44.1
42.5°	38.4	37.1	37.1	35.0	33.7	32.6	31.4	32.6
45°	29.1	28.0	28.0	26.7	25.6	24.4	24.4	24.4
47.5°	25.6	24.4	25.6	24.4	23.3	23.3	23.3	23.3
50°	19.7	19.7	19.7	18.6	17.4	17.4	16.3	15.1
52.5°	12.7	11.7	11.7	10.4	10.4	9.3	9.3	9.3
55°	10.4	9.3	9.3	8.1	8.1	7.0	7.0	7.0
57.5°	8.1	8.1	7.0	7.0	5.7	5.7	5.7	5.7
60°	7.0	7.0	7.0	5.7	5.7	4.7	4.7	4.7
62.5°	7.0	5.7	5.7	5.7	4.7	4.7	4.7	4.7
65°	7.0	5.7	5.7	5.7	4.7	4.7	4.7	4.7
67.5°	7.0	5.7	5.7	5.7	4.7	4.7	4.7	4.7
70°	8.1	7.0	7.0	5.7	5.7	5.7	4.7	4.7
72.5°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
75°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
77.5°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
80°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
82.5°	7.0	7.0	7.0	5.7	5.7	5.7	5.7	5.7
85°	7.0	5.7	5.7	5.7	4.7	4.7	4.7	4.7
87.5°	4.7	4.7	3.4	3.4	3.4	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)