

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192774

Luminaire Tested: **LDA6A75927D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192774
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26684)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75927D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4793.5 lumens
Efficiency: N/A
Efficacy: 55.2 lumens/watt
Spacing Criteria (0/90/45): 2.21 / 1.07 / 1.54
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192774

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192774

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	61		
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54		
6	77	65	57	51	75	64	57	51	62	56	51	61	55	50	59	54	50	48		
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35		
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	75619	75619	75619
5°	120135	74692	48514
10°	180246	71670	32570
15°	258288	67923	24098
20°	340953	63507	20080
25°	409227	61909	29336
30°	457267	62060	44317
35°	470121	55580	37825
40°	453027	44197	28138
45°	399266	32817	21638
50°	311367	24306	14976
55°	180075	17777	9672
60°	84171	12367	4331
65°	39369	6797	1816
70°	18256	2981	1298
75°	7646	1970	1483
80°	3283	2210	1799
85°	692	3585	2956

TEST NUMBER: P1192774

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.6	3.0
10°-20°	523.6	10.9
20°-30°	1036.6	21.6
30°-40°	1340.2	28.0
40°-50°	1101.3	23.0
50°-60°	509.1	10.6
60°-70°	116.2	2.4
70°-80°	19.0	0.4
80°-90°	4.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1702.8	35.5
0°-40°	3043.0	63.5
0°-60°	4653.5	97.1
0°-90°	4793.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4793.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1379	1379	1379	1379	1379	
5°	2183	1877	1357	982	882	241
15°	4551	3044	1197	536	425	1329
25°	6766	3787	1024	502	485	3115
35°	7025	3466	830	551	565	4349
45°	5150	2340	423	281	279	3919
55°	1884	911	186	120	101	1771
65°	304	186	52	20	14	348
75°	36	21	9	8	7	48
85°	1	3	6	6	5	3
90°	0	0	0	0	0	

TEST NUMBER: P1192774

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4
2.5°	1751.5	1724.8	1741.1	1749.2	1707.4	1716.7	1721.4	1688.8	1679.4	1662.0	1610.9
5°	2183.1	2151.7	2164.4	2164.4	2102.8	2106.3	2104.0	2042.3	2008.6	1964.4	1877.1
7.5°	2691.3	2659.9	2662.2	2650.5	2563.4	2557.6	2520.3	2444.8	2378.4	2297.0	2166.8
10°	3238.0	3219.3	3207.7	3178.6	3063.5	3043.7	2989.0	2869.2	2760.0	2635.5	2451.8
12.5°	3879.9	3842.8	3809.1	3762.5	3612.5	3575.2	3498.4	3325.2	3164.6	2990.3	2747.2
15°	4551.0	4521.9	4467.4	4394.0	4202.1	4142.9	4042.8	3810.2	3610.2	3355.5	3043.7
17.5°	5245.3	5191.8	5111.7	5008.2	4776.6	4693.0	4568.5	4270.8	4005.5	3688.0	3311.2
20°	5844.4	5802.4	5691.9	5558.3	5293.0	5181.4	5034.9	4669.7	4345.2	3968.4	3525.2
22.5°	6364.2	6308.4	6172.3	6010.7	5714.2	5575.7	5410.5	5002.3	4606.9	4169.6	3682.3
25°	6765.5	6723.7	6562.0	6373.5	6048.0	5887.4	5704.8	5241.9	4803.5	4323.1	3786.9
27.5°	7092.3	7021.4	6841.1	6628.2	6277.0	6089.8	5896.8	5389.7	4915.1	4401.0	3826.5
30°	7223.7	7150.4	6959.7	6723.7	6351.5	6145.6	5946.6	5405.8	4907.0	4374.3	3778.8
32.5°	7199.3	7116.7	6913.2	6663.2	6282.8	6063.0	5861.8	5300.0	4790.6	4253.4	3649.6
35°	7024.8	6956.3	6745.7	6484.0	6104.8	5873.4	5662.9	5107.0	4596.3	4066.1	3465.9
37.5°	6762.0	6664.3	6467.7	6204.9	5803.7	5588.4	5380.3	4831.3	4332.3	3806.7	3236.7
40°	6330.5	6213.0	6016.4	5787.3	5405.8	5191.8	5002.3	4489.4	3998.5	3507.7	2963.5
42.5°	5787.3	5695.5	5512.9	5276.9	4926.7	4722.1	4552.2	4059.1	3624.1	3169.3	2662.2
45°	5150.0	5061.6	4905.8	4693.0	4376.6	4198.7	4042.8	3604.3	3212.3	2797.1	2340.1
47.5°	4460.4	4373.0	4237.1	4049.8	3767.1	3613.6	3477.6	3118.2	2748.3	2385.4	1984.2
50°	3650.9	3531.1	3456.6	3299.7	3063.5	2933.2	2828.5	2506.3	2233.1	1941.1	1607.3
52.5°	2725.0	2686.6	2579.7	2469.2	2302.9	2206.3	2137.7	1930.7	1703.8	1492.2	1237.5
55°	1884.1	1849.3	1784.2	1716.7	1605.0	1556.2	1504.9	1379.4	1228.1	1083.9	910.7
57.5°	1191.0	1216.5	1174.7	1136.3	1068.9	1051.5	1011.8	938.6	845.5	754.8	646.6
60°	767.7	781.5	754.8	732.7	695.6	681.6	662.9	618.8	562.9	510.7	437.3
62.5°	486.1	493.1	478.0	465.3	444.3	438.5	425.6	400.2	366.4	334.9	288.4
65°	303.5	309.4	298.8	290.8	278.0	279.1	267.4	252.4	232.6	212.9	186.0
67.5°	187.3	190.7	183.7	179.2	170.9	170.9	163.9	154.6	141.9	130.2	112.8
70°	113.9	115.2	110.5	108.2	102.4	101.2	97.7	90.8	82.5	74.4	64.0
72.5°	66.4	67.4	64.0	61.7	58.1	58.1	55.8	52.4	48.8	41.8	36.1
75°	36.1	37.1	35.0	33.7	31.4	32.6	30.3	29.1	25.6	23.3	21.0
77.5°	18.6	19.7	18.6	17.4	17.4	17.4	16.3	15.1	15.1	12.7	12.7
80°	10.4	10.4	10.4	10.4	10.4	9.3	9.3	9.3	9.3	9.3	8.1
82.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	4.7
85°	1.1	1.1	2.3	2.3	2.3	2.3	2.3	2.3	2.3	3.4	3.4
87.5°	0.0	0.0	1.1	1.1	1.1	1.1	1.1	2.3	2.3	2.3	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192774

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4
2.5°	1595.7	1594.6	1541.0	1517.8	1499.2	1470.1	1449.1	1427.1	1407.3	1371.3	1341.0
5°	1833.0	1800.3	1712.1	1656.1	1621.3	1574.9	1523.6	1472.4	1422.4	1357.3	1303.8
7.5°	2081.9	2012.2	1879.4	1786.5	1732.9	1667.8	1581.7	1501.5	1420.1	1330.6	1253.8
10°	2319.1	2205.2	2036.6	1894.7	1821.3	1737.6	1619.0	1507.3	1400.3	1287.5	1192.1
12.5°	2561.0	2398.2	2178.4	1994.6	1901.7	1798.0	1645.7	1507.3	1374.7	1244.5	1131.6
15°	2800.7	2585.4	2312.1	2084.3	1971.4	1848.0	1664.4	1499.2	1343.3	1196.8	1071.2
17.5°	3005.3	2739.0	2409.8	2145.8	2013.2	1873.7	1663.1	1474.8	1301.5	1143.3	1009.5
20°	3164.6	2849.5	2478.5	2177.2	2028.3	1876.0	1644.6	1438.7	1253.8	1088.6	951.4
22.5°	3272.8	2921.6	2513.3	2183.1	2023.7	1863.3	1615.4	1402.7	1210.7	1045.5	908.3
25°	3340.2	2957.6	2523.9	2174.9	2007.5	1841.1	1588.7	1371.3	1182.8	1023.5	895.6
27.5°	3353.1	2947.2	2502.9	2141.1	1969.1	1801.6	1550.3	1341.0	1158.4	1010.7	895.6
30°	3290.3	2879.8	2431.9	2065.6	1897.0	1732.9	1486.4	1286.3	1115.3	980.4	875.8
32.5°	3170.5	2755.3	2314.4	1953.9	1789.9	1636.4	1399.1	1208.4	1043.2	918.7	824.6
35°	2997.3	2589.0	2162.1	1813.2	1653.8	1510.8	1277.1	1102.6	945.6	830.5	743.1
37.5°	2786.7	2388.8	1984.2	1652.7	1501.5	1367.7	1144.4	980.4	835.1	727.0	649.0
40°	2530.7	2172.5	1784.2	1475.9	1331.6	1210.7	1004.8	846.6	709.4	617.6	546.7
42.5°	2263.3	1930.7	1571.3	1278.2	1150.3	1035.1	852.5	710.7	588.5	513.0	457.0
45°	1987.6	1662.0	1348.0	1087.5	990.8	861.9	693.3	578.1	479.1	423.3	379.2
47.5°	1677.1	1401.4	1111.9	882.7	781.5	694.3	553.5	460.6	396.6	347.8	314.1
50°	1343.3	1123.6	880.4	685.0	601.3	535.1	431.6	367.5	318.7	285.0	259.4
52.5°	1032.8	859.5	662.9	502.4	450.0	400.2	336.1	292.0	257.0	231.4	212.9
55°	767.7	626.9	476.8	372.2	334.9	302.4	264.0	229.1	203.6	186.0	170.9
57.5°	540.8	437.3	334.9	269.8	250.0	229.1	200.0	176.8	159.3	145.5	133.8
60°	361.8	297.8	236.1	197.7	183.7	169.9	151.2	134.9	122.1	112.8	101.2
62.5°	243.0	200.0	165.2	141.9	132.6	123.2	110.5	98.8	89.5	80.2	71.0
65°	155.9	132.6	111.6	96.5	89.5	84.8	75.5	67.4	60.5	52.4	45.4
67.5°	95.4	82.5	69.8	60.5	57.0	53.5	47.7	41.8	37.1	31.4	26.7
70°	55.8	48.8	41.8	36.1	35.0	32.6	28.0	24.4	22.1	18.6	16.3
72.5°	32.6	29.1	24.4	22.1	21.0	18.6	17.4	15.1	12.7	11.7	10.4
75°	18.6	16.3	14.0	12.7	12.7	11.7	10.4	10.4	9.3	9.3	8.1
77.5°	11.7	10.4	9.3	9.3	9.3	8.1	8.1	8.1	8.1	7.0	7.0
80°	8.1	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
82.5°	4.7	4.7	4.7	4.7	4.7	5.7	5.7	5.7	5.7	5.7	7.0
85°	3.4	4.7	4.7	4.7	4.7	4.7	5.7	5.7	5.7	5.7	5.7
87.5°	3.4	4.7	4.7	4.7	4.7	4.7	5.7	5.7	5.7	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192774

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4
2.5°	1323.6	1304.9	1247.9	1267.8	1231.7	1202.7	1200.3	1182.8	1152.6	1136.3	1128.2
5°	1263.1	1221.2	1151.4	1156.0	1114.2	1068.9	1044.5	1021.2	981.7	957.1	941.0
7.5°	1188.7	1131.6	1049.1	1043.2	999.1	944.4	909.6	876.9	833.9	802.5	782.8
10°	1110.7	1040.9	944.4	937.4	890.9	831.6	792.1	754.8	710.7	679.3	658.3
12.5°	1038.6	958.4	861.9	844.3	799.1	738.5	695.6	656.0	612.9	586.2	561.8
15°	970.0	882.7	780.4	764.1	720.0	659.5	611.8	576.9	536.1	510.7	488.4
17.5°	901.3	811.8	710.7	692.0	650.2	591.9	550.1	513.0	475.7	451.3	431.6
20°	842.1	752.5	653.6	635.0	596.6	540.8	502.4	467.6	433.9	410.6	394.3
22.5°	803.7	716.4	626.9	610.6	574.5	524.5	488.4	458.3	429.2	407.0	394.3
25°	801.4	725.7	645.5	636.2	605.9	564.1	538.5	519.8	502.4	485.0	480.3
27.5°	815.2	753.7	686.3	683.9	659.5	631.6	619.9	614.2	604.8	598.9	607.2
30°	807.2	754.8	697.8	697.8	679.3	659.5	653.6	651.3	645.5	646.6	656.0
32.5°	764.1	716.4	661.7	662.9	651.3	629.2	625.7	624.6	617.6	616.5	623.3
35°	686.3	642.0	596.6	597.8	588.5	567.5	562.9	560.5	551.2	546.7	551.2
37.5°	596.6	560.5	517.5	517.5	508.3	492.0	487.3	482.7	476.8	472.3	472.3
40°	504.7	475.7	440.7	439.6	432.6	416.3	411.7	408.2	402.5	394.3	396.6
42.5°	426.9	400.2	372.2	369.9	365.2	351.2	346.5	341.9	336.1	329.1	329.1
45°	354.8	337.2	312.8	311.7	307.1	295.4	292.0	286.1	281.4	274.4	274.4
47.5°	295.4	281.4	261.7	260.5	257.0	246.6	243.0	238.4	233.7	229.1	229.1
50°	247.7	233.7	217.6	216.3	214.0	205.9	201.2	197.7	194.3	190.7	188.3
52.5°	203.6	191.9	179.2	177.9	175.6	167.5	163.9	161.6	158.2	152.3	152.3
55°	163.9	154.6	143.1	141.9	139.6	132.6	129.1	124.5	119.8	113.9	112.8
57.5°	127.9	119.8	110.5	109.4	105.8	100.1	94.2	89.5	84.8	80.2	77.9
60°	96.5	87.2	79.1	76.8	74.4	66.4	61.7	57.0	52.4	48.8	46.5
62.5°	65.1	59.4	50.0	48.8	46.5	41.8	36.1	33.7	31.4	29.1	28.0
65°	40.7	36.1	31.4	30.3	28.0	24.4	22.1	21.0	19.7	18.6	17.4
67.5°	24.4	22.1	18.6	18.6	17.4	16.3	14.0	14.0	12.7	12.7	11.7
70°	15.1	14.0	12.7	11.7	11.7	11.7	10.4	10.4	10.4	10.4	10.4
72.5°	10.4	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
75°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
77.5°	8.1	8.1	7.0	8.1	8.1	8.1	8.1	7.0	8.1	7.0	7.0
80°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
82.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	5.7	5.7	5.7	5.7
85°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	4.7
87.5°	5.7	5.7	5.7	5.7	5.7	4.7	4.7	4.7	4.7	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192774

CATALOG NUMBER: LDA6A75927D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4	1379.4
2.5°	1130.6	1097.9	1110.7	1092.2	1086.3	1081.6	1074.6	1096.8
5°	934.0	899.0	907.2	888.6	880.4	872.3	864.2	881.6
7.5°	771.1	737.4	740.8	724.6	716.4	707.1	699.0	713.0
10°	644.3	612.9	614.2	598.9	590.8	581.5	574.5	585.1
12.5°	547.8	518.7	518.7	507.1	500.1	489.7	483.8	492.0
15°	474.6	449.0	449.0	437.3	431.6	422.2	416.3	424.6
17.5°	418.7	395.5	395.5	387.3	381.5	373.3	368.6	375.6
20°	381.5	361.8	362.9	354.8	350.1	340.8	338.5	344.2
22.5°	384.9	366.4	368.6	362.9	358.2	351.2	348.9	357.1
25°	481.4	467.6	475.7	475.7	478.0	467.6	472.3	485.0
27.5°	618.8	611.8	624.6	619.9	629.2	629.2	633.9	650.2
30°	668.7	662.9	676.9	675.7	685.0	682.7	685.0	700.1
32.5°	632.6	626.9	638.5	637.3	644.3	638.5	639.6	652.5
35°	555.9	550.1	558.2	557.1	561.8	554.8	558.2	565.2
37.5°	474.6	468.7	473.4	472.3	473.4	465.3	469.9	473.4
40°	398.9	391.9	398.9	394.3	395.5	387.3	388.5	393.2
42.5°	333.8	325.7	331.5	331.5	331.5	325.7	326.8	331.5
45°	278.0	272.1	275.7	274.4	275.7	271.0	274.4	279.1
47.5°	230.3	225.6	228.0	226.7	226.7	222.1	223.3	223.3
50°	189.6	184.9	186.0	184.9	181.5	175.6	174.5	175.6
52.5°	150.0	144.2	144.2	141.9	139.6	134.9	134.9	136.1
55°	110.5	105.8	105.8	104.7	102.4	98.8	98.8	101.2
57.5°	74.4	71.0	72.1	71.0	71.0	66.4	68.7	68.7
60°	45.4	43.0	43.0	41.8	39.5	38.4	37.1	39.5
62.5°	26.7	25.6	25.6	24.4	24.4	23.3	23.3	23.3
65°	17.4	16.3	16.3	15.1	15.1	14.0	12.7	14.0
67.5°	11.7	10.4	10.4	10.4	10.4	9.3	9.3	9.3
70°	10.4	9.3	9.3	9.3	9.3	8.1	8.1	8.1
72.5°	9.3	8.1	9.3	8.1	8.1	8.1	8.1	8.1
75°	8.1	8.1	8.1	7.0	7.0	7.0	7.0	7.0
77.5°	7.0	7.0	7.0	7.0	7.0	5.7	5.7	5.7
80°	7.0	5.7	5.7	5.7	5.7	5.7	5.7	5.7
82.5°	5.7	5.7	5.7	5.7	5.7	4.7	4.7	4.7
85°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
87.5°	3.4	3.4	3.4	3.4	3.4	2.3	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)