

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192777

Luminaire Tested: **LDA6A75927D010TE LARH40FL 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192777
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26691)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75927D010TE LARH40FL 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6250.6 lumens
Efficiency: N/A
Efficacy: 71.9 lumens/watt
Spacing Criteria (0/90/45): 2.62 / 0.52 / 1.36
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192777

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192777

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	50	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	44	40	38		
10	60	48	41	37	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	66749	66749	66749
5°	177151	61886	23679
10°	386683	50044	7058
15°	583681	36567	6141
20°	678948	25103	9638
25°	748767	27080	64153
30°	828425	20389	19952
35°	840728	10433	7469
40°	860069	4251	3578
45°	867284	2613	2171
50°	730603	1791	1390
55°	241310	1214	774
60°	47430	1140	515
65°	5578	1518	610
70°	1491	1667	753
75°	233	2203	1207
80°	0	3694	1799
85°	0	7359	2956



TEST NUMBER: P1192777

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	162.0	2.6
10°-20°	818.3	13.1
20°-30°	1615.1	25.8
30°-40°	1821.8	29.1
40°-50°	1446.3	23.1
50°-60°	353.6	5.7
60°-70°	18.9	0.3
70°-80°	8.0	0.1
80°-90°	6.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2595.4	41.5
0°-40°	4417.2	70.7
0°-60°	6217.0	99.5
0°-90°	6250.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6250.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1218	1218	1218	1218	1218	
5°	3219	2412	1125	565	430	425
15°	10284	5466	644	127	108	2885
25°	12379	6626	448	811	1061	5733
35°	12563	4217	156	123	112	7901
45°	11187	1314	34	35	28	8384
55°	2525	57	13	13	8	2962
65°	43	10	12	9	5	105
75°	1	6	10	9	6	3
85°	0	6	12	8	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192777

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6
2.5°	2113.2	2072.4	2091.1	2062.0	1979.4	1953.9	1974.7	1943.3	1849.1	1813.1	1775.9
5°	3219.2	3183.1	3194.8	3128.4	2973.8	2920.3	2916.8	2821.5	2630.7	2523.7	2412.0
7.5°	4881.0	4831.0	4817.2	4657.7	4360.1	4248.4	4193.7	3958.9	3599.4	3344.7	3094.7
10°	6946.5	6995.4	6945.4	6687.1	6219.7	6010.4	5877.8	5433.5	4785.8	4300.8	3833.2
12.5°	9017.9	9048.0	8953.8	8632.9	8038.7	7787.4	7592.0	7023.3	6169.6	5346.3	4648.4
15°	10284.4	10427.4	10338.9	10114.5	9653.9	9349.3	9173.7	8471.2	7396.7	6491.8	5466.1
17.5°	11186.8	11319.4	11246.2	11062.3	10542.5	10297.1	10183.2	9605.1	8435.1	7285.0	6077.8
20°	11638.1	11799.7	11733.4	11525.3	11143.8	10939.1	10800.6	10236.7	9181.8	7874.6	6486.0
22.5°	11943.9	12123.0	12050.9	11861.4	11472.9	11234.5	11169.4	10635.6	9572.6	8228.1	6659.3
25°	12378.9	12528.9	12325.4	12091.6	11707.9	11456.6	11417.1	10871.7	9759.8	8361.9	6625.6
27.5°	12690.5	12868.4	12523.1	12285.8	11847.4	11583.4	11532.3	11019.3	9777.3	8256.1	6352.2
30°	13087.1	12972.1	12668.4	12324.2	11856.8	11575.3	11510.1	10933.4	9602.8	7866.5	5817.3
32.5°	12930.1	12902.1	12598.6	12194.0	11757.9	11474.0	11386.8	10668.1	9123.7	7194.2	5060.2
35°	12562.6	12651.0	12397.6	12146.3	11604.4	11309.0	11187.9	10277.4	8401.4	6328.9	4217.0
37.5°	12347.5	12403.3	12242.8	11935.9	11398.5	11010.0	10780.9	9620.2	7455.9	5238.2	3404.1
40°	12018.4	12160.3	12005.6	11653.2	11033.3	10500.7	10101.8	8432.9	6210.4	4129.8	2662.0
42.5°	11657.8	11784.6	11636.9	11214.8	10338.9	9624.9	8962.1	7037.3	4862.4	3155.1	1996.9
45°	11186.8	11300.7	11035.6	10378.6	9138.8	8153.7	7492.0	5526.6	3666.9	2317.8	1314.2
47.5°	10337.8	10307.5	9931.9	8910.8	7383.8	6501.1	5731.2	3958.9	2437.6	1313.0	653.6
50°	8566.6	8284.0	7731.6	6546.5	4955.5	4001.9	3476.2	2043.4	1106.0	636.2	410.6
52.5°	5548.7	5233.5	4727.5	3633.2	2379.5	1909.6	1531.6	923.4	576.9	359.3	161.6
55°	2524.8	2301.5	1978.3	1467.6	1021.2	849.0	718.7	467.5	309.4	133.8	57.0
57.5°	961.8	887.3	788.5	629.2	472.1	408.2	338.5	224.4	96.5	50.0	33.7
60°	432.6	401.2	368.6	288.4	202.3	145.3	110.5	60.5	40.7	29.1	22.1
62.5°	147.6	123.2	102.4	73.2	54.7	47.7	41.8	33.7	24.4	19.7	15.1
65°	43.0	41.8	39.5	35.0	28.0	25.6	24.4	19.7	15.1	12.7	10.4
67.5°	21.0	19.7	18.6	17.4	14.0	12.7	12.7	11.7	9.3	8.1	7.0
70°	9.3	9.3	8.1	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
72.5°	4.7	4.7	4.7	3.4	3.4	3.4	3.4	4.7	4.7	5.7	5.7
75°	1.1	2.3	2.3	2.3	2.3	3.4	3.4	4.7	4.7	5.7	5.7
77.5°	1.1	1.1	1.1	2.3	2.3	2.3	3.4	4.7	4.7	5.7	5.7
80°	0.0	1.1	1.1	2.3	2.3	2.3	3.4	3.4	4.7	5.7	5.7
82.5°	0.0	1.1	1.1	2.3	2.3	2.3	3.4	3.4	4.7	5.7	5.7
85°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
87.5°	0.0	0.0	1.1	1.1	2.3	2.3	3.4	3.4	4.7	5.7	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192777

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6
2.5°	1685.2	1660.8	1564.3	1489.8	1454.9	1452.5	1374.7	1327.0	1243.2	1178.1	1116.4
5°	2215.6	2107.4	1911.9	1757.3	1682.9	1644.5	1490.9	1380.4	1236.2	1124.6	1014.2
7.5°	2755.1	2549.2	2274.8	1980.6	1859.5	1785.3	1548.0	1371.1	1179.4	1023.5	886.3
10°	3307.6	2944.7	2535.4	2146.9	1972.4	1846.8	1542.1	1302.6	1081.6	899.0	749.0
12.5°	3883.2	3311.0	2741.1	2255.0	2024.7	1859.5	1489.8	1202.5	961.8	767.5	624.6
15°	4368.2	3594.8	2871.4	2280.7	2008.4	1808.4	1378.1	1075.7	833.9	644.3	514.1
17.5°	4742.7	3754.1	2895.8	2217.8	1917.8	1694.5	1233.9	936.1	699.0	531.5	402.3
20°	4931.1	3778.6	2819.2	2069.0	1753.7	1523.6	1069.9	794.3	586.2	430.3	319.8
22.5°	4945.1	3664.5	2651.6	1877.1	1573.5	1339.7	935.1	685.0	514.1	386.2	303.5
25°	4763.6	3444.8	2427.2	1680.5	1388.7	1178.1	838.6	657.0	517.5	447.7	411.7
27.5°	4419.3	3140.1	2180.6	1483.9	1229.2	1066.5	798.9	657.0	560.5	505.8	518.7
30°	3942.6	2751.7	1837.5	1216.5	1000.2	858.3	628.0	492.0	386.2	322.1	310.5
32.5°	3323.8	2251.5	1424.7	899.0	729.1	618.7	424.6	308.2	249.0	243.0	236.1
35°	2735.4	1778.3	1081.6	664.0	537.2	437.3	271.0	181.4	165.2	155.9	148.9
37.5°	2160.9	1330.4	776.9	482.7	368.6	278.0	139.6	117.5	102.4	93.1	84.8
40°	1624.7	956.0	547.8	291.8	193.0	119.8	83.8	72.1	64.0	59.4	57.0
42.5°	1149.0	636.2	339.6	123.2	91.8	75.5	58.1	51.1	46.5	44.1	41.8
45°	667.6	395.3	137.2	72.1	58.1	52.4	43.0	38.4	36.1	33.7	32.6
47.5°	417.6	159.3	71.0	46.5	40.7	37.1	31.4	30.3	28.0	26.7	26.7
50°	168.6	71.0	44.1	32.6	29.1	28.0	24.4	23.3	21.0	21.0	21.0
52.5°	64.0	41.8	30.3	23.3	21.0	19.7	17.4	17.4	16.3	16.3	16.3
55°	37.1	28.0	21.0	16.3	15.1	15.1	14.0	14.0	12.7	12.7	12.7
57.5°	24.4	18.6	15.1	11.7	11.7	11.7	10.4	10.4	10.4	10.4	10.4
60°	16.3	12.7	10.4	9.3	9.3	9.3	9.3	10.4	10.4	10.4	10.4
62.5°	11.7	10.4	9.3	9.3	9.3	9.3	9.3	10.4	10.4	10.4	11.7
65°	9.3	8.1	8.1	8.1	8.1	9.3	9.3	10.4	10.4	11.7	11.7
67.5°	7.0	7.0	7.0	7.0	8.1	8.1	9.3	10.4	10.4	10.4	11.7
70°	5.7	7.0	7.0	8.1	8.1	8.1	9.3	9.3	10.4	10.4	11.7
72.5°	5.7	7.0	7.0	8.1	8.1	8.1	9.3	10.4	10.4	10.4	11.7
75°	5.7	7.0	7.0	8.1	8.1	8.1	9.3	10.4	10.4	10.4	11.7
77.5°	7.0	7.0	8.1	8.1	8.1	9.3	9.3	10.4	10.4	11.7	11.7
80°	7.0	7.0	8.1	8.1	8.1	9.3	9.3	10.4	10.4	11.7	11.7
82.5°	7.0	7.0	8.1	8.1	8.1	9.3	9.3	10.4	10.4	11.7	11.7
85°	7.0	7.0	8.1	8.1	8.1	9.3	9.3	10.4	10.4	11.7	11.7
87.5°	7.0	7.0	8.1	8.1	8.1	9.3	9.3	10.4	10.4	10.4	11.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192777

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6
2.5°	1086.3	1032.8	974.5	956.0	937.4	901.3	879.3	839.6	810.6	781.5	758.2
5°	940.8	856.0	785.1	754.8	725.7	675.7	640.9	598.9	565.2	536.1	509.4
7.5°	789.6	692.0	621.0	590.8	561.8	507.1	462.9	410.6	370.9	338.5	311.7
10°	650.0	557.1	480.3	444.3	410.6	353.5	311.7	269.8	236.1	208.2	183.7
12.5°	529.1	429.1	351.2	324.5	291.8	245.4	205.9	160.5	140.8	132.6	126.8
15°	410.6	321.1	255.8	231.4	202.3	158.2	140.8	132.6	126.8	123.2	118.6
17.5°	312.8	238.4	174.5	158.2	148.9	139.6	134.9	129.1	125.6	124.5	120.9
20°	245.4	180.3	163.9	159.3	159.3	157.0	153.5	153.5	152.3	155.9	155.9
22.5°	252.4	252.4	266.4	265.1	283.8	302.4	316.4	361.6	387.3	442.0	479.1
25°	440.7	482.7	531.5	546.6	582.6	636.2	692.0	761.8	810.6	863.0	883.9
27.5°	550.1	557.1	550.1	567.5	544.2	530.4	535.1	543.1	543.1	546.6	560.5
30°	325.6	341.9	357.1	368.6	362.9	357.1	354.8	337.2	337.2	330.2	324.5
32.5°	221.0	218.7	216.3	221.0	216.3	216.3	212.9	214.0	207.0	202.3	200.0
35°	151.2	144.2	136.1	137.2	132.6	131.5	127.9	127.9	123.2	120.9	119.8
37.5°	83.8	83.8	80.2	81.4	80.2	80.2	80.2	81.4	80.2	80.2	81.4
40°	57.0	57.0	55.8	57.0	55.8	57.0	58.1	58.1	58.1	58.1	57.0
42.5°	43.0	43.0	41.8	43.0	41.8	43.0	44.1	44.1	44.1	44.1	44.1
45°	33.7	33.7	33.7	33.7	33.7	33.7	33.7	35.0	35.0	33.7	33.7
47.5°	26.7	28.0	26.7	26.7	26.7	26.7	28.0	28.0	26.7	26.7	26.7
50°	22.1	22.1	21.0	21.0	21.0	21.0	21.0	21.0	21.0	21.0	21.0
52.5°	17.4	16.3	16.3	15.1	15.1	15.1	15.1	15.1	15.1	15.1	14.0
55°	12.7	12.7	11.7	11.7	11.7	12.7	12.7	12.7	12.7	11.7	11.7
57.5°	11.7	11.7	11.7	10.4	10.4	11.7	11.7	10.4	10.4	10.4	9.3
60°	10.4	11.7	10.4	10.4	10.4	10.4	10.4	9.3	9.3	9.3	8.1
62.5°	11.7	11.7	10.4	10.4	10.4	10.4	9.3	9.3	9.3	8.1	8.1
65°	11.7	11.7	11.7	10.4	10.4	10.4	10.4	9.3	9.3	8.1	8.1
67.5°	11.7	11.7	11.7	11.7	10.4	10.4	10.4	9.3	9.3	9.3	8.1
70°	11.7	11.7	11.7	11.7	11.7	10.4	10.4	10.4	9.3	9.3	8.1
72.5°	11.7	11.7	11.7	10.4	10.4	10.4	10.4	10.4	9.3	9.3	8.1
75°	11.7	11.7	11.7	10.4	10.4	10.4	10.4	9.3	9.3	9.3	8.1
77.5°	11.7	11.7	11.7	10.4	10.4	10.4	10.4	9.3	9.3	9.3	8.1
80°	11.7	11.7	11.7	10.4	10.4	10.4	10.4	9.3	9.3	9.3	8.1
82.5°	11.7	11.7	11.7	10.4	10.4	10.4	10.4	9.3	9.3	8.1	8.1
85°	11.7	11.7	10.4	10.4	10.4	10.4	9.3	9.3	8.1	8.1	7.0
87.5°	10.4	10.4	10.4	10.4	9.3	9.3	9.3	8.1	7.0	7.0	5.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192777

CATALOG NUMBER: LDA6A75927D010TE LARH40FL 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6	1217.6
2.5°	730.4	725.7	722.2	729.1	726.8	697.8	701.3	700.1
5°	479.1	468.7	460.6	464.0	454.7	442.0	432.6	430.3
7.5°	285.0	273.4	266.4	259.4	257.0	240.7	233.7	238.4
10°	157.0	140.8	139.6	136.1	131.5	127.9	125.6	126.8
12.5°	120.9	119.8	117.5	116.2	113.9	112.8	111.6	110.5
15°	115.2	113.9	112.8	111.6	110.5	109.2	108.2	108.2
17.5°	118.6	118.6	117.5	116.2	116.2	117.5	116.2	115.2
20°	154.6	154.6	157.0	160.5	160.5	163.9	168.6	165.2
22.5°	502.4	528.1	559.4	568.8	623.3	667.6	749.0	713.0
25°	918.7	976.9	990.8	1010.6	1040.9	1056.0	1040.9	1060.6
27.5°	558.2	577.9	580.3	581.5	588.5	587.3	572.2	581.5
30°	324.5	331.5	329.1	327.9	325.6	312.8	310.5	315.2
32.5°	203.6	201.2	200.0	198.9	198.9	191.9	195.3	193.0
35°	116.2	119.8	118.6	117.5	113.9	112.8	112.8	111.6
37.5°	77.9	79.1	77.9	76.8	74.4	73.2	72.1	71.0
40°	55.8	57.0	55.8	54.7	53.5	52.4	51.1	50.0
42.5°	41.8	43.0	41.8	41.8	39.5	38.4	37.1	36.1
45°	32.6	31.4	31.4	31.4	30.3	29.1	28.0	28.0
47.5°	26.7	26.7	26.7	25.6	24.4	24.4	24.4	23.3
50°	19.7	21.0	19.7	19.7	18.6	17.4	17.4	16.3
52.5°	14.0	14.0	12.7	12.7	11.7	10.4	10.4	10.4
55°	10.4	10.4	10.4	9.3	9.3	8.1	8.1	8.1
57.5°	9.3	8.1	8.1	8.1	7.0	7.0	5.7	5.7
60°	8.1	7.0	7.0	5.7	5.7	4.7	4.7	4.7
62.5°	7.0	5.7	5.7	5.7	4.7	4.7	4.7	4.7
65°	7.0	5.7	5.7	5.7	4.7	4.7	4.7	4.7
67.5°	7.0	7.0	5.7	5.7	5.7	4.7	4.7	4.7
70°	7.0	7.0	7.0	5.7	5.7	5.7	4.7	4.7
72.5°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
75°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
77.5°	8.1	7.0	7.0	7.0	5.7	5.7	5.7	5.7
80°	7.0	7.0	7.0	5.7	5.7	5.7	5.7	5.7
82.5°	7.0	7.0	7.0	7.0	5.7	5.7	5.7	5.7
85°	7.0	5.7	5.7	5.7	4.7	4.7	4.7	4.7
87.5°	5.7	4.7	4.7	3.4	3.4	3.4	2.3	2.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)