

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203127

Luminaire Tested: **LE_6B15D010 EC6B10209035 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203127
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10209035 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1500.6 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203127

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203127

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	100	108	105	102	99	101	98	96		97	95	93		93
2	103	96	90	86	100	94	89	85	91	86	83		88	84	81		85
3	95	86	80	74	93	85	79	74	82	77	72		80	75	71		77
4	89	78	71	65	86	77	70	65	75	69	64		72	67	63		70
5	82	71	64	58	80	70	63	58	68	62	57		66	61	56		65
6	77	65	57	52	75	64	57	52	63	56	51		61	55	51		60
7	72	60	52	47	70	59	52	47	58	51	46		56	50	46		55
8	67	55	48	42	66	55	47	42	53	47	42		52	46	42		51
9	63	51	44	39	62	51	44	39	50	43	39		49	43	38		48
10	60	48	40	36	58	47	40	36	46	40	36		45	40	35		45

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203127

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.4	5.3
10°-20°	222.6	14.8
20°-30°	320.7	21.4
30°-40°	332.9	22.2
40°-50°	246.2	16.4
50°-60°	147.0	9.8
60°-70°	89.3	6.0
70°-80°	48.9	3.3
80°-90°	13.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	622.6	41.5
0°-40°	955.5	63.7
0°-60°	1348.7	89.9
0°-90°	1500.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1500.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	843	
5°	837	79
15°	790	223
25°	699	321
35°	537	333
45°	317	246
55°	160	147
65°	89	89
75°	46	49
85°	11	14
90°	0	



TEST NUMBER: P203127

CATALOG NUMBER: LE_6B15D010 EC6B10209035 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	842.8
2.5°	842.8
5°	837.2
7.5°	830.0
10°	819.0
12.5°	806.2
15°	789.9
17.5°	771.8
20°	753.5
22.5°	728.0
25°	698.9
27.5°	668.0
30°	627.9
32.5°	587.9
35°	536.9
37.5°	484.1
40°	425.9
42.5°	369.5
45°	316.8
47.5°	269.4
50°	227.5
52.5°	191.1
55°	160.1
57.5°	136.5
60°	116.5
62.5°	101.9
65°	89.1
67.5°	78.2
70°	67.4
72.5°	56.4
75°	45.5
77.5°	36.4
80°	27.2
82.5°	20.0
85°	10.9
87.5°	5.5
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)