

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192781

Luminaire Tested: **LDA6A75930D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192781
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75930D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6265.4 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192781

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192781

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	96966	96966	96966
5°	187893	92400	31163
10°	319216	80855	13994
15°	491893	64501	22253
20°	712073	41974	38702
25°	1044744	40502	49763
30°	1214757	38373	38139
35°	1229544	20325	20157
40°	1017972	7664	8466
45°	768832	2605	3086
50°	526021	955	955
55°	73163	832	115
60°	1908	822	0
65°	480	1129	0
70°	192	1394	0
75°	0	1843	0
80°	0	3125	379
85°	0	6227	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192781

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	185.6	3.0
10°-20°	784.4	12.5
20°-30°	1789.4	28.6
30°-40°	2070.7	33.1
40°-50°	1248.8	19.9
50°-60°	169.7	2.7
60°-70°	5.5	0.1
70°-80°	5.9	0.1
80°-90°	5.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2759.3	44.0
0°-40°	4830.0	77.1
0°-60°	6248.5	99.7
0°-90°	6265.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6265.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1769	1769	1769	1769	1769	
5°	3414	2796	1679	919	566	397
15°	8667	4872	1136	350	392	2566
25°	17272	5773	670	805	823	7816
35°	18372	4402	304	310	301	11072
45°	9917	1199	34	41	40	7754
55°	766	9	9	6	1	1501
65°	4	5	9	5	0	6
75°	0	6	9	6	0	0
85°	0	6	10	6	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P1192781

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8
2.5°	2557.9	2534.3	2544.3	2518.1	2452.1	2438.4	2437.2	2419.8	2363.8	2320.2	2267.9
5°	3414.4	3413.1	3419.3	3363.4	3247.6	3211.4	3194.0	3151.7	3016.1	2911.5	2795.7
7.5°	4483.5	4476.1	4468.6	4366.5	4184.8	4115.1	4070.3	3917.2	3730.4	3545.0	3338.4
10°	5734.5	5730.8	5702.2	5523.0	5231.6	5103.4	5016.4	4773.7	4473.6	4209.7	3858.6
12.5°	7187.2	7153.5	7102.5	6839.9	6440.4	6301.0	6109.2	5724.6	5264.1	4859.4	4369.0
15°	8667.1	8618.6	8527.7	8190.5	7695.1	7457.3	7219.5	6712.9	6088.1	5500.5	4871.9
17.5°	10114.8	10061.2	9848.5	9275.8	8791.6	8501.6	8237.7	7541.8	6807.6	6052.0	5255.3
20°	12205.9	12011.8	11640.9	10738.5	9838.5	9315.6	9007.0	8271.3	7362.7	6482.6	5528.0
22.5°	14999.2	14568.5	13778.2	12311.8	11026.0	10271.6	9766.3	8787.9	7762.2	6763.9	5696.0
25°	17272.1	17076.7	16178.0	14091.8	12085.2	11196.4	10493.3	9198.7	8053.6	6951.9	5773.2
27.5°	18737.2	18688.6	17661.7	15565.6	12950.3	11784.0	10998.6	9470.1	8194.2	6991.7	5735.8
30°	19190.2	19266.2	18280.3	16066.0	13200.5	11902.3	11043.4	9473.8	8085.9	6811.3	5496.7
32.5°	19156.6	19160.4	17951.8	15634.0	12793.5	11558.7	10669.9	9158.8	7686.4	6359.4	5042.5
35°	18372.5	18179.5	16812.9	14307.1	11846.2	10757.1	9930.5	8548.9	7027.8	5679.8	4401.5
37.5°	16650.9	16398.2	14805.1	12608.0	10724.8	9717.8	9050.5	7748.5	6243.6	4954.1	3739.1
40°	14224.9	13866.4	12552.0	11028.5	9497.4	8740.6	8180.5	6853.6	5404.7	4242.0	3118.2
42.5°	11796.5	11621.0	10752.2	9513.6	8465.6	7753.5	7168.6	5916.3	4598.1	3540.1	2332.6
45°	9916.9	9766.3	9182.4	8365.9	7337.8	6688.1	6124.1	4939.2	3572.4	2375.0	1198.6
47.5°	8547.6	8425.6	7866.8	7009.1	5881.4	5170.7	4589.4	3238.9	2024.0	1025.7	299.9
50°	6167.8	6043.3	5495.5	4502.3	3484.0	2889.1	2470.7	1446.3	573.9	207.9	31.1
52.5°	3023.5	2921.4	2549.2	1908.2	1280.8	921.1	673.4	271.3	66.0	22.4	14.9
55°	765.5	703.4	586.3	368.5	180.4	108.3	69.8	24.9	16.2	12.4	8.7
57.5°	43.5	42.3	38.5	28.6	21.1	18.6	16.2	12.4	8.7	7.5	6.2
60°	17.4	16.2	14.9	12.4	9.9	8.7	8.7	6.2	5.0	5.0	5.0
62.5°	7.5	7.5	7.5	6.2	5.0	5.0	5.0	3.7	5.0	5.0	5.0
65°	3.7	3.7	3.7	2.5	2.5	2.5	3.7	3.7	3.7	5.0	5.0
67.5°	2.5	1.2	1.2	1.2	2.5	2.5	2.5	3.7	3.7	5.0	5.0
70°	1.2	1.2	1.2	1.2	2.5	2.5	2.5	3.7	3.7	5.0	6.2
72.5°	0.0	1.2	1.2	1.2	2.5	2.5	2.5	3.7	3.7	5.0	6.2
75°	0.0	1.2	1.2	1.2	2.5	2.5	2.5	3.7	5.0	5.0	6.2
77.5°	0.0	1.2	1.2	1.2	2.5	2.5	2.5	3.7	5.0	5.0	6.2
80°	0.0	1.2	1.2	1.2	2.5	2.5	2.5	3.7	5.0	5.0	6.2
82.5°	0.0	0.0	1.2	1.2	2.5	2.5	2.5	3.7	5.0	5.0	6.2
85°	0.0	0.0	1.2	1.2	2.5	2.5	2.5	3.7	5.0	5.0	6.2
87.5°	0.0	0.0	1.2	1.2	2.5	2.5	2.5	3.7	3.7	5.0	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192781

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8
2.5°	2200.7	2155.9	2089.9	2046.3	2004.1	1964.1	1898.2	1860.9	1793.7	1731.5	1677.9
5°	2656.3	2544.3	2408.6	2292.8	2218.1	2144.7	2011.5	1913.2	1789.9	1679.1	1577.0
7.5°	3116.9	2918.9	2696.1	2505.7	2389.9	2276.6	2077.4	1918.1	1743.9	1585.9	1435.1
10°	3535.1	3237.7	2922.7	2650.1	2493.3	2346.4	2083.6	1872.1	1648.0	1452.5	1263.4
12.5°	3923.5	3516.5	3105.6	2749.7	2555.4	2378.7	2057.5	1798.6	1532.3	1300.7	1080.5
15°	4269.5	3746.8	3238.9	2806.9	2579.1	2370.0	1996.6	1695.3	1395.4	1136.5	857.7
17.5°	4532.2	3889.9	3297.3	2798.2	2536.8	2304.0	1892.0	1565.8	1249.7	936.0	621.1
20°	4691.4	3950.8	3284.9	2731.0	2445.9	2199.4	1767.5	1425.2	1074.1	719.5	547.6
22.5°	4758.7	3945.8	3226.3	2630.2	2333.8	2084.9	1648.0	1288.3	890.0	651.0	571.4
25°	4769.9	3894.9	3144.3	2519.4	2223.2	1975.5	1527.3	1132.7	773.0	669.6	639.8
27.5°	4684.0	3775.4	2989.9	2360.1	2067.5	1811.1	1346.9	899.9	725.7	667.1	687.0
30°	4430.1	3502.8	2717.2	2079.9	1797.4	1541.0	962.3	705.8	602.5	606.2	611.2
32.5°	3983.1	3049.6	2279.1	1670.4	1361.8	1015.7	598.8	471.8	458.1	458.1	455.6
35°	3387.0	2495.8	1788.7	1056.7	677.1	488.0	309.9	311.1	304.9	303.7	302.4
37.5°	2770.8	1969.3	1132.7	436.8	293.7	204.2	182.9	185.4	182.9	186.6	184.2
40°	2184.5	1216.2	413.2	139.4	103.3	99.6	102.1	104.6	104.6	107.1	107.1
42.5°	1269.6	403.3	108.3	55.9	55.9	53.5	54.7	57.2	58.4	59.7	58.4
45°	377.2	83.5	34.8	31.1	31.1	29.8	29.8	31.1	32.3	33.6	33.6
47.5°	59.7	23.6	19.9	17.4	17.4	17.4	17.4	17.4	18.6	18.6	19.9
50°	18.6	14.9	12.4	11.2	11.2	9.9	9.9	11.2	11.2	11.2	12.4
52.5°	11.2	8.7	8.7	7.5	8.7	8.7	7.5	8.7	8.7	8.7	9.9
55°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	8.7	8.7	8.7
57.5°	6.2	6.2	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
60°	6.2	6.2	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	8.7
62.5°	6.2	6.2	7.5	7.5	7.5	7.5	7.5	7.5	8.7	8.7	8.7
65°	6.2	6.2	7.5	7.5	7.5	7.5	7.5	8.7	8.7	8.7	8.7
67.5°	6.2	7.5	7.5	7.5	7.5	8.7	8.7	8.7	8.7	8.7	8.7
70°	6.2	7.5	7.5	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
72.5°	6.2	7.5	7.5	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
75°	7.5	7.5	7.5	8.7	8.7	8.7	8.7	8.7	8.7	8.7	9.9
77.5°	7.5	7.5	8.7	8.7	8.7	8.7	8.7	8.7	9.9	9.9	9.9
80°	7.5	7.5	8.7	8.7	8.7	8.7	8.7	9.9	9.9	9.9	9.9
82.5°	7.5	7.5	8.7	8.7	8.7	8.7	8.7	9.9	9.9	9.9	9.9
85°	7.5	7.5	8.7	8.7	8.7	8.7	8.7	9.9	9.9	9.9	9.9
87.5°	7.5	7.5	8.7	8.7	8.7	8.7	8.7	9.9	9.9	9.9	9.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192781

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8
2.5°	1631.9	1574.5	1547.2	1508.6	1481.3	1420.2	1395.4	1353.1	1318.1	1260.9	1264.7
5°	1490.0	1381.7	1308.2	1251.0	1211.2	1114.1	1049.3	980.9	918.6	841.5	812.8
7.5°	1293.3	1160.1	1048.0	979.7	928.5	799.1	656.0	543.9	459.4	398.3	374.7
10°	1096.7	923.6	745.6	639.8	566.3	441.8	378.4	348.6	321.2	287.5	265.1
12.5°	867.6	621.1	459.4	416.9	387.1	346.1	304.9	272.6	278.8	280.0	288.7
15°	592.6	446.9	395.8	367.2	334.9	311.1	324.9	333.6	349.8	351.1	362.2
17.5°	481.7	419.4	378.4	377.2	379.6	393.3	414.5	425.6	446.9	451.9	468.1
20°	481.7	445.7	480.5	480.5	486.7	505.4	532.7	548.9	572.7	581.4	601.3
22.5°	548.9	573.9	617.4	622.4	624.9	644.8	679.6	695.7	723.2	728.2	749.4
25°	669.6	692.0	731.9	735.7	736.9	751.8	777.9	786.6	805.3	795.4	807.8
27.5°	708.3	718.3	743.1	745.6	739.4	745.6	755.6	755.6	761.8	741.9	745.6
30°	622.4	624.9	637.3	638.5	624.9	627.4	628.6	627.4	626.1	605.0	605.0
32.5°	461.9	461.9	478.0	474.3	459.4	463.1	463.1	463.1	461.9	444.5	441.8
35°	306.1	307.4	321.2	318.7	307.4	309.9	309.9	313.6	309.9	299.9	297.4
37.5°	186.6	187.9	194.3	195.5	191.8	193.0	194.3	193.0	195.5	190.5	187.9
40°	108.3	110.8	115.8	117.0	115.8	115.8	117.0	118.3	123.2	117.0	114.5
42.5°	63.6	64.8	67.3	67.3	67.3	67.3	68.5	69.8	71.0	69.8	68.5
45°	36.1	37.3	38.5	38.5	39.8	38.5	39.8	39.8	41.0	39.8	39.8
47.5°	21.1	21.1	22.4	22.4	23.6	22.4	23.6	23.6	23.6	22.4	22.4
50°	12.4	13.7	13.7	13.7	13.7	13.7	13.7	13.7	13.7	12.4	12.4
52.5°	9.9	9.9	9.9	9.9	9.9	8.7	8.7	8.7	8.7	7.5	7.5
55°	8.7	8.7	8.7	8.7	8.7	8.7	7.5	6.2	6.2	5.0	5.0
57.5°	7.5	8.7	8.7	8.7	8.7	7.5	7.5	6.2	5.0	3.7	3.7
60°	8.7	8.7	8.7	8.7	7.5	7.5	7.5	6.2	5.0	3.7	3.7
62.5°	8.7	8.7	8.7	8.7	8.7	7.5	7.5	6.2	5.0	3.7	3.7
65°	8.7	8.7	8.7	8.7	8.7	7.5	7.5	6.2	5.0	3.7	3.7
67.5°	8.7	8.7	8.7	8.7	8.7	7.5	7.5	6.2	5.0	5.0	3.7
70°	8.7	9.9	9.9	8.7	8.7	8.7	7.5	6.2	6.2	5.0	3.7
72.5°	8.7	9.9	9.9	8.7	8.7	8.7	7.5	6.2	6.2	5.0	3.7
75°	9.9	9.9	9.9	9.9	8.7	8.7	7.5	7.5	6.2	5.0	3.7
77.5°	9.9	9.9	9.9	9.9	8.7	8.7	7.5	7.5	6.2	5.0	3.7
80°	9.9	9.9	9.9	9.9	9.9	8.7	8.7	7.5	6.2	5.0	5.0
82.5°	9.9	9.9	9.9	9.9	9.9	8.7	8.7	7.5	6.2	5.0	5.0
85°	9.9	9.9	9.9	9.9	9.9	8.7	8.7	7.5	6.2	5.0	3.7
87.5°	9.9	9.9	9.9	9.9	8.7	8.7	7.5	7.5	6.2	5.0	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192781

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8	1768.8
2.5°	1218.7	1189.9	1177.5	1197.4	1187.4	1157.6	1163.8	1145.2
5°	727.0	683.3	656.0	668.4	628.6	592.6	592.6	566.3
7.5°	351.1	337.4	329.9	332.4	323.7	312.4	306.1	306.1
10°	246.5	241.5	242.7	242.7	250.2	249.0	252.7	251.4
12.5°	292.5	295.0	296.2	301.2	307.4	307.4	311.1	308.6
15°	374.7	372.2	379.6	380.9	390.8	392.1	397.1	392.1
17.5°	476.8	481.7	489.2	488.0	507.9	509.1	509.1	507.9
20°	613.7	617.4	624.9	627.4	651.0	653.5	662.2	663.4
22.5°	763.0	763.0	766.8	771.7	794.1	795.4	799.1	799.1
25°	814.0	806.5	807.8	814.0	826.6	821.5	825.3	822.7
27.5°	748.1	736.9	734.4	743.1	751.8	738.2	743.1	743.1
30°	607.5	597.5	595.0	603.7	610.0	595.0	600.0	602.5
32.5°	444.5	438.1	436.8	443.1	448.2	435.6	440.6	444.5
35°	299.9	297.4	295.0	296.2	303.7	293.7	298.7	301.2
37.5°	190.5	185.4	186.6	189.1	194.3	187.9	193.0	193.0
40°	117.0	114.5	114.5	117.0	119.5	114.5	117.0	118.3
42.5°	68.5	68.5	68.5	69.8	71.0	68.5	68.5	69.8
45°	39.8	38.5	38.5	39.8	41.0	38.5	39.8	39.8
47.5°	22.4	21.1	21.1	22.4	22.4	21.1	22.4	22.4
50°	12.4	11.2	11.2	12.4	12.4	11.2	11.2	11.2
52.5°	6.2	6.2	6.2	6.2	6.2	6.2	5.0	5.0
55°	3.7	3.7	2.5	2.5	2.5	2.5	2.5	1.2
57.5°	2.5	2.5	1.2	1.2	1.2	1.2	0.0	0.0
60°	2.5	2.5	1.2	1.2	1.2	0.0	0.0	0.0
62.5°	2.5	2.5	1.2	1.2	1.2	0.0	0.0	0.0
65°	2.5	2.5	1.2	1.2	1.2	0.0	0.0	0.0
67.5°	2.5	2.5	1.2	1.2	1.2	0.0	0.0	0.0
70°	3.7	2.5	2.5	1.2	1.2	1.2	0.0	0.0
72.5°	3.7	2.5	2.5	2.5	1.2	1.2	0.0	0.0
75°	3.7	2.5	2.5	2.5	1.2	1.2	0.0	0.0
77.5°	3.7	2.5	2.5	2.5	1.2	1.2	1.2	0.0
80°	3.7	2.5	2.5	2.5	1.2	1.2	1.2	1.2
82.5°	3.7	2.5	2.5	2.5	1.2	1.2	1.2	1.2
85°	3.7	2.5	2.5	2.5	1.2	1.2	1.2	0.0
87.5°	3.7	2.5	2.5	2.5	1.2	1.2	1.2	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)