

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192783

Luminaire Tested: **LDA6A75930D010TE LARH20SP 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192783
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26689)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75930D010TE LARH20SP 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5771.3 lumens
Efficiency: N/A
Efficacy: 66.4 lumens/watt
Spacing Criteria (0/90/45): 2.34 / 0.96 / 1.3
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192783

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LAL1LI 30°

Luminous Intensity Polar Plot





TEST NUMBER: P1192783

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	76	72	68	67		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60		
6	80	70	62	57	79	69	62	57	67	61	57	66	60	56	64	59	56	54		
7	75	64	57	51	74	63	56	51	62	56	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	46	57	51	46	56	50	46	55	50	46	44		
9	66	54	47	42	64	54	47	42	53	46	42	52	46	42	51	45	42	40		
10	62	50	43	38	61	50	43	38	49	43	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	90064	90064	90064
5°	176089	85610	31229
10°	296387	73507	6930
15°	451365	55659	11368
20°	652241	45096	126851
25°	970701	72954	36661
30°	1121185	24979	7248
35°	1121537	5588	3908
40°	916682	3113	2405
45°	694157	2023	1543
50°	461000	1382	1058
55°	74119	1185	832
60°	4638	1228	680
65°	1453	1608	804
70°	801	1795	994
75°	530	2097	1313
80°	379	3125	1957
85°	755	6227	2327



TEST NUMBER: P1192783

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.5	3.0
10°-20°	733.3	12.7
20°-30°	1726.2	29.9
30°-40°	1818.7	31.5
40°-50°	1134.0	19.6
50°-60°	162.9	2.8
60°-70°	10.4	0.2
70°-80°	8.1	0.1
80°-90°	6.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2630.9	45.6
0°-40°	4449.7	77.1
0°-60°	5746.7	99.6
0°-90°	5771.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5771.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1643	1643	1643	1643	1643	
5°	3200	2590	1556	808	568	371
15°	7953	4502	981	170	200	2368
25°	16048	5397	1206	872	606	7221
35°	16759	3953	84	77	58	10109
45°	8954	1094	26	29	20	7008
55°	776	20	12	14	9	1393
65°	11	9	12	10	6	16
75°	2	6	10	10	6	3
85°	1	6	10	8	4	1
90°	0	0	0	0	0	

TEST NUMBER: P1192783

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9
2.5°	2398.3	2382.2	2387.1	2349.8	2300.0	2322.5	2266.4	2267.6	2232.8	2144.4	2105.9
5°	3199.9	3197.4	3193.7	3125.1	3036.9	3046.8	2964.6	2933.5	2843.9	2688.3	2590.1
7.5°	4195.6	4196.8	4178.2	4011.4	3913.0	3906.8	3777.4	3684.0	3517.2	3272.0	3092.8
10°	5324.4	5359.2	5325.6	5069.2	4886.3	4888.8	4656.0	4476.8	4209.2	3852.1	3596.9
12.5°	6650.0	6655.0	6602.6	6265.4	5986.6	5965.4	5653.1	5310.7	4903.7	4437.1	4066.1
15°	7953.0	7987.9	7920.7	7505.0	7116.7	7058.2	6659.9	6208.0	5702.8	5012.0	4501.7
17.5°	9398.0	9343.3	9165.3	8570.3	8103.6	8017.7	7589.6	6998.4	6353.8	5518.7	4849.0
20°	11180.3	11198.9	10821.9	9933.2	9144.2	8809.3	8312.8	7665.5	6861.5	5890.7	5080.4
22.5°	13726.7	13626.0	12817.0	11379.5	10193.3	9746.5	9038.4	8145.9	7241.1	6173.2	5253.5
25°	16048.0	15782.8	15037.4	13059.7	11202.7	10650.1	9917.0	8555.4	7556.0	6382.4	5396.7
27.5°	17381.0	17262.7	16417.7	14422.5	12017.9	11240.1	10208.2	8856.6	7742.6	6485.6	5437.7
30°	17712.0	17733.1	16981.5	14874.4	12210.9	11322.2	10255.6	8847.8	7617.1	6301.4	5201.2
32.5°	17627.3	17512.9	16573.2	14375.2	11696.8	10887.8	9792.5	8452.2	7116.7	5752.5	4612.5
35°	16758.6	16590.6	15434.4	13077.1	10824.4	10037.8	9044.6	7803.7	6418.4	5053.1	3952.8
37.5°	15105.8	14911.7	13577.4	11518.9	9777.6	9111.7	8253.0	7081.9	5712.8	4401.0	3372.9
40°	12809.5	12568.0	11452.9	10025.3	8652.5	8187.1	7461.3	6257.9	4981.0	3783.6	2837.7
42.5°	10662.5	10546.9	9877.2	8652.5	7727.7	7278.4	6546.6	5426.5	4251.5	3152.7	2100.9
45°	8953.7	8876.6	8432.1	7654.4	6715.9	6295.2	5605.7	4512.9	3234.7	2123.3	1094.0
47.5°	7837.3	7640.7	7206.3	6389.8	5346.8	4822.9	4165.7	2973.3	1824.6	941.0	336.0
50°	5405.4	5424.0	4933.6	4033.8	3146.4	2703.2	2232.8	1367.9	603.6	205.3	58.4
52.5°	2846.4	2636.1	2291.3	1711.3	1191.2	908.6	663.4	273.8	109.6	41.0	31.1
55°	775.5	680.8	543.9	384.6	207.8	145.6	95.9	51.0	36.1	28.6	19.9
57.5°	76.0	72.3	65.9	53.5	46.0	42.3	38.5	31.1	24.9	17.4	12.4
60°	42.3	41.0	38.5	33.6	29.8	27.4	24.9	21.1	14.9	11.2	9.9
62.5°	23.6	22.4	21.1	18.6	16.2	14.9	14.9	12.4	9.9	8.7	8.7
65°	11.2	11.2	11.2	11.2	11.2	9.9	8.7	8.7	8.7	8.7	8.7
67.5°	8.7	8.7	8.7	7.5	7.5	7.5	7.5	7.5	7.5	6.2	7.5
70°	5.0	5.0	6.2	5.0	5.0	5.0	5.0	5.0	5.0	5.0	6.2
72.5°	2.5	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	6.2
75°	2.5	2.5	2.5	2.5	3.7	3.7	3.7	3.7	5.0	5.0	6.2
77.5°	2.5	2.5	2.5	2.5	2.5	2.5	3.7	3.7	5.0	5.0	6.2
80°	1.2	1.2	1.2	2.5	2.5	2.5	2.5	3.7	5.0	5.0	6.2
82.5°	1.2	1.2	1.2	1.2	2.5	2.5	2.5	3.7	5.0	5.0	6.2
85°	1.2	1.2	1.2	1.2	2.5	2.5	2.5	3.7	3.7	5.0	6.2
87.5°	0.0	0.0	1.2	1.2	2.5	2.5	2.5	3.7	3.7	5.0	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192783

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9
2.5°	2066.1	2005.0	1944.1	1883.0	1880.5	1844.5	1791.0	1720.0	1661.6	1611.8	1563.2
5°	2491.7	2366.0	2240.3	2114.6	2077.3	2012.5	1896.8	1766.2	1654.1	1555.7	1461.1
7.5°	2918.6	2707.0	2507.9	2311.3	2232.8	2134.5	1954.0	1764.9	1603.0	1458.6	1318.0
10°	3299.5	2992.0	2711.9	2435.6	2322.5	2194.3	1951.5	1711.3	1506.0	1320.5	1141.3
12.5°	3650.4	3222.3	2867.6	2519.1	2364.8	2209.2	1913.0	1626.8	1381.5	1159.9	953.4
15°	3959.0	3433.9	2977.0	2556.4	2367.2	2180.6	1832.0	1509.7	1234.7	980.7	756.7
17.5°	4179.4	3539.6	3013.3	2522.8	2302.6	2093.4	1712.5	1367.9	1071.7	806.5	589.9
20°	4313.8	3583.3	2994.5	2460.6	2226.6	2010.0	1624.3	1289.4	1001.9	773.0	626.0
22.5°	4402.2	3625.5	3002.1	2459.4	2225.4	2021.2	1661.6	1348.0	1113.9	990.7	973.3
25°	4496.7	3685.2	3056.8	2515.3	2297.5	2108.3	1759.9	1453.6	1258.3	1206.1	1213.5
27.5°	4491.8	3659.1	3004.6	2466.9	2237.8	2046.2	1637.9	1250.8	1067.9	921.1	867.5
30°	4224.2	3356.7	2648.5	2046.2	1776.1	1540.8	1003.1	652.2	450.5	394.6	338.5
32.5°	3598.2	2719.4	1980.1	1415.1	1111.4	830.2	394.6	209.0	177.9	149.3	135.7
35°	2992.0	2168.2	1481.1	855.0	540.2	334.7	141.9	93.4	88.4	83.5	83.5
37.5°	2473.1	1702.6	957.1	361.0	197.8	120.7	68.4	62.2	59.7	58.4	58.4
40°	1934.1	1110.2	414.5	119.5	63.4	54.7	48.5	46.0	44.8	43.5	44.8
42.5°	1141.3	446.8	120.7	44.8	42.3	39.8	36.1	34.8	34.8	33.6	34.8
45°	388.4	115.8	39.8	32.3	29.8	29.8	27.4	27.4	27.4	26.1	28.6
47.5°	100.9	36.1	26.1	23.6	22.4	22.4	21.1	21.1	21.1	21.1	22.4
50°	34.8	23.6	18.6	17.4	16.2	17.4	16.2	16.2	16.2	16.2	17.4
52.5°	21.1	16.2	13.7	13.7	13.7	13.7	13.7	13.7	13.7	13.7	13.7
55°	13.7	12.4	11.2	11.2	11.2	11.2	11.2	12.4	12.4	12.4	12.4
57.5°	11.2	9.9	9.9	9.9	9.9	9.9	11.2	9.9	9.9	11.2	12.4
60°	9.9	9.9	9.9	9.9	9.9	9.9	9.9	9.9	11.2	11.2	12.4
62.5°	8.7	9.9	9.9	9.9	9.9	9.9	9.9	11.2	11.2	11.2	12.4
65°	8.7	8.7	8.7	9.9	9.9	9.9	11.2	11.2	11.2	12.4	12.4
67.5°	7.5	7.5	8.7	8.7	9.9	9.9	9.9	11.2	11.2	11.2	12.4
70°	7.5	7.5	7.5	8.7	8.7	8.7	8.7	9.9	9.9	11.2	11.2
72.5°	6.2	7.5	7.5	8.7	8.7	8.7	8.7	9.9	9.9	9.9	11.2
75°	6.2	7.5	7.5	8.7	8.7	8.7	8.7	8.7	9.9	9.9	11.2
77.5°	6.2	7.5	7.5	8.7	8.7	8.7	8.7	9.9	9.9	9.9	11.2
80°	6.2	7.5	7.5	8.7	8.7	8.7	8.7	9.9	9.9	9.9	9.9
82.5°	6.2	7.5	7.5	8.7	8.7	8.7	8.7	9.9	9.9	9.9	9.9
85°	6.2	7.5	7.5	8.7	8.7	8.7	8.7	8.7	9.9	9.9	9.9
87.5°	6.2	7.5	7.5	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192783

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9
2.5°	1496.1	1474.9	1400.2	1390.2	1377.8	1316.7	1291.9	1249.6	1189.9	1172.4	1151.2
5°	1350.4	1280.7	1171.1	1141.3	1109.0	1013.1	954.6	884.9	807.8	765.4	725.6
7.5°	1164.9	1067.9	922.3	863.7	827.7	723.1	629.8	536.4	423.2	358.5	317.3
10°	958.4	825.2	673.4	606.1	557.6	405.8	317.3	276.3	237.8	206.5	179.2
12.5°	750.4	599.9	428.1	351.1	312.4	258.9	210.4	159.3	141.9	140.6	135.7
15°	550.1	382.1	288.7	260.1	232.8	166.7	165.5	165.5	170.5	174.2	175.4
17.5°	405.8	336.0	263.9	246.5	258.9	268.8	286.3	312.4	333.5	393.3	380.9
20°	594.9	589.9	643.5	711.9	760.4	863.7	994.4	1142.5	1296.8	1468.7	1599.2
22.5°	1020.5	1145.0	1242.1	1324.2	1367.9	1484.9	1588.1	1639.2	1669.0	1654.1	1633.0
25°	1247.1	1291.9	1262.0	1233.4	1237.2	1131.3	1054.3	955.9	872.4	796.6	751.7
27.5°	745.5	682.1	592.4	530.2	517.8	446.8	394.6	339.7	323.5	273.8	252.7
30°	268.8	250.2	221.6	199.1	196.6	177.9	166.7	154.3	153.1	141.9	135.7
32.5°	122.0	122.0	112.0	114.5	112.0	108.3	107.1	103.3	103.3	99.6	97.1
35°	79.7	81.0	79.7	79.7	78.5	78.5	78.5	76.0	77.2	74.7	71.0
37.5°	58.4	59.7	57.2	58.4	58.4	58.4	58.4	57.2	55.9	53.5	52.2
40°	44.8	44.8	44.8	44.8	44.8	44.8	44.8	43.5	43.5	42.3	39.8
42.5°	34.8	36.1	36.1	36.1	36.1	36.1	36.1	36.1	36.1	34.8	34.8
45°	28.6	29.8	28.6	29.8	29.8	29.8	28.6	28.6	28.6	27.4	26.1
47.5°	22.4	22.4	21.1	21.1	21.1	21.1	21.1	21.1	21.1	21.1	19.9
50°	17.4	17.4	17.4	17.4	17.4	17.4	18.6	17.4	17.4	17.4	17.4
52.5°	13.7	14.9	14.9	16.2	16.2	16.2	16.2	16.2	14.9	14.9	13.7
55°	12.4	13.7	13.7	14.9	14.9	14.9	14.9	13.7	13.7	13.7	12.4
57.5°	12.4	13.7	13.7	13.7	13.7	13.7	13.7	12.4	12.4	11.2	11.2
60°	12.4	12.4	12.4	13.7	13.7	12.4	12.4	11.2	11.2	9.9	9.9
62.5°	12.4	12.4	12.4	13.7	13.7	12.4	12.4	11.2	9.9	9.9	8.7
65°	12.4	13.7	12.4	13.7	13.7	12.4	12.4	11.2	9.9	9.9	8.7
67.5°	12.4	13.7	13.7	13.7	12.4	12.4	12.4	11.2	9.9	9.9	8.7
70°	11.2	12.4	12.4	12.4	12.4	12.4	11.2	11.2	9.9	9.9	8.7
72.5°	11.2	12.4	11.2	12.4	12.4	11.2	11.2	11.2	9.9	9.9	8.7
75°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	9.9	9.9	8.7	8.7
77.5°	11.2	11.2	11.2	11.2	11.2	11.2	9.9	9.9	9.9	8.7	8.7
80°	11.2	11.2	11.2	11.2	11.2	11.2	9.9	9.9	8.7	8.7	7.5
82.5°	9.9	11.2	11.2	11.2	11.2	11.2	9.9	9.9	8.7	8.7	7.5
85°	9.9	9.9	9.9	9.9	9.9	9.9	8.7	8.7	7.5	6.2	6.2
87.5°	8.7	9.9	8.7	8.7	8.7	8.7	7.5	6.2	5.0	5.0	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192783

CATALOG NUMBER: LDA6A75930D010TE LARH20SP 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9	1642.9
2.5°	1117.7	1086.6	1087.8	1092.8	1061.7	1045.4	1041.7	1025.5
5°	672.1	636.1	629.8	624.7	581.2	563.8	550.1	567.5
7.5°	288.7	275.1	272.6	268.8	249.0	239.0	234.0	239.0
10°	143.1	134.4	135.7	136.9	130.7	127.0	125.7	124.5
12.5°	141.9	140.6	141.9	141.9	143.1	140.6	141.9	141.9
15°	184.2	184.2	187.9	190.4	196.6	195.3	197.8	200.3
17.5°	459.2	435.6	448.0	448.0	504.1	454.2	496.7	458.0
20°	1804.7	1889.4	1975.2	2047.4	2120.8	2143.2	2186.8	2174.4
22.5°	1600.5	1610.6	1598.0	1584.3	1580.6	1584.3	1517.2	1527.1
25°	687.0	682.1	662.2	641.0	647.3	652.2	628.6	606.1
27.5°	235.3	229.1	222.8	217.9	215.4	211.7	204.0	199.1
30°	133.2	129.5	127.0	125.7	123.2	120.7	117.0	114.5
32.5°	95.9	93.4	92.2	90.9	88.4	85.9	82.2	81.0
35°	71.0	68.4	67.1	65.9	63.4	60.9	59.7	58.4
37.5°	52.2	49.7	49.7	49.7	46.0	43.5	42.3	41.0
40°	39.8	38.5	38.5	38.5	36.1	34.8	33.6	33.6
42.5°	34.8	33.6	33.6	33.6	31.1	29.8	29.8	28.6
45°	26.1	24.9	24.9	23.6	22.4	22.4	21.1	19.9
47.5°	19.9	18.6	18.6	18.6	17.4	16.2	16.2	14.9
50°	16.2	16.2	14.9	16.2	13.7	13.7	13.7	12.4
52.5°	13.7	13.7	12.4	12.4	11.2	11.2	11.2	9.9
55°	12.4	11.2	11.2	11.2	9.9	9.9	9.9	8.7
57.5°	9.9	9.9	8.7	8.7	7.5	7.5	7.5	7.5
60°	8.7	8.7	7.5	7.5	6.2	6.2	6.2	6.2
62.5°	8.7	7.5	7.5	7.5	6.2	6.2	6.2	6.2
65°	8.7	7.5	7.5	7.5	6.2	6.2	6.2	6.2
67.5°	8.7	7.5	7.5	7.5	6.2	6.2	6.2	6.2
70°	8.7	8.7	7.5	7.5	7.5	6.2	6.2	6.2
72.5°	8.7	8.7	7.5	7.5	7.5	7.5	6.2	6.2
75°	7.5	7.5	7.5	7.5	6.2	6.2	6.2	6.2
77.5°	7.5	7.5	7.5	7.5	6.2	6.2	6.2	6.2
80°	7.5	7.5	6.2	6.2	6.2	6.2	6.2	6.2
82.5°	7.5	6.2	6.2	6.2	6.2	5.0	5.0	5.0
85°	5.0	5.0	5.0	5.0	3.7	3.7	3.7	3.7
87.5°	3.7	2.5	2.5	2.5	1.2	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)