

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192786

Luminaire Tested: **LDA6A75930D010TE LARH30NF 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192786
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26687)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75930D010TE LARH30NF 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 30°
Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6845.4 lumens
Efficiency: N/A
Efficacy: 78.8 lumens/watt
Spacing Criteria (0/90/45): 2.58 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192786

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192786

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	43	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	67692	67692	67692
5°	173646	61584	19183
10°	338471	47327	9213
15°	607608	32140	12367
20°	902104	24397	20407
25°	1025376	20106	31998
30°	1111525	21984	30100
35°	1170792	14248	18658
40°	1196112	6326	9088
45°	1080329	2411	3372
50°	711141	955	955
55°	194746	832	0
60°	38900	954	0
65°	2737	1284	0
70°	401	1587	0
75°	0	2372	0
80°	0	3536	379
85°	0	7045	755



TEST NUMBER: P1192786

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.3	2.2
10°-20°	803.6	11.7
20°-30°	1821.3	26.6
30°-40°	2186.2	31.9
40°-50°	1540.8	22.5
50°-60°	317.9	4.6
60°-70°	11.2	0.2
70°-80°	6.7	0.1
80°-90°	6.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2776.1	40.6
0°-40°	4962.3	72.5
0°-60°	6820.9	99.6
0°-90°	6845.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6845.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1235	1235	1235	1235	1235	
5°	3156	2299	1119	466	349	388
15°	10706	4710	566	202	218	3177
25°	16952	5697	332	466	529	7823
35°	17495	3989	213	279	279	10876
45°	13935	1368	31	42	44	10249
55°	2038	27	9	6	0	2685
65°	21	6	10	6	0	63
75°	0	6	11	8	0	0
85°	0	8	11	8	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192786

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8
2.5°	2104.8	2041.4	2066.2	1992.9	1976.6	1962.9	1976.6	1897.0	1852.1	1794.9	1748.9
5°	3155.5	3079.5	3096.9	2968.7	2910.2	2870.3	2862.8	2698.6	2575.3	2439.7	2299.0
7.5°	4392.6	4320.5	4310.6	4111.3	3990.6	3922.2	3893.5	3658.3	3445.4	3203.9	2940.1
10°	6080.4	5916.2	5865.2	5576.3	5346.2	5200.5	5021.2	4645.3	4271.9	3907.1	3571.2
12.5°	8044.7	7955.1	7828.1	7319.0	6915.7	6709.0	6441.4	5854.0	5288.8	4686.5	4123.8
15°	10706.0	10387.3	10170.6	9435.1	8785.4	8466.6	8075.8	7177.1	6323.2	5560.2	4710.1
17.5°	13306.2	13139.3	12800.8	11846.0	10845.4	10342.5	9759.9	8538.9	7332.7	6247.3	5209.3
20°	15463.3	15306.4	14920.5	14020.6	12910.4	12168.5	11435.3	9759.9	8184.1	6795.0	5542.7
22.5°	16496.5	16396.8	16081.8	15311.4	14365.4	13659.7	12871.7	10799.2	8814.0	7153.5	5694.6
25°	16951.9	16905.9	16703.0	16095.7	15204.4	14605.7	13861.3	11534.9	9206.1	7320.2	5697.1
27.5°	17413.8	17422.5	16974.3	16494.0	15648.7	15073.7	14356.7	11861.1	9276.9	7226.8	5510.4
30°	17559.4	17467.3	17269.4	16579.8	15776.9	15165.7	14396.5	11710.4	8985.7	6843.5	5138.2
32.5°	17499.6	17463.5	17245.8	16516.3	15559.1	14885.7	14011.9	11113.0	8410.7	6295.8	4610.5
35°	17494.6	17427.5	16928.3	16302.2	15123.5	14291.9	13140.5	10147.0	7596.5	5573.8	3989.3
37.5°	17178.5	17011.8	16637.1	15793.1	14239.7	13185.4	11894.7	8967.0	6600.7	4763.6	3373.2
40°	16714.2	16490.2	15997.3	14720.2	12708.7	11493.9	10234.2	7626.4	5546.5	3964.5	2718.5
42.5°	15744.6	15406.0	14709.0	12952.7	10668.5	9573.3	8525.1	6268.5	4523.3	3230.0	2074.9
45°	13934.8	13471.7	12529.5	10601.4	8618.5	7724.8	6882.2	5043.6	3620.9	2396.2	1368.0
47.5°	11200.0	10770.6	9913.0	8439.3	6758.9	6003.4	5331.2	3751.6	2454.6	1387.9	653.5
50°	8338.4	7970.0	7300.3	5865.2	4537.0	3943.3	3368.2	2131.0	1150.1	659.7	271.3
52.5°	4975.2	4792.2	4198.5	3252.4	2240.4	1930.6	1549.7	902.4	580.1	239.0	73.5
55°	2037.6	1880.8	1658.0	1330.6	974.7	826.4	707.1	445.5	180.4	49.7	27.4
57.5°	921.1	886.3	785.4	617.4	448.0	375.9	253.9	84.7	39.8	24.9	16.2
60°	354.8	319.8	273.8	148.1	63.4	53.5	43.5	28.6	19.9	13.7	9.9
62.5°	51.0	48.5	43.5	34.8	27.4	24.9	21.1	14.9	11.2	8.7	7.5
65°	21.1	21.1	18.6	14.9	12.4	11.2	9.9	7.5	6.2	6.2	6.2
67.5°	8.7	8.7	7.5	6.2	5.0	5.0	5.0	3.7	5.0	5.0	6.2
70°	2.5	2.5	2.5	2.5	2.5	2.5	3.7	3.7	5.0	5.0	6.2
72.5°	0.0	0.0	1.2	1.2	2.5	2.5	2.5	3.7	5.0	6.2	6.2
75°	0.0	0.0	1.2	1.2	2.5	2.5	2.5	3.7	5.0	6.2	6.2
77.5°	0.0	0.0	1.2	1.2	2.5	2.5	3.7	3.7	5.0	6.2	6.2
80°	0.0	0.0	1.2	1.2	2.5	2.5	3.7	3.7	5.0	6.2	7.5
82.5°	0.0	0.0	1.2	1.2	2.5	2.5	3.7	3.7	5.0	6.2	7.5
85°	0.0	0.0	1.2	1.2	2.5	2.5	3.7	3.7	5.0	6.2	7.5
87.5°	0.0	0.0	1.2	1.2	2.5	2.5	3.7	3.7	5.0	6.2	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192786

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8
2.5°	1709.0	1629.4	1607.0	1537.2	1478.8	1450.1	1414.0	1333.0	1272.1	1191.2	1142.7
5°	2200.7	2050.1	1930.6	1785.0	1689.1	1626.9	1529.8	1381.7	1262.2	1119.1	1017.0
7.5°	2732.1	2457.1	2241.7	2001.6	1863.4	1755.1	1589.5	1376.7	1201.1	1010.7	852.7
10°	3245.0	2834.2	2495.6	2150.9	1969.1	1818.5	1590.7	1323.1	1090.5	850.2	683.3
12.5°	3696.9	3166.6	2689.9	2246.8	2021.5	1833.4	1548.4	1227.4	945.9	699.5	552.6
15°	4074.0	3424.3	2826.8	2282.9	2025.2	1801.1	1460.0	1090.5	785.4	566.3	463.1
17.5°	4360.3	3560.0	2869.0	2239.2	1952.9	1709.0	1324.3	917.3	637.3	480.5	389.6
20°	4508.4	3586.1	2808.1	2121.1	1819.8	1569.6	1146.4	744.4	540.2	418.2	326.2
22.5°	4527.0	3512.6	2662.5	1951.7	1651.8	1400.3	949.7	621.1	481.7	369.7	287.5
25°	4416.2	3353.3	2454.6	1760.1	1467.5	1206.1	773.0	556.3	438.1	332.4	331.2
27.5°	4179.9	3079.5	2205.6	1537.2	1244.8	980.9	656.0	502.9	390.8	352.3	374.7
30°	3846.2	2728.4	1899.5	1256.0	972.2	754.3	552.6	414.5	343.6	347.3	366.0
32.5°	3394.3	2292.8	1539.7	919.8	695.7	567.5	414.5	282.5	285.0	286.3	302.4
35°	2826.8	1838.4	1150.1	618.7	489.2	399.5	234.0	207.9	211.7	212.9	224.1
37.5°	2265.5	1412.8	764.3	412.0	307.4	210.4	145.6	139.4	141.9	140.6	153.1
40°	1735.2	984.6	458.1	204.2	118.3	98.4	89.7	85.9	87.2	88.4	95.9
42.5°	1228.6	534.0	226.6	77.2	62.2	57.2	53.5	51.0	52.2	52.2	57.2
45°	623.6	252.7	77.2	42.3	38.5	34.8	32.3	31.1	31.1	31.1	33.6
47.5°	270.1	83.5	36.1	26.1	23.6	22.4	19.9	18.6	18.6	18.6	19.9
50°	84.7	33.6	22.4	17.4	14.9	13.7	12.4	12.4	12.4	11.2	12.4
52.5°	31.1	21.1	14.9	11.2	9.9	9.9	9.9	8.7	9.9	8.7	9.9
55°	18.6	13.7	9.9	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7
57.5°	12.4	9.9	8.7	8.7	7.5	7.5	8.7	8.7	8.7	8.7	8.7
60°	8.7	8.7	7.5	7.5	7.5	7.5	8.7	8.7	8.7	8.7	8.7
62.5°	7.5	7.5	7.5	7.5	7.5	7.5	8.7	8.7	8.7	8.7	9.9
65°	6.2	7.5	7.5	7.5	7.5	7.5	8.7	8.7	9.9	9.9	9.9
67.5°	6.2	7.5	7.5	8.7	8.7	8.7	8.7	9.9	9.9	9.9	9.9
70°	7.5	7.5	8.7	8.7	8.7	8.7	9.9	9.9	9.9	9.9	11.2
72.5°	7.5	7.5	8.7	8.7	8.7	8.7	9.9	9.9	11.2	11.2	11.2
75°	7.5	8.7	8.7	8.7	8.7	9.9	9.9	9.9	11.2	11.2	11.2
77.5°	7.5	8.7	8.7	9.9	9.9	9.9	9.9	11.2	11.2	11.2	11.2
80°	7.5	8.7	8.7	9.9	9.9	9.9	11.2	11.2	11.2	11.2	12.4
82.5°	7.5	8.7	8.7	9.9	9.9	9.9	11.2	11.2	11.2	11.2	12.4
85°	8.7	8.7	9.9	9.9	9.9	9.9	11.2	11.2	11.2	11.2	12.4
87.5°	8.7	8.7	9.9	9.9	9.9	9.9	11.2	11.2	12.4	11.2	12.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192786

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8
2.5°	1077.9	1005.8	955.9	937.2	901.2	844.0	810.3	779.2	720.8	708.3	675.8
5°	899.9	784.2	702.0	670.9	629.8	581.4	534.0	502.9	465.6	450.7	428.1
7.5°	709.6	593.8	522.8	497.9	469.3	429.4	387.1	356.0	317.3	297.4	278.8
10°	557.6	471.8	412.0	387.1	357.3	314.8	271.3	230.3	196.7	175.4	171.7
12.5°	453.2	382.1	318.6	292.5	257.7	215.4	184.2	182.9	180.4	179.2	181.7
15°	370.9	302.4	235.3	206.7	196.7	195.5	199.2	203.0	201.7	205.4	207.9
17.5°	304.9	231.5	216.6	217.9	219.1	222.8	229.1	239.0	240.3	246.5	251.4
20°	249.0	245.2	251.4	256.4	260.1	267.6	281.3	293.7	297.4	306.1	316.1
22.5°	282.5	293.7	307.4	313.6	318.6	332.4	347.3	367.2	374.7	385.9	399.5
25°	341.1	359.8	380.9	388.4	395.8	418.2	435.6	459.4	465.6	479.3	492.9
27.5°	389.6	409.5	431.9	441.8	448.0	470.6	485.5	500.4	500.4	507.9	517.8
30°	382.1	398.3	416.9	424.4	426.9	443.1	458.1	463.1	460.6	464.3	471.8
32.5°	317.3	329.9	344.8	351.1	353.5	364.7	377.2	377.2	375.9	375.9	380.9
35°	235.3	244.0	251.4	257.7	261.4	268.8	280.0	278.8	278.8	276.3	280.0
37.5°	158.0	163.0	171.7	174.2	175.4	180.4	189.1	189.1	186.6	187.9	190.4
40°	95.9	102.1	107.1	108.3	110.8	114.5	120.7	120.7	120.7	120.7	122.0
42.5°	57.2	60.9	64.8	64.8	66.0	71.0	73.5	73.5	73.5	73.5	74.7
45°	33.6	34.8	37.3	38.5	38.5	41.0	42.3	42.3	42.3	42.3	43.5
47.5°	19.9	21.1	21.1	22.4	22.4	23.6	24.9	24.9	23.6	23.6	23.6
50°	12.4	12.4	12.4	12.4	13.7	13.7	13.7	13.7	13.7	13.7	12.4
52.5°	9.9	9.9	9.9	9.9	8.7	8.7	8.7	8.7	7.5	7.5	6.2
55°	8.7	8.7	8.7	8.7	8.7	7.5	7.5	7.5	6.2	5.0	3.7
57.5°	8.7	8.7	8.7	8.7	8.7	7.5	7.5	6.2	5.0	5.0	3.7
60°	8.7	8.7	8.7	8.7	8.7	7.5	7.5	6.2	5.0	5.0	3.7
62.5°	9.9	9.9	8.7	8.7	8.7	7.5	7.5	6.2	6.2	5.0	3.7
65°	9.9	9.9	8.7	8.7	8.7	8.7	7.5	7.5	6.2	5.0	3.7
67.5°	9.9	9.9	9.9	9.9	8.7	8.7	8.7	7.5	6.2	5.0	3.7
70°	11.2	11.2	9.9	9.9	9.9	8.7	8.7	7.5	6.2	6.2	5.0
72.5°	11.2	11.2	9.9	9.9	9.9	9.9	8.7	7.5	7.5	6.2	5.0
75°	11.2	11.2	11.2	11.2	9.9	9.9	8.7	8.7	7.5	6.2	5.0
77.5°	11.2	11.2	11.2	11.2	9.9	9.9	9.9	8.7	7.5	6.2	5.0
80°	11.2	11.2	11.2	11.2	11.2	9.9	9.9	8.7	7.5	6.2	5.0
82.5°	12.4	12.4	11.2	11.2	11.2	9.9	9.9	8.7	7.5	6.2	6.2
85°	12.4	12.4	11.2	11.2	11.2	9.9	9.9	8.7	7.5	7.5	6.2
87.5°	12.4	12.4	11.2	11.2	11.2	9.9	9.9	8.7	7.5	7.5	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192786

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8	1234.8
2.5°	656.0	618.7	606.2	614.9	605.0	597.5	587.6	582.6
5°	410.7	383.4	374.7	377.2	368.5	361.0	351.1	348.6
7.5°	252.7	226.6	216.6	216.6	206.7	198.0	191.6	187.9
10°	169.2	164.3	165.5	166.7	165.5	166.7	163.0	165.5
12.5°	181.7	179.2	181.7	182.9	182.9	185.4	180.4	184.2
15°	211.7	209.2	212.9	215.4	215.4	219.1	214.1	217.9
17.5°	258.9	257.7	263.9	266.4	267.6	273.8	267.6	272.6
20°	327.4	326.2	334.9	338.6	337.4	349.8	341.1	349.8
22.5°	415.7	413.2	425.6	429.4	430.6	446.8	439.3	445.5
25°	504.1	506.6	512.8	519.0	520.3	534.0	522.8	529.0
27.5°	522.8	519.0	522.8	530.2	531.5	537.7	527.7	532.7
30°	473.0	466.8	468.1	476.8	479.3	481.7	473.0	475.5
32.5°	384.6	374.7	374.7	383.4	385.9	389.6	374.7	380.9
35°	283.8	275.1	275.1	281.3	282.5	285.0	273.8	278.8
37.5°	194.3	186.6	189.1	191.6	193.0	195.5	194.3	193.0
40°	124.5	119.5	123.2	123.2	124.5	125.7	125.7	127.0
42.5°	76.0	72.3	74.7	74.7	76.0	76.0	76.0	77.2
45°	43.5	42.3	42.3	43.5	43.5	43.5	42.3	43.5
47.5°	23.6	22.4	23.6	23.6	23.6	23.6	23.6	23.6
50°	12.4	11.2	11.2	11.2	11.2	11.2	11.2	11.2
52.5°	6.2	5.0	5.0	5.0	3.7	5.0	3.7	3.7
55°	3.7	2.5	2.5	2.5	1.2	1.2	0.0	0.0
57.5°	2.5	1.2	1.2	1.2	0.0	0.0	0.0	0.0
60°	2.5	1.2	1.2	1.2	0.0	0.0	0.0	0.0
62.5°	2.5	1.2	1.2	1.2	0.0	0.0	0.0	0.0
65°	2.5	1.2	1.2	1.2	0.0	0.0	0.0	0.0
67.5°	3.7	2.5	1.2	1.2	1.2	0.0	0.0	0.0
70°	3.7	2.5	2.5	1.2	1.2	0.0	0.0	0.0
72.5°	3.7	2.5	2.5	2.5	1.2	1.2	0.0	0.0
75°	3.7	2.5	2.5	2.5	1.2	1.2	0.0	0.0
77.5°	3.7	3.7	2.5	2.5	1.2	1.2	1.2	0.0
80°	5.0	3.7	2.5	2.5	2.5	1.2	1.2	1.2
82.5°	5.0	3.7	2.5	2.5	2.5	1.2	1.2	1.2
85°	5.0	3.7	3.7	2.5	2.5	1.2	1.2	1.2
87.5°	5.0	3.7	3.7	2.5	2.5	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)