

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192788

Luminaire Tested: **LDA6A75930D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192788
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26690)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75930D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6358.7 lumens
Efficiency: N/A
Efficacy: 73.2 lumens/watt
Spacing Criteria (0/90/45): 2.55 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192788

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192788

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	75	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65		
5	85	74	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	64074	64074	64074
5°	165408	59382	18567
10°	313794	45312	6235
15°	561093	29455	6220
20°	836054	20045	11323
25°	953958	24993	71145
30°	1031659	20877	21275
35°	1083692	10159	6666
40°	1100834	3650	3378
45°	980792	2411	2023
50°	629898	1697	1382
55°	165834	1185	717
60°	36993	1228	548
65°	3554	1453	649
70°	1202	1795	801
75°	254	2372	1313
80°	0	3915	1957
85°	0	7045	3145



TEST NUMBER: P1192788

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.9	2.2
10°-20°	740.7	11.6
20°-30°	1738.0	27.3
30°-40°	1999.1	31.4
40°-50°	1420.1	22.3
50°-60°	288.7	4.5
60°-70°	14.4	0.2
70°-80°	8.6	0.1
80°-90°	7.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2620.7	41.2
0°-40°	4619.8	72.7
0°-60°	6328.6	99.5
0°-90°	6358.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6358.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1169	1169	1169	1169	1169	
5°	3006	2174	1079	432	337	366
15°	9886	4445	519	117	110	2966
25°	15771	5353	413	902	1176	7269
35°	16193	3759	152	112	100	10060
45°	12651	1337	31	34	26	9323
55°	1735	35	12	12	8	2340
65°	27	10	11	10	5	66
75°	1	6	11	10	6	3
85°	0	6	11	9	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192788

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8
2.5°	2013.9	1952.9	1923.0	1921.7	1834.7	1863.3	1834.7	1812.3	1731.3	1697.8	1641.7
5°	3005.8	2931.2	2871.4	2845.3	2695.9	2663.6	2648.7	2572.7	2403.5	2305.1	2174.4
7.5°	4175.8	4097.5	3999.1	3920.7	3704.2	3643.1	3603.3	3472.6	3222.4	3024.6	2780.6
10°	5637.1	5591.1	5431.8	5287.4	4958.7	4831.8	4712.3	4407.4	4080.1	3683.0	3368.0
12.5°	7604.9	7496.6	7212.9	6924.1	6408.8	6219.7	6021.7	5533.7	5033.5	4411.1	3890.8
15°	9886.4	9794.3	9357.4	8887.0	8153.8	7842.7	7532.7	6764.8	5995.6	5194.0	4444.7
17.5°	12512.7	12338.3	11904.0	11108.6	10083.0	9593.9	9016.3	8038.0	6927.8	5838.8	4907.8
20°	14331.1	14227.7	13860.7	13097.6	11930.1	11284.1	10567.2	9224.2	7705.8	6355.3	5211.4
22.5°	15325.7	15222.3	14947.2	14273.9	13316.8	12668.3	11835.6	10183.8	8293.2	6702.5	5354.6
25°	15771.2	15704.1	15553.3	15004.4	14118.3	13534.5	12746.6	10847.3	8660.4	6860.6	5353.3
27.5°	16183.2	16200.6	15828.4	15376.6	14560.1	13974.0	13227.1	11145.9	8732.5	6781.0	5181.6
30°	16297.7	16254.2	16091.0	15455.1	14694.6	14056.0	13255.7	10987.9	8451.3	6428.7	4840.5
32.5°	16226.7	16227.9	16074.8	15399.0	14505.4	13790.9	12891.0	10421.6	7903.6	5876.1	4310.2
35°	16193.1	16181.9	15784.9	15191.2	14056.0	13215.9	12081.9	9513.0	7144.3	5170.4	3758.9
37.5°	15859.6	15792.3	15506.1	14700.8	13215.9	12141.8	10920.8	8401.5	6209.6	4436.0	3193.8
40°	15382.8	15298.1	14832.7	13677.6	11779.5	10580.9	9367.4	7143.1	5231.3	3705.4	2564.0
42.5°	14405.8	14266.4	13560.6	12028.5	9929.9	8814.7	7809.0	5883.5	4276.7	3008.4	1969.1
45°	12650.9	12423.0	11446.0	9845.4	8015.7	7140.6	6290.5	4716.0	3424.1	2240.4	1336.8
47.5°	10157.7	9908.8	9022.7	7736.9	6275.6	5566.2	4844.2	3472.6	2316.3	1305.7	670.9
50°	7385.8	7214.1	6431.2	5347.1	4149.7	3554.8	3000.8	1936.6	1111.4	631.1	275.1
52.5°	4255.5	4132.3	3587.2	2814.2	2041.2	1709.0	1374.1	845.1	566.3	250.2	88.4
55°	1735.1	1664.1	1425.2	1207.3	906.2	782.9	653.5	421.9	190.4	59.7	34.8
57.5°	848.8	840.1	700.7	561.3	413.2	333.5	251.4	84.7	46.0	29.8	22.4
60°	337.4	324.8	222.8	129.5	72.3	58.4	49.7	34.8	26.1	19.9	16.2
62.5°	58.4	57.2	48.5	41.0	33.6	29.8	27.4	21.1	17.4	13.7	12.4
65°	27.4	27.4	24.9	22.4	18.6	17.4	16.2	13.7	11.2	9.9	9.9
67.5°	13.7	13.7	12.4	11.2	9.9	9.9	8.7	8.7	7.5	7.5	7.5
70°	7.5	7.5	7.5	6.2	6.2	6.2	6.2	6.2	5.0	6.2	6.2
72.5°	5.0	5.0	5.0	3.7	2.5	3.7	3.7	3.7	5.0	6.2	6.2
75°	1.2	1.2	1.2	2.5	2.5	2.5	3.7	3.7	5.0	6.2	6.2
77.5°	1.2	1.2	1.2	1.2	2.5	2.5	2.5	3.7	5.0	6.2	6.2
80°	0.0	1.2	1.2	1.2	2.5	2.5	2.5	3.7	5.0	6.2	6.2
82.5°	0.0	0.0	1.2	1.2	2.5	2.5	2.5	3.7	5.0	6.2	6.2
85°	0.0	0.0	1.2	1.2	2.5	2.5	2.5	3.7	5.0	6.2	6.2
87.5°	0.0	0.0	1.2	1.2	2.5	2.5	2.5	3.7	5.0	6.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192788

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8
2.5°	1616.8	1552.2	1509.7	1435.1	1404.1	1390.2	1321.9	1255.8	1192.4	1146.4	1075.4
5°	2074.9	1971.6	1813.5	1665.3	1600.6	1559.6	1425.2	1300.7	1182.5	1079.1	955.9
7.5°	2567.7	2355.0	2107.3	1869.5	1757.4	1682.9	1474.9	1293.3	1123.9	967.1	799.1
10°	3040.8	2705.9	2345.0	2005.2	1853.3	1741.3	1470.0	1237.2	1017.0	814.0	633.6
12.5°	3444.0	3010.9	2531.7	2091.1	1893.1	1750.0	1424.0	1140.2	872.6	654.7	497.9
15°	3783.7	3244.8	2654.9	2119.7	1881.9	1712.7	1334.3	1007.0	714.4	519.0	402.0
17.5°	4022.8	3358.1	2683.5	2071.1	1803.4	1608.1	1198.6	836.4	561.3	419.4	317.3
20°	4162.1	3373.0	2613.9	1952.9	1666.5	1460.0	1028.1	657.2	455.5	343.6	246.5
22.5°	4183.3	3299.7	2477.0	1793.5	1508.5	1309.4	856.3	550.1	414.5	321.1	241.5
25°	4081.3	3154.1	2298.9	1637.9	1365.4	1161.3	740.6	556.3	465.4	413.2	429.4
27.5°	3883.4	2913.8	2094.8	1478.7	1216.0	1009.5	699.5	582.4	507.9	516.6	546.4
30°	3579.7	2575.2	1801.0	1208.6	931.0	769.2	556.3	419.4	348.6	329.8	331.0
32.5°	3132.8	2150.8	1414.0	838.9	626.1	519.0	352.3	234.0	235.3	217.9	216.6
35°	2622.6	1731.3	1058.0	562.6	433.1	361.0	207.9	164.3	158.0	151.8	143.1
37.5°	2117.2	1338.0	704.4	384.6	276.3	200.3	104.6	85.9	79.7	74.7	74.7
40°	1611.8	936.0	435.6	201.7	112.0	82.2	62.2	52.2	51.0	51.0	49.7
42.5°	1170.0	552.6	236.5	79.7	62.2	54.7	43.5	38.5	38.5	38.5	38.5
45°	622.4	281.3	90.9	49.7	41.0	38.5	32.3	29.8	29.8	31.1	31.1
47.5°	287.5	105.8	46.0	33.6	28.6	28.6	24.9	23.6	23.6	24.9	24.9
50°	103.3	43.5	29.8	23.6	21.1	22.4	19.9	18.6	19.9	19.9	19.9
52.5°	39.8	27.4	21.1	18.6	16.2	17.4	14.9	14.9	16.2	16.2	16.2
55°	24.9	19.9	16.2	13.7	12.4	13.7	12.4	12.4	12.4	12.4	12.4
57.5°	17.4	14.9	12.4	11.2	9.9	11.2	11.2	11.2	11.2	11.2	11.2
60°	13.7	11.2	9.9	9.9	9.9	9.9	9.9	9.9	9.9	11.2	11.2
62.5°	11.2	9.9	9.9	9.9	9.9	9.9	9.9	9.9	11.2	11.2	11.2
65°	9.9	8.7	9.9	9.9	8.7	9.9	9.9	9.9	11.2	11.2	12.4
67.5°	7.5	7.5	7.5	8.7	8.7	8.7	9.9	9.9	11.2	11.2	11.2
70°	7.5	7.5	8.7	8.7	8.7	8.7	9.9	9.9	11.2	11.2	11.2
72.5°	7.5	7.5	8.7	8.7	8.7	9.9	9.9	9.9	11.2	11.2	11.2
75°	7.5	7.5	8.7	8.7	8.7	9.9	9.9	9.9	11.2	11.2	11.2
77.5°	7.5	7.5	8.7	8.7	8.7	9.9	9.9	11.2	11.2	11.2	11.2
80°	7.5	8.7	8.7	9.9	9.9	9.9	9.9	11.2	11.2	12.4	12.4
82.5°	7.5	8.7	8.7	9.9	9.9	9.9	9.9	11.2	11.2	12.4	12.4
85°	7.5	8.7	8.7	9.9	9.9	9.9	9.9	11.2	11.2	11.2	11.2
87.5°	7.5	8.7	8.7	9.9	9.9	9.9	9.9	9.9	11.2	11.2	11.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192788

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8
2.5°	1028.1	967.1	906.2	876.3	850.1	812.8	765.5	726.8	685.8	664.7	616.2
5°	858.8	754.3	665.9	623.6	591.2	546.4	497.9	462.9	431.9	414.5	383.4
7.5°	664.7	565.0	488.0	455.5	431.9	387.1	351.1	314.8	282.5	258.9	227.8
10°	514.1	436.8	373.4	342.4	316.1	268.8	225.3	191.6	156.8	133.2	123.2
12.5°	408.2	336.1	271.3	240.3	212.9	164.3	131.9	125.7	119.5	117.0	113.3
15°	313.6	247.7	179.2	148.1	136.9	130.7	123.2	122.0	117.0	117.0	113.3
17.5°	235.3	161.8	136.9	134.4	133.2	130.7	127.0	125.7	124.5	124.5	123.2
20°	169.2	156.8	153.1	155.6	156.8	159.3	158.0	158.0	163.0	174.2	171.7
22.5°	237.8	257.7	278.8	286.3	313.6	341.1	366.0	397.1	470.6	555.1	575.0
25°	470.6	530.2	584.9	614.9	659.7	720.6	779.2	851.3	902.4	944.7	993.2
27.5°	584.9	607.5	598.6	602.5	597.4	588.7	591.2	606.2	598.6	576.2	584.9
30°	346.1	363.5	353.5	358.5	344.8	344.8	341.1	348.6	343.6	334.9	332.3
32.5°	225.3	235.3	234.0	234.0	229.1	226.6	217.9	215.4	206.7	190.4	186.6
35°	135.7	129.5	123.2	119.5	117.0	117.0	115.8	115.8	112.0	108.3	107.1
37.5°	73.5	74.7	74.7	74.7	74.7	77.2	76.0	76.0	76.0	73.5	73.5
40°	51.0	53.5	53.5	53.5	54.7	54.7	54.7	55.9	54.7	54.7	54.7
42.5°	39.8	41.0	39.8	39.8	41.0	41.0	41.0	42.3	42.3	42.3	41.0
45°	32.3	32.3	31.1	32.3	32.3	33.6	33.6	33.6	33.6	32.3	32.3
47.5°	26.1	26.1	26.1	26.1	27.4	27.4	27.4	27.4	27.4	27.4	27.4
50°	21.1	21.1	21.1	22.4	22.4	22.4	21.1	22.4	22.4	22.4	21.1
52.5°	16.2	16.2	16.2	16.2	16.2	14.9	14.9	14.9	14.9	14.9	13.7
55°	12.4	12.4	12.4	12.4	12.4	13.7	12.4	13.7	12.4	12.4	11.2
57.5°	11.2	11.2	11.2	11.2	12.4	12.4	11.2	11.2	11.2	9.9	9.9
60°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2	9.9	8.7	8.7
62.5°	12.4	12.4	11.2	11.2	11.2	11.2	9.9	9.9	9.9	8.7	8.7
65°	12.4	12.4	11.2	12.4	12.4	11.2	11.2	9.9	9.9	8.7	8.7
67.5°	12.4	12.4	12.4	12.4	12.4	12.4	11.2	11.2	9.9	9.9	8.7
70°	12.4	12.4	12.4	12.4	12.4	12.4	11.2	11.2	9.9	9.9	8.7
72.5°	12.4	12.4	12.4	12.4	12.4	12.4	11.2	11.2	11.2	9.9	8.7
75°	12.4	12.4	12.4	12.4	12.4	11.2	11.2	11.2	9.9	9.9	8.7
77.5°	12.4	12.4	12.4	12.4	12.4	11.2	11.2	11.2	9.9	9.9	8.7
80°	12.4	12.4	12.4	12.4	12.4	12.4	11.2	11.2	9.9	9.9	8.7
82.5°	12.4	12.4	12.4	12.4	12.4	11.2	11.2	11.2	9.9	9.9	8.7
85°	12.4	11.2	11.2	11.2	11.2	11.2	9.9	9.9	8.7	8.7	7.5
87.5°	11.2	11.2	11.2	11.2	11.2	9.9	9.9	8.7	7.5	6.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192788

CATALOG NUMBER: LDA6A75930D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8	1168.8
2.5°	616.2	605.0	599.9	591.2	583.7	580.0	566.3	582.4
5°	377.2	363.5	359.8	352.3	343.6	338.6	328.5	337.4
7.5°	215.4	199.1	191.6	185.4	176.7	169.2	160.5	165.5
10°	120.7	115.8	117.0	113.3	112.0	110.8	109.6	112.0
12.5°	112.0	108.3	109.6	107.1	105.8	105.8	104.6	105.8
15°	113.3	109.6	112.0	109.6	108.3	108.3	107.1	109.6
17.5°	123.2	120.7	123.2	120.7	122.0	120.7	122.0	123.2
20°	173.0	176.7	184.2	179.2	182.9	187.9	194.1	194.1
22.5°	608.7	688.3	698.2	738.2	840.1	836.4	904.9	907.4
25°	1063.0	1067.9	1112.7	1097.8	1099.0	1151.4	1146.4	1176.2
27.5°	611.2	610.0	618.7	602.5	607.5	611.2	597.4	613.7
30°	341.1	334.9	338.6	329.8	329.8	332.3	328.5	336.1
32.5°	189.1	184.2	184.2	177.9	176.7	175.4	171.7	175.4
35°	108.3	104.6	105.8	103.3	100.9	99.6	98.4	99.6
37.5°	74.7	72.3	73.5	71.0	68.5	67.3	65.9	67.3
40°	54.7	53.5	53.5	51.0	49.7	48.5	47.2	47.2
42.5°	41.0	39.8	39.8	37.3	36.1	34.8	33.6	34.8
45°	31.1	29.8	29.8	28.6	27.4	26.1	26.1	26.1
47.5°	27.4	26.1	27.4	26.1	24.9	24.9	24.9	24.9
50°	21.1	21.1	21.1	19.9	18.6	18.6	17.4	16.2
52.5°	13.7	12.4	12.4	11.2	11.2	9.9	9.9	9.9
55°	11.2	9.9	9.9	8.7	8.7	7.5	7.5	7.5
57.5°	8.7	8.7	7.5	7.5	6.2	6.2	6.2	6.2
60°	7.5	7.5	7.5	6.2	6.2	5.0	5.0	5.0
62.5°	7.5	6.2	6.2	6.2	5.0	5.0	5.0	5.0
65°	7.5	6.2	6.2	6.2	5.0	5.0	5.0	5.0
67.5°	7.5	6.2	6.2	6.2	5.0	5.0	5.0	5.0
70°	8.7	7.5	7.5	6.2	6.2	6.2	5.0	5.0
72.5°	8.7	7.5	7.5	7.5	6.2	6.2	6.2	6.2
75°	8.7	7.5	7.5	7.5	6.2	6.2	6.2	6.2
77.5°	8.7	7.5	7.5	7.5	6.2	6.2	6.2	6.2
80°	8.7	7.5	7.5	7.5	6.2	6.2	6.2	6.2
82.5°	7.5	7.5	7.5	6.2	6.2	6.2	6.2	6.2
85°	7.5	6.2	6.2	6.2	5.0	5.0	5.0	5.0
87.5°	5.0	5.0	3.7	3.7	3.7	2.5	2.5	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)