

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203329

Luminaire Tested: **LE_6B15D010 EC6B10208050 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203329
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208050 6LBMWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1497.9 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203329

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203329

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	85	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	87	78	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203329

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.8	11.4
10°-20°	419.4	28.0
20°-30°	485.3	32.4
30°-40°	310.2	20.7
40°-50°	88.0	5.9
50°-60°	15.7	1.0
60°-70°	6.4	0.4
70°-80°	2.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1075.5	71.8
0°-40°	1385.6	92.5
0°-60°	1489.3	99.4
0°-90°	1497.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1497.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1869	
5°	1835	171
15°	1504	419
25°	1071	485
35°	490	310
45°	102	88
55°	15	16
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P203329

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBMWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1868.6
2.5°	1866.5
5°	1835.2
7.5°	1779.1
10°	1699.9
12.5°	1608.2
15°	1504.1
17.5°	1395.8
20°	1289.5
22.5°	1185.4
25°	1070.8
27.5°	945.8
30°	806.2
32.5°	650.0
35°	489.5
37.5°	354.1
40°	245.9
42.5°	162.5
45°	102.1
47.5°	60.4
50°	35.4
52.5°	20.9
55°	14.6
57.5°	12.5
60°	10.4
62.5°	8.4
65°	6.2
67.5°	4.1
70°	4.1
72.5°	2.1
75°	2.1
77.5°	2.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)