

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192792

Luminaire Tested: **LDA6A75930D010TE LARH40FL 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192792
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26688)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75930D010TE LARH40FL 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7198.9 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 2.63 / 0.54 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192792

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192792

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	91	82	75	70	89	80	74	69	78	73	68	76	71	67	74	70	67	65		
5	85	74	67	62	83	73	66	61	71	65	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	54	64	58	54	62	57	54	52		
7	74	62	55	49	72	61	54	49	60	53	49	59	53	49	57	52	48	46		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	47	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	41	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	73963	73963	73963
5°	203010	68149	27812
10°	444876	55772	10599
15°	679544	42458	12435
20°	787312	31584	19310
25°	858860	25973	31169
30°	959078	23561	31834
35°	975805	16162	21817
40°	992953	7664	11042
45°	994568	3179	4822
50°	840817	1382	1484
55°	270748	946	239
60°	53779	1085	0
65°	5487	1284	0
70°	593	1795	0
75°	0	2372	0
80°	0	3915	379
85°	0	7799	755

TEST NUMBER: P1192792

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.1	2.5
10°-20°	947.2	13.2
20°-30°	1813.7	25.2
30°-40°	2136.8	29.7
40°-50°	1678.4	23.3
50°-60°	409.0	5.7
60°-70°	17.5	0.2
70°-80°	6.6	0.1
80°-90°	6.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2944.0	40.9
0°-40°	5080.8	70.6
0°-60°	7168.2	99.6
0°-90°	7198.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7198.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1349	1349	1349	1349	1349	
5°	3689	2670	1238	648	505	488
15°	11974	6150	748	214	219	3343
25°	14199	7478	429	449	515	6618
35°	14581	4727	242	311	326	9143
45°	12829	1461	41	57	62	9639
55°	2833	54	10	6	2	3372
65°	42	6	10	6	0	112
75°	0	6	11	8	0	0
85°	0	8	12	8	1	0
90°	0	0	0	0	0	

TEST NUMBER: P1192792

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2
2.5°	2312.5	2307.6	2274.0	2305.1	2210.4	2206.7	2164.4	2145.8	2090.9	2038.7	1964.0
5°	3689.1	3608.3	3542.2	3544.7	3363.1	3329.5	3234.9	3139.0	2992.1	2855.2	2669.8
7.5°	5623.2	5527.5	5388.1	5329.5	4982.4	4880.3	4684.9	4429.8	4109.8	3791.2	3447.6
10°	7991.9	8006.8	7826.4	7659.5	7134.4	6927.7	6611.6	6108.7	5502.7	4903.9	4295.3
12.5°	10375.3	10365.4	10150.1	9897.4	9250.2	8959.0	8538.3	7910.9	7108.1	6179.7	5227.6
15°	11973.5	12044.5	11953.6	11752.0	11199.4	10865.8	10391.6	9540.2	8561.9	7434.3	6149.7
17.5°	12976.7	13043.9	13011.6	12853.5	12365.5	12009.7	11613.9	10916.7	9785.4	8367.8	6876.7
20°	13495.6	13601.5	13586.5	13414.8	13046.4	12751.4	12314.6	11668.6	10689.1	9016.1	7347.1
22.5°	13841.7	13922.7	13945.1	13750.8	13370.1	13089.9	12770.1	12115.3	11194.4	9412.0	7533.9
25°	14199.0	14342.1	14201.5	13962.5	13612.6	13343.8	13002.8	12375.5	11435.8	9573.9	7477.8
27.5°	14637.1	14705.4	14386.9	14169.0	13780.8	13489.4	13127.3	12526.1	11478.2	9444.4	7158.0
30°	15151.1	14867.4	14644.5	14212.7	13772.1	13488.2	13119.9	12431.6	11255.3	9014.9	6538.1
32.5°	15066.4	14806.3	14553.6	14096.9	13661.3	13380.0	12969.3	12116.6	10728.8	8296.8	5683.1
35°	14581.0	14637.1	14364.5	13986.1	13493.1	13203.2	12755.1	11668.6	9835.3	7306.1	4727.2
37.5°	14171.5	14294.7	14116.8	13767.0	13266.7	12874.6	12269.7	10949.2	8669.0	6049.0	3821.0
40°	13875.3	13915.2	13819.3	13427.3	12826.2	12259.7	11560.2	9657.2	7252.5	4748.3	3015.7
42.5°	13416.1	13521.9	13352.5	12924.4	12013.4	11372.4	10359.1	8164.9	5633.3	3626.9	2270.3
45°	12828.6	12929.3	12720.3	12008.4	10741.3	9801.6	8565.6	6366.4	4167.1	2673.5	1461.3
47.5°	11870.3	11932.4	11527.9	10543.4	8701.3	7816.4	6549.3	4438.5	2684.7	1494.8	710.7
50°	9858.9	9828.9	8995.0	7784.0	5820.0	4891.5	3898.3	2405.9	1206.1	708.2	444.3
52.5°	6353.9	6285.4	5460.2	4358.7	2947.4	2249.1	1690.2	1038.1	628.6	395.8	175.4
55°	2832.8	2806.7	2297.6	1784.8	1206.1	1038.1	792.9	509.1	334.7	138.2	53.5
57.5°	1050.5	1026.9	904.9	759.3	582.4	484.2	384.6	244.0	85.9	46.0	28.6
60°	490.5	489.2	430.6	354.8	246.5	186.6	108.3	57.2	36.1	24.9	16.2
62.5°	156.8	153.1	107.1	78.5	55.9	48.5	38.5	28.6	18.6	13.7	9.9
65°	42.3	42.3	38.5	32.3	26.1	22.4	18.6	13.7	8.7	7.5	6.2
67.5°	16.2	16.2	14.9	13.7	9.9	8.7	7.5	6.2	5.0	6.2	6.2
70°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	5.0	5.0	6.2
72.5°	0.0	0.0	1.2	1.2	2.5	2.5	3.7	3.7	5.0	6.2	6.2
75°	0.0	0.0	1.2	1.2	2.5	2.5	3.7	3.7	5.0	6.2	6.2
77.5°	0.0	0.0	1.2	1.2	2.5	2.5	3.7	3.7	5.0	6.2	6.2
80°	0.0	0.0	1.2	1.2	2.5	2.5	3.7	3.7	5.0	6.2	6.2
82.5°	0.0	0.0	1.2	2.5	2.5	2.5	3.7	5.0	5.0	6.2	7.5
85°	0.0	0.0	1.2	2.5	2.5	3.7	3.7	5.0	5.0	6.2	7.5
87.5°	0.0	0.0	1.2	2.5	2.5	3.7	3.7	5.0	5.0	6.2	7.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192792

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2
2.5°	1909.3	1827.1	1713.9	1647.9	1631.7	1596.9	1535.8	1445.1	1370.3	1298.2	1255.8
5°	2513.0	2318.8	2100.9	1947.8	1885.7	1802.2	1654.1	1501.0	1360.4	1238.4	1142.5
7.5°	3152.7	2832.8	2480.5	2196.8	2094.7	1962.7	1721.4	1493.6	1300.7	1131.3	1003.1
10°	3788.7	3273.4	2795.5	2384.8	2217.9	2038.7	1720.2	1425.2	1198.6	1001.9	860.0
12.5°	4424.8	3684.1	3026.9	2497.9	2281.5	2054.9	1669.0	1320.6	1069.2	868.7	733.0
15°	5012.2	4011.6	3183.7	2536.6	2275.2	2007.6	1565.8	1193.6	933.5	748.1	622.4
17.5°	5450.3	4183.3	3219.9	2478.1	2176.9	1880.7	1407.6	1044.3	804.1	641.0	512.8
20°	5665.7	4210.6	3134.0	2311.3	2007.6	1700.3	1234.7	901.2	693.3	541.4	433.1
22.5°	5665.7	4081.2	2947.4	2102.1	1796.0	1492.3	1067.9	782.9	606.1	471.6	380.9
25°	5450.3	3823.5	2697.2	1860.8	1563.4	1286.9	923.6	694.5	538.9	429.4	353.5
27.5°	5032.1	3467.7	2376.1	1591.9	1334.3	1104.0	809.0	613.7	488.0	387.1	388.4
30°	4457.1	3030.7	2007.6	1308.2	1099.0	907.4	680.8	514.1	390.8	372.2	383.4
32.5°	3792.4	2507.9	1590.7	1014.3	851.3	714.4	517.8	363.5	311.1	313.6	326.0
35°	3110.4	1974.1	1197.4	751.8	633.6	517.8	339.9	239.0	236.5	241.5	250.2
37.5°	2455.7	1477.4	866.2	550.1	425.6	318.6	182.9	164.3	164.3	169.2	174.2
40°	1839.7	1048.0	596.1	326.0	206.7	145.6	115.8	107.1	105.8	107.1	113.3
42.5°	1263.3	663.4	354.8	130.7	99.6	84.7	73.5	67.1	65.9	67.1	71.0
45°	709.4	408.2	138.2	69.8	59.7	53.5	46.0	42.3	41.0	41.0	43.5
47.5°	444.3	161.8	62.2	43.5	37.3	34.8	29.8	27.4	26.1	26.1	27.4
50°	170.5	63.4	38.5	28.6	24.9	22.4	19.9	17.4	16.2	16.2	17.4
52.5°	58.4	37.3	24.9	18.6	16.2	14.9	12.4	11.2	11.2	11.2	11.2
55°	32.3	22.4	14.9	11.2	9.9	9.9	9.9	9.9	9.9	9.9	9.9
57.5°	19.9	13.7	9.9	8.7	8.7	8.7	8.7	8.7	8.7	9.9	9.9
60°	11.2	8.7	7.5	7.5	7.5	7.5	8.7	8.7	8.7	9.9	9.9
62.5°	7.5	7.5	7.5	7.5	7.5	7.5	8.7	8.7	9.9	9.9	9.9
65°	6.2	6.2	6.2	7.5	7.5	7.5	8.7	8.7	9.9	9.9	9.9
67.5°	6.2	6.2	7.5	7.5	7.5	8.7	8.7	9.9	9.9	9.9	9.9
70°	6.2	7.5	7.5	8.7	8.7	8.7	9.9	9.9	9.9	11.2	11.2
72.5°	6.2	7.5	7.5	8.7	8.7	8.7	9.9	9.9	11.2	11.2	11.2
75°	7.5	7.5	7.5	8.7	8.7	8.7	9.9	11.2	11.2	11.2	11.2
77.5°	7.5	7.5	8.7	8.7	8.7	9.9	9.9	11.2	11.2	11.2	11.2
80°	7.5	7.5	8.7	8.7	9.9	9.9	11.2	11.2	11.2	12.4	12.4
82.5°	7.5	7.5	8.7	9.9	9.9	9.9	11.2	11.2	12.4	12.4	12.4
85°	7.5	8.7	8.7	9.9	9.9	9.9	11.2	11.2	12.4	12.4	12.4
87.5°	7.5	8.7	8.7	9.9	9.9	9.9	11.2	11.2	12.4	12.4	12.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192792

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2
2.5°	1199.9	1147.5	1095.3	1056.7	1038.1	1019.4	978.3	924.8	902.4	869.9	851.3
5°	1045.5	957.1	887.5	841.3	814.0	777.9	730.5	678.3	648.5	614.9	592.4
7.5°	886.3	782.9	715.6	673.4	646.0	601.1	541.4	479.3	443.1	405.8	379.6
10°	746.9	648.5	572.5	524.0	489.2	436.8	377.2	333.5	302.4	270.1	244.0
12.5°	623.6	517.8	436.8	395.8	372.2	322.3	272.6	224.1	205.4	199.1	199.1
15°	505.4	409.5	341.1	306.1	281.3	227.8	217.9	215.4	214.1	212.9	215.4
17.5°	412.0	331.0	258.9	241.5	239.0	237.8	239.0	239.0	240.3	244.0	250.2
20°	346.1	271.3	266.4	267.6	267.6	272.6	278.8	283.8	288.7	295.0	306.1
22.5°	307.4	306.1	314.8	316.1	322.3	329.8	341.1	348.6	361.0	367.2	383.4
25°	354.8	363.5	379.6	384.6	394.6	407.0	424.4	434.4	449.3	456.7	475.5
27.5°	402.0	415.7	435.6	441.8	450.5	470.4	483.0	491.7	499.2	504.1	515.3
30°	398.3	410.7	430.6	431.9	444.3	458.0	465.4	472.9	478.0	476.8	483.0
32.5°	337.2	348.6	367.2	367.2	380.9	392.1	395.8	402.0	402.0	402.0	404.5
35°	258.9	266.4	278.8	282.5	293.7	301.2	303.7	311.1	311.1	308.6	308.6
37.5°	179.2	189.1	197.8	200.3	207.9	212.9	219.1	220.4	217.9	219.1	219.1
40°	117.0	123.2	129.5	130.7	136.9	140.6	146.9	146.9	148.1	146.9	149.3
42.5°	72.3	77.2	81.0	83.5	85.9	88.4	92.2	93.4	94.6	93.4	95.9
45°	44.8	47.2	49.7	51.0	52.2	53.5	57.2	57.2	57.2	57.2	58.4
47.5°	27.4	28.6	29.8	29.8	31.1	32.3	33.6	33.6	33.6	33.6	34.8
50°	16.2	17.4	17.4	17.4	18.6	18.6	19.9	19.9	19.9	18.6	19.9
52.5°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2	9.9	11.2
55°	9.9	9.9	8.7	8.7	8.7	8.7	8.7	7.5	6.2	6.2	5.0
57.5°	8.7	8.7	8.7	8.7	8.7	7.5	7.5	6.2	6.2	5.0	3.7
60°	8.7	8.7	8.7	8.7	8.7	7.5	7.5	6.2	5.0	5.0	3.7
62.5°	9.9	8.7	8.7	8.7	8.7	7.5	7.5	6.2	5.0	5.0	3.7
65°	9.9	9.9	8.7	8.7	8.7	7.5	7.5	6.2	6.2	5.0	3.7
67.5°	9.9	9.9	9.9	8.7	9.9	8.7	7.5	7.5	6.2	5.0	5.0
70°	11.2	9.9	9.9	9.9	9.9	8.7	8.7	7.5	6.2	5.0	5.0
72.5°	11.2	11.2	9.9	9.9	9.9	8.7	8.7	7.5	6.2	6.2	5.0
75°	11.2	11.2	9.9	9.9	9.9	8.7	8.7	7.5	7.5	6.2	5.0
77.5°	11.2	11.2	11.2	9.9	9.9	9.9	8.7	8.7	7.5	6.2	5.0
80°	11.2	11.2	11.2	11.2	11.2	9.9	9.9	8.7	7.5	6.2	5.0
82.5°	12.4	11.2	11.2	11.2	11.2	9.9	9.9	8.7	7.5	6.2	6.2
85°	12.4	12.4	11.2	11.2	11.2	9.9	9.9	8.7	7.5	7.5	6.2
87.5°	12.4	11.2	11.2	11.2	11.2	9.9	9.9	8.7	7.5	6.2	6.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192792

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2	1349.2
2.5°	832.6	822.7	822.7	805.3	802.8	789.1	800.3	792.9
5°	567.5	551.4	546.4	529.0	522.8	506.6	511.6	505.4
7.5°	357.3	341.1	336.0	323.5	316.1	303.7	304.9	301.2
10°	217.9	202.8	199.1	195.3	191.6	190.4	191.6	190.4
12.5°	197.8	196.6	194.1	195.3	192.9	194.1	195.3	194.1
15°	215.4	217.9	215.4	216.6	215.4	217.9	219.1	219.1
17.5°	252.7	257.7	255.2	258.9	257.7	263.9	263.9	263.9
20°	309.9	318.6	316.1	321.1	321.1	328.5	328.5	331.0
22.5°	389.6	400.8	399.5	410.7	408.2	416.9	416.9	419.4
25°	485.5	496.7	497.9	505.4	504.1	512.8	512.8	515.3
27.5°	525.3	531.5	530.2	534.0	535.2	540.2	543.9	541.4
30°	492.9	497.9	496.7	499.2	499.2	502.9	506.6	502.9
32.5°	414.5	418.2	418.2	423.2	419.4	420.7	426.9	423.2
35°	317.3	319.8	317.3	319.8	321.1	321.1	327.3	326.0
37.5°	226.6	227.8	227.8	231.5	227.8	227.8	234.0	235.3
40°	151.8	153.1	151.8	156.8	154.3	154.3	158.0	154.3
42.5°	97.1	98.4	97.1	100.9	98.4	100.9	102.1	103.3
45°	59.7	59.7	58.4	60.9	59.7	60.9	62.2	62.2
47.5°	34.8	34.8	33.6	36.1	34.8	34.8	34.8	36.1
50°	18.6	18.6	18.6	19.9	18.6	18.6	18.6	17.4
52.5°	9.9	9.9	8.7	9.9	8.7	8.7	8.7	8.7
55°	5.0	3.7	3.7	3.7	2.5	2.5	2.5	2.5
57.5°	3.7	2.5	2.5	1.2	1.2	1.2	0.0	0.0
60°	2.5	2.5	1.2	1.2	0.0	0.0	0.0	0.0
62.5°	2.5	2.5	1.2	1.2	0.0	0.0	0.0	0.0
65°	2.5	2.5	1.2	1.2	0.0	0.0	0.0	0.0
67.5°	3.7	2.5	2.5	1.2	1.2	0.0	0.0	0.0
70°	3.7	2.5	2.5	1.2	1.2	0.0	0.0	0.0
72.5°	3.7	2.5	2.5	2.5	1.2	1.2	0.0	0.0
75°	3.7	3.7	2.5	2.5	1.2	1.2	0.0	0.0
77.5°	5.0	3.7	2.5	2.5	1.2	1.2	0.0	0.0
80°	5.0	3.7	2.5	2.5	2.5	1.2	1.2	1.2
82.5°	5.0	3.7	3.7	2.5	2.5	1.2	1.2	1.2
85°	5.0	3.7	3.7	2.5	2.5	1.2	1.2	1.2
87.5°	5.0	3.7	3.7	2.5	2.5	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)