

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192797

Luminaire Tested: **LDA6A75930D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192797
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26685)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75930D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5429.0 lumens
Efficiency: N/A
Efficacy: 62.5 lumens/watt
Spacing Criteria (0/90/45): 2.12 / 1.05 / 1.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192797

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192797

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	76	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55		
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44		
8	67	55	47	42	65	54	47	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	43	38	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	96078	96078	96078
5°	154391	94189	60076
10°	228308	90218	40330
15°	311114	85341	29949
20°	384794	80530	28393
25°	445798	79281	46606
30°	486398	75955	46646
35°	499895	65645	36486
40°	486812	51668	28418
45°	441402	38213	22382
50°	347775	28246	15172
55°	207362	20109	8688
60°	106044	13376	3267
65°	50693	7095	1453
70°	23930	3190	1394
75°	9743	2097	1589
80°	4704	2368	1578
85°	2327	3900	2327

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192797

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	179.9	3.3
10°-20°	635.6	11.7
20°-30°	1196.4	22.0
30°-40°	1456.9	26.8
40°-50°	1212.7	22.3
50°-60°	580.8	10.7
60°-70°	139.5	2.6
70°-80°	22.0	0.4
80°-90°	5.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2011.9	37.1
0°-40°	3468.9	63.9
0°-60°	5262.4	96.9
0°-90°	5429.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5429.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1753	1753	1753	1753	1753	
5°	2806	2380	1712	1245	1092	307
15°	5482	3724	1504	682	528	1571
25°	7370	4353	1311	743	770	3385
35°	7470	3823	981	571	545	4628
45°	5694	2555	493	304	289	4311
55°	2170	1054	210	118	91	2044
65°	391	228	55	17	11	447
75°	46	24	10	9	8	63
85°	4	4	6	5	4	5
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192797

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6
2.5°	2266.7	2187.0	2211.8	2206.9	2201.9	2175.8	2157.1	2141.0	2100.0	2100.0	2047.6
5°	2805.6	2712.2	2736.0	2718.5	2696.1	2656.3	2620.2	2579.1	2503.2	2470.9	2380.0
7.5°	3421.8	3316.0	3337.1	3302.3	3255.1	3201.4	3143.0	3065.8	2945.0	2871.7	2731.0
10°	4101.4	3950.8	3963.2	3911.0	3832.5	3760.4	3704.3	3557.5	3385.8	3263.8	3067.0
12.5°	4745.1	4613.0	4616.7	4543.4	4430.1	4341.6	4257.1	4062.8	3833.8	3659.6	3400.7
15°	5481.8	5320.1	5281.5	5181.9	5033.8	4925.5	4809.7	4564.5	4277.0	4046.7	3724.2
17.5°	6075.6	5908.9	5884.0	5790.6	5579.0	5448.3	5302.6	5026.3	4661.6	4375.4	3979.4
20°	6595.9	6430.4	6388.1	6267.4	6024.6	5875.2	5699.7	5373.5	4975.2	4623.1	4176.1
22.5°	7021.7	6839.9	6780.2	6630.7	6360.6	6192.6	5978.5	5622.5	5178.2	4784.8	4293.2
25°	7370.1	7163.6	7087.6	6918.4	6614.6	6429.2	6193.9	5795.6	5311.4	4877.0	4352.8
27.5°	7593.0	7386.3	7303.0	7108.7	6767.8	6568.6	6312.1	5881.4	5358.6	4889.4	4340.4
30°	7683.9	7469.7	7375.1	7154.9	6787.7	6577.3	6309.7	5844.1	5297.7	4799.8	4235.8
32.5°	7627.8	7417.5	7311.7	7072.7	6690.5	6464.0	6196.4	5699.7	5137.1	4621.8	4054.1
35°	7469.7	7261.8	7152.4	6897.2	6498.8	6262.4	5995.9	5481.8	4913.1	4386.6	3822.6
37.5°	7197.2	7000.4	6874.7	6622.0	6221.2	5979.7	5715.9	5196.8	4615.5	4120.2	3555.0
40°	6802.6	6615.8	6491.3	6221.2	5842.8	5598.8	5349.9	4823.4	4275.7	3792.8	3247.6
42.5°	6299.7	6127.8	6008.3	5745.7	5384.9	5144.6	4916.8	4411.4	3889.9	3430.5	2915.2
45°	5693.5	5544.1	5427.1	5209.3	4853.2	4625.6	4420.1	3962.0	3455.4	3033.5	2555.4
47.5°	4980.2	4857.0	4743.8	4545.8	4224.6	4009.4	3840.0	3420.6	2991.2	2594.1	2187.0
50°	4077.8	3989.5	3901.1	3695.6	3469.1	3281.2	3157.9	2784.5	2437.2	2126.1	1788.7
52.5°	3074.5	3021.0	2958.7	2811.9	2660.0	2550.5	2440.9	2157.1	1897.0	1665.4	1402.8
55°	2169.6	2142.2	2093.7	2033.9	1918.1	1843.5	1748.9	1604.5	1402.8	1247.3	1054.3
57.5°	1466.4	1458.9	1425.2	1389.1	1325.6	1300.7	1221.2	1127.8	1014.5	898.7	761.8
60°	967.2	951.1	943.4	923.6	875.1	855.2	826.6	766.8	697.1	616.2	531.5
62.5°	622.4	613.7	607.5	598.8	568.8	568.8	540.2	512.8	460.6	410.7	356.0
65°	390.8	383.4	382.1	375.9	364.7	359.8	338.6	318.7	293.7	266.4	227.8
67.5°	251.4	240.3	234.0	230.3	222.8	214.1	206.7	198.0	177.9	161.8	136.9
70°	149.3	139.4	138.2	139.4	130.7	129.5	122.0	115.8	102.1	92.2	77.2
72.5°	84.7	79.7	78.5	78.5	73.5	72.3	67.3	63.6	55.9	48.5	42.3
75°	46.0	42.3	42.3	42.3	39.8	38.5	36.1	34.8	29.8	27.4	23.6
77.5°	26.1	24.9	24.9	23.6	22.4	21.1	19.9	19.9	17.4	16.2	14.9
80°	14.9	14.9	14.9	14.9	13.7	13.7	12.4	12.4	11.2	11.2	9.9
82.5°	8.7	8.7	8.7	8.7	8.7	8.7	7.5	7.5	7.5	7.5	6.2
85°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
87.5°	0.0	0.0	1.2	1.2	1.2	1.2	1.2	2.5	2.5	2.5	3.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192797

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6
2.5°	2024.0	1986.7	1984.2	1929.3	1894.5	1865.9	1844.8	1818.5	1760.1	1727.8	1704.0
5°	2316.4	2239.4	2199.4	2100.0	2045.1	1996.6	1936.8	1874.6	1778.7	1711.6	1656.7
7.5°	2620.2	2492.0	2407.3	2259.2	2184.5	2108.7	2007.8	1906.9	1776.3	1675.4	1592.1
10°	2902.8	2721.1	2586.5	2387.5	2290.3	2190.7	2048.8	1913.2	1750.1	1620.7	1511.1
12.5°	3180.3	2941.3	2755.9	2503.2	2385.0	2261.7	2079.9	1909.4	1717.8	1562.1	1433.9
15°	3445.4	3145.5	2909.0	2604.1	2465.8	2317.7	2100.0	1898.2	1680.4	1503.7	1358.1
17.5°	3657.1	3301.1	3017.3	2666.2	2510.7	2342.7	2092.5	1865.9	1629.4	1441.4	1282.1
20°	3802.7	3400.7	3077.0	2691.1	2520.6	2340.1	2063.7	1821.0	1575.8	1380.4	1218.7
22.5°	3881.2	3445.4	3093.1	2683.6	2505.7	2316.4	2028.9	1780.0	1533.5	1338.2	1183.7
25°	3909.8	3449.2	3075.7	2651.3	2472.1	2279.1	1987.9	1741.4	1499.9	1310.7	1166.3
27.5°	3876.2	3396.9	3012.3	2584.0	2402.4	2211.8	1921.9	1686.6	1450.1	1270.9	1135.2
30°	3761.7	3275.0	2887.8	2464.5	2286.6	2103.7	1817.3	1585.9	1369.3	1199.9	1070.4
32.5°	3579.9	3095.6	2712.2	2300.3	2128.5	1952.9	1679.1	1458.9	1257.2	1097.9	982.1
35°	3354.7	2881.6	2508.2	2108.7	1946.7	1781.2	1521.1	1313.2	1124.0	980.9	867.6
37.5°	3099.5	2643.9	2282.9	1915.6	1751.4	1595.8	1343.1	1165.1	983.4	852.7	749.4
40°	2813.1	2371.3	2042.6	1685.3	1541.0	1399.1	1165.1	1003.3	837.8	722.0	632.3
42.5°	2507.0	2095.0	1791.2	1470.1	1325.6	1196.1	985.9	840.3	693.3	597.5	526.5
45°	2182.0	1818.5	1527.3	1239.8	1109.1	997.1	805.3	673.4	566.3	492.9	439.3
47.5°	1842.3	1521.1	1262.2	1012.0	896.2	799.1	644.8	543.9	459.4	405.8	364.7
50°	1499.9	1213.7	1008.3	795.4	695.9	618.7	504.1	434.4	372.2	331.2	299.9
52.5°	1172.5	938.5	771.7	600.0	524.0	470.6	393.3	344.8	297.4	266.4	242.7
55°	866.4	707.1	563.8	435.6	390.8	357.3	302.4	267.6	234.0	210.4	193.0
57.5°	626.1	506.6	402.0	320.0	290.0	267.6	227.8	204.2	180.4	163.0	149.3
60°	439.3	349.8	283.8	234.0	212.9	198.0	169.2	154.3	136.9	122.0	108.3
62.5°	288.7	235.3	198.0	165.5	153.1	141.9	122.0	110.8	95.9	85.9	73.5
65°	187.9	154.3	131.9	110.8	100.9	95.9	82.2	73.5	63.6	54.7	47.2
67.5°	114.5	95.9	83.5	69.8	64.8	59.7	51.0	44.8	38.5	32.3	28.6
70°	63.6	55.9	48.5	41.0	37.3	34.8	29.8	27.4	22.4	19.9	16.2
72.5°	37.3	32.3	28.6	23.6	22.4	21.1	17.4	16.2	13.7	12.4	11.2
75°	22.4	18.6	17.4	14.9	13.7	13.7	12.4	11.2	9.9	9.9	8.7
77.5°	13.7	12.4	11.2	9.9	9.9	9.9	8.7	8.7	8.7	7.5	7.5
80°	8.7	8.7	8.7	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
82.5°	6.2	6.2	6.2	5.0	6.2	5.0	6.2	6.2	6.2	6.2	6.2
85°	3.7	3.7	5.0	5.0	5.0	5.0	5.0	6.2	6.2	6.2	6.2
87.5°	3.7	3.7	5.0	5.0	5.0	5.0	5.0	6.2	6.2	6.2	5.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192797

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6
2.5°	1676.6	1630.6	1597.1	1572.1	1580.8	1537.2	1523.6	1476.3	1458.9	1458.9	1433.9
5°	1600.8	1527.3	1470.1	1433.9	1431.4	1369.3	1336.9	1277.1	1244.8	1221.2	1197.4
7.5°	1509.9	1415.3	1339.4	1295.7	1283.3	1210.0	1166.3	1106.6	1058.0	1026.9	998.3
10°	1412.8	1299.5	1213.7	1163.8	1145.2	1065.4	1008.3	953.6	901.2	868.9	839.0
12.5°	1319.4	1196.1	1101.6	1050.5	1026.9	944.7	886.3	829.1	779.2	745.6	715.8
15°	1233.6	1102.9	1003.3	952.3	926.0	845.2	786.6	730.7	682.1	651.0	623.6
17.5°	1152.6	1019.4	919.8	870.1	841.5	766.8	710.8	656.0	612.4	583.8	558.8
20°	1091.7	959.8	867.6	824.1	795.4	725.7	677.1	629.8	593.8	572.7	548.9
22.5°	1065.4	943.4	865.1	825.3	805.3	749.4	715.8	682.1	658.4	654.7	639.8
25°	1061.7	954.8	890.0	856.4	844.0	801.6	781.7	760.5	743.1	748.1	750.6
27.5°	1045.5	945.9	892.5	863.9	853.9	819.0	804.1	784.2	771.7	777.9	780.4
30°	989.6	897.5	847.7	824.1	814.0	779.2	766.8	744.4	734.4	735.7	734.4
32.5°	902.4	815.2	769.2	748.1	736.9	705.8	692.0	672.1	657.2	656.0	653.5
35°	796.6	718.3	675.8	657.2	646.0	619.9	607.5	588.8	571.4	570.2	567.5
37.5°	688.3	618.7	582.6	566.3	556.3	535.2	520.3	507.9	496.7	491.7	490.5
40°	583.8	521.5	495.4	483.0	475.5	453.2	445.7	433.1	424.4	419.4	418.2
42.5°	485.5	441.8	420.7	409.5	403.3	387.1	378.4	368.5	359.8	354.8	353.5
45°	412.0	375.9	356.0	347.3	342.4	327.4	321.2	311.1	303.7	299.9	298.7
47.5°	343.6	314.8	301.2	291.2	290.0	277.5	268.8	261.4	253.9	250.2	249.0
50°	281.3	257.7	246.5	240.3	239.0	226.6	220.4	214.1	207.9	204.2	201.7
52.5°	231.5	209.2	201.7	193.0	191.8	180.4	175.4	169.2	163.0	158.0	154.3
55°	182.9	165.5	158.0	150.6	149.3	136.9	131.9	124.5	118.3	113.3	108.3
57.5°	139.4	125.7	118.3	110.8	109.6	100.9	92.2	85.9	79.7	73.5	69.8
60°	102.1	88.4	79.7	76.0	72.3	63.6	57.2	52.2	47.2	43.5	39.8
62.5°	67.3	57.2	51.0	46.0	43.5	37.3	33.6	29.8	27.4	26.1	24.9
65°	41.0	34.8	29.8	27.4	27.4	23.6	21.1	18.6	17.4	17.4	16.2
67.5°	24.9	21.1	18.6	17.4	16.2	14.9	13.7	13.7	12.4	12.4	11.2
70°	14.9	13.7	12.4	11.2	11.2	11.2	11.2	11.2	9.9	9.9	9.9
72.5°	11.2	9.9	9.9	9.9	9.9	9.9	9.9	9.9	8.7	8.7	8.7
75°	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	8.7	7.5
77.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
80°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	6.2	6.2	6.2
82.5°	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2	6.2
85°	6.2	6.2	6.2	6.2	6.2	6.2	5.0	5.0	5.0	5.0	5.0
87.5°	6.2	5.0	5.0	5.0	5.0	5.0	3.7	3.7	3.7	3.7	2.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192797

CATALOG NUMBER: LDA6A75930D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6	1752.6
2.5°	1421.5	1431.4	1416.5	1406.5	1396.6	1404.1	1369.3	1354.3
5°	1175.0	1163.8	1156.4	1147.6	1132.7	1135.2	1105.4	1091.7
7.5°	972.2	964.7	945.9	936.0	921.1	921.1	893.7	882.5
10°	811.5	800.3	782.9	774.2	760.5	749.4	735.7	724.5
12.5°	689.5	677.1	662.2	654.7	641.0	632.3	618.7	621.1
15°	598.8	586.3	572.7	565.0	553.9	545.2	534.0	527.7
17.5°	535.2	524.0	512.8	505.4	496.7	489.2	479.3	478.0
20°	530.2	521.5	515.3	510.3	502.9	497.9	492.9	486.7
22.5°	634.8	636.1	637.3	637.3	638.5	638.5	639.8	627.4
25°	749.4	763.0	763.0	766.8	777.9	777.9	775.5	770.5
27.5°	779.2	792.9	789.1	791.6	802.8	805.3	796.6	797.8
30°	729.5	741.9	734.4	735.7	743.1	743.1	731.9	736.9
32.5°	646.0	653.5	643.5	643.5	649.7	648.5	641.0	641.0
35°	557.6	561.3	552.6	556.3	556.3	552.6	545.2	545.2
37.5°	481.7	483.0	474.3	475.5	475.5	471.8	464.3	464.3
40°	409.5	413.2	405.8	408.2	405.8	402.0	398.3	397.1
42.5°	346.1	348.6	342.4	346.1	344.8	344.8	343.6	344.8
45°	291.2	293.7	288.7	291.2	292.5	291.2	287.5	288.7
47.5°	241.5	244.0	244.0	241.5	240.3	234.0	230.3	230.3
50°	195.5	194.3	193.0	189.1	185.4	181.7	177.9	177.9
52.5°	146.9	144.4	143.1	139.4	138.2	134.4	134.4	130.7
55°	100.9	99.6	99.6	95.9	95.9	92.2	90.9	90.9
57.5°	63.6	60.9	62.2	59.7	58.4	54.7	54.7	53.5
60°	36.1	34.8	34.8	33.6	32.3	29.8	29.8	29.8
62.5°	23.6	22.4	22.4	21.1	21.1	19.9	19.9	18.6
65°	14.9	13.7	13.7	12.4	12.4	11.2	11.2	11.2
67.5°	11.2	9.9	9.9	9.9	9.9	9.9	8.7	8.7
70°	9.9	9.9	8.7	8.7	8.7	8.7	8.7	8.7
72.5°	8.7	8.7	8.7	8.7	7.5	7.5	7.5	7.5
75°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
77.5°	7.5	6.2	6.2	6.2	6.2	6.2	6.2	6.2
80°	6.2	6.2	6.2	6.2	6.2	6.2	5.0	5.0
82.5°	6.2	5.0	5.0	5.0	5.0	5.0	5.0	5.0
85°	5.0	3.7	3.7	3.7	3.7	3.7	3.7	3.7
87.5°	2.5	2.5	2.5	2.5	1.2	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)