

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203844

Luminaire Tested: **LE_6B15D010 EC6B10208050 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208050 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 954.3 lumens
Efficiency: N/A
Efficacy: 66.7 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203844

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203844

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203844

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.0	11.0
10°-20°	259.0	27.1
20°-30°	313.8	32.9
30°-40°	213.9	22.4
40°-50°	50.9	5.3
50°-60°	8.0	0.8
60°-70°	2.9	0.3
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	677.8	71.0
0°-40°	891.7	93.4
0°-60°	950.6	99.6
0°-90°	954.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	954.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1160	
5°	1127	105
15°	927	259
25°	686	314
35°	342	214
45°	54	51
55°	9	8
65°	2	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203844

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1160.1
2.5°	1153.5
5°	1127.4
7.5°	1092.6
10°	1042.5
12.5°	986.0
15°	927.2
17.5°	866.2
20°	805.2
22.5°	744.4
25°	685.6
27.5°	631.1
30°	552.9
32.5°	450.5
35°	341.8
37.5°	243.8
40°	161.0
42.5°	100.1
45°	54.4
47.5°	28.2
50°	15.2
52.5°	10.9
55°	8.8
57.5°	6.5
60°	4.4
62.5°	4.4
65°	2.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)