

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192798

Luminaire Tested: **LDA6A75935D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192798
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75935D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6688.2 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192798

CATALOG NUMBER: LDA6A75935D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192798

CATALOG NUMBER: LDA6A75935D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	112	109	106	104	110	107	104	102		103	101	99			99	97	96			96
2	105	100	95	91	103	98	94	90		95	91	88			92	89	86			89
3	99	91	85	80	96	89	84	80		87	82	78			84	80	77			82
4	92	83	76	71	90	82	76	71		79	74	70			77	73	69			75
5	86	76	69	64	84	75	68	63		73	67	63			71	66	62			69
6	80	69	62	57	79	69	62	57		67	61	56			65	60	56			64
7	75	64	56	51	73	63	56	51		62	55	51			60	55	50			59
8	70	59	51	46	69	58	51	46		57	50	46			56	50	46			54
9	66	54	47	42	64	53	47	42		52	46	42			51	46	42			50
10	61	50	43	38	60	49	43	38		48	42	38			48	42	38			47

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	103506	103506	103506
5°	200566	98635	33265
10°	340759	86315	14941
15°	525082	68848	23752
20°	760114	44804	41315
25°	1115230	43242	53126
30°	1296719	40962	40709
35°	1312495	21696	21516
40°	1086657	8172	9031
45°	820705	2783	3303
50°	561500	1023	1023
55°	78095	889	134
60°	2039	866	0
65°	519	1206	0
70°	224	1491	0
75°	0	1970	0
80°	0	3346	442
85°	0	6667	0

TEST NUMBER: P1192798

CATALOG NUMBER: LDA6A75935D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	198.1	3.0
10°-20°	837.3	12.5
20°-30°	1910.1	28.6
30°-40°	2210.4	33.0
40°-50°	1333.1	19.9
50°-60°	181.1	2.7
60°-70°	5.8	0.1
70°-80°	6.3	0.1
80°-90°	5.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2945.5	44.0
0°-40°	5155.9	77.1
0°-60°	6670.1	99.7
0°-90°	6688.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6688.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1888	1888	1888	1888	1888	
5°	3645	2984	1792	981	604	424
15°	9252	5201	1213	373	418	2739
25°	18437	6163	715	860	878	8344
35°	19612	4698	324	331	322	11819
45°	10586	1280	36	44	43	8278
55°	817	9	9	7	1	1602
65°	4	5	9	5	0	6
75°	0	7	9	7	0	0
85°	0	7	11	7	0	0
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192798

CATALOG NUMBER: LDA6A75935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1
2.5°	2730.6	2705.2	2716.0	2688.0	2617.6	2603.0	2601.6	2583.1	2523.3	2476.8	2420.9
5°	3644.7	3643.4	3649.9	3590.3	3466.7	3428.2	3409.5	3364.3	3219.5	3107.9	2984.4
7.5°	4786.1	4778.2	4770.1	4661.1	4467.2	4392.8	4344.9	4181.6	3982.2	3784.2	3563.7
10°	6121.5	6117.4	6087.0	5895.5	5584.7	5447.8	5354.7	5095.7	4775.4	4493.8	4119.1
12.5°	7672.1	7636.2	7581.8	7301.3	6874.9	6726.0	6521.3	6110.7	5619.2	5187.3	4663.8
15°	9251.9	9200.1	9103.2	8743.0	8214.1	7960.3	7706.6	7165.8	6498.8	5871.6	5200.7
17.5°	10797.2	10740.0	10512.8	9901.6	9384.8	9075.2	8793.5	8050.8	7266.8	6460.2	5609.9
20°	13029.4	12822.3	12426.3	11463.0	10502.3	9944.2	9614.6	8829.4	7859.5	6920.1	5900.8
22.5°	16011.1	15551.5	14707.6	13142.4	11769.9	10964.6	10425.2	9380.7	8285.9	7220.3	6080.3
25°	18437.4	18228.7	17269.4	15042.5	12900.6	11951.9	11201.1	9819.3	8596.9	7420.9	6162.6
27.5°	20001.3	19949.5	18853.3	16615.6	13824.0	12579.1	11740.7	10108.9	8747.0	7463.5	6122.7
30°	20485.0	20566.0	19513.6	17149.9	14091.1	12705.3	11788.4	10113.0	8631.4	7270.8	5867.7
32.5°	20449.1	20453.0	19162.9	16688.8	13656.6	12338.5	11389.8	9776.7	8204.9	6788.5	5382.7
35°	19612.0	19406.1	17947.1	15272.3	12645.4	11482.9	10600.6	9125.7	7501.9	6063.0	4698.4
37.5°	17774.3	17504.6	15803.8	13458.6	11448.4	10373.4	9661.2	8271.3	6664.9	5288.4	3991.5
40°	15184.7	14801.9	13398.8	11772.5	10138.2	9330.4	8732.4	7315.9	5769.3	4528.3	3328.4
42.5°	12592.3	12405.0	11477.6	10155.4	9036.7	8276.6	7652.2	6315.4	4908.2	3778.9	2490.0
45°	10586.0	10425.2	9802.0	8930.4	7832.9	7139.2	6537.3	5272.3	3813.4	2535.2	1279.6
47.5°	9124.3	8994.1	8397.5	7482.0	6278.3	5519.6	4899.1	3457.4	2160.6	1094.8	320.3
50°	6583.8	6450.9	5866.3	4806.0	3719.1	3084.0	2637.5	1543.9	612.6	221.9	33.3
52.5°	3227.4	3118.5	2721.3	2036.9	1367.2	983.2	718.9	289.7	70.4	23.9	16.0
55°	817.1	750.8	625.8	393.3	192.7	115.6	74.4	26.6	17.2	13.4	9.3
57.5°	46.5	45.2	41.2	30.6	22.5	19.9	17.2	13.4	9.3	7.9	6.7
60°	18.6	17.2	16.0	13.4	10.6	9.3	9.3	6.7	5.3	5.3	5.3
62.5°	7.9	7.9	7.9	6.7	5.3	5.3	5.3	4.0	5.3	5.3	5.3
65°	4.0	4.0	4.0	2.6	2.6	2.6	4.0	4.0	4.0	5.3	5.3
67.5°	2.6	1.4	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.3	5.3
70°	1.4	1.4	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.3	6.7
72.5°	0.0	1.4	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.3	6.7
75°	0.0	1.4	1.4	1.4	2.6	2.6	2.6	4.0	5.3	5.3	6.7
77.5°	0.0	1.4	1.4	1.4	2.6	2.6	2.6	4.0	5.3	5.3	6.7
80°	0.0	1.4	1.4	1.4	2.6	2.6	2.6	4.0	5.3	5.3	6.7
82.5°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	5.3	5.3	6.7
85°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	5.3	5.3	6.7
87.5°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.3	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192798

CATALOG NUMBER: LDA6A75935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1
2.5°	2349.2	2301.4	2231.0	2184.5	2139.3	2096.7	2026.3	1986.5	1914.7	1848.2	1791.2
5°	2835.5	2716.0	2571.1	2447.4	2367.7	2289.4	2147.2	2042.3	1910.7	1792.4	1683.5
7.5°	3327.2	3115.8	2878.1	2674.8	2551.1	2430.2	2217.6	2047.6	1861.6	1692.8	1532.0
10°	3773.6	3456.0	3119.9	2828.8	2661.4	2504.6	2224.3	1998.5	1759.2	1550.6	1348.6
12.5°	4188.1	3753.6	3315.2	2935.1	2727.9	2539.1	2196.5	1920.0	1635.6	1388.5	1153.4
15°	4557.5	3999.4	3457.4	2996.3	2753.1	2530.0	2131.3	1809.7	1489.5	1213.1	915.5
17.5°	4837.8	4152.2	3519.9	2987.0	2707.9	2459.4	2019.6	1671.5	1334.0	999.2	663.1
20°	5008.0	4217.3	3506.5	2915.2	2610.9	2347.8	1886.7	1521.4	1146.7	768.0	584.6
22.5°	5079.6	4212.0	3444.0	2807.7	2491.4	2225.7	1759.2	1375.2	950.0	695.0	610.0
25°	5091.6	4157.6	3356.4	2689.4	2373.2	2108.7	1630.3	1209.2	825.2	714.9	683.0
27.5°	4999.9	4030.1	3191.7	2519.2	2207.0	1933.4	1437.6	960.7	774.7	712.2	733.5
30°	4728.9	3739.0	2900.6	2220.2	1918.8	1644.9	1027.1	753.4	643.1	647.1	652.4
32.5°	4252.0	3255.4	2432.8	1783.1	1453.6	1084.2	639.2	503.7	488.9	488.9	486.3
35°	3615.4	2664.1	1909.4	1128.1	722.8	520.9	330.9	332.3	325.6	324.2	322.9
37.5°	2957.8	2102.0	1209.2	466.4	313.6	217.9	195.3	198.0	195.3	199.4	196.6
40°	2332.0	1298.2	441.2	148.9	110.3	106.3	108.9	111.6	111.6	114.2	114.2
42.5°	1355.3	430.5	115.6	59.8	59.8	57.2	58.4	61.1	62.5	63.7	62.5
45°	402.6	89.0	37.1	33.3	33.3	31.9	31.9	33.3	34.5	35.9	35.9
47.5°	63.7	25.2	21.3	18.6	18.6	18.6	18.6	18.6	19.9	19.9	21.3
50°	19.9	16.0	13.4	12.0	12.0	10.6	10.6	12.0	12.0	12.0	13.4
52.5°	12.0	9.3	9.3	7.9	9.3	9.3	7.9	9.3	9.3	9.3	10.6
55°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	9.3	9.3	9.3
57.5°	6.7	6.7	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
60°	6.7	6.7	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	9.3
62.5°	6.7	6.7	7.9	7.9	7.9	7.9	7.9	7.9	9.3	9.3	9.3
65°	6.7	6.7	7.9	7.9	7.9	7.9	7.9	9.3	9.3	9.3	9.3
67.5°	6.7	7.9	7.9	7.9	7.9	9.3	9.3	9.3	9.3	9.3	9.3
70°	6.7	7.9	7.9	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
72.5°	6.7	7.9	7.9	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
75°	7.9	7.9	7.9	9.3	9.3	9.3	9.3	9.3	9.3	9.3	10.6
77.5°	7.9	7.9	9.3	9.3	9.3	9.3	9.3	9.3	10.6	10.6	10.6
80°	7.9	7.9	9.3	9.3	9.3	9.3	9.3	10.6	10.6	10.6	10.6
82.5°	7.9	7.9	9.3	9.3	9.3	9.3	9.3	10.6	10.6	10.6	10.6
85°	7.9	7.9	9.3	9.3	9.3	9.3	9.3	10.6	10.6	10.6	10.6
87.5°	7.9	7.9	9.3	9.3	9.3	9.3	9.3	10.6	10.6	10.6	10.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192798

CATALOG NUMBER: LDA6A75935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1
2.5°	1741.9	1680.8	1651.6	1610.4	1581.2	1516.1	1489.5	1444.3	1407.2	1345.9	1350.0
5°	1590.5	1474.9	1396.4	1335.4	1292.8	1189.1	1120.1	1047.1	980.6	898.2	867.6
7.5°	1380.6	1238.4	1118.7	1045.7	991.2	853.0	700.2	580.6	490.3	425.2	400.0
10°	1170.6	985.9	796.0	683.0	604.5	471.6	403.9	372.0	342.8	306.9	283.0
12.5°	926.0	663.1	490.3	445.1	413.2	369.4	325.6	290.9	297.6	299.0	308.3
15°	632.5	477.1	422.5	391.9	357.4	332.3	346.9	356.0	373.4	374.7	386.6
17.5°	514.2	447.7	403.9	402.6	405.3	419.9	442.4	454.4	477.1	482.4	499.6
20°	514.2	475.7	512.8	512.8	519.5	539.4	568.6	586.0	611.2	620.5	641.8
22.5°	586.0	612.6	659.1	664.3	667.0	688.3	725.4	742.8	772.0	777.3	799.9
25°	714.9	738.8	781.4	785.2	786.6	802.5	830.5	839.8	859.7	849.1	862.3
27.5°	756.0	766.6	793.2	796.0	789.3	796.0	806.5	806.5	813.2	791.9	796.0
30°	664.3	667.0	680.4	681.6	667.0	669.6	671.0	669.6	668.4	645.7	645.7
32.5°	492.9	492.9	510.2	506.3	490.3	494.3	494.3	494.3	492.9	474.3	471.6
35°	326.8	328.2	342.8	340.2	328.2	330.9	330.9	334.9	330.9	320.3	317.6
37.5°	199.4	200.6	207.3	208.6	204.7	205.9	207.3	205.9	208.6	203.3	200.6
40°	115.6	118.3	123.5	124.9	123.5	123.5	124.9	126.2	131.5	124.9	122.3
42.5°	67.8	69.2	71.8	71.8	71.8	71.8	73.0	74.4	75.7	74.4	73.0
45°	38.5	39.9	41.2	41.2	42.6	41.2	42.6	42.6	43.8	42.6	42.6
47.5°	22.5	22.5	23.9	23.9	25.2	23.9	25.2	25.2	25.2	23.9	23.9
50°	13.4	14.6	14.6	14.6	14.6	14.6	14.6	14.6	14.6	13.4	13.4
52.5°	10.6	10.6	10.6	10.6	10.6	9.3	9.3	9.3	9.3	7.9	7.9
55°	9.3	9.3	9.3	9.3	9.3	9.3	7.9	6.7	6.7	5.3	5.3
57.5°	7.9	9.3	9.3	9.3	9.3	7.9	7.9	6.7	5.3	4.0	4.0
60°	9.3	9.3	9.3	9.3	7.9	7.9	7.9	6.7	5.3	4.0	4.0
62.5°	9.3	9.3	9.3	9.3	9.3	7.9	7.9	6.7	5.3	4.0	4.0
65°	9.3	9.3	9.3	9.3	9.3	7.9	7.9	6.7	5.3	4.0	4.0
67.5°	9.3	9.3	9.3	9.3	9.3	7.9	7.9	6.7	5.3	5.3	4.0
70°	9.3	10.6	10.6	9.3	9.3	9.3	7.9	6.7	6.7	5.3	4.0
72.5°	9.3	10.6	10.6	9.3	9.3	9.3	7.9	6.7	6.7	5.3	4.0
75°	10.6	10.6	10.6	10.6	9.3	9.3	7.9	7.9	6.7	5.3	4.0
77.5°	10.6	10.6	10.6	10.6	9.3	9.3	7.9	7.9	6.7	5.3	4.0
80°	10.6	10.6	10.6	10.6	10.6	9.3	9.3	7.9	6.7	5.3	5.3
82.5°	10.6	10.6	10.6	10.6	10.6	9.3	9.3	7.9	6.7	5.3	5.3
85°	10.6	10.6	10.6	10.6	10.6	9.3	9.3	7.9	6.7	5.3	4.0
87.5°	10.6	10.6	10.6	10.6	9.3	9.3	7.9	7.9	6.7	5.3	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192798

CATALOG NUMBER: LDA6A75935D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1	1888.1
2.5°	1300.9	1270.3	1257.1	1278.2	1267.6	1235.8	1242.3	1222.4
5°	775.9	729.5	700.2	713.5	671.0	632.5	632.5	604.5
7.5°	374.7	360.1	352.1	354.8	345.5	333.5	326.8	326.8
10°	263.1	257.8	259.1	259.1	267.1	265.7	269.8	268.4
12.5°	312.2	314.8	316.2	321.5	328.2	328.2	332.3	329.5
15°	400.0	397.4	405.3	406.5	417.3	418.5	423.9	418.5
17.5°	508.9	514.2	522.2	520.9	542.0	543.4	543.4	542.0
20°	655.0	659.1	667.0	669.6	695.0	697.6	706.9	708.2
22.5°	814.5	814.5	818.5	823.8	847.7	849.1	853.0	853.0
25°	869.0	861.1	862.3	869.0	882.2	876.9	881.0	878.3
27.5°	798.6	786.6	784.0	793.2	802.5	787.9	793.2	793.2
30°	648.5	637.8	635.1	644.5	651.1	635.1	640.4	643.1
32.5°	474.3	467.8	466.4	473.0	478.3	465.1	470.4	474.3
35°	320.3	317.6	314.8	316.2	324.2	313.6	318.9	321.5
37.5°	203.3	198.0	199.4	202.0	207.3	200.6	205.9	205.9
40°	124.9	122.3	122.3	124.9	127.6	122.3	124.9	126.2
42.5°	73.0	73.0	73.0	74.4	75.7	73.0	73.0	74.4
45°	42.6	41.2	41.2	42.6	43.8	41.2	42.6	42.6
47.5°	23.9	22.5	22.5	23.9	23.9	22.5	23.9	23.9
50°	13.4	12.0	12.0	13.4	13.4	12.0	12.0	12.0
52.5°	6.7	6.7	6.7	6.7	6.7	6.7	5.3	5.3
55°	4.0	4.0	2.6	2.6	2.6	2.6	2.6	1.4
57.5°	2.6	2.6	1.4	1.4	1.4	1.4	0.0	0.0
60°	2.6	2.6	1.4	1.4	1.4	0.0	0.0	0.0
62.5°	2.6	2.6	1.4	1.4	1.4	0.0	0.0	0.0
65°	2.6	2.6	1.4	1.4	1.4	0.0	0.0	0.0
67.5°	2.6	2.6	1.4	1.4	1.4	0.0	0.0	0.0
70°	4.0	2.6	2.6	1.4	1.4	1.4	0.0	0.0
72.5°	4.0	2.6	2.6	2.6	1.4	1.4	0.0	0.0
75°	4.0	2.6	2.6	2.6	1.4	1.4	0.0	0.0
77.5°	4.0	2.6	2.6	2.6	1.4	1.4	1.4	0.0
80°	4.0	2.6	2.6	2.6	1.4	1.4	1.4	1.4
82.5°	4.0	2.6	2.6	2.6	1.4	1.4	1.4	1.4
85°	4.0	2.6	2.6	2.6	1.4	1.4	1.4	0.0
87.5°	4.0	2.6	2.6	2.6	1.4	1.4	1.4	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)