

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204050

Luminaire Tested: **LE_6B15D010 EC6B10208050 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204050
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208050 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1369.6 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204050

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204050

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90		
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66		
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47		
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204050

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.3	7.6
10°-20°	276.5	20.2
20°-30°	369.1	26.9
30°-40°	297.8	21.7
40°-50°	142.8	10.4
50°-60°	84.6	6.2
60°-70°	56.2	4.1
70°-80°	30.1	2.2
80°-90°	8.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	749.9	54.8
0°-40°	1047.7	76.5
0°-60°	1275.0	93.1
0°-90°	1369.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1369.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1123	
5°	1110	104
15°	984	276
25°	808	369
35°	477	298
45°	176	143
55°	94	85
65°	57	56
75°	28	30
85°	6	8
90°	0	



TEST NUMBER: P204050

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1123.2
2.5°	1123.2
5°	1110.1
7.5°	1088.4
10°	1057.9
12.5°	1025.2
15°	983.9
17.5°	944.8
20°	901.2
22.5°	855.5
25°	807.6
27.5°	757.5
30°	685.8
32.5°	585.6
35°	476.8
37.5°	376.6
40°	291.8
42.5°	226.4
45°	176.4
47.5°	139.4
50°	117.5
52.5°	104.5
55°	93.6
57.5°	84.9
60°	74.0
62.5°	65.2
65°	56.6
67.5°	47.9
70°	41.4
72.5°	34.9
75°	28.2
77.5°	21.8
80°	17.4
82.5°	13.0
85°	6.5
87.5°	2.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)