

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192808

Luminaire Tested: **LDA6A75935D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26684)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75935D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5476.5 lumens
Efficiency: N/A
Efficacy: 63.0 lumens/watt
Spacing Criteria (0/90/45): 2.21 / 1.07 / 1.54
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192808

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192808

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	61		
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54		
6	77	65	57	51	75	64	57	51	62	56	51	61	55	50	59	54	50	48		
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35		
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	86391	86391	86391
5°	137249	85329	55426
10°	205919	81879	37207
15°	295093	77594	27526
20°	389526	72555	22944
25°	467531	70722	33522
30°	522422	70903	50634
35°	537111	63490	43226
40°	517570	50487	32139
45°	456148	37492	24723
50°	355724	27769	17108
55°	205737	20319	11049
60°	96144	14122	4956
65°	44998	7757	2075
70°	20869	3414	1491
75°	8727	2245	1673
80°	3788	2494	2115
85°	881	4214	3334

TEST NUMBER: P1192808

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.0	3.0
10°-20°	598.2	10.9
20°-30°	1184.3	21.6
30°-40°	1531.2	28.0
40°-50°	1258.2	23.0
50°-60°	581.7	10.6
60°-70°	132.8	2.4
70°-80°	21.7	0.4
80°-90°	5.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1945.4	35.5
0°-40°	3476.6	63.5
0°-60°	5316.5	97.1
0°-90°	5476.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5476.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1576	1576	1576	1576	1576	
5°	2494	2145	1551	1122	1007	275
15°	5200	3477	1367	613	485	1519
25°	7729	4326	1169	574	554	3559
35°	8026	3960	949	630	646	4969
45°	5884	2674	484	322	319	4478
55°	2153	1040	213	137	116	2023
65°	347	213	60	22	16	397
75°	41	24	11	9	8	55
85°	1	4	7	7	5	4
90°	0	0	0	0	0	

TEST NUMBER: P1192808

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9
2.5°	2001.1	1970.5	1989.2	1998.5	1950.6	1961.2	1966.6	1929.3	1918.8	1898.9	1840.3
5°	2494.1	2458.2	2472.8	2472.8	2402.4	2406.4	2403.8	2333.4	2294.8	2244.3	2144.6
7.5°	3074.8	3038.9	3041.5	3028.2	2928.6	2921.9	2879.5	2793.1	2717.4	2624.3	2475.4
10°	3699.2	3678.1	3664.7	3631.4	3500.0	3477.4	3415.0	3278.1	3153.1	3010.9	2801.0
12.5°	4432.7	4390.3	4351.7	4298.6	4127.2	4084.6	3997.0	3799.0	3615.6	3416.2	3138.5
15°	5199.5	5166.2	5103.7	5020.1	4800.9	4733.1	4618.7	4353.0	4124.5	3833.5	3477.4
17.5°	5992.8	5931.6	5839.9	5721.6	5457.3	5361.5	5219.4	4879.2	4576.3	4213.4	3783.0
20°	6677.0	6629.2	6503.0	6350.2	6047.2	5919.6	5752.2	5335.0	4964.2	4533.7	4027.4
22.5°	7271.0	7207.3	7051.7	6867.1	6528.2	6370.1	6181.5	5715.1	5263.2	4763.6	4206.9
25°	7729.4	7681.6	7496.9	7281.5	6909.5	6726.1	6517.6	5988.8	5487.7	4939.0	4326.4
27.5°	8102.8	8021.7	7815.8	7572.6	7171.4	6957.4	6736.9	6157.5	5615.3	5028.1	4371.6
30°	8253.0	8169.2	7951.3	7681.6	7256.4	7021.2	6793.9	6176.2	5606.0	4997.4	4317.1
32.5°	8225.0	8130.7	7898.2	7612.6	7178.0	6926.9	6696.9	6055.1	5473.1	4859.3	4169.6
35°	8025.8	7947.3	7706.9	7407.9	6974.6	6710.3	6469.7	5834.6	5251.2	4645.3	3959.7
37.5°	7725.4	7613.8	7389.2	7089.0	6630.6	6384.7	6146.8	5519.7	4949.6	4349.1	3698.0
40°	7232.4	7098.3	6873.6	6611.9	6176.2	5931.6	5715.1	5129.1	4568.2	4007.5	3385.8
42.5°	6611.9	6507.0	6298.3	6028.5	5628.7	5394.8	5200.7	4637.4	4140.4	3620.9	3041.5
45°	5883.7	5782.8	5604.8	5361.5	5000.1	4796.8	4618.7	4117.9	3670.0	3195.7	2673.5
47.5°	5095.8	4996.2	4840.6	4626.8	4303.9	4128.4	3973.0	3562.4	3139.9	2725.3	2266.9
50°	4171.0	4034.1	3949.1	3769.8	3500.0	3351.1	3231.6	2863.4	2551.2	2217.8	1836.4
52.5°	3113.3	3069.5	2947.2	2821.0	2631.0	2520.6	2442.3	2205.8	1946.6	1704.8	1413.9
55°	2152.6	2112.7	2038.3	1961.2	1833.8	1778.0	1719.4	1575.9	1403.1	1238.4	1040.4
57.5°	1360.7	1389.9	1342.1	1298.2	1221.2	1201.3	1156.0	1072.3	966.0	862.3	738.8
60°	876.9	892.9	862.3	837.2	794.6	778.7	757.4	706.9	643.1	583.4	499.6
62.5°	555.4	563.3	546.1	531.5	507.5	501.0	486.3	457.0	418.5	382.8	329.6
65°	346.9	353.4	341.4	332.3	317.6	318.9	305.7	288.3	265.7	243.2	212.6
67.5°	214.0	217.9	209.9	204.7	195.3	195.3	187.4	176.7	162.1	148.9	128.8
70°	130.2	131.5	126.2	123.5	116.9	115.6	111.6	103.7	94.3	85.0	73.0
72.5°	75.7	77.1	73.0	70.4	66.5	66.5	63.7	59.8	55.8	47.9	41.2
75°	41.2	42.6	39.9	38.5	35.9	37.1	34.5	33.3	29.2	26.6	23.9
77.5°	21.3	22.5	21.3	19.9	19.9	19.9	18.6	17.2	17.2	14.6	14.6
80°	12.0	12.0	12.0	12.0	12.0	10.6	10.6	10.6	10.6	10.6	9.3
82.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.3
85°	1.4	1.4	2.6	2.6	2.6	2.6	2.6	2.6	2.6	4.0	4.0
87.5°	0.0	0.0	1.4	1.4	1.4	1.4	1.4	2.6	2.6	2.6	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192808

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9
2.5°	1823.0	1821.8	1760.6	1734.0	1712.8	1679.6	1655.7	1630.3	1607.8	1566.6	1532.1
5°	2094.2	2056.9	1955.9	1892.2	1852.2	1799.1	1740.7	1682.2	1625.0	1550.6	1489.5
7.5°	2378.4	2298.7	2147.4	2040.9	1979.8	1905.4	1807.2	1715.5	1622.4	1520.1	1432.3
10°	2649.6	2519.4	2326.7	2164.6	2080.8	1985.1	1849.6	1722.0	1599.9	1470.9	1361.9
12.5°	2925.9	2739.9	2488.8	2278.8	2172.5	2054.3	1880.2	1722.0	1570.7	1421.8	1292.9
15°	3199.6	2953.9	2641.5	2381.1	2252.3	2111.5	1901.5	1712.8	1534.8	1367.2	1223.8
17.5°	3433.5	3129.2	2753.3	2451.6	2300.1	2140.7	1900.1	1684.9	1486.9	1306.2	1153.4
20°	3615.6	3255.5	2831.6	2487.4	2317.4	2143.3	1878.8	1643.7	1432.3	1243.7	1086.9
22.5°	3739.1	3337.9	2871.5	2494.1	2312.1	2128.7	1845.7	1602.5	1383.2	1194.6	1037.8
25°	3816.2	3379.1	2883.3	2484.7	2293.4	2103.4	1815.1	1566.6	1351.4	1169.2	1023.2
27.5°	3830.8	3367.1	2859.6	2446.2	2249.6	2058.3	1771.3	1532.1	1323.4	1154.6	1023.2
30°	3759.0	3290.0	2778.4	2359.9	2167.2	1979.8	1698.1	1469.6	1274.3	1120.1	1000.5
32.5°	3622.3	3147.8	2644.2	2232.4	2044.9	1869.5	1598.5	1380.6	1191.9	1049.7	942.1
35°	3424.3	2957.8	2470.1	2071.5	1889.5	1726.1	1458.9	1259.7	1080.4	948.7	849.1
37.5°	3183.7	2729.3	2266.9	1888.1	1715.5	1562.6	1307.6	1120.1	954.0	830.5	741.4
40°	2891.4	2482.1	2038.3	1686.3	1521.4	1383.2	1148.1	967.4	810.6	705.5	624.6
42.5°	2585.7	2205.8	1795.2	1460.3	1314.1	1182.6	973.9	811.8	672.4	586.0	522.2
45°	2270.9	1898.9	1540.0	1242.4	1132.1	984.6	791.9	660.5	547.5	483.6	433.1
47.5°	1916.1	1601.1	1270.3	1008.6	892.9	793.3	632.5	526.2	453.2	397.4	358.8
50°	1534.8	1283.6	1005.9	782.6	687.0	611.2	492.9	419.9	364.1	325.6	296.4
52.5°	1180.0	982.0	757.4	574.1	514.2	457.0	384.0	333.5	293.7	264.5	243.2
55°	876.9	716.3	544.8	425.2	382.8	345.5	301.6	261.7	232.5	212.6	195.3
57.5°	617.9	499.6	382.8	308.3	285.6	261.7	228.6	202.0	182.0	166.1	152.8
60°	413.2	340.2	269.8	226.0	209.9	193.9	172.8	154.2	139.6	128.8	115.6
62.5°	277.7	228.6	188.7	162.1	151.5	140.8	126.2	113.0	102.3	91.7	81.1
65°	178.1	151.5	127.6	110.3	102.3	97.0	86.4	77.1	69.2	59.8	51.7
67.5°	108.9	94.3	79.7	69.2	65.1	61.1	54.5	47.9	42.6	35.9	30.6
70°	63.7	55.8	47.9	41.2	39.9	37.1	31.9	28.0	25.2	21.3	18.6
72.5°	37.1	33.3	28.0	25.2	23.9	21.3	19.9	17.2	14.6	13.4	12.0
75°	21.3	18.6	16.0	14.6	14.6	13.4	12.0	12.0	10.6	10.6	9.3
77.5°	13.4	12.0	10.6	10.6	10.6	9.3	9.3	9.3	9.3	7.9	7.9
80°	9.3	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
82.5°	5.3	5.3	5.3	5.3	5.3	6.7	6.7	6.7	6.7	6.7	7.9
85°	4.0	5.3	5.3	5.3	5.3	5.3	6.7	6.7	6.7	6.7	6.7
87.5°	4.0	5.3	5.3	5.3	5.3	5.3	6.7	6.7	6.7	6.7	6.7
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192808

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9
2.5°	1512.1	1490.9	1425.8	1448.4	1407.2	1373.9	1371.3	1351.4	1316.7	1298.2	1288.9
5°	1443.1	1395.2	1315.5	1320.8	1272.9	1221.2	1193.2	1166.6	1121.5	1093.6	1074.9
7.5°	1358.1	1292.9	1198.6	1191.9	1141.4	1079.0	1039.0	1001.9	952.8	916.9	894.2
10°	1269.0	1189.3	1079.0	1071.0	1017.9	950.1	904.9	862.3	811.8	775.9	752.1
12.5°	1186.7	1095.0	984.6	964.7	912.8	843.8	794.6	749.4	700.2	669.6	641.8
15°	1108.2	1008.6	891.5	873.1	822.5	753.4	699.0	659.1	612.6	583.4	558.1
17.5°	1029.9	927.4	811.8	790.7	742.8	676.3	628.4	586.0	543.4	515.6	492.9
20°	962.1	859.7	746.7	725.6	681.6	617.9	574.1	534.1	495.6	469.0	450.5
22.5°	918.1	818.5	716.3	697.6	656.4	599.2	558.1	523.6	490.3	465.1	450.5
25°	915.5	829.1	737.5	726.8	692.3	644.5	615.2	593.9	574.1	554.2	548.7
27.5°	931.5	861.1	784.0	781.4	753.4	721.5	708.2	701.6	690.9	684.2	693.6
30°	922.2	862.3	797.2	797.2	775.9	753.4	746.7	744.1	737.5	738.8	749.4
32.5°	873.1	818.5	756.0	757.4	744.1	718.9	714.9	713.6	705.5	704.3	712.2
35°	784.0	733.5	681.6	683.0	672.4	648.5	643.1	640.4	629.8	624.6	629.8
37.5°	681.6	640.4	591.3	591.3	580.7	562.1	556.8	551.4	544.8	539.4	539.4
40°	576.7	543.4	503.7	502.3	494.3	475.7	470.4	466.4	459.7	450.5	453.2
42.5°	487.7	457.0	425.2	422.5	417.3	401.2	396.0	390.7	384.0	376.1	376.1
45°	405.3	385.4	357.4	356.2	350.7	337.5	333.5	326.8	321.5	313.6	313.6
47.5°	337.5	321.5	299.0	297.6	293.7	281.7	277.7	272.4	267.1	261.7	261.7
50°	283.0	267.1	248.5	247.1	244.4	235.1	229.8	226.0	221.9	217.9	215.2
52.5°	232.5	219.3	204.7	203.3	200.6	191.3	187.4	184.8	180.7	174.1	174.1
55°	187.4	176.7	163.5	162.1	159.4	151.5	147.5	142.2	136.9	130.2	128.8
57.5°	146.2	136.9	126.2	124.9	120.9	114.2	107.7	102.3	97.0	91.7	89.0
60°	110.3	99.6	90.3	87.6	85.0	75.7	70.4	65.1	59.8	55.8	53.1
62.5°	74.4	67.8	57.2	55.8	53.1	47.9	41.2	38.5	35.9	33.3	31.9
65°	46.5	41.2	35.9	34.5	31.9	28.0	25.2	23.9	22.5	21.3	19.9
67.5°	28.0	25.2	21.3	21.3	19.9	18.6	16.0	16.0	14.6	14.6	13.4
70°	17.2	16.0	14.6	13.4	13.4	13.4	12.0	12.0	12.0	12.0	12.0
72.5°	12.0	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.6
75°	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3	9.3
77.5°	9.3	9.3	7.9	9.3	9.3	9.3	9.3	7.9	9.3	7.9	7.9
80°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9
82.5°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	6.7	6.7	6.7	6.7
85°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	5.3
87.5°	6.7	6.7	6.7	6.7	6.7	5.3	5.3	5.3	5.3	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192808

CATALOG NUMBER: LDA6A75935D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9	1575.9
2.5°	1291.6	1254.4	1269.0	1247.7	1241.0	1235.8	1227.8	1253.0
5°	1067.0	1027.2	1036.4	1015.2	1005.9	996.6	987.3	1007.2
7.5°	881.0	842.4	846.5	827.8	818.5	807.9	798.6	814.5
10°	736.1	700.2	701.6	684.2	675.1	664.3	656.4	668.4
12.5°	625.8	592.7	592.7	579.3	571.4	559.4	552.8	562.1
15°	542.2	512.8	512.8	499.6	492.9	482.4	475.7	485.0
17.5°	478.3	451.8	451.8	442.4	435.9	426.6	421.1	429.2
20°	435.9	413.2	414.6	405.3	400.0	389.3	386.6	393.3
22.5°	439.8	418.5	421.1	414.6	409.3	401.2	398.6	407.9
25°	550.1	534.1	543.4	543.4	546.1	534.1	539.4	554.2
27.5°	706.9	699.0	713.6	708.2	718.9	718.9	724.2	742.8
30°	764.1	757.4	773.3	772.0	782.6	780.0	782.6	799.9
32.5°	722.8	716.3	729.5	728.2	736.1	729.5	730.9	745.5
35°	635.1	628.4	637.8	636.5	641.8	633.9	637.8	645.9
37.5°	542.2	535.5	540.8	539.4	540.8	531.5	536.8	540.8
40°	455.8	447.9	455.8	450.5	451.8	442.4	443.8	449.1
42.5°	381.4	372.0	378.7	378.7	378.7	372.0	373.4	378.7
45°	317.6	311.0	314.8	313.6	314.8	309.6	313.6	318.9
47.5°	263.1	257.8	260.5	259.1	259.1	253.8	255.2	255.2
50°	216.6	211.3	212.6	211.3	207.3	200.6	199.4	200.6
52.5°	171.4	164.7	164.7	162.1	159.4	154.2	154.2	155.4
55°	126.2	120.9	120.9	119.7	116.9	113.0	113.0	115.6
57.5°	85.0	81.1	82.4	81.1	81.1	75.7	78.3	78.3
60°	51.7	49.1	49.1	47.9	45.2	43.8	42.6	45.2
62.5°	30.6	29.2	29.2	28.0	28.0	26.6	26.6	26.6
65°	19.9	18.6	18.6	17.2	17.2	16.0	14.6	16.0
67.5°	13.4	12.0	12.0	12.0	12.0	10.6	10.6	10.6
70°	12.0	10.6	10.6	10.6	10.6	9.3	9.3	9.3
72.5°	10.6	9.3	10.6	9.3	9.3	9.3	9.3	9.3
75°	9.3	9.3	9.3	7.9	7.9	7.9	7.9	7.9
77.5°	7.9	7.9	7.9	7.9	7.9	6.7	6.7	6.7
80°	7.9	6.7	6.7	6.7	6.7	6.7	6.7	6.7
82.5°	6.7	6.7	6.7	6.7	6.7	5.3	5.3	5.3
85°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3
87.5°	4.0	4.0	4.0	4.0	4.0	2.6	2.6	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)