

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192815

Luminaire Tested: **LDA6A75940D010TE LARH20SP 6LA1LI 30°**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192815
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26686)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75940D010TE LARH20SP 6LA1LI 30°
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6839.9 lumens
Efficiency: N/A
Efficacy: 78.7 lumens/watt
Spacing Criteria (0/90/45): 2.35 / 0.6 / 1.31
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192815

CATALOG NUMBER: LDA6A75940D010TE LARH20SP 6LA1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192815

CATALOG NUMBER: LDA6A75940D010TE LARH20SP 6LA1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91		
2	105	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82		
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	74		
4	92	83	76	71	90	82	76	71	79	74	70	77	73	69	75	71	68	66		
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	69	65	61	60		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	55	54		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	50	59	54	50	49		
8	70	59	51	46	69	58	51	46	57	50	46	56	50	46	54	49	46	44		
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	50	45	41	40		
10	61	50	43	38	60	49	43	38	48	42	38	48	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	105858	105858	105858
5°	205112	100875	34025
10°	348491	88280	15275
15°	536995	70409	24291
20°	777371	45819	42255
25°	1140538	44216	54330
30°	1326141	41886	41633
35°	1342276	22192	22004
40°	1111311	8366	9239
45°	839320	2845	3372
50°	574250	1049	1049
55°	79882	908	134
60°	2083	888	0
65°	519	1232	0
70°	224	1523	0
75°	0	2012	0
80°	0	3441	442
85°	0	6856	0



TEST NUMBER: P1192815

CATALOG NUMBER: LDA6A75940D010TE LARH20SP 6LA1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.6	3.0
10°-20°	856.3	12.5
20°-30°	1953.4	28.6
30°-40°	2260.6	33.1
40°-50°	1363.3	19.9
50°-60°	185.2	2.7
60°-70°	5.9	0.1
70°-80°	6.5	0.1
80°-90°	6.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3012.3	44.0
0°-40°	5272.9	77.1
0°-60°	6821.4	99.7
0°-90°	6839.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6839.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1931	1931	1931	1931	1931	
5°	3727	3052	1833	1003	618	434
15°	9462	5319	1241	382	428	2801
25°	18856	6302	731	879	898	8533
35°	20057	4805	332	338	329	12087
45°	10826	1309	37	45	44	8465
55°	836	10	10	7	1	1638
65°	4	5	10	5	0	6
75°	0	7	10	7	0	0
85°	0	7	11	7	0	0
90°	0	0	0	0	0	

TEST NUMBER: P1192815

CATALOG NUMBER: LDA6A75940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0
2.5°	2792.4	2766.6	2777.5	2749.1	2677.0	2662.0	2660.6	2641.7	2580.5	2532.9	2475.9
5°	3727.3	3726.1	3732.8	3671.7	3545.4	3505.9	3486.9	3440.6	3292.5	3178.4	3052.1
7.5°	4894.7	4886.5	4878.4	4767.0	4568.5	4492.4	4443.6	4276.4	4072.6	3870.1	3644.5
10°	6260.4	6256.4	6225.0	6029.3	5711.4	5571.3	5476.2	5211.3	4883.8	4595.7	4212.5
12.5°	7846.1	7809.4	7753.8	7467.1	7030.9	6878.6	6669.4	6249.5	5746.6	5305.1	4769.6
15°	9461.8	9408.9	9309.7	8941.4	8400.6	8141.1	7881.6	7328.5	6646.3	6004.9	5318.7
17.5°	11042.3	10983.9	10751.4	10126.3	9597.8	9281.1	8993.0	8233.4	7431.7	6606.9	5737.2
20°	13325.2	13113.2	12708.2	11723.1	10740.7	10169.9	9832.8	9029.8	8037.7	7077.0	6034.8
22.5°	16374.5	15904.4	15041.4	13440.6	12037.0	11213.5	10661.7	9593.6	8473.9	7384.1	6218.3
25°	18855.8	18642.4	17661.4	15383.9	13193.4	12223.0	11455.3	10042.1	8791.9	7589.4	6302.5
27.5°	20455.2	20402.2	19281.1	16992.8	14137.8	12864.5	12007.0	10338.3	8945.4	7632.8	6261.6
30°	20949.8	21032.7	19956.5	17539.1	14411.0	12993.5	12056.0	10342.4	8827.3	7435.9	6000.9
32.5°	20913.2	20917.2	19597.8	17067.6	13966.5	12618.5	11648.4	9998.6	8391.1	6942.5	5504.8
35°	20057.0	19846.5	18354.4	15618.9	12932.5	11743.5	10841.2	9332.7	7672.2	6200.6	4805.0
37.5°	18177.8	17901.9	16162.5	13764.0	11708.0	10608.7	9880.3	8459.0	6816.1	5408.3	4082.1
40°	15529.2	15137.9	13702.9	12039.7	10368.3	9542.0	8930.5	7482.0	5900.3	4631.0	3403.9
42.5°	12878.1	12686.4	11738.0	10385.9	9241.8	8464.5	7825.8	6458.7	5019.7	3864.7	2546.6
45°	10826.1	10661.7	10024.4	9133.0	8010.5	7301.3	6685.7	5392.0	3900.0	2592.7	1308.6
47.5°	9331.5	9198.3	8588.2	7651.9	6420.8	5644.8	5010.2	3535.9	2209.5	1119.7	327.4
50°	6733.3	6597.3	5999.5	4915.1	3803.5	3153.9	2697.3	1579.0	626.4	226.9	34.0
52.5°	3300.8	3189.3	2783.0	2083.2	1398.3	1005.6	735.2	296.2	72.0	24.4	16.3
55°	835.8	767.7	640.1	402.2	197.1	118.3	76.1	27.2	17.7	13.5	9.5
57.5°	47.6	46.2	42.1	31.2	23.2	20.4	17.7	13.5	9.5	8.1	6.8
60°	19.0	17.7	16.3	13.5	10.9	9.5	9.5	6.8	5.4	5.4	5.4
62.5°	8.1	8.1	8.1	6.8	5.4	5.4	5.4	4.0	5.4	5.4	5.4
65°	4.0	4.0	4.0	2.6	2.6	2.6	4.0	4.0	4.0	5.4	5.4
67.5°	2.6	1.4	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.4	5.4
70°	1.4	1.4	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.4	6.8
72.5°	0.0	1.4	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.4	6.8
75°	0.0	1.4	1.4	1.4	2.6	2.6	2.6	4.0	5.4	5.4	6.8
77.5°	0.0	1.4	1.4	1.4	2.6	2.6	2.6	4.0	5.4	5.4	6.8
80°	0.0	1.4	1.4	1.4	2.6	2.6	2.6	4.0	5.4	5.4	6.8
82.5°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	5.4	5.4	6.8
85°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	5.4	5.4	6.8
87.5°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.4	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192815

CATALOG NUMBER: LDA6A75940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0
2.5°	2402.5	2353.6	2281.6	2234.1	2187.8	2144.2	2072.3	2031.6	1958.1	1890.2	1831.7
5°	2899.8	2777.5	2629.4	2503.1	2421.5	2341.3	2196.0	2088.6	1954.0	1833.1	1721.7
7.5°	3402.7	3186.5	2943.3	2735.4	2609.1	2485.4	2267.9	2094.1	1903.8	1731.2	1566.8
10°	3859.3	3534.5	3190.6	2893.1	2721.9	2561.5	2274.8	2043.7	1799.1	1585.9	1379.2
12.5°	4283.2	3838.8	3390.4	3001.8	2789.8	2596.8	2246.2	1963.5	1672.8	1420.1	1179.5
15°	4661.0	4090.2	3535.9	3064.2	2815.6	2587.3	2179.7	1850.8	1523.3	1240.6	936.3
17.5°	4947.7	4246.5	3599.7	3054.7	2769.4	2515.3	2065.5	1709.4	1364.3	1021.9	678.0
20°	5121.6	4313.0	3586.1	2981.4	2670.1	2401.1	1929.6	1555.9	1172.7	785.4	597.8
22.5°	5195.0	4307.6	3522.2	2871.4	2547.8	2276.2	1799.1	1406.4	971.6	710.7	623.8
25°	5207.2	4252.0	3432.5	2750.3	2426.9	2156.5	1667.3	1236.5	843.8	731.0	698.5
27.5°	5113.5	4121.4	3264.1	2576.4	2257.1	1977.2	1470.3	982.5	792.2	728.4	750.1
30°	4836.3	3823.8	2966.5	2270.7	1962.3	1682.2	1050.4	770.5	657.7	661.7	667.1
32.5°	4348.5	3329.2	2488.2	1823.6	1486.6	1108.8	653.6	515.0	500.1	500.1	497.3
35°	3697.5	2724.5	1952.6	1153.7	739.3	532.7	338.3	339.7	332.9	331.6	330.2
37.5°	3024.9	2149.7	1236.5	476.9	320.8	222.8	199.7	202.5	199.7	203.9	201.1
40°	2384.8	1327.6	451.1	152.1	112.8	108.8	111.4	114.2	114.2	116.9	116.9
42.5°	1386.0	440.3	118.3	61.1	61.1	58.4	59.8	62.5	63.9	65.3	63.9
45°	411.8	91.1	38.1	34.0	34.0	32.6	32.6	34.0	35.3	36.7	36.7
47.5°	65.3	25.8	21.8	19.0	19.0	19.0	19.0	19.0	20.4	20.4	21.8
50°	20.4	16.3	13.5	12.3	12.3	10.9	10.9	12.3	12.3	12.3	13.5
52.5°	12.3	9.5	9.5	8.1	9.5	9.5	8.1	9.5	9.5	9.5	10.9
55°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	9.5	9.5	9.5
57.5°	6.8	6.8	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
60°	6.8	6.8	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	9.5
62.5°	6.8	6.8	8.1	8.1	8.1	8.1	8.1	8.1	9.5	9.5	9.5
65°	6.8	6.8	8.1	8.1	8.1	8.1	8.1	9.5	9.5	9.5	9.5
67.5°	6.8	8.1	8.1	8.1	8.1	9.5	9.5	9.5	9.5	9.5	9.5
70°	6.8	8.1	8.1	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
72.5°	6.8	8.1	8.1	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
75°	8.1	8.1	8.1	9.5	9.5	9.5	9.5	9.5	9.5	9.5	10.9
77.5°	8.1	8.1	9.5	9.5	9.5	9.5	9.5	9.5	10.9	10.9	10.9
80°	8.1	8.1	9.5	9.5	9.5	9.5	9.5	10.9	10.9	10.9	10.9
82.5°	8.1	8.1	9.5	9.5	9.5	9.5	9.5	10.9	10.9	10.9	10.9
85°	8.1	8.1	9.5	9.5	9.5	9.5	9.5	10.9	10.9	10.9	10.9
87.5°	8.1	8.1	9.5	9.5	9.5	9.5	9.5	10.9	10.9	10.9	10.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192815

CATALOG NUMBER: LDA6A75940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0
2.5°	1781.5	1718.9	1689.1	1647.0	1617.1	1550.5	1523.3	1477.1	1439.0	1376.6	1380.6
5°	1626.6	1508.3	1428.2	1365.7	1322.2	1216.2	1145.5	1070.7	1002.8	918.6	887.3
7.5°	1411.8	1266.5	1144.2	1069.5	1013.7	872.4	716.1	593.8	501.5	434.8	409.0
10°	1197.2	1008.3	814.0	698.5	618.3	482.4	413.1	380.4	350.6	313.9	289.5
12.5°	947.2	678.0	501.5	455.2	422.5	377.8	332.9	297.6	304.4	305.7	315.3
15°	646.8	487.8	432.2	400.9	365.5	339.7	354.6	364.1	381.8	383.2	395.5
17.5°	525.9	458.0	413.1	411.8	414.5	429.4	452.5	464.8	487.8	493.2	511.0
20°	525.9	486.4	524.5	524.5	531.3	551.7	581.7	599.2	625.0	634.7	656.3
22.5°	599.2	626.4	674.0	679.4	682.2	704.0	741.9	759.6	789.4	794.9	818.0
25°	731.0	755.6	799.1	803.1	804.5	820.8	849.3	858.8	879.3	868.4	881.9
27.5°	773.1	784.0	811.2	814.0	807.2	814.0	824.9	824.9	831.6	810.0	814.0
30°	679.4	682.2	695.7	697.1	682.2	684.9	686.3	684.9	683.5	660.5	660.5
32.5°	504.1	504.1	521.8	517.8	501.5	505.5	505.5	505.5	504.1	485.2	482.4
35°	334.3	335.7	350.6	347.9	335.7	338.3	338.3	342.5	338.3	327.4	324.8
37.5°	203.9	205.1	212.0	213.4	209.3	210.6	212.0	210.6	213.4	207.9	205.1
40°	118.3	120.9	126.3	127.7	126.3	126.3	127.7	129.1	134.6	127.7	124.9
42.5°	69.3	70.7	73.4	73.4	73.4	73.4	74.7	76.1	77.4	76.1	74.7
45°	39.5	40.7	42.1	42.1	43.5	42.1	43.5	43.5	44.9	43.5	43.5
47.5°	23.2	23.2	24.4	24.4	25.8	24.4	25.8	25.8	25.8	24.4	24.4
50°	13.5	14.9	14.9	14.9	14.9	14.9	14.9	14.9	14.9	13.5	13.5
52.5°	10.9	10.9	10.9	10.9	10.9	9.5	9.5	9.5	9.5	8.1	8.1
55°	9.5	9.5	9.5	9.5	9.5	9.5	8.1	6.8	6.8	5.4	5.4
57.5°	8.1	9.5	9.5	9.5	9.5	8.1	8.1	6.8	5.4	4.0	4.0
60°	9.5	9.5	9.5	9.5	8.1	8.1	8.1	6.8	5.4	4.0	4.0
62.5°	9.5	9.5	9.5	9.5	9.5	8.1	8.1	6.8	5.4	4.0	4.0
65°	9.5	9.5	9.5	9.5	9.5	8.1	8.1	6.8	5.4	4.0	4.0
67.5°	9.5	9.5	9.5	9.5	9.5	8.1	8.1	6.8	5.4	5.4	4.0
70°	9.5	10.9	10.9	9.5	9.5	9.5	8.1	6.8	6.8	5.4	4.0
72.5°	9.5	10.9	10.9	9.5	9.5	9.5	8.1	6.8	6.8	5.4	4.0
75°	10.9	10.9	10.9	10.9	9.5	9.5	8.1	8.1	6.8	5.4	4.0
77.5°	10.9	10.9	10.9	10.9	9.5	9.5	8.1	8.1	6.8	5.4	4.0
80°	10.9	10.9	10.9	10.9	10.9	9.5	9.5	8.1	6.8	5.4	5.4
82.5°	10.9	10.9	10.9	10.9	10.9	9.5	9.5	8.1	6.8	5.4	5.4
85°	10.9	10.9	10.9	10.9	10.9	9.5	9.5	8.1	6.8	5.4	4.0
87.5°	10.9	10.9	10.9	10.9	9.5	9.5	8.1	8.1	6.8	5.4	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192815

CATALOG NUMBER: LDA6A75940D010TE LARH20SP 6LA1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0	1931.0
2.5°	1330.4	1299.0	1285.5	1307.2	1296.4	1263.7	1270.6	1250.2
5°	793.6	746.1	716.1	729.8	686.3	646.8	646.8	618.3
7.5°	383.2	368.3	360.1	362.9	353.4	341.1	334.3	334.3
10°	269.0	263.6	265.0	265.0	273.2	271.8	275.8	274.4
12.5°	319.4	322.0	323.4	328.8	335.7	335.7	339.7	337.1
15°	409.0	406.4	414.5	415.9	426.7	428.0	433.4	428.0
17.5°	520.4	525.9	534.0	532.7	554.5	555.7	555.7	554.5
20°	669.9	674.0	682.2	684.9	710.7	713.5	722.9	724.3
22.5°	833.0	833.0	837.0	842.4	867.0	868.4	872.4	872.4
25°	888.7	880.5	881.9	888.7	902.3	896.8	900.9	898.2
27.5°	816.6	804.5	801.7	811.2	820.8	805.8	811.2	811.2
30°	663.1	652.2	649.6	659.1	665.9	649.6	655.0	657.7
32.5°	485.2	478.3	476.9	483.8	489.2	475.5	481.0	485.2
35°	327.4	324.8	322.0	323.4	331.6	320.8	326.2	328.8
37.5°	207.9	202.5	203.9	206.5	212.0	205.1	210.6	210.6
40°	127.7	124.9	124.9	127.7	130.4	124.9	127.7	129.1
42.5°	74.7	74.7	74.7	76.1	77.4	74.7	74.7	76.1
45°	43.5	42.1	42.1	43.5	44.9	42.1	43.5	43.5
47.5°	24.4	23.2	23.2	24.4	24.4	23.2	24.4	24.4
50°	13.5	12.3	12.3	13.5	13.5	12.3	12.3	12.3
52.5°	6.8	6.8	6.8	6.8	6.8	6.8	5.4	5.4
55°	4.0	4.0	2.6	2.6	2.6	2.6	2.6	1.4
57.5°	2.6	2.6	1.4	1.4	1.4	1.4	0.0	0.0
60°	2.6	2.6	1.4	1.4	1.4	0.0	0.0	0.0
62.5°	2.6	2.6	1.4	1.4	1.4	0.0	0.0	0.0
65°	2.6	2.6	1.4	1.4	1.4	0.0	0.0	0.0
67.5°	2.6	2.6	1.4	1.4	1.4	0.0	0.0	0.0
70°	4.0	2.6	2.6	1.4	1.4	1.4	0.0	0.0
72.5°	4.0	2.6	2.6	2.6	1.4	1.4	0.0	0.0
75°	4.0	2.6	2.6	2.6	1.4	1.4	0.0	0.0
77.5°	4.0	2.6	2.6	2.6	1.4	1.4	1.4	0.0
80°	4.0	2.6	2.6	2.6	1.4	1.4	1.4	1.4
82.5°	4.0	2.6	2.6	2.6	1.4	1.4	1.4	1.4
85°	4.0	2.6	2.6	2.6	1.4	1.4	1.4	0.0
87.5°	4.0	2.6	2.6	2.6	1.4	1.4	1.4	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)