

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P203741

Luminaire Tested: **LE_6B15D010 EC6B10208050 6LBNWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203741
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208050 6LBNWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1278.2 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203741

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBNWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203741

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBNWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94
3	104	98	93	90	102	97	92	89	94	91	88		92	89	86		89
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		78
7	87	78	73	69	85	77	72	69	76	72	68		75	71	68		74
8	83	74	69	65	82	74	68	65	73	68	65		72	67	64		71
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203741

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBNWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	212.4	16.6
10°-20°	408.2	31.9
20°-30°	371.1	29.0
30°-40°	224.9	17.6
40°-50°	51.2	4.0
50°-60°	6.6	0.5
60°-70°	2.9	0.2
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	991.8	77.6
0°-40°	1216.7	95.2
0°-60°	1274.5	99.7
0°-90°	1278.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1278.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2510	
5°	2366	212
15°	1470	408
25°	805	371
35°	357	225
45°	56	51
55°	6	7
65°	2	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203741

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBNWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2509.8
2.5°	2479.2
5°	2366.1
7.5°	2183.5
10°	1950.8
12.5°	1709.4
15°	1470.1
17.5°	1252.6
20°	1070.0
22.5°	922.1
25°	804.6
27.5°	700.2
30°	598.1
32.5°	478.5
35°	356.6
37.5°	250.1
40°	165.2
42.5°	102.2
45°	56.5
47.5°	26.1
50°	10.9
52.5°	8.8
55°	6.5
57.5°	6.5
60°	4.4
62.5°	4.4
65°	2.1
67.5°	2.1
70°	2.1
72.5°	2.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)