

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192822

Luminaire Tested: **LDA6A75940D010TE LARH30NF 6LAL1LI 30°**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192822
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26690)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75940D010TE LARH30NF 6LAL1LI 30°
Description: PORTFOLIO 6" Lensed Adjustable, Self-flanged, 30° Narrow Flood, 30° Tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6941.9 lumens
Efficiency: N/A
Efficacy: 79.9 lumens/watt
Spacing Criteria (0/90/45): 2.55 / 0.46 / 1.37
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192822

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LAL1LI 30°

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192822

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LAL1LI 30°

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	77	75	73		
4	91	82	75	70	89	81	74	69	78	73	68	76	71	68	74	70	67	65		
5	85	74	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58		
6	79	68	60	55	77	67	60	55	65	59	55	64	58	54	62	58	54	52		
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47		
8	69	57	49	44	67	56	49	44	55	49	44	54	48	44	53	48	44	42		
9	64	52	45	40	63	52	45	40	51	44	40	50	44	40	49	43	39	38		
10	60	48	41	36	59	48	41	36	47	40	36	46	40	36	45	40	36	34		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	69945	69945	69945
5°	180580	64830	20267
10°	342562	49465	6808
15°	612540	32157	6782
20°	912716	21877	12368
25°	1041423	27286	77672
30°	1126249	22795	23225
35°	1183066	11096	7268
40°	1201773	3979	3693
45°	1070716	2636	2217
50°	687662	1859	1510
55°	181040	1290	774
60°	40381	1349	592
65°	3866	1596	700
70°	1298	1971	866
75°	297	2605	1440
80°	0	4262	2147
85°	0	7737	3397

TEST NUMBER: P1192822

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LAL1LI 30°

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.9	2.2
10°-20°	808.7	11.6
20°-30°	1897.4	27.3
30°-40°	2182.4	31.4
40°-50°	1550.3	22.3
50°-60°	315.2	4.5
60°-70°	15.8	0.2
70°-80°	9.4	0.1
80°-90°	7.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2861.0	41.2
0°-40°	5043.4	72.7
0°-60°	6908.9	99.5
0°-90°	6941.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6941.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1276	1276	1276	1276	1276	
5°	3282	2374	1178	472	368	400
15°	10793	4852	567	128	120	3238
25°	17217	5844	451	985	1284	7935
35°	17678	4104	166	122	109	10982
45°	13811	1459	34	37	29	10178
55°	1894	38	14	14	8	2555
65°	30	11	12	11	5	72
75°	1	7	12	11	7	3
85°	0	7	12	10	5	0
90°	0	0	0	0	0	

TEST NUMBER: P1192822

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9
2.5°	2198.5	2132.0	2099.3	2097.9	2002.8	2034.1	2002.8	1978.4	1890.0	1853.3	1792.3
5°	3281.5	3199.9	3134.8	3106.2	2943.2	2907.9	2891.6	2808.6	2623.8	2516.4	2373.8
7.5°	4558.7	4473.1	4365.7	4280.3	4043.7	3977.2	3933.7	3791.0	3517.8	3301.8	3035.5
10°	6153.9	6103.7	5929.7	5772.1	5413.5	5274.8	5144.4	4811.4	4454.2	4020.7	3676.8
12.5°	8302.2	8184.0	7874.3	7558.9	6996.4	6789.9	6573.8	6041.1	5495.0	4815.6	4247.6
15°	10792.9	10692.3	10215.4	9701.8	8901.5	8561.8	8223.4	7385.0	6545.2	5670.2	4852.3
17.5°	13659.9	13469.7	12995.5	12127.2	11007.6	10473.5	9843.0	8775.1	7563.0	6374.1	5357.7
20°	15645.2	15532.3	15131.6	14298.6	13024.0	12318.8	11536.2	10070.1	8412.3	6938.0	5689.3
22.5°	16730.8	16618.0	16317.7	15582.7	14537.8	13829.7	12920.8	11117.7	9053.6	7317.1	5845.5
25°	17217.2	17143.9	16979.4	16380.2	15412.8	14775.5	13915.4	11841.8	9454.5	7489.6	5844.2
27.5°	17667.1	17686.1	17279.8	16786.6	15895.2	15255.1	14439.9	12168.0	9533.3	7402.8	5656.7
30°	17792.0	17744.5	17566.6	16872.1	16041.9	15344.9	14471.1	11995.4	9226.3	7018.1	5284.3
32.5°	17714.7	17715.9	17548.8	16811.0	15835.4	15055.4	14073.0	11377.2	8628.3	6414.9	4705.4
35°	17678.0	17665.7	17232.3	16584.1	15344.9	14427.7	13189.8	10385.2	7799.5	5644.4	4103.6
37.5°	17313.7	17240.4	16927.9	16048.7	14427.7	13255.1	11922.0	9171.9	6779.0	4842.8	3486.6
40°	16793.3	16701.0	16192.8	14931.7	12859.6	11551.1	10226.3	7798.1	5711.0	4045.1	2799.1
42.5°	15726.7	15574.5	14804.1	13131.4	10840.4	9623.0	8525.1	6422.9	4668.8	3284.3	2149.7
45°	13810.8	13562.1	12495.5	10748.1	8750.6	7795.5	6867.4	5148.5	3738.1	2445.9	1459.4
47.5°	11089.1	10817.4	9849.9	8446.3	6851.1	6076.6	5288.4	3791.0	2528.7	1425.4	732.4
50°	8063.1	7875.5	7020.9	5837.4	4530.1	3880.7	3276.0	2114.3	1213.4	688.9	300.2
52.5°	4645.8	4511.2	3916.0	3072.2	2228.5	1865.6	1500.1	922.6	618.2	273.0	96.5
55°	1894.2	1816.7	1555.9	1318.0	989.1	854.7	713.3	460.6	207.9	65.3	38.1
57.5°	926.7	917.2	765.0	612.8	451.1	364.1	274.4	92.5	50.4	32.6	24.4
60°	368.3	354.6	243.2	141.3	78.8	63.9	54.4	38.1	28.6	21.8	17.7
62.5°	63.9	62.5	53.0	44.9	36.7	32.6	29.8	23.2	19.0	14.9	13.5
65°	29.8	29.8	27.2	24.4	20.4	19.0	17.7	14.9	12.3	10.9	10.9
67.5°	14.9	14.9	13.5	12.3	10.9	10.9	9.5	9.5	8.1	8.1	8.1
70°	8.1	8.1	8.1	6.8	6.8	6.8	6.8	6.8	5.4	6.8	6.8
72.5°	5.4	5.4	5.4	4.0	2.6	4.0	4.0	4.0	5.4	6.8	6.8
75°	1.4	1.4	1.4	2.6	2.6	2.6	4.0	4.0	5.4	6.8	6.8
77.5°	1.4	1.4	1.4	1.4	2.6	2.6	2.6	4.0	5.4	6.8	6.8
80°	0.0	1.4	1.4	1.4	2.6	2.6	2.6	4.0	5.4	6.8	6.8
82.5°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	5.4	6.8	6.8
85°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	5.4	6.8	6.8
87.5°	0.0	0.0	1.4	1.4	2.6	2.6	2.6	4.0	5.4	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192822

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9
2.5°	1765.1	1694.4	1648.2	1566.6	1532.7	1517.8	1443.1	1371.0	1301.7	1251.5	1174.1
5°	2265.1	2152.3	1979.8	1818.1	1747.3	1702.6	1555.9	1419.9	1290.9	1178.1	1043.5
7.5°	2803.2	2570.8	2300.4	2040.9	1918.6	1837.0	1610.1	1411.8	1227.1	1055.8	872.3
10°	3319.6	2954.0	2559.9	2189.0	2023.2	1900.9	1604.7	1350.6	1110.2	888.6	691.7
12.5°	3759.8	3286.9	2763.8	2282.7	2066.7	1910.5	1554.5	1244.6	952.5	714.7	543.4
15°	4130.8	3542.4	2898.3	2314.1	2054.4	1869.6	1456.6	1099.3	780.0	566.6	438.9
17.5°	4391.7	3665.9	2929.5	2261.1	1969.0	1755.6	1308.5	913.1	612.8	458.0	346.5
20°	4543.8	3682.3	2853.5	2132.0	1819.5	1593.8	1122.3	717.5	497.3	375.0	269.0
22.5°	4567.0	3602.2	2704.0	1958.1	1646.8	1429.4	934.9	600.6	452.5	350.6	263.6
25°	4455.5	3443.3	2509.8	1788.2	1490.6	1267.8	808.4	607.3	508.2	451.1	468.8
27.5°	4239.4	3180.9	2286.9	1614.3	1327.6	1102.0	763.6	635.9	554.3	564.0	596.4
30°	3907.9	2811.4	1966.2	1319.4	1016.3	839.8	607.3	458.0	380.4	360.1	361.5
32.5°	3420.1	2348.0	1543.6	915.8	683.5	566.6	384.5	255.5	256.9	237.8	236.4
35°	2863.0	1890.0	1155.0	614.2	472.9	394.1	226.9	179.3	172.5	165.8	156.3
37.5°	2311.3	1460.6	769.1	419.9	301.6	218.8	114.1	93.7	87.0	81.6	81.6
40°	1759.6	1021.8	475.5	220.1	122.3	89.7	67.9	57.0	55.6	55.6	54.4
42.5°	1277.3	603.3	258.1	87.0	67.9	59.8	47.6	42.1	42.1	42.1	42.1
45°	679.4	307.1	99.1	54.4	44.9	42.1	35.3	32.6	32.6	34.0	34.0
47.5°	313.9	115.5	50.4	36.7	31.2	31.2	27.2	25.8	25.8	27.2	27.2
50°	112.8	47.6	32.6	25.8	23.2	24.4	21.8	20.4	21.8	21.8	21.8
52.5°	43.5	29.8	23.2	20.4	17.7	19.0	16.3	16.3	17.7	17.7	17.7
55°	27.2	21.8	17.7	14.9	13.5	14.9	13.5	13.5	13.5	13.5	13.5
57.5°	19.0	16.3	13.5	12.3	10.9	12.3	12.3	12.3	12.3	12.3	12.3
60°	14.9	12.3	10.9	10.9	10.9	10.9	10.9	10.9	10.9	12.3	12.3
62.5°	12.3	10.9	10.9	10.9	10.9	10.9	10.9	10.9	12.3	12.3	12.3
65°	10.9	9.5	10.9	10.9	9.5	10.9	10.9	10.9	12.3	12.3	13.5
67.5°	8.1	8.1	8.1	9.5	9.5	9.5	10.9	10.9	12.3	12.3	12.3
70°	8.1	8.1	9.5	9.5	9.5	9.5	10.9	10.9	12.3	12.3	12.3
72.5°	8.1	8.1	9.5	9.5	9.5	10.9	10.9	10.9	12.3	12.3	12.3
75°	8.1	8.1	9.5	9.5	9.5	10.9	10.9	10.9	12.3	12.3	12.3
77.5°	8.1	8.1	9.5	9.5	9.5	10.9	10.9	12.3	12.3	12.3	12.3
80°	8.1	9.5	9.5	10.9	10.9	10.9	10.9	12.3	12.3	13.5	13.5
82.5°	8.1	9.5	9.5	10.9	10.9	10.9	10.9	12.3	12.3	13.5	13.5
85°	8.1	9.5	9.5	10.9	10.9	10.9	10.9	12.3	12.3	12.3	12.3
87.5°	8.1	9.5	9.5	10.9	10.9	10.9	10.9	10.9	12.3	12.3	12.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192822

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9
2.5°	1122.3	1055.8	989.1	956.7	928.1	887.3	835.6	793.5	748.7	725.6	672.6
5°	937.5	823.5	727.0	680.8	645.4	596.4	543.4	505.5	471.5	452.5	418.5
7.5°	725.6	616.9	532.7	497.3	471.5	422.5	383.2	343.8	308.5	282.7	248.6
10°	561.2	476.9	407.6	373.7	345.1	293.6	246.0	209.3	171.3	145.5	134.6
12.5°	445.7	366.9	296.2	262.3	232.3	179.3	144.1	137.2	130.4	127.7	123.7
15°	342.4	270.4	195.7	161.6	149.5	142.7	134.6	133.2	127.7	127.7	123.7
17.5°	256.9	176.7	149.5	146.7	145.5	142.7	138.6	137.2	135.8	135.8	134.6
20°	184.8	171.3	167.1	169.9	171.3	173.9	172.5	172.5	177.9	190.2	187.6
22.5°	259.5	281.3	304.4	312.5	342.4	372.3	399.5	433.4	513.6	606.1	627.8
25°	513.6	578.9	638.7	671.2	720.1	786.8	850.7	929.5	985.1	1031.3	1084.2
27.5°	638.7	663.1	653.6	657.7	652.2	642.7	645.4	661.7	653.6	629.1	638.7
30°	377.8	396.7	385.9	391.3	376.4	376.4	372.3	380.4	375.0	365.5	362.9
32.5°	246.0	256.9	255.5	255.5	250.0	247.2	237.8	235.1	225.5	207.9	203.9
35°	148.1	141.3	134.6	130.4	127.7	127.7	126.3	126.3	122.3	118.3	116.9
37.5°	80.2	81.6	81.6	81.6	81.6	84.2	82.8	82.8	82.8	80.2	80.2
40°	55.6	58.4	58.4	58.4	59.8	59.8	59.8	61.1	59.8	59.8	59.8
42.5°	43.5	44.9	43.5	43.5	44.9	44.9	44.9	46.2	46.2	46.2	44.9
45°	35.3	35.3	34.0	35.3	35.3	36.7	36.7	36.7	36.7	35.3	35.3
47.5°	28.6	28.6	28.6	28.6	29.8	29.8	29.8	29.8	29.8	29.8	29.8
50°	23.2	23.2	23.2	24.4	24.4	24.4	23.2	24.4	24.4	24.4	23.2
52.5°	17.7	17.7	17.7	17.7	17.7	16.3	16.3	16.3	16.3	16.3	14.9
55°	13.5	13.5	13.5	13.5	13.5	14.9	13.5	14.9	13.5	13.5	12.3
57.5°	12.3	12.3	12.3	12.3	13.5	13.5	12.3	12.3	12.3	10.9	10.9
60°	12.3	12.3	12.3	12.3	12.3	12.3	12.3	12.3	10.9	9.5	9.5
62.5°	13.5	13.5	12.3	12.3	12.3	12.3	10.9	10.9	10.9	9.5	9.5
65°	13.5	13.5	12.3	13.5	13.5	12.3	12.3	10.9	10.9	9.5	9.5
67.5°	13.5	13.5	13.5	13.5	13.5	13.5	12.3	12.3	10.9	10.9	9.5
70°	13.5	13.5	13.5	13.5	13.5	13.5	12.3	12.3	10.9	10.9	9.5
72.5°	13.5	13.5	13.5	13.5	13.5	13.5	12.3	12.3	12.3	10.9	9.5
75°	13.5	13.5	13.5	13.5	13.5	12.3	12.3	12.3	10.9	10.9	9.5
77.5°	13.5	13.5	13.5	13.5	13.5	12.3	12.3	12.3	10.9	10.9	9.5
80°	13.5	13.5	13.5	13.5	13.5	13.5	12.3	12.3	10.9	10.9	9.5
82.5°	13.5	13.5	13.5	13.5	13.5	12.3	12.3	12.3	10.9	10.9	9.5
85°	13.5	12.3	12.3	12.3	12.3	12.3	10.9	10.9	9.5	9.5	8.1
87.5°	12.3	12.3	12.3	12.3	12.3	10.9	10.9	9.5	8.1	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192822

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LAL1LI 30°

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9	1275.9
2.5°	672.6	660.3	654.9	645.4	637.3	633.3	618.2	635.9
5°	411.7	396.7	392.7	384.5	375.0	369.5	358.7	368.3
7.5°	235.1	217.4	209.3	202.5	193.0	184.8	175.3	180.7
10°	131.8	126.3	127.7	123.7	122.3	120.9	119.5	122.3
12.5°	122.3	118.3	119.5	116.9	115.5	115.5	114.1	115.5
15°	123.7	119.5	122.3	119.5	118.3	118.3	116.9	119.5
17.5°	134.6	131.8	134.6	131.8	133.2	131.8	133.2	134.6
20°	188.8	193.0	201.1	195.7	199.7	205.1	212.0	212.0
22.5°	664.5	751.4	762.2	805.8	917.2	913.1	987.9	990.5
25°	1160.4	1165.8	1214.8	1198.5	1199.9	1256.9	1251.5	1284.1
27.5°	667.1	665.7	675.4	657.7	663.1	667.1	652.2	669.9
30°	372.3	365.5	369.5	360.1	360.1	362.9	358.7	366.9
32.5°	206.5	201.1	201.1	194.3	193.0	191.6	187.6	191.6
35°	118.3	114.1	115.5	112.8	110.0	108.6	107.4	108.6
37.5°	81.6	78.8	80.2	77.4	74.7	73.4	72.0	73.4
40°	59.8	58.4	58.4	55.6	54.4	53.0	51.6	51.6
42.5°	44.9	43.5	43.5	40.7	39.5	38.1	36.7	38.1
45°	34.0	32.6	32.6	31.2	29.8	28.6	28.6	28.6
47.5°	29.8	28.6	29.8	28.6	27.2	27.2	27.2	27.2
50°	23.2	23.2	23.2	21.8	20.4	20.4	19.0	17.7
52.5°	14.9	13.5	13.5	12.3	12.3	10.9	10.9	10.9
55°	12.3	10.9	10.9	9.5	9.5	8.1	8.1	8.1
57.5°	9.5	9.5	8.1	8.1	6.8	6.8	6.8	6.8
60°	8.1	8.1	8.1	6.8	6.8	5.4	5.4	5.4
62.5°	8.1	6.8	6.8	6.8	5.4	5.4	5.4	5.4
65°	8.1	6.8	6.8	6.8	5.4	5.4	5.4	5.4
67.5°	8.1	6.8	6.8	6.8	5.4	5.4	5.4	5.4
70°	9.5	8.1	8.1	6.8	6.8	6.8	5.4	5.4
72.5°	9.5	8.1	8.1	8.1	6.8	6.8	6.8	6.8
75°	9.5	8.1	8.1	8.1	6.8	6.8	6.8	6.8
77.5°	9.5	8.1	8.1	8.1	6.8	6.8	6.8	6.8
80°	9.5	8.1	8.1	8.1	6.8	6.8	6.8	6.8
82.5°	8.1	8.1	8.1	6.8	6.8	6.8	6.8	6.8
85°	8.1	6.8	6.8	6.8	5.4	5.4	5.4	5.4
87.5°	5.4	5.4	4.0	4.0	4.0	2.6	2.6	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)