

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P205384

Luminaire Tested: **LE_6B15D010 EC6B10208050 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205384
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208050 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2045.7 lumens
Efficiency: N/A
Efficacy: 143.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205384

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBSLI1

Luminous Intensity Polar Plot






TEST NUMBER: P205384

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	111	107	104	101	109	105	102	99		101	99	96			97	95	93			94
2	103	96	91	86	100	94	89	85		91	87	83			88	84	81			85
3	95	86	79	74	93	85	78	73		82	76	72			79	75	71			77
4	88	78	70	64	86	77	69	64		74	68	63			72	67	62			70
5	82	71	63	57	80	70	62	57		67	61	56			66	60	55			64
6	76	64	56	51	74	63	56	51		62	55	50			60	54	50			59
7	71	59	51	46	70	58	51	45		57	50	45			55	49	45			54
8	67	54	47	41	65	54	46	41		52	46	41			51	45	41			50
9	63	50	43	38	61	50	43	38		49	42	38			48	42	37			47
10	59	47	40	35	58	46	39	35		45	39	35			45	39	34			44

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205384

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.0	5.8
10°-20°	302.8	14.8
20°-30°	386.2	18.9
30°-40°	400.5	19.6
40°-50°	369.0	18.0
50°-60°	277.6	13.6
60°-70°	149.8	7.3
70°-80°	40.2	2.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	808.0	39.5
0°-40°	1208.5	59.1
0°-60°	1855.1	90.7
0°-90°	2045.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2045.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1291	
5°	1271	119
15°	1080	303
25°	839	386
35°	639	400
45°	480	369
55°	311	278
65°	150	150
75°	35	40
85°	0	1
90°	0	



TEST NUMBER: P205384

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBSLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1291.0
2.5°	1286.6
5°	1271.4
7.5°	1243.1
10°	1193.1
12.5°	1143.1
15°	1080.1
17.5°	1021.5
20°	960.6
22.5°	897.6
25°	838.9
27.5°	782.4
30°	730.2
32.5°	682.4
35°	639.0
37.5°	597.6
40°	558.5
42.5°	517.2
45°	480.2
47.5°	439.0
50°	397.8
52.5°	354.2
55°	310.8
57.5°	267.4
60°	226.0
62.5°	186.9
65°	150.0
67.5°	115.1
70°	84.8
72.5°	58.6
75°	34.8
77.5°	15.2
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)