

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P204566

Luminaire Tested: **LE_6B15D010 EC6B10208050 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204566
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LE_6B15D010 EC6B10208050 6LBSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2129.6 lumens
Efficiency: N/A
Efficacy: 148.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204566

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204566

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63		
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54		
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47		
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42		
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37		
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33		
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30		
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204566

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.3	3.8
10°-20°	231.7	10.9
20°-30°	349.0	16.4
30°-40°	415.3	19.5
40°-50°	414.5	19.5
50°-60°	337.1	15.8
60°-70°	207.4	9.7
70°-80°	80.3	3.8
80°-90°	12.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	662.0	31.1
0°-40°	1077.4	50.6
0°-60°	1829.0	85.9
0°-90°	2129.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2129.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	858	
5°	856	81
15°	823	232
25°	760	349
35°	665	415
45°	539	415
55°	377	337
65°	208	207
75°	73	80
85°	10	13
90°	0	



TEST NUMBER: P204566

CATALOG NUMBER: LE_6B15D010 EC6B10208050 6LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	858.0
2.5°	859.2
5°	855.5
7.5°	850.5
10°	844.1
12.5°	832.8
15°	822.8
17.5°	807.5
20°	791.1
22.5°	776.0
25°	759.6
27.5°	736.9
30°	714.1
32.5°	692.8
35°	665.0
37.5°	634.8
40°	606.9
42.5°	572.9
45°	538.8
47.5°	502.2
50°	463.1
52.5°	422.8
55°	377.2
57.5°	333.1
60°	290.2
62.5°	248.6
65°	208.2
67.5°	170.4
70°	135.0
72.5°	102.2
75°	73.1
77.5°	48.0
80°	29.0
82.5°	17.6
85°	10.1
87.5°	5.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)