

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192825

Luminaire Tested: **LDA6A75940D010TE LARH30NF 6LLWW1**

Issue Date: 3/3/2020



Test Information

Test Method: LM-41-14
Report Number: P1192825
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26684)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75940D010TE LARH30NF 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 30° Narrow Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5600.7 lumens
Efficiency: N/A
Efficacy: 64.5 lumens/watt
Spacing Criteria (0/90/45): 2.21 / 1.07 / 1.54
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192825

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192825

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70		
4	89	79	72	66	87	78	71	66	76	70	65	73	68	64	71	67	63	61		
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54		
6	77	65	57	51	75	64	57	51	62	56	51	61	55	50	59	54	50	48		
7	71	59	51	46	70	58	51	46	57	50	45	56	50	45	54	49	45	43		
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	41	37	47	41	36	46	40	36	35		
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	88354	88354	88354
5°	140358	87271	56680
10°	210601	83738	38048
15°	301784	79359	28150
20°	398364	74206	23464
25°	478147	72331	34272
30°	534272	72517	51780
35°	549298	64935	44203
40°	529313	51632	32876
45°	466506	38345	25289
50°	363792	28391	17492
55°	210401	20778	11307
60°	98325	14451	5065
65°	45997	7939	2114
70°	21350	3494	1523
75°	8917	2309	1716
80°	3883	2557	2147
85°	881	4277	3397



TEST NUMBER: P1192825

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.7	3.0
10°-20°	611.8	10.9
20°-30°	1211.1	21.6
30°-40°	1566.0	28.0
40°-50°	1286.8	23.0
50°-60°	594.8	10.6
60°-70°	135.8	2.4
70°-80°	22.2	0.4
80°-90°	5.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1989.6	35.5
0°-40°	3555.5	63.5
0°-60°	5437.1	97.1
0°-90°	5600.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5600.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1612	1612	1612	1612	1612	
5°	2551	2193	1586	1147	1030	282
15°	5317	3556	1398	626	496	1553
25°	7905	4425	1196	587	567	3640
35°	8208	4050	970	644	660	5082
45°	6017	2734	495	329	326	4579
55°	2201	1064	217	140	118	2069
65°	355	217	61	23	16	406
75°	42	24	11	10	8	56
85°	1	4	7	7	5	4
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192825

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7
2.5°	2046.5	2015.3	2034.4	2043.9	1994.9	2005.8	2011.2	1973.1	1962.3	1941.9	1882.1
5°	2550.6	2513.9	2529.0	2529.0	2456.9	2461.0	2458.3	2386.2	2346.9	2295.1	2193.4
7.5°	3144.6	3107.9	3110.5	3097.0	2995.1	2988.2	2944.7	2856.5	2778.9	2683.8	2531.7
10°	3783.3	3761.5	3747.8	3714.0	3579.4	3556.2	3492.4	3352.5	3224.8	3079.3	2864.5
12.5°	4533.4	4489.9	4450.4	4396.0	4220.7	4177.4	4087.6	3885.2	3697.7	3493.8	3209.7
15°	5317.4	5283.5	5219.7	5134.0	4909.8	4840.5	4723.6	4451.8	4218.1	3920.5	3556.2
17.5°	6128.8	6066.1	5972.4	5851.5	5581.1	5483.2	5337.8	4990.0	4680.1	4309.2	3868.9
20°	6828.5	6779.6	6650.6	6494.3	6184.4	6054.0	5882.8	5456.0	5076.8	4636.6	4118.9
22.5°	7436.0	7370.7	7211.8	7023.0	6676.4	6514.6	6321.6	5844.7	5382.7	4871.7	4302.3
25°	7904.9	7855.9	7666.9	7446.9	7066.3	6878.9	6665.5	6124.6	5612.4	5051.1	4424.6
27.5°	8286.7	8203.9	7993.1	7744.5	7334.1	7115.3	6889.8	6297.2	5742.7	5142.1	4470.8
30°	8440.2	8354.6	8131.8	7855.9	7421.1	7180.5	6948.2	6316.2	5733.3	5110.9	4415.1
32.5°	8411.6	8315.3	8077.4	7785.2	7340.9	7084.0	6848.9	6192.6	5597.4	4969.6	4264.2
35°	8207.9	8127.7	7881.7	7576.0	7133.0	6862.6	6616.6	5967.0	5370.4	4750.8	4049.6
37.5°	7900.7	7786.6	7556.9	7249.8	6781.0	6529.6	6286.3	5645.0	5061.9	4447.8	3781.9
40°	7396.5	7259.3	7029.6	6762.0	6316.2	6066.1	5844.7	5245.5	4672.0	4098.4	3462.5
42.5°	6762.0	6654.7	6441.3	6165.4	5756.4	5517.3	5318.8	4742.6	4234.4	3703.1	3110.5
45°	6017.3	5914.0	5731.9	5483.2	5113.7	4905.8	4723.6	4211.3	3753.3	3268.3	2734.2
47.5°	5211.4	5109.5	4950.5	4731.7	4401.5	4222.1	4063.2	3643.3	3211.1	2787.1	2318.3
50°	4265.6	4125.6	4038.8	3855.2	3579.4	3427.2	3304.9	2928.4	2609.1	2268.1	1878.0
52.5°	3183.9	3139.1	3014.0	2885.0	2690.6	2577.8	2497.6	2255.8	1990.9	1743.5	1445.9
55°	2201.4	2160.7	2084.6	2005.8	1875.2	1818.2	1758.4	1611.7	1435.0	1266.5	1064.0
57.5°	1391.5	1421.5	1372.5	1327.6	1248.8	1228.5	1182.3	1096.7	987.9	881.9	755.6
60°	896.8	913.1	881.9	856.1	812.6	796.3	774.5	722.9	657.7	596.6	511.0
62.5°	568.0	576.2	558.5	543.6	519.0	512.4	497.3	467.5	428.1	391.3	337.1
65°	354.6	361.5	349.2	339.7	324.8	326.2	312.5	295.0	271.8	248.6	217.4
67.5°	218.8	222.8	214.8	209.3	199.7	199.7	191.6	180.7	165.8	152.1	131.8
70°	133.2	134.6	129.1	126.3	119.7	118.3	114.2	106.0	96.5	87.0	74.7
72.5°	77.4	78.8	74.7	72.0	67.9	67.9	65.3	61.2	57.0	49.0	42.1
75°	42.1	43.5	40.7	39.5	36.7	38.1	35.3	34.0	29.8	27.2	24.4
77.5°	21.8	23.2	21.8	20.4	20.4	20.4	19.0	17.7	17.7	14.9	14.9
80°	12.3	12.3	12.3	12.3	12.3	10.9	10.9	10.9	10.9	10.9	9.5
82.5°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	5.4
85°	1.4	1.4	2.6	2.6	2.6	2.6	2.6	2.6	2.6	4.0	4.0
87.5°	0.0	0.0	1.4	1.4	1.4	1.4	1.4	2.6	2.6	2.6	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192825

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7
2.5°	1864.4	1863.1	1800.5	1773.5	1751.7	1717.7	1693.3	1667.3	1644.3	1602.2	1566.8
5°	2141.6	2103.5	2000.3	1935.1	1894.4	1840.0	1780.1	1720.5	1662.0	1585.9	1523.4
7.5°	2432.5	2350.9	2196.0	2087.4	2024.7	1948.7	1848.2	1754.3	1659.2	1554.6	1465.0
10°	2709.8	2576.6	2379.5	2213.7	2128.1	2030.2	1891.6	1761.2	1636.1	1504.3	1392.9
12.5°	2992.3	2802.1	2545.2	2330.6	2221.8	2100.9	1922.8	1761.2	1606.2	1454.1	1322.2
15°	3272.3	3020.9	2701.5	2435.2	2303.4	2159.3	1944.6	1751.7	1569.6	1398.3	1251.6
17.5°	3511.5	3200.2	2815.7	2507.3	2352.3	2189.2	1943.3	1723.1	1520.6	1335.8	1179.5
20°	3697.7	3329.3	2895.9	2543.9	2369.9	2192.0	1921.6	1681.0	1465.0	1272.0	1111.6
22.5°	3824.0	3413.6	2936.6	2550.6	2364.5	2177.0	1887.5	1638.9	1414.6	1221.6	1061.2
25°	3902.8	3455.7	2948.9	2541.1	2345.5	2151.2	1856.3	1602.2	1382.0	1195.8	1046.3
27.5°	3917.7	3443.6	2924.4	2501.8	2300.6	2104.9	1811.4	1566.8	1353.6	1180.9	1046.3
30°	3844.4	3364.6	2841.5	2413.4	2216.4	2024.7	1736.6	1502.9	1303.2	1145.6	1023.3
32.5°	3704.3	3219.3	2704.3	2283.0	2091.4	1912.1	1634.8	1412.0	1219.0	1073.5	963.5
35°	3502.0	3024.9	2526.2	2118.6	1932.4	1765.2	1492.0	1288.3	1104.8	970.3	868.4
37.5°	3256.0	2791.2	2318.3	1931.0	1754.3	1598.2	1337.2	1145.6	975.8	849.3	758.2
40°	2957.0	2538.5	2084.6	1724.5	1555.9	1414.6	1174.1	989.3	828.9	721.5	638.7
42.5°	2644.5	2255.8	1835.9	1493.4	1343.9	1209.5	996.1	830.3	687.7	599.2	534.1
45°	2322.3	1941.9	1575.0	1270.6	1157.7	1007.0	810.0	675.4	559.9	494.6	443.1
47.5°	1959.6	1637.5	1299.2	1031.4	913.1	811.2	646.8	538.2	463.4	406.4	366.9
50°	1569.6	1312.7	1028.8	800.5	702.6	625.0	504.1	429.4	372.3	332.9	303.0
52.5°	1206.7	1004.2	774.5	587.1	525.9	467.5	392.7	341.1	300.4	270.4	248.6
55°	896.8	732.4	557.1	434.8	391.3	353.4	308.5	267.8	237.8	217.4	199.7
57.5°	631.9	511.0	391.3	315.3	292.2	267.8	233.7	206.5	186.2	169.9	156.3
60°	422.7	347.9	275.8	231.1	214.8	198.4	176.7	157.6	142.7	131.8	118.3
62.5°	284.1	233.7	193.0	165.8	154.9	144.1	129.1	115.5	104.6	93.7	82.8
65°	182.1	154.9	130.4	112.8	104.6	99.1	88.3	78.8	70.7	61.2	53.0
67.5°	111.4	96.5	81.6	70.7	66.5	62.5	55.8	49.0	43.5	36.7	31.2
70°	65.3	57.0	49.0	42.1	40.7	38.1	32.6	28.6	25.8	21.8	19.0
72.5°	38.1	34.0	28.6	25.8	24.4	21.8	20.4	17.7	14.9	13.5	12.3
75°	21.8	19.0	16.3	14.9	14.9	13.5	12.3	12.3	10.9	10.9	9.5
77.5°	13.5	12.3	10.9	10.9	10.9	9.5	9.5	9.5	9.5	8.1	8.1
80°	9.5	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
82.5°	5.4	5.4	5.4	5.4	5.4	6.8	6.8	6.8	6.8	6.8	8.1
85°	4.0	5.4	5.4	5.4	5.4	5.4	6.8	6.8	6.8	6.8	6.8
87.5°	4.0	5.4	5.4	5.4	5.4	5.4	6.8	6.8	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192825

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7
2.5°	1546.4	1524.7	1458.1	1481.1	1439.0	1405.2	1402.4	1382.0	1346.7	1327.6	1318.1
5°	1475.9	1426.9	1345.3	1350.8	1301.8	1248.8	1220.4	1193.2	1146.9	1118.4	1099.3
7.5°	1388.8	1322.2	1225.8	1219.0	1167.4	1103.5	1062.6	1024.6	974.4	937.7	914.5
10°	1297.8	1216.2	1103.5	1095.3	1040.9	971.6	925.4	881.9	830.3	793.6	769.1
12.5°	1213.5	1119.7	1007.0	986.7	933.5	863.0	812.6	766.4	716.1	684.9	656.4
15°	1133.4	1031.4	911.9	892.8	841.2	770.5	714.9	674.0	626.4	596.6	570.8
17.5°	1053.2	948.6	830.3	808.6	759.6	691.7	642.7	599.2	555.7	527.3	504.1
20°	983.9	879.3	763.6	741.9	697.1	631.9	587.1	546.2	506.9	479.7	460.6
22.5°	938.9	837.2	732.4	713.5	671.3	612.9	570.8	535.4	501.5	475.7	460.6
25°	936.3	848.0	754.2	743.3	708.0	659.1	629.2	607.5	587.1	566.6	561.2
27.5°	952.6	880.5	801.7	799.1	770.5	737.9	724.3	717.5	706.6	699.8	709.4
30°	943.1	881.9	815.4	815.4	793.6	770.5	763.6	761.0	754.2	755.6	766.4
32.5°	892.8	837.2	773.3	774.5	761.0	735.2	731.2	729.8	721.5	720.3	728.4
35°	801.7	750.1	697.1	698.5	687.7	663.1	657.7	655.0	644.1	638.7	644.1
37.5°	697.1	655.0	604.7	604.7	593.8	574.8	569.4	564.0	557.1	551.7	551.7
40°	589.8	555.7	515.0	513.6	505.5	486.6	481.1	476.9	470.2	460.6	463.4
42.5°	498.7	467.5	434.8	432.2	426.7	410.4	405.0	399.5	392.7	384.6	384.6
45°	414.5	394.1	365.5	364.3	358.8	345.1	341.1	334.3	328.8	320.8	320.8
47.5°	345.1	328.8	305.8	304.4	300.4	288.1	284.1	278.6	273.2	267.8	267.8
50°	289.5	273.2	254.1	252.7	250.0	240.6	235.1	231.1	226.9	222.8	220.2
52.5°	237.8	224.2	209.3	207.9	205.1	195.7	191.6	188.8	184.8	178.1	178.1
55°	191.6	180.7	167.2	165.8	163.0	154.9	150.9	145.5	140.0	133.2	131.8
57.5°	149.5	140.0	129.1	127.7	123.7	116.9	110.0	104.6	99.1	93.7	91.1
60°	112.8	101.9	92.5	89.7	87.0	77.4	72.0	66.5	61.2	57.0	54.4
62.5°	76.1	69.3	58.4	57.0	54.4	49.0	42.1	39.5	36.7	34.0	32.6
65°	47.6	42.1	36.7	35.3	32.6	28.6	25.8	24.4	23.2	21.8	20.4
67.5°	28.6	25.8	21.8	21.8	20.4	19.0	16.3	16.3	14.9	14.9	13.5
70°	17.7	16.3	14.9	13.5	13.5	13.5	12.3	12.3	12.3	12.3	12.3
72.5°	12.3	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9
75°	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5
77.5°	9.5	9.5	8.1	9.5	9.5	9.5	9.5	8.1	9.5	8.1	8.1
80°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
82.5°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	6.8	6.8	6.8	6.8
85°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	5.4
87.5°	6.8	6.8	6.8	6.8	6.8	5.4	5.4	5.4	5.4	4.0	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192825

CATALOG NUMBER: LDA6A75940D010TE LARH30NF 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7	1611.7
2.5°	1320.9	1282.8	1297.8	1276.0	1269.2	1263.7	1255.7	1281.5
5°	1091.2	1050.4	1060.0	1038.2	1028.8	1019.1	1009.7	1030.0
7.5°	901.0	861.6	865.6	846.6	837.2	826.3	816.6	833.0
10°	752.8	716.1	717.5	699.8	690.3	679.4	671.3	683.5
12.5°	640.1	606.1	606.1	592.6	584.3	572.0	565.4	574.8
15°	554.5	524.5	524.5	511.0	504.1	493.2	486.6	496.0
17.5°	489.2	462.0	462.0	452.5	445.7	436.2	430.8	438.9
20°	445.7	422.7	423.9	414.5	409.0	398.1	395.5	402.2
22.5°	449.7	428.1	430.8	423.9	418.5	410.4	407.6	417.3
25°	562.6	546.2	555.7	555.7	558.5	546.2	551.7	566.6
27.5°	722.9	714.9	729.8	724.3	735.2	735.2	740.6	759.6
30°	781.4	774.5	790.8	789.6	800.5	797.7	800.5	818.0
32.5°	739.3	732.4	746.1	744.7	752.8	746.1	747.3	762.4
35°	649.6	642.7	652.2	651.0	656.4	648.2	652.2	660.5
37.5°	554.5	547.6	553.1	551.7	553.1	543.6	549.0	553.1
40°	466.1	458.0	466.1	460.6	462.0	452.5	453.9	459.4
42.5°	390.1	380.4	387.3	387.3	387.3	380.4	381.8	387.3
45°	324.8	318.0	322.0	320.8	322.0	316.6	320.8	326.2
47.5°	269.0	263.6	266.4	265.0	265.0	259.5	260.9	260.9
50°	221.4	216.0	217.4	216.0	212.0	205.1	203.9	205.1
52.5°	175.3	168.5	168.5	165.8	163.0	157.6	157.6	159.0
55°	129.1	123.7	123.7	122.3	119.7	115.5	115.5	118.3
57.5°	87.0	82.8	84.2	82.8	82.8	77.4	80.2	80.2
60°	53.0	50.4	50.4	49.0	46.2	44.9	43.5	46.2
62.5°	31.2	29.8	29.8	28.6	28.6	27.2	27.2	27.2
65°	20.4	19.0	19.0	17.7	17.7	16.3	14.9	16.3
67.5°	13.5	12.3	12.3	12.3	12.3	10.9	10.9	10.9
70°	12.3	10.9	10.9	10.9	10.9	9.5	9.5	9.5
72.5°	10.9	9.5	10.9	9.5	9.5	9.5	9.5	9.5
75°	9.5	9.5	9.5	8.1	8.1	8.1	8.1	8.1
77.5°	8.1	8.1	8.1	8.1	8.1	6.8	6.8	6.8
80°	8.1	6.8	6.8	6.8	6.8	6.8	6.8	6.8
82.5°	6.8	6.8	6.8	6.8	6.8	5.4	5.4	5.4
85°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
87.5°	4.0	4.0	4.0	4.0	4.0	2.6	2.6	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)