

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P1192831

Luminaire Tested: **LDA6A75940D010TE LARH40FL 6LLWW1**

Issue Date: 3/3/2020

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P1192831
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26685)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A75940D010TE LARH40FL 6LLWW1
Description: PORTFOLIO 6" Lensed Wall Wash, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5926.8 lumens
Efficiency: N/A
Efficacy: 68.2 lumens/watt
Spacing Criteria (0/90/45): 2.12 / 1.05 / 1.48
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 86.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P1192831

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LLWW1

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192831

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LLWW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90		
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79		
3	96	88	81	76	94	86	80	76	84	78	74	81	77	73	79	75	72	70		
4	89	79	72	67	87	78	71	66	76	70	65	74	69	64	72	67	64	62		
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55		
6	77	65	58	52	75	64	57	52	63	56	51	61	55	51	60	55	51	49		
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44		
8	67	55	47	42	65	54	47	41	53	46	41	51	45	41	50	45	41	39		
9	62	50	43	38	61	50	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	104887	104887	104887
5°	168556	102817	65584
10°	249244	98490	44021
15°	339650	93162	32702
20°	420077	87910	30995
25°	486681	86551	50882
30°	530987	82918	50926
35°	545731	71655	39833
40°	531439	56406	31015
45°	481872	41725	24444
50°	379663	30831	16571
55°	226372	21954	9472
60°	115758	14604	3574
65°	55350	7757	1596
70°	26126	3494	1523
75°	10675	2309	1716
80°	5146	2557	1705
85°	2516	4277	2516

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192831

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LLWW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.4	3.3
10°-20°	693.9	11.7
20°-30°	1306.1	22.0
30°-40°	1590.5	26.8
40°-50°	1323.9	22.3
50°-60°	634.1	10.7
60°-70°	152.3	2.6
70°-80°	24.0	0.4
80°-90°	5.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2196.4	37.1
0°-40°	3786.9	63.9
0°-60°	5745.0	96.9
0°-90°	5926.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5926.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1913	1913	1913	1913	1913	
5°	3063	2598	1868	1359	1192	335
15°	5985	4066	1642	745	576	1715
25°	8046	4752	1431	811	841	3696
35°	8155	4173	1071	624	595	5053
45°	6216	2790	538	332	315	4706
55°	2368	1151	230	129	99	2231
65°	427	249	60	19	12	488
75°	50	26	11	10	8	69
85°	4	4	7	5	4	6
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192831

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3
2.5°	2474.5	2387.6	2414.8	2409.4	2403.9	2375.3	2355.0	2337.3	2292.5	2292.5	2235.3
5°	3063.0	2961.0	2986.8	2967.7	2943.3	2899.8	2860.5	2815.6	2732.8	2697.3	2598.2
7.5°	3735.6	3620.1	3643.1	3605.2	3553.4	3495.0	3431.1	3346.9	3215.1	3134.9	2981.4
10°	4477.5	4313.0	4326.7	4269.7	4184.1	4105.1	4044.0	3883.7	3696.1	3562.9	3348.3
12.5°	5180.0	5036.0	5040.2	4960.0	4836.3	4739.8	4647.3	4435.3	4185.3	3995.1	3712.4
15°	5984.6	5807.9	5765.7	5657.0	5495.3	5377.1	5250.7	4983.0	4669.1	4417.8	4065.8
17.5°	6632.7	6450.6	6423.4	6321.5	6090.5	5947.9	5788.9	5487.1	5089.0	4776.5	4344.3
20°	7200.7	7020.0	6973.8	6841.9	6577.0	6413.9	6222.3	5866.3	5431.5	5046.9	4559.0
22.5°	7665.4	7467.1	7401.8	7238.8	6943.9	6760.5	6526.8	6138.1	5652.9	5223.5	4686.8
25°	8046.0	7820.3	7737.5	7552.7	7221.1	7018.6	6761.7	6326.9	5798.4	5324.1	4752.1
27.5°	8289.2	8063.7	7972.6	7760.7	7388.3	7170.9	6890.9	6420.8	5850.0	5337.8	4738.4
30°	8388.3	8154.6	8051.4	7810.8	7410.1	7180.4	6888.2	6379.9	5783.5	5239.9	4624.3
32.5°	8327.2	8097.6	7982.1	7721.2	7303.9	7056.7	6764.5	6222.3	5608.2	5045.5	4425.9
35°	8154.6	7927.7	7808.2	7529.6	7094.8	6836.5	6545.7	5984.6	5363.6	4788.7	4173.2
37.5°	7857.0	7642.4	7505.2	7229.3	6791.7	6528.0	6240.0	5673.3	5038.8	4498.0	3881.0
40°	7426.2	7222.5	7086.5	6791.7	6378.7	6112.3	5840.5	5265.7	4667.8	4140.5	3545.4
42.5°	6877.3	6689.8	6559.4	6272.7	5878.6	5616.3	5367.6	4815.9	4246.5	3745.0	3182.5
45°	6215.5	6052.5	5924.7	5687.0	5298.3	5049.7	4825.4	4325.3	3772.2	3311.6	2789.8
47.5°	5436.9	5302.3	5178.6	4962.6	4612.0	4376.9	4192.1	3734.2	3265.3	2831.9	2387.6
50°	4451.7	4355.2	4258.8	4034.6	3787.2	3582.0	3447.5	3039.8	2660.6	2320.9	1952.8
52.5°	3356.4	3298.0	3230.0	3069.7	2904.0	2784.3	2664.8	2355.0	2070.9	1818.2	1531.5
55°	2368.5	2338.7	2285.7	2220.4	2094.1	2012.5	1909.3	1751.5	1531.5	1361.6	1150.9
57.5°	1600.8	1592.6	1555.9	1516.6	1447.3	1420.1	1333.0	1231.1	1107.6	981.1	831.6
60°	1055.8	1038.2	1030.0	1008.3	955.3	933.5	902.3	837.0	761.0	672.6	580.3
62.5°	679.4	669.9	663.1	653.6	621.0	621.0	589.8	559.9	502.7	448.5	388.7
65°	426.7	418.5	417.1	410.4	398.1	392.7	369.5	347.9	320.8	290.8	248.6
67.5°	274.4	262.3	255.5	251.4	243.2	233.7	225.6	216.0	194.3	176.7	149.5
70°	163.0	152.1	150.9	152.1	142.7	141.3	133.2	126.3	111.4	100.5	84.2
72.5°	92.5	87.0	85.6	85.6	80.2	78.8	73.4	69.3	61.1	53.0	46.2
75°	50.4	46.2	46.2	46.2	43.5	42.1	39.5	38.1	32.6	29.8	25.8
77.5°	28.6	27.2	27.2	25.8	24.4	23.2	21.8	21.8	19.0	17.7	16.3
80°	16.3	16.3	16.3	16.3	14.9	14.9	13.5	13.5	12.3	12.3	10.9
82.5°	9.5	9.5	9.5	9.5	9.5	9.5	8.1	8.1	8.1	8.1	6.8
85°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
87.5°	0.0	0.0	1.4	1.4	1.4	1.4	1.4	2.6	2.6	2.6	4.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192831

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3
2.5°	2209.5	2168.8	2166.0	2106.3	2068.3	2037.0	2013.9	1985.3	1921.4	1886.1	1860.3
5°	2528.9	2444.6	2401.1	2292.5	2232.7	2179.7	2114.4	2046.5	1941.9	1868.4	1808.7
7.5°	2860.5	2720.5	2628.0	2466.4	2384.8	2302.0	2192.0	2081.8	1939.1	1829.1	1738.0
10°	3169.0	2970.5	2823.8	2606.4	2500.3	2391.6	2236.7	2088.6	1910.5	1769.3	1649.8
12.5°	3472.0	3211.1	3008.6	2732.8	2603.6	2469.0	2270.7	2084.6	1875.2	1705.4	1565.4
15°	3761.4	3433.9	3175.7	2842.8	2691.9	2530.3	2292.5	2072.3	1834.5	1641.5	1482.5
17.5°	3992.4	3603.8	3293.9	2910.7	2740.8	2557.5	2284.3	2037.0	1778.7	1573.6	1399.7
20°	4151.4	3712.4	3359.2	2937.9	2751.7	2554.7	2253.0	1988.1	1720.3	1506.9	1330.4
22.5°	4237.1	3761.4	3376.9	2929.8	2735.4	2528.9	2215.0	1943.2	1674.2	1460.8	1292.3
25°	4268.3	3765.4	3357.8	2894.4	2698.7	2488.2	2170.2	1901.0	1637.5	1430.9	1273.2
27.5°	4231.6	3708.4	3288.5	2821.0	2622.6	2414.8	2098.1	1841.2	1583.1	1387.4	1239.3
30°	4106.5	3575.2	3152.7	2690.6	2496.2	2296.5	1984.0	1731.2	1494.8	1309.9	1168.6
32.5°	3908.2	3379.5	2961.0	2511.2	2323.7	2132.1	1833.1	1592.6	1372.5	1198.5	1072.1
35°	3662.2	3145.8	2738.2	2302.0	2125.3	1944.6	1660.6	1433.6	1227.1	1070.7	947.2
37.5°	3383.6	2886.3	2492.2	2091.3	1911.9	1742.1	1466.2	1272.0	1073.5	930.9	818.0
40°	3071.1	2588.7	2229.9	1840.0	1682.2	1527.5	1272.0	1095.3	914.5	788.2	690.3
42.5°	2736.8	2287.1	1955.4	1604.8	1447.3	1305.8	1076.2	917.2	757.0	652.2	574.8
45°	2382.2	1985.3	1667.3	1353.4	1210.7	1088.4	879.3	735.2	618.3	538.2	479.7
47.5°	2011.2	1660.6	1378.0	1104.8	978.4	872.4	704.0	593.8	501.5	443.1	398.1
50°	1637.5	1325.0	1100.7	868.4	759.6	675.4	550.3	474.3	406.4	361.5	327.4
52.5°	1280.1	1024.6	842.4	655.0	572.0	513.6	429.4	376.4	324.8	290.8	265.0
55°	945.8	771.9	615.5	475.5	426.7	390.1	330.2	292.2	255.5	229.7	210.6
57.5°	683.5	553.1	438.9	349.2	316.6	292.2	248.6	222.8	197.1	177.9	163.0
60°	479.7	381.8	309.9	255.5	232.3	216.0	184.8	168.5	149.5	133.2	118.3
62.5°	315.3	256.9	216.0	180.7	167.2	154.9	133.2	120.9	104.6	93.7	80.2
65°	205.1	168.5	144.1	120.9	110.0	104.6	89.7	80.2	69.3	59.8	51.6
67.5°	124.9	104.6	91.1	76.1	70.7	65.3	55.8	49.0	42.1	35.3	31.2
70°	69.3	61.1	53.0	44.9	40.7	38.1	32.6	29.8	24.4	21.8	17.7
72.5°	40.7	35.3	31.2	25.8	24.4	23.2	19.0	17.7	14.9	13.5	12.3
75°	24.4	20.4	19.0	16.3	14.9	14.9	13.5	12.3	10.9	10.9	9.5
77.5°	14.9	13.5	12.3	10.9	10.9	10.9	9.5	9.5	9.5	8.1	8.1
80°	9.5	9.5	9.5	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
82.5°	6.8	6.8	6.8	5.4	6.8	5.4	6.8	6.8	6.8	6.8	6.8
85°	4.0	4.0	5.4	5.4	5.4	5.4	5.4	6.8	6.8	6.8	6.8
87.5°	4.0	4.0	5.4	5.4	5.4	5.4	5.4	6.8	6.8	6.8	5.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1192831

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3
2.5°	1830.5	1780.1	1743.5	1716.3	1725.7	1678.2	1663.3	1611.7	1592.6	1592.6	1565.4
5°	1747.5	1667.3	1604.8	1565.4	1562.7	1494.8	1459.4	1394.3	1358.8	1333.0	1307.2
7.5°	1648.4	1545.0	1462.2	1414.6	1401.0	1320.8	1273.2	1208.1	1155.1	1121.1	1089.8
10°	1542.4	1418.7	1325.0	1270.6	1250.2	1163.2	1100.7	1040.9	983.9	948.6	915.9
12.5°	1440.4	1305.8	1202.7	1146.9	1121.1	1031.4	967.5	905.1	850.7	814.0	781.4
15°	1346.7	1203.9	1095.3	1039.5	1011.0	922.6	858.8	797.7	744.7	710.7	680.8
17.5°	1258.3	1113.0	1004.2	949.8	918.6	837.0	775.9	716.1	668.5	637.3	610.1
20°	1191.8	1047.7	947.2	899.6	868.4	792.2	739.3	687.7	648.2	625.0	599.2
22.5°	1163.2	1030.0	944.4	900.9	879.3	818.0	781.4	744.7	718.9	714.7	698.5
25°	1159.1	1042.3	971.6	934.9	921.4	875.1	853.3	830.3	811.2	816.6	819.4
27.5°	1141.4	1032.8	974.4	943.1	932.3	894.2	877.9	856.1	842.4	849.3	852.1
30°	1080.4	979.8	925.4	899.6	888.7	850.7	837.0	812.6	801.7	803.1	801.7
32.5°	985.3	890.0	839.8	816.6	804.5	770.5	755.6	733.8	717.5	716.1	713.5
35°	869.6	784.0	737.9	717.5	705.2	676.8	663.1	642.7	623.8	622.4	619.6
37.5°	751.5	675.4	635.9	618.3	607.5	584.3	568.0	554.5	542.2	536.8	535.4
40°	637.3	569.4	540.8	527.3	519.0	494.6	486.4	472.9	463.4	458.0	456.6
42.5°	529.9	482.4	459.4	447.1	440.3	422.5	413.1	402.2	392.7	387.3	385.9
45°	449.7	410.4	388.7	379.2	373.7	357.4	350.6	339.7	331.6	327.4	326.2
47.5°	375.0	343.8	328.8	318.0	316.6	303.0	293.6	285.3	277.2	273.2	271.8
50°	307.1	281.3	269.0	262.3	260.9	247.2	240.6	233.7	226.9	222.8	220.2
52.5°	252.7	228.3	220.2	210.6	209.3	197.1	191.6	184.8	177.9	172.7	168.5
55°	199.7	180.7	172.7	164.4	163.0	149.5	144.1	135.8	129.1	123.7	118.3
57.5°	152.1	137.2	129.1	120.9	119.5	110.0	100.5	93.7	87.0	80.2	76.1
60°	111.4	96.5	87.0	82.8	78.8	69.3	62.5	57.0	51.6	47.6	43.5
62.5°	73.4	62.5	55.8	50.4	47.6	40.7	36.7	32.6	29.8	28.6	27.2
65°	44.9	38.1	32.6	29.8	29.8	25.8	23.2	20.4	19.0	19.0	17.7
67.5°	27.2	23.2	20.4	19.0	17.7	16.3	14.9	14.9	13.5	13.5	12.3
70°	16.3	14.9	13.5	12.3	12.3	12.3	12.3	12.3	10.9	10.9	10.9
72.5°	12.3	10.9	10.9	10.9	10.9	10.9	10.9	10.9	9.5	9.5	9.5
75°	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	9.5	8.1
77.5°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
80°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1	6.8	6.8	6.8
82.5°	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8	6.8
85°	6.8	6.8	6.8	6.8	6.8	6.8	5.4	5.4	5.4	5.4	5.4
87.5°	6.8	5.4	5.4	5.4	5.4	5.4	4.0	4.0	4.0	4.0	2.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P1192831

CATALOG NUMBER: LDA6A75940D010TE LARH40FL 6LLWW1

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3	1913.3
2.5°	1551.9	1562.7	1546.4	1535.5	1524.7	1532.9	1494.8	1478.5
5°	1282.8	1270.6	1262.3	1252.9	1236.5	1239.3	1206.7	1191.8
7.5°	1061.2	1053.2	1032.8	1021.9	1005.6	1005.6	975.6	963.5
10°	886.0	873.8	854.7	845.2	830.3	818.0	803.1	790.8
12.5°	752.8	739.3	722.9	714.7	699.8	690.3	675.4	678.0
15°	653.6	640.1	625.0	616.9	604.7	595.2	582.9	576.2
17.5°	584.3	572.0	559.9	551.7	542.2	534.0	523.2	521.8
20°	578.9	569.4	562.6	557.1	549.0	543.6	538.2	531.3
22.5°	693.1	694.3	695.7	695.7	697.1	697.1	698.5	684.9
25°	818.0	833.0	833.0	837.0	849.3	849.3	846.6	841.2
27.5°	850.7	865.6	861.6	864.2	876.5	879.3	869.6	871.0
30°	796.3	810.0	801.7	803.1	811.2	811.2	799.1	804.5
32.5°	705.2	713.5	702.6	702.6	709.4	708.0	699.8	699.8
35°	608.7	612.9	603.3	607.5	607.5	603.3	595.2	595.2
37.5°	525.9	527.3	517.8	519.0	519.0	515.0	506.9	506.9
40°	447.1	451.1	443.1	445.7	443.1	438.9	434.8	433.4
42.5°	377.8	380.4	373.7	377.8	376.4	376.4	375.0	376.4
45°	318.0	320.8	315.3	318.0	319.4	318.0	313.9	315.3
47.5°	263.6	266.4	266.4	263.6	262.3	255.5	251.4	251.4
50°	213.4	212.0	210.6	206.5	202.5	198.4	194.3	194.3
52.5°	160.4	157.6	156.3	152.1	150.9	146.7	146.7	142.7
55°	110.0	108.8	108.8	104.6	104.6	100.5	99.1	99.1
57.5°	69.3	66.5	67.9	65.3	63.9	59.8	59.8	58.4
60°	39.5	38.1	38.1	36.7	35.3	32.6	32.6	32.6
62.5°	25.8	24.4	24.4	23.2	23.2	21.8	21.8	20.4
65°	16.3	14.9	14.9	13.5	13.5	12.3	12.3	12.3
67.5°	12.3	10.9	10.9	10.9	10.9	10.9	9.5	9.5
70°	10.9	10.9	9.5	9.5	9.5	9.5	9.5	9.5
72.5°	9.5	9.5	9.5	9.5	8.1	8.1	8.1	8.1
75°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
77.5°	8.1	6.8	6.8	6.8	6.8	6.8	6.8	6.8
80°	6.8	6.8	6.8	6.8	6.8	6.8	5.4	5.4
82.5°	6.8	5.4	5.4	5.4	5.4	5.4	5.4	5.4
85°	5.4	4.0	4.0	4.0	4.0	4.0	4.0	4.0
87.5°	2.6	2.6	2.6	2.6	1.4	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)